

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333641-840

Luminaire Tested: **S125RDIW-S375D470U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333641-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D470U840-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3115.3 lumens
Efficiency: N/A
Efficacy: 135.4 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47						47		
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41						41		
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35						35		
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30						30		
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	32	29	26						26		
5	69	57	49	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23						23		
6	63	51	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20						20		
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18						18		
8	54	42	35	29	50	39	33	28	34	28	25	29	24	21	24	21	18	16						16		
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	16	14						14		
10	47	35	28	23	43	33	27	22	28	23	20	24	20	17	20	17	15	13						13		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3672	3672	3672	3672
5°	4224	3676	3247	3676
10°	4845	3657	2865	3657
15°	5233	3620	2546	3620
20°	5770	3577	2351	3577
25°	6678	3518	2182	3518
30°	7267	3457	2071	3457
35°	6130	3387	1968	3387
40°	4281	3260	1881	3260
45°	3176	3088	1795	3088
50°	2533	2910	1721	2910
55°	2149	2688	1655	2688
60°	1856	2490	1550	2490
65°	1655	2275	1334	2275
70°	1456	2085	1216	2085
75°	1258	1804	1140	1804
80°	956	1517	956	1517
85°	793	1193	897	1193



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	1.7
10°-20°	159.7	5.1
20°-30°	253.3	8.1
30°-40°	305.4	9.8
40°-50°	272.8	8.8
50°-60°	209.2	6.7
60°-70°	135.9	4.4
70°-80°	66.1	2.1
80°-90°	17.1	0.5
90°-100°	39.4	1.3
100°-110°	116.3	3.7
110°-120°	197.1	6.3
120°-130°	259.3	8.3
130°-140°	290.6	9.3
140°-150°	284.8	9.1
150°-160°	239.2	7.7
160°-170°	159.0	5.1
170°-180°	55.6	1.8
0°-30°	467.5	15.0
0°-40°	773.0	24.8
0°-60°	1254.9	40.3
0°-90°	1474.0	47.3
90°-120°	352.8	11.3
90°-150°	1187.4	38.1
90°-180°	1641.0	52.7
0°-180°	3115.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	568	568	568	568	568	
5°	652	567	501	567	652	65
15°	783	541	381	541	783	224
25°	937	494	306	494	937	430
35°	778	430	250	430	778	470
45°	348	338	196	338	348	277
55°	191	239	147	239	191	173
65°	108	149	87	149	108	108
75°	50	72	46	72	50	54
85°	11	16	12	16	11	13
90°	11	0	11	0	11	7
95°	39	30	39	30	39	40
105°	114	104	114	104	114	120
115°	199	197	199	197	199	197
125°	290	288	290	288	290	259
135°	376	374	376	374	376	290
145°	455	454	455	454	455	284
155°	519	519	519	519	519	239
165°	563	564	563	564	563	159
175°	584	587	584	587	584	56
180°	588	588	588	588	588	



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	597.9	597.5	598.3	596.2	596.4	593.3	593.3	590.9	587.6	585.2	584.1
5°	651.5	652.0	651.1	647.5	645.2	641.7	637.7	630.8	624.9	619.2	614.9
7.5°	706.7	707.0	703.9	702.9	696.9	692.7	683.9	674.3	665.9	655.1	646.9
10°	738.8	738.5	735.3	732.7	727.6	721.0	712.4	701.3	690.7	679.0	667.8
12.5°	757.4	756.8	755.8	752.7	747.9	742.1	734.8	723.8	710.8	698.1	685.0
15°	782.6	781.0	778.0	774.0	767.2	760.4	752.3	742.6	730.1	715.7	703.6
17.5°	813.9	813.9	809.2	803.7	794.5	782.5	769.9	754.2	737.3	721.4	708.5
20°	839.6	838.9	834.2	823.4	812.9	798.0	783.6	764.2	743.7	722.9	706.8
22.5°	876.6	874.7	869.9	855.8	839.5	820.2	798.1	774.5	749.6	726.1	704.9
25°	937.2	935.7	926.1	909.8	887.0	857.3	828.4	796.0	760.2	729.2	703.6
27.5°	978.6	977.0	969.9	956.3	935.2	904.0	864.9	821.5	777.0	734.3	697.3
30°	974.4	978.0	977.0	970.7	954.8	926.9	890.7	841.9	788.9	738.8	694.7
32.5°	915.8	919.0	927.2	939.6	940.5	929.3	902.2	857.2	802.3	745.3	692.6
35°	777.5	781.7	797.6	822.5	855.3	882.5	888.1	863.8	814.6	753.3	689.5
37.5°	597.7	620.7	634.1	660.4	709.7	759.9	808.2	826.0	805.1	749.9	684.6
40°	507.8	513.3	537.1	566.8	608.3	660.6	729.4	779.1	780.7	742.6	676.7
42.5°	434.5	441.7	458.0	481.7	517.3	569.5	640.6	706.2	736.5	722.0	666.4
45°	347.7	353.0	365.0	383.1	410.4	453.6	514.7	590.6	650.8	674.4	638.9
47.5°	285.6	288.5	298.8	312.8	333.0	364.4	411.7	477.6	549.8	600.4	595.4
50°	252.1	255.3	263.2	273.7	290.7	317.3	355.2	410.0	484.4	546.2	558.7
52.5°	225.9	228.6	233.6	243.5	257.5	277.9	308.5	358.1	425.1	490.8	519.5
55°	190.9	192.8	196.7	202.3	213.5	228.2	254.6	288.9	343.1	409.3	451.3
57.5°	162.1	163.0	165.5	170.7	178.4	189.1	208.2	237.2	276.1	335.8	382.1
60°	143.7	144.7	147.9	151.5	157.5	167.3	182.3	202.6	239.8	289.1	336.0
62.5°	129.2	129.8	131.2	134.6	140.0	147.5	159.3	175.8	205.5	248.8	293.1
65°	108.3	108.5	109.0	111.8	115.0	120.7	128.4	140.0	162.4	195.1	234.3
67.5°	88.2	88.6	90.2	91.2	94.5	97.5	102.0	110.9	126.7	148.8	179.3
70°	77.1	76.7	78.4	79.6	80.7	84.2	87.3	94.5	104.3	121.1	146.5
72.5°	66.6	65.9	66.7	67.1	68.6	71.0	74.0	78.5	86.0	97.6	117.0
75°	50.4	50.6	50.6	51.1	52.3	53.2	54.1	56.5	60.7	68.4	78.9
77.5°	35.3	35.0	36.0	36.2	36.9	37.9	38.7	39.6	41.3	44.4	49.9
80°	25.7	25.7	25.9	26.6	26.4	26.9	28.0	29.0	31.0	32.9	34.7
82.5°	19.7	19.5	19.7	19.9	19.8	20.3	20.7	20.9	21.7	22.6	23.9
85°	10.7	10.7	11.0	11.0	11.2	11.2	11.4	11.4	11.4	11.7	11.9
87.5°	6.3	6.1	5.9	5.8	5.9	6.2	5.9	5.6	5.5	5.4	5.5
90°	11.0	10.7	10.4	10.1	9.8	9.4	8.9	8.4	7.9	7.4	6.6
92.5°	21.6	21.4	21.1	20.9	20.7	20.3	19.6	18.9	18.3	17.6	16.7
95°	39.4	39.2	39.0	38.8	38.6	38.1	37.4	36.7	36.0	35.2	34.2
97.5°	59.7	59.6	59.5	59.3	59.2	58.8	58.2	57.5	56.8	56.1	54.7
100°	75.0	74.8	74.6	74.4	74.2	73.7	72.8	71.9	71.0	70.0	68.7
102.5°	90.5	90.2	89.9	89.6	89.3	88.7	87.7	86.6	85.6	84.6	84.0
105°	113.5	113.2	112.9	112.6	112.3	111.8	111.2	110.6	110.0	109.4	108.8
107.5°	137.1	137.1	137.1	137.2	137.2	137.0	136.7	136.4	136.1	135.8	135.4
110°	154.7	154.8	154.9	155.0	155.1	155.0	154.7	154.4	154.1	153.8	153.5



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	171.9	172.1	172.3	172.5	172.7	172.7	172.5	172.4	172.3	172.1	171.7
115°	199.1	199.2	199.3	199.4	199.5	199.7	199.8	199.9	200.0	200.1	199.9
117.5°	225.6	226.0	226.5	226.9	227.3	227.4	227.3	227.3	227.2	227.1	226.9
120°	244.0	244.4	244.8	245.2	245.6	245.8	245.8	245.8	245.8	245.8	245.7
122.5°	262.3	262.6	263.0	263.3	263.6	263.8	263.9	264.0	264.0	264.1	263.9
125°	289.7	289.8	289.9	290.0	290.1	290.3	290.5	290.7	290.9	291.1	291.0
127.5°	316.1	316.3	316.5	316.7	316.9	317.1	317.2	317.3	317.4	317.5	317.3
130°	333.7	333.9	334.1	334.3	334.5	334.7	334.8	334.9	335.0	335.1	334.9
132.5°	350.1	350.4	350.7	351.0	351.3	351.4	351.5	351.6	351.7	351.8	351.9
135°	375.8	376.2	376.6	377.0	377.4	377.6	377.6	377.6	377.6	377.6	377.5
137.5°	400.8	401.3	401.9	402.4	402.9	403.1	402.9	402.8	402.7	402.6	402.3
140°	417.0	417.5	418.0	418.5	419.0	419.2	419.0	418.8	418.6	418.4	418.1
142.5°	432.3	432.8	433.3	433.8	434.3	434.5	434.4	434.3	434.2	434.1	433.7
145°	455.4	455.8	456.1	456.4	456.7	456.8	456.8	456.8	456.8	456.8	456.5
147.5°	475.1	475.7	476.5	477.2	477.9	478.1	477.9	477.6	477.4	477.2	476.9
150°	489.8	490.0	490.2	490.4	490.6	490.7	490.7	490.7	490.7	490.7	490.3
152.5°	501.8	502.2	502.6	502.9	503.3	503.3	503.1	502.9	502.6	502.4	502.2
155°	519.1	519.6	520.1	520.6	521.1	521.1	520.7	520.3	519.9	519.5	519.4
157.5°	533.4	534.1	534.7	535.4	536.1	536.2	535.8	535.4	535.0	534.6	534.5
160°	543.3	543.8	544.3	544.8	545.3	545.4	545.0	544.6	544.2	543.7	543.6
162.5°	551.7	552.3	552.9	553.5	554.1	554.1	553.6	553.2	552.7	552.2	552.2
165°	563.0	563.6	564.2	564.8	565.4	565.5	565.1	564.7	564.3	563.9	563.8
167.5°	572.0	572.6	573.2	573.8	574.5	574.5	573.9	573.3	572.7	572.1	572.1
170°	576.7	577.4	578.1	578.9	579.6	579.7	579.0	578.3	577.7	577.1	577.1
172.5°	580.8	581.4	582.0	582.6	583.3	583.3	582.7	582.1	581.5	580.9	580.9
175°	584.5	585.2	585.9	586.6	587.3	587.4	586.8	586.1	585.5	584.9	584.9
177.5°	586.7	587.2	587.8	588.4	589.0	589.1	588.5	588.0	587.5	587.0	587.1
180°	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	584.1	582.8	580.4	578.1	575.3	572.9	571.2	569.2	566.5	563.4	560.8
5°	610.0	604.8	598.0	592.2	584.7	579.0	572.9	567.0	561.2	553.7	547.1
7.5°	638.6	628.0	617.7	604.7	593.0	582.5	572.4	562.2	552.2	541.6	531.4
10°	656.2	643.3	629.1	612.8	597.8	583.6	570.6	557.6	544.1	532.3	519.5
12.5°	672.6	656.0	639.7	619.1	601.2	583.8	567.1	551.2	536.7	521.3	507.5
15°	687.4	671.1	652.9	627.7	602.7	581.7	562.1	541.4	523.4	506.1	490.7
17.5°	693.2	676.0	654.9	630.7	603.4	576.9	551.7	529.0	507.8	487.7	470.4
20°	690.9	674.4	652.7	629.5	600.4	572.9	545.5	520.4	496.8	475.5	457.2
22.5°	685.5	668.4	647.4	623.0	595.3	566.1	536.9	510.1	485.4	463.4	443.3
25°	677.4	654.1	632.6	608.7	582.4	553.5	523.4	493.7	467.4	444.9	423.0
27.5°	668.9	639.9	612.5	588.9	561.0	535.2	506.1	475.7	448.1	425.3	402.7
30°	661.3	628.6	598.5	571.7	545.3	520.8	493.3	463.6	435.2	411.6	388.8
32.5°	651.8	617.0	584.0	553.0	527.6	503.3	478.4	450.0	422.3	398.0	374.8
35°	639.9	595.5	559.6	526.6	498.5	474.8	452.4	429.6	401.8	376.6	354.0
37.5°	624.2	573.8	532.3	496.4	466.7	443.0	425.3	404.3	379.0	355.0	334.0
40°	614.6	558.2	512.7	477.2	446.0	420.9	404.3	386.7	363.6	340.9	319.9
42.5°	602.0	543.8	492.9	456.0	424.4	400.4	383.6	368.2	348.8	327.5	305.0
45°	577.0	515.9	462.5	422.8	391.1	367.5	351.8	338.1	323.5	303.8	284.2
47.5°	544.7	486.9	430.9	387.6	356.6	334.7	319.5	308.6	298.1	281.4	262.5
50°	518.8	462.9	408.4	366.4	333.3	312.5	298.2	289.6	280.0	264.9	248.9
52.5°	488.1	438.3	384.9	341.9	310.6	291.1	277.5	268.8	260.9	248.6	233.5
55°	439.9	396.2	347.2	308.2	279.5	259.9	246.9	238.7	234.1	223.6	211.7
57.5°	384.2	352.9	309.7	272.2	246.7	227.4	217.8	210.9	205.6	198.1	189.8
60°	345.4	323.5	284.7	248.9	225.6	207.2	198.5	192.8	187.8	181.6	175.0
62.5°	306.0	290.0	256.3	225.6	204.2	188.7	180.7	175.4	169.8	165.5	159.2
65°	253.2	238.9	215.6	191.6	171.8	159.4	153.5	148.9	145.4	140.7	136.2
67.5°	196.9	191.2	175.0	158.4	144.2	133.2	128.2	124.9	120.8	118.0	114.9
70°	162.4	159.6	148.1	137.2	123.9	116.4	111.8	110.4	105.2	102.4	100.4
72.5°	131.8	130.5	123.9	116.3	106.9	100.4	96.1	94.5	91.2	89.0	87.7
75°	90.3	90.8	89.6	84.7	81.2	77.1	73.3	72.3	70.0	68.2	67.0
77.5°	57.2	59.5	59.6	59.4	58.0	55.4	53.8	53.1	50.9	50.2	49.9
80°	39.2	41.8	44.1	43.8	43.4	42.7	41.5	40.8	39.7	39.0	38.5
82.5°	26.2	28.5	30.5	31.7	31.6	30.9	30.2	29.8	29.6	29.1	29.0
85°	12.3	12.8	13.5	15.1	16.4	16.6	16.4	16.1	15.5	15.7	15.9
87.5°	5.5	5.4	5.4	5.3	4.8	5.7	6.1	6.1	5.9	5.7	5.5
90°	5.9	5.2	4.4	3.7	2.9	2.1	1.3	0.5	1.3	2.1	2.9
92.5°	15.9	14.9	14.0	13.3	12.8	12.2	11.6	11.1	11.6	12.2	12.8
95°	33.2	32.2	31.2	30.6	30.4	30.2	30.0	29.8	30.0	30.2	30.4
97.5°	53.3	51.9	50.5	49.8	49.7	49.6	49.5	49.4	49.5	49.6	49.7
100°	67.4	66.0	64.7	64.1	64.1	64.1	64.1	64.1	64.1	64.1	64.1
102.5°	83.3	82.7	82.0	81.5	81.1	80.7	80.2	79.8	80.2	80.7	81.1
105°	108.2	107.6	106.9	106.4	105.8	105.3	104.8	104.3	104.8	105.3	105.8
107.5°	134.9	134.4	134.0	133.5	133.0	132.5	132.0	131.5	132.0	132.5	133.0
110°	153.2	152.9	152.6	152.2	151.7	151.2	150.7	150.2	150.7	151.2	151.7



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	171.4	171.0	170.6	170.3	170.0	169.7	169.5	169.2	169.5	169.7	170.0
115°	199.7	199.4	199.2	198.9	198.5	198.1	197.6	197.2	197.6	198.1	198.5
117.5°	226.7	226.6	226.4	226.2	226.0	225.8	225.6	225.5	225.6	225.8	226.0
120°	245.6	245.5	245.4	245.1	244.6	244.1	243.6	243.1	243.6	244.1	244.6
122.5°	263.6	263.3	263.1	262.8	262.7	262.5	262.3	262.1	262.3	262.5	262.7
125°	290.9	290.8	290.7	290.3	289.7	289.1	288.5	287.9	288.5	289.1	289.7
127.5°	317.2	317.1	317.0	316.8	316.4	316.1	315.7	315.4	315.7	316.1	316.4
130°	334.7	334.5	334.3	333.9	333.4	332.9	332.3	331.8	332.3	332.9	333.4
132.5°	351.9	352.0	352.0	351.6	350.8	350.0	349.1	348.3	349.1	350.0	350.8
135°	377.4	377.3	377.2	376.9	376.3	375.7	375.1	374.4	375.1	375.7	376.3
137.5°	402.1	401.9	401.7	401.3	400.7	400.1	399.5	398.9	399.5	400.1	400.7
140°	417.8	417.5	417.2	416.7	416.2	415.7	415.2	414.7	415.2	415.7	416.2
142.5°	433.3	432.9	432.5	432.1	431.7	431.3	430.8	430.4	430.8	431.3	431.7
145°	456.2	455.9	455.6	455.2	454.8	454.4	454.0	453.6	454.0	454.4	454.8
147.5°	476.7	476.4	476.2	475.9	475.6	475.4	475.2	475.0	475.2	475.4	475.6
150°	489.9	489.5	489.1	488.9	489.0	489.1	489.2	489.3	489.2	489.1	489.0
152.5°	502.1	501.9	501.7	501.6	501.4	501.3	501.2	501.0	501.2	501.3	501.4
155°	519.3	519.2	519.1	519.1	519.1	519.1	519.1	519.1	519.1	519.1	519.1
157.5°	534.4	534.3	534.2	534.2	534.5	534.7	534.9	535.1	534.9	534.7	534.5
160°	543.5	543.4	543.3	543.4	543.7	544.0	544.4	544.7	544.4	544.0	543.7
162.5°	552.1	552.1	552.1	552.2	552.4	552.7	552.9	553.1	552.9	552.7	552.4
165°	563.7	563.6	563.5	563.5	563.7	563.9	564.1	564.3	564.1	563.9	563.7
167.5°	572.1	572.1	572.1	572.3	572.7	573.1	573.5	573.9	573.5	573.1	572.7
170°	577.1	577.1	577.1	577.3	577.7	578.1	578.6	579.0	578.6	578.1	577.7
172.5°	580.9	580.9	580.9	581.1	581.5	581.9	582.3	582.7	582.3	581.9	581.5
175°	584.9	584.9	584.9	585.1	585.5	585.9	586.3	586.8	586.3	585.9	585.5
177.5°	587.2	587.3	587.3	587.5	587.9	588.2	588.5	588.9	588.5	588.2	587.9
180°	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	558.9	556.3	554.4	550.7	548.1	546.9	544.9	544.3	546.4	544.9	544.7
5°	542.3	535.5	530.2	524.8	519.0	515.2	509.6	508.7	507.3	505.2	504.7
7.5°	522.4	513.5	506.6	497.8	490.1	483.8	476.9	473.5	471.7	469.0	465.3
10°	509.0	498.5	489.1	480.2	470.7	462.9	456.0	450.6	447.1	443.8	442.4
12.5°	495.6	484.9	473.0	462.3	451.6	443.0	435.3	431.7	427.9	424.0	420.8
15°	475.0	460.9	447.8	435.5	426.4	417.0	409.5	404.3	398.6	396.9	390.6
17.5°	453.2	439.3	423.9	411.0	400.4	390.1	381.9	376.1	371.7	365.7	362.8
20°	439.6	423.0	408.1	396.2	384.6	372.4	364.1	359.1	355.0	350.0	347.7
22.5°	425.1	408.9	393.5	379.6	367.8	355.8	349.8	344.8	340.0	335.5	332.3
25°	403.6	387.4	371.2	356.8	344.5	335.8	328.8	323.0	320.4	316.0	312.7
27.5°	382.5	365.2	348.5	334.1	324.4	315.8	310.0	305.5	300.8	297.0	294.1
30°	368.9	351.2	333.0	321.5	311.2	303.2	296.8	292.4	288.9	285.4	283.3
32.5°	355.3	337.0	320.8	308.5	298.8	291.8	285.3	280.9	277.3	273.5	270.9
35°	333.5	314.8	301.7	289.6	280.0	273.5	269.0	263.0	259.9	257.1	254.6
37.5°	313.2	295.8	281.7	271.0	262.7	256.2	250.4	247.2	243.5	241.0	238.8
40°	298.2	282.4	269.5	258.3	252.3	245.0	239.6	235.4	232.7	229.3	227.0
42.5°	284.8	270.0	257.5	247.5	239.9	233.8	228.6	224.4	220.9	218.5	216.6
45°	265.8	251.1	238.9	229.6	222.6	216.8	211.4	209.3	204.6	201.9	200.9
47.5°	246.1	233.0	221.3	212.7	205.5	200.0	194.9	190.7	188.0	185.3	183.8
50°	232.9	220.3	209.3	200.9	193.9	187.8	183.2	180.4	176.8	174.3	172.5
52.5°	219.6	207.9	197.0	188.9	182.9	176.8	171.6	168.8	165.5	163.9	162.6
55°	200.7	188.3	178.9	171.1	164.7	159.2	154.2	151.5	149.4	147.7	147.2
57.5°	179.3	169.5	160.8	153.6	147.0	141.8	137.4	134.8	133.0	132.7	131.3
60°	165.2	156.3	148.5	140.7	135.1	130.2	126.4	123.4	121.6	121.4	120.9
62.5°	151.2	142.7	135.3	128.6	123.5	118.9	115.2	111.9	110.8	109.6	108.6
65°	130.5	122.7	116.6	111.3	105.9	102.0	98.5	96.3	93.8	92.4	89.9
67.5°	110.1	104.1	98.3	93.7	89.5	85.7	82.8	79.7	78.0	76.9	75.0
70°	96.6	91.9	86.1	81.2	78.0	74.9	72.6	69.1	67.9	67.0	66.0
72.5°	83.9	79.8	74.9	70.9	67.7	64.8	62.1	60.5	59.3	58.4	57.9
75°	66.0	62.1	57.9	55.0	52.7	50.4	49.0	47.9	47.4	47.2	46.3
77.5°	48.5	46.4	43.0	40.8	39.3	38.3	37.1	36.5	36.4	35.3	35.0
80°	37.1	36.0	33.1	32.2	31.0	30.1	29.4	28.3	27.1	26.6	25.9
82.5°	27.6	26.5	25.2	23.8	22.8	22.2	21.6	21.1	21.3	20.6	20.3
85°	14.7	13.5	13.0	12.8	12.3	12.8	12.6	12.3	12.1	11.9	12.1
87.5°	5.5	5.6	5.6	6.1	5.7	6.0	6.1	6.0	6.1	6.2	6.1
90°	3.7	4.4	5.2	5.9	6.6	7.4	7.9	8.4	8.9	9.4	9.8
92.5°	13.3	14.0	14.9	15.9	16.7	17.6	18.3	18.9	19.6	20.3	20.7
95°	30.6	31.2	32.2	33.2	34.2	35.2	36.0	36.7	37.4	38.1	38.6
97.5°	49.8	50.5	51.9	53.3	54.7	56.1	56.8	57.5	58.2	58.8	59.2
100°	64.1	64.7	66.0	67.4	68.7	70.0	71.0	71.9	72.8	73.7	74.2
102.5°	81.5	82.0	82.7	83.3	84.0	84.6	85.6	86.6	87.7	88.7	89.3
105°	106.4	106.9	107.6	108.2	108.8	109.4	110.0	110.6	111.2	111.8	112.3
107.5°	133.5	134.0	134.4	134.9	135.4	135.8	136.1	136.4	136.7	137.0	137.2
110°	152.2	152.6	152.9	153.2	153.5	153.8	154.1	154.4	154.7	155.0	155.1



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.3	170.6	171.0	171.4	171.7	172.1	172.3	172.4	172.5	172.7	172.7
115°	198.9	199.2	199.4	199.7	199.9	200.1	200.0	199.9	199.8	199.7	199.5
117.5°	226.2	226.4	226.6	226.7	226.9	227.1	227.2	227.3	227.3	227.4	227.3
120°	245.1	245.4	245.5	245.6	245.7	245.8	245.8	245.8	245.8	245.8	245.6
122.5°	262.8	263.1	263.3	263.6	263.9	264.1	264.0	264.0	263.9	263.8	263.6
125°	290.3	290.7	290.8	290.9	291.0	291.1	290.9	290.7	290.5	290.3	290.1
127.5°	316.8	317.0	317.1	317.2	317.3	317.5	317.4	317.3	317.2	317.1	316.9
130°	333.9	334.3	334.5	334.7	334.9	335.1	335.0	334.9	334.8	334.7	334.5
132.5°	351.6	352.0	352.0	351.9	351.9	351.8	351.7	351.6	351.5	351.4	351.3
135°	376.9	377.2	377.3	377.4	377.5	377.6	377.6	377.6	377.6	377.6	377.4
137.5°	401.3	401.7	401.9	402.1	402.3	402.6	402.7	402.8	402.9	403.1	402.9
140°	416.7	417.2	417.5	417.8	418.1	418.4	418.6	418.8	419.0	419.2	419.0
142.5°	432.1	432.5	432.9	433.3	433.7	434.1	434.2	434.3	434.4	434.5	434.3
145°	455.2	455.6	455.9	456.2	456.5	456.8	456.8	456.8	456.8	456.8	456.7
147.5°	475.9	476.2	476.4	476.7	476.9	477.2	477.4	477.6	477.9	478.1	477.9
150°	488.9	489.1	489.5	489.9	490.3	490.7	490.7	490.7	490.7	490.7	490.6
152.5°	501.6	501.7	501.9	502.1	502.2	502.4	502.6	502.9	503.1	503.3	503.3
155°	519.1	519.1	519.2	519.3	519.4	519.5	519.9	520.3	520.7	521.1	521.1
157.5°	534.2	534.2	534.3	534.4	534.5	534.6	535.0	535.4	535.8	536.2	536.1
160°	543.4	543.3	543.4	543.5	543.6	543.7	544.2	544.6	545.0	545.4	545.3
162.5°	552.2	552.1	552.1	552.1	552.2	552.2	552.7	553.2	553.6	554.1	554.1
165°	563.5	563.5	563.6	563.7	563.8	563.9	564.3	564.7	565.1	565.5	565.4
167.5°	572.3	572.1	572.1	572.1	572.1	572.1	572.7	573.3	573.9	574.5	574.5
170°	577.3	577.1	577.1	577.1	577.1	577.1	577.7	578.3	579.0	579.7	579.6
172.5°	581.1	580.9	580.9	580.9	580.9	580.9	581.5	582.1	582.7	583.3	583.3
175°	585.1	584.9	584.9	584.9	584.9	584.9	585.5	586.1	586.8	587.4	587.3
177.5°	587.5	587.3	587.3	587.2	587.1	587.0	587.5	588.0	588.5	589.1	589.0
180°	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	544.5	542.5	541.9	542.7	541.9	542.5	544.5	544.7	544.9	546.4	544.3
5°	502.4	500.1	501.2	500.8	501.2	500.1	502.4	504.7	505.2	507.3	508.7
7.5°	465.3	462.4	459.4	460.3	459.4	462.4	465.3	465.3	469.0	471.7	473.5
10°	439.4	437.1	435.7	436.9	435.7	437.1	439.4	442.4	443.8	447.1	450.6
12.5°	417.6	416.2	415.0	414.4	415.0	416.2	417.6	420.8	424.0	427.9	431.7
15°	387.8	385.1	383.8	380.8	383.8	385.1	387.8	390.6	396.9	398.6	404.3
17.5°	360.4	359.5	356.5	355.2	356.5	359.5	360.4	362.8	365.7	371.7	376.1
20°	344.2	343.3	340.2	342.0	340.2	343.3	344.2	347.7	350.0	355.0	359.1
22.5°	330.7	328.7	327.7	327.2	327.7	328.7	330.7	332.3	335.5	340.0	344.8
25°	311.7	308.7	307.5	306.2	307.5	308.7	311.7	312.7	316.0	320.4	323.0
27.5°	292.8	291.1	289.6	289.2	289.6	291.1	292.8	294.1	297.0	300.8	305.5
30°	280.4	278.8	277.7	277.7	277.7	278.8	280.4	283.3	285.4	288.9	292.4
32.5°	269.4	268.2	267.0	266.8	267.0	268.2	269.4	270.9	273.5	277.3	280.9
35°	253.4	251.6	251.1	249.6	251.1	251.6	253.4	254.6	257.1	259.9	263.0
37.5°	236.7	235.2	235.2	235.0	235.2	235.2	236.7	238.8	241.0	243.5	247.2
40°	226.1	224.9	224.7	223.1	224.7	224.9	226.1	227.0	229.3	232.7	235.4
42.5°	214.7	214.1	213.3	212.6	213.3	214.1	214.7	216.6	218.5	220.9	224.4
45°	199.2	197.6	197.6	196.5	197.6	197.6	199.2	200.9	201.9	204.6	209.3
47.5°	183.3	182.1	182.2	181.0	182.2	182.1	183.3	183.8	185.3	188.0	190.7
50°	172.7	172.0	171.8	171.3	171.8	172.0	172.7	172.5	174.3	176.8	180.4
52.5°	162.1	161.7	162.6	161.6	162.6	161.7	162.1	162.6	163.9	165.5	168.8
55°	147.7	147.0	148.5	147.0	148.5	147.0	147.7	147.2	147.7	149.4	151.5
57.5°	131.3	130.6	131.9	131.2	131.9	130.6	131.3	131.3	132.7	133.0	134.8
60°	120.4	119.0	119.7	120.0	119.7	119.0	120.4	120.9	121.4	121.6	123.4
62.5°	107.6	106.6	107.2	106.1	107.2	106.6	107.6	108.6	109.6	110.8	111.9
65°	89.4	88.7	87.8	87.3	87.8	88.7	89.4	89.9	92.4	93.8	96.3
67.5°	75.1	73.4	73.3	73.7	73.3	73.4	75.1	75.0	76.9	78.0	79.7
70°	64.6	64.6	64.4	64.4	64.4	64.6	64.6	66.0	67.0	67.9	69.1
72.5°	57.4	57.2	56.8	56.6	56.8	57.2	57.4	57.9	58.4	59.3	60.5
75°	46.3	46.5	45.9	45.7	45.9	46.5	46.3	46.3	47.2	47.4	47.9
77.5°	34.1	33.1	33.6	33.1	33.6	33.1	34.1	35.0	35.3	36.4	36.5
80°	25.9	25.7	26.4	25.7	26.4	25.7	25.9	25.9	26.6	27.1	28.3
82.5°	20.5	20.3	20.6	20.1	20.6	20.3	20.5	20.3	20.6	21.3	21.1
85°	12.3	12.1	11.9	12.1	11.9	12.1	12.3	12.1	11.9	12.1	12.3
87.5°	6.3	6.2	6.3	6.3	6.3	6.2	6.3	6.1	6.2	6.1	6.0
90°	10.1	10.4	10.7	11.0	10.7	10.4	10.1	9.8	9.4	8.9	8.4
92.5°	20.9	21.1	21.4	21.6	21.4	21.1	20.9	20.7	20.3	19.6	18.9
95°	38.8	39.0	39.2	39.4	39.2	39.0	38.8	38.6	38.1	37.4	36.7
97.5°	59.3	59.5	59.6	59.7	59.6	59.5	59.3	59.2	58.8	58.2	57.5
100°	74.4	74.6	74.8	75.0	74.8	74.6	74.4	74.2	73.7	72.8	71.9
102.5°	89.6	89.9	90.2	90.5	90.2	89.9	89.6	89.3	88.7	87.7	86.6
105°	112.6	112.9	113.2	113.5	113.2	112.9	112.6	112.3	111.8	111.2	110.6
107.5°	137.2	137.1	137.1	137.1	137.1	137.1	137.2	137.2	137.0	136.7	136.4
110°	155.0	154.9	154.8	154.7	154.8	154.9	155.0	155.1	155.0	154.7	154.4



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	172.5	172.3	172.1	171.9	172.1	172.3	172.5	172.7	172.7	172.5	172.4
115°	199.4	199.3	199.2	199.1	199.2	199.3	199.4	199.5	199.7	199.8	199.9
117.5°	226.9	226.5	226.0	225.6	226.0	226.5	226.9	227.3	227.4	227.3	227.3
120°	245.2	244.8	244.4	244.0	244.4	244.8	245.2	245.6	245.8	245.8	245.8
122.5°	263.3	263.0	262.6	262.3	262.6	263.0	263.3	263.6	263.8	263.9	264.0
125°	290.0	289.9	289.8	289.7	289.8	289.9	290.0	290.1	290.3	290.5	290.7
127.5°	316.7	316.5	316.3	316.1	316.3	316.5	316.7	316.9	317.1	317.2	317.3
130°	334.3	334.1	333.9	333.7	333.9	334.1	334.3	334.5	334.7	334.8	334.9
132.5°	351.0	350.7	350.4	350.1	350.4	350.7	351.0	351.3	351.4	351.5	351.6
135°	377.0	376.6	376.2	375.8	376.2	376.6	377.0	377.4	377.6	377.6	377.6
137.5°	402.4	401.9	401.3	400.8	401.3	401.9	402.4	402.9	403.1	402.9	402.8
140°	418.5	418.0	417.5	417.0	417.5	418.0	418.5	419.0	419.2	419.0	418.8
142.5°	433.8	433.3	432.8	432.3	432.8	433.3	433.8	434.3	434.5	434.4	434.3
145°	456.4	456.1	455.8	455.4	455.8	456.1	456.4	456.7	456.8	456.8	456.8
147.5°	477.2	476.5	475.7	475.1	475.7	476.5	477.2	477.9	478.1	477.9	477.6
150°	490.4	490.2	490.0	489.8	490.0	490.2	490.4	490.6	490.7	490.7	490.7
152.5°	502.9	502.6	502.2	501.8	502.2	502.6	502.9	503.3	503.3	503.1	502.9
155°	520.6	520.1	519.6	519.1	519.6	520.1	520.6	521.1	521.1	520.7	520.3
157.5°	535.4	534.7	534.1	533.4	534.1	534.7	535.4	536.1	536.2	535.8	535.4
160°	544.8	544.3	543.8	543.3	543.8	544.3	544.8	545.3	545.4	545.0	544.6
162.5°	553.5	552.9	552.3	551.7	552.3	552.9	553.5	554.1	554.1	553.6	553.2
165°	564.8	564.2	563.6	563.0	563.6	564.2	564.8	565.4	565.5	565.1	564.7
167.5°	573.8	573.2	572.6	572.0	572.6	573.2	573.8	574.5	574.5	573.9	573.3
170°	578.9	578.1	577.4	576.7	577.4	578.1	578.9	579.6	579.7	579.0	578.3
172.5°	582.6	582.0	581.4	580.8	581.4	582.0	582.6	583.3	583.3	582.7	582.1
175°	586.6	585.9	585.2	584.5	585.2	585.9	586.6	587.3	587.4	586.8	586.1
177.5°	588.4	587.8	587.2	586.7	587.2	587.8	588.4	589.0	589.1	588.5	588.0
180°	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	544.9	546.9	548.1	550.7	554.4	556.3	558.9	560.8	563.4	566.5	569.2
5°	509.6	515.2	519.0	524.8	530.2	535.5	542.3	547.1	553.7	561.2	567.0
7.5°	476.9	483.8	490.1	497.8	506.6	513.5	522.4	531.4	541.6	552.2	562.2
10°	456.0	462.9	470.7	480.2	489.1	498.5	509.0	519.5	532.3	544.1	557.6
12.5°	435.3	443.0	451.6	462.3	473.0	484.9	495.6	507.5	521.3	536.7	551.2
15°	409.5	417.0	426.4	435.5	447.8	460.9	475.0	490.7	506.1	523.4	541.4
17.5°	381.9	390.1	400.4	411.0	423.9	439.3	453.2	470.4	487.7	507.8	529.0
20°	364.1	372.4	384.6	396.2	408.1	423.0	439.6	457.2	475.5	496.8	520.4
22.5°	349.8	355.8	367.8	379.6	393.5	408.9	425.1	443.3	463.4	485.4	510.1
25°	328.8	335.8	344.5	356.8	371.2	387.4	403.6	423.0	444.9	467.4	493.7
27.5°	310.0	315.8	324.4	334.1	348.5	365.2	382.5	402.7	425.3	448.1	475.7
30°	296.8	303.2	311.2	321.5	333.0	351.2	368.9	388.8	411.6	435.2	463.6
32.5°	285.3	291.8	298.8	308.5	320.8	337.0	355.3	374.8	398.0	422.3	450.0
35°	269.0	273.5	280.0	289.6	301.7	314.8	333.5	354.0	376.6	401.8	429.6
37.5°	250.4	256.2	262.7	271.0	281.7	295.8	313.2	334.0	355.0	379.0	404.3
40°	239.6	245.0	252.3	258.3	269.5	282.4	298.2	319.9	340.9	363.6	386.7
42.5°	228.6	233.8	239.9	247.5	257.5	270.0	284.8	305.0	327.5	348.8	368.2
45°	211.4	216.8	222.6	229.6	238.9	251.1	265.8	284.2	303.8	323.5	338.1
47.5°	194.9	200.0	205.5	212.7	221.3	233.0	246.1	262.5	281.4	298.1	308.6
50°	183.2	187.8	193.9	200.9	209.3	220.3	232.9	248.9	264.9	280.0	289.6
52.5°	171.6	176.8	182.9	188.9	197.0	207.9	219.6	233.5	248.6	260.9	268.8
55°	154.2	159.2	164.7	171.1	178.9	188.3	200.7	211.7	223.6	234.1	238.7
57.5°	137.4	141.8	147.0	153.6	160.8	169.5	179.3	189.8	198.1	205.6	210.9
60°	126.4	130.2	135.1	140.7	148.5	156.3	165.2	175.0	181.6	187.8	192.8
62.5°	115.2	118.9	123.5	128.6	135.3	142.7	151.2	159.2	165.5	169.8	175.4
65°	98.5	102.0	105.9	111.3	116.6	122.7	130.5	136.2	140.7	145.4	148.9
67.5°	82.8	85.7	89.5	93.7	98.3	104.1	110.1	114.9	118.0	120.8	124.9
70°	72.6	74.9	78.0	81.2	86.1	91.9	96.6	100.4	102.4	105.2	110.4
72.5°	62.1	64.8	67.7	70.9	74.9	79.8	83.9	87.7	89.0	91.2	94.5
75°	49.0	50.4	52.7	55.0	57.9	62.1	66.0	67.0	68.2	70.0	72.3
77.5°	37.1	38.3	39.3	40.8	43.0	46.4	48.5	49.9	50.2	50.9	53.1
80°	29.4	30.1	31.0	32.2	33.1	36.0	37.1	38.5	39.0	39.7	40.8
82.5°	21.6	22.2	22.8	23.8	25.2	26.5	27.6	29.0	29.1	29.6	29.8
85°	12.6	12.8	12.3	12.8	13.0	13.5	14.7	15.9	15.7	15.5	16.1
87.5°	6.1	6.0	5.7	6.1	5.6	5.6	5.5	5.5	5.7	5.9	6.1
90°	7.9	7.4	6.6	5.9	5.2	4.4	3.7	2.9	2.1	1.3	0.5
92.5°	18.3	17.6	16.7	15.9	14.9	14.0	13.3	12.8	12.2	11.6	11.1
95°	36.0	35.2	34.2	33.2	32.2	31.2	30.6	30.4	30.2	30.0	29.8
97.5°	56.8	56.1	54.7	53.3	51.9	50.5	49.8	49.7	49.6	49.5	49.4
100°	71.0	70.0	68.7	67.4	66.0	64.7	64.1	64.1	64.1	64.1	64.1
102.5°	85.6	84.6	84.0	83.3	82.7	82.0	81.5	81.1	80.7	80.2	79.8
105°	110.0	109.4	108.8	108.2	107.6	106.9	106.4	105.8	105.3	104.8	104.3
107.5°	136.1	135.8	135.4	134.9	134.4	134.0	133.5	133.0	132.5	132.0	131.5
110°	154.1	153.8	153.5	153.2	152.9	152.6	152.2	151.7	151.2	150.7	150.2



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	172.3	172.1	171.7	171.4	171.0	170.6	170.3	170.0	169.7	169.5	169.2
115°	200.0	200.1	199.9	199.7	199.4	199.2	198.9	198.5	198.1	197.6	197.2
117.5°	227.2	227.1	226.9	226.7	226.6	226.4	226.2	226.0	225.8	225.6	225.5
120°	245.8	245.8	245.7	245.6	245.5	245.4	245.1	244.6	244.1	243.6	243.1
122.5°	264.0	264.1	263.9	263.6	263.3	263.1	262.8	262.7	262.5	262.3	262.1
125°	290.9	291.1	291.0	290.9	290.8	290.7	290.3	289.7	289.1	288.5	287.9
127.5°	317.4	317.5	317.3	317.2	317.1	317.0	316.8	316.4	316.1	315.7	315.4
130°	335.0	335.1	334.9	334.7	334.5	334.3	333.9	333.4	332.9	332.3	331.8
132.5°	351.7	351.8	351.9	351.9	352.0	352.0	351.6	350.8	350.0	349.1	348.3
135°	377.6	377.6	377.5	377.4	377.3	377.2	376.9	376.3	375.7	375.1	374.4
137.5°	402.7	402.6	402.3	402.1	401.9	401.7	401.3	400.7	400.1	399.5	398.9
140°	418.6	418.4	418.1	417.8	417.5	417.2	416.7	416.2	415.7	415.2	414.7
142.5°	434.2	434.1	433.7	433.3	432.9	432.5	432.1	431.7	431.3	430.8	430.4
145°	456.8	456.8	456.5	456.2	455.9	455.6	455.2	454.8	454.4	454.0	453.6
147.5°	477.4	477.2	476.9	476.7	476.4	476.2	475.9	475.6	475.4	475.2	475.0
150°	490.7	490.7	490.3	489.9	489.5	489.1	488.9	489.0	489.1	489.2	489.3
152.5°	502.6	502.4	502.2	502.1	501.9	501.7	501.6	501.4	501.3	501.2	501.0
155°	519.9	519.5	519.4	519.3	519.2	519.1	519.1	519.1	519.1	519.1	519.1
157.5°	535.0	534.6	534.5	534.4	534.3	534.2	534.2	534.5	534.7	534.9	535.1
160°	544.2	543.7	543.6	543.5	543.4	543.3	543.4	543.7	544.0	544.4	544.7
162.5°	552.7	552.2	552.2	552.1	552.1	552.1	552.2	552.4	552.7	552.9	553.1
165°	564.3	563.9	563.8	563.7	563.6	563.5	563.5	563.7	563.9	564.1	564.3
167.5°	572.7	572.1	572.1	572.1	572.1	572.1	572.3	572.7	573.1	573.5	573.9
170°	577.7	577.1	577.1	577.1	577.1	577.1	577.3	577.7	578.1	578.6	579.0
172.5°	581.5	580.9	580.9	580.9	580.9	580.9	581.1	581.5	581.9	582.3	582.7
175°	585.5	584.9	584.9	584.9	584.9	584.9	585.1	585.5	585.9	586.3	586.8
177.5°	587.5	587.0	587.1	587.2	587.3	587.3	587.5	587.9	588.2	588.5	588.9
180°	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	571.2	572.9	575.3	578.1	580.4	582.8	584.1	584.1	585.2	587.6	590.9
5°	572.9	579.0	584.7	592.2	598.0	604.8	610.0	614.9	619.2	624.9	630.8
7.5°	572.4	582.5	593.0	604.7	617.7	628.0	638.6	646.9	655.1	665.9	674.3
10°	570.6	583.6	597.8	612.8	629.1	643.3	656.2	667.8	679.0	690.7	701.3
12.5°	567.1	583.8	601.2	619.1	639.7	656.0	672.6	685.0	698.1	710.8	723.8
15°	562.1	581.7	602.7	627.7	652.9	671.1	687.4	703.6	715.7	730.1	742.6
17.5°	551.7	576.9	603.4	630.7	654.9	676.0	693.2	708.5	721.4	737.3	754.2
20°	545.5	572.9	600.4	629.5	652.7	674.4	690.9	706.8	722.9	743.7	764.2
22.5°	536.9	566.1	595.3	623.0	647.4	668.4	685.5	704.9	726.1	749.6	774.5
25°	523.4	553.5	582.4	608.7	632.6	654.1	677.4	703.6	729.2	760.2	796.0
27.5°	506.1	535.2	561.0	588.9	612.5	639.9	668.9	697.3	734.3	777.0	821.5
30°	493.3	520.8	545.3	571.7	598.5	628.6	661.3	694.7	738.8	788.9	841.9
32.5°	478.4	503.3	527.6	553.0	584.0	617.0	651.8	692.6	745.3	802.3	857.2
35°	452.4	474.8	498.5	526.6	559.6	595.5	639.9	689.5	753.3	814.6	863.8
37.5°	425.3	443.0	466.7	496.4	532.3	573.8	624.2	684.6	749.9	805.1	826.0
40°	404.3	420.9	446.0	477.2	512.7	558.2	614.6	676.7	742.6	780.7	779.1
42.5°	383.6	400.4	424.4	456.0	492.9	543.8	602.0	666.4	722.0	736.5	706.2
45°	351.8	367.5	391.1	422.8	462.5	515.9	577.0	638.9	674.4	650.8	590.6
47.5°	319.5	334.7	356.6	387.6	430.9	486.9	544.7	595.4	600.4	549.8	477.6
50°	298.2	312.5	333.3	366.4	408.4	462.9	518.8	558.7	546.2	484.4	410.0
52.5°	277.5	291.1	310.6	341.9	384.9	438.3	488.1	519.5	490.8	425.1	358.1
55°	246.9	259.9	279.5	308.2	347.2	396.2	439.9	451.3	409.3	343.1	288.9
57.5°	217.8	227.4	246.7	272.2	309.7	352.9	384.2	382.1	335.8	276.1	237.2
60°	198.5	207.2	225.6	248.9	284.7	323.5	345.4	336.0	289.1	239.8	202.6
62.5°	180.7	188.7	204.2	225.6	256.3	290.0	306.0	293.1	248.8	205.5	175.8
65°	153.5	159.4	171.8	191.6	215.6	238.9	253.2	234.3	195.1	162.4	140.0
67.5°	128.2	133.2	144.2	158.4	175.0	191.2	196.9	179.3	148.8	126.7	110.9
70°	111.8	116.4	123.9	137.2	148.1	159.6	162.4	146.5	121.1	104.3	94.5
72.5°	96.1	100.4	106.9	116.3	123.9	130.5	131.8	117.0	97.6	86.0	78.5
75°	73.3	77.1	81.2	84.7	89.6	90.8	90.3	78.9	68.4	60.7	56.5
77.5°	53.8	55.4	58.0	59.4	59.6	59.5	57.2	49.9	44.4	41.3	39.6
80°	41.5	42.7	43.4	43.8	44.1	41.8	39.2	34.7	32.9	31.0	29.0
82.5°	30.2	30.9	31.6	31.7	30.5	28.5	26.2	23.9	22.6	21.7	20.9
85°	16.4	16.6	16.4	15.1	13.5	12.8	12.3	11.9	11.7	11.4	11.4
87.5°	6.1	5.7	4.8	5.3	5.4	5.4	5.5	5.5	5.4	5.5	5.6
90°	1.3	2.1	2.9	3.7	4.4	5.2	5.9	6.6	7.4	7.9	8.4
92.5°	11.6	12.2	12.8	13.3	14.0	14.9	15.9	16.7	17.6	18.3	18.9
95°	30.0	30.2	30.4	30.6	31.2	32.2	33.2	34.2	35.2	36.0	36.7
97.5°	49.5	49.6	49.7	49.8	50.5	51.9	53.3	54.7	56.1	56.8	57.5
100°	64.1	64.1	64.1	64.1	64.7	66.0	67.4	68.7	70.0	71.0	71.9
102.5°	80.2	80.7	81.1	81.5	82.0	82.7	83.3	84.0	84.6	85.6	86.6
105°	104.8	105.3	105.8	106.4	106.9	107.6	108.2	108.8	109.4	110.0	110.6
107.5°	132.0	132.5	133.0	133.5	134.0	134.4	134.9	135.4	135.8	136.1	136.4
110°	150.7	151.2	151.7	152.2	152.6	152.9	153.2	153.5	153.8	154.1	154.4



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	169.5	169.7	170.0	170.3	170.6	171.0	171.4	171.7	172.1	172.3	172.4
115°	197.6	198.1	198.5	198.9	199.2	199.4	199.7	199.9	200.1	200.0	199.9
117.5°	225.6	225.8	226.0	226.2	226.4	226.6	226.7	226.9	227.1	227.2	227.3
120°	243.6	244.1	244.6	245.1	245.4	245.5	245.6	245.7	245.8	245.8	245.8
122.5°	262.3	262.5	262.7	262.8	263.1	263.3	263.6	263.9	264.1	264.0	264.0
125°	288.5	289.1	289.7	290.3	290.7	290.8	290.9	291.0	291.1	290.9	290.7
127.5°	315.7	316.1	316.4	316.8	317.0	317.1	317.2	317.3	317.5	317.4	317.3
130°	332.3	332.9	333.4	333.9	334.3	334.5	334.7	334.9	335.1	335.0	334.9
132.5°	349.1	350.0	350.8	351.6	352.0	352.0	351.9	351.9	351.8	351.7	351.6
135°	375.1	375.7	376.3	376.9	377.2	377.3	377.4	377.5	377.6	377.6	377.6
137.5°	399.5	400.1	400.7	401.3	401.7	401.9	402.1	402.3	402.6	402.7	402.8
140°	415.2	415.7	416.2	416.7	417.2	417.5	417.8	418.1	418.4	418.6	418.8
142.5°	430.8	431.3	431.7	432.1	432.5	432.9	433.3	433.7	434.1	434.2	434.3
145°	454.0	454.4	454.8	455.2	455.6	455.9	456.2	456.5	456.8	456.8	456.8
147.5°	475.2	475.4	475.6	475.9	476.2	476.4	476.7	476.9	477.2	477.4	477.6
150°	489.2	489.1	489.0	488.9	489.1	489.5	489.9	490.3	490.7	490.7	490.7
152.5°	501.2	501.3	501.4	501.6	501.7	501.9	502.1	502.2	502.4	502.6	502.9
155°	519.1	519.1	519.1	519.1	519.1	519.2	519.3	519.4	519.5	519.9	520.3
157.5°	534.9	534.7	534.5	534.2	534.2	534.3	534.4	534.5	534.6	535.0	535.4
160°	544.4	544.0	543.7	543.4	543.3	543.4	543.5	543.6	543.7	544.2	544.6
162.5°	552.9	552.7	552.4	552.2	552.1	552.1	552.1	552.2	552.2	552.7	553.2
165°	564.1	563.9	563.7	563.5	563.5	563.6	563.7	563.8	563.9	564.3	564.7
167.5°	573.5	573.1	572.7	572.3	572.1	572.1	572.1	572.1	572.1	572.7	573.3
170°	578.6	578.1	577.7	577.3	577.1	577.1	577.1	577.1	577.1	577.7	578.3
172.5°	582.3	581.9	581.5	581.1	580.9	580.9	580.9	580.9	580.9	581.5	582.1
175°	586.3	585.9	585.5	585.1	584.9	584.9	584.9	584.9	584.9	585.5	586.1
177.5°	588.5	588.2	587.9	587.5	587.3	587.3	587.2	587.1	587.0	587.5	588.0
180°	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	593.3	593.3	596.4	596.2	598.3	597.5	597.9
5°	637.7	641.7	645.2	647.5	651.1	652.0	651.5
7.5°	683.9	692.7	696.9	702.9	703.9	707.0	706.7
10°	712.4	721.0	727.6	732.7	735.3	738.5	738.8
12.5°	734.8	742.1	747.9	752.7	755.8	756.8	757.4
15°	752.3	760.4	767.2	774.0	778.0	781.0	782.6
17.5°	769.9	782.5	794.5	803.7	809.2	813.9	813.9
20°	783.6	798.0	812.9	823.4	834.2	838.9	839.6
22.5°	798.1	820.2	839.5	855.8	869.9	874.7	876.6
25°	828.4	857.3	887.0	909.8	926.1	935.7	937.2
27.5°	864.9	904.0	935.2	956.3	969.9	977.0	978.6
30°	890.7	926.9	954.8	970.7	977.0	978.0	974.4
32.5°	902.2	929.3	940.5	939.6	927.2	919.0	915.8
35°	888.1	882.5	855.3	822.5	797.6	781.7	777.5
37.5°	808.2	759.9	709.7	660.4	634.1	620.7	597.7
40°	729.4	660.6	608.3	566.8	537.1	513.3	507.8
42.5°	640.6	569.5	517.3	481.7	458.0	441.7	434.5
45°	514.7	453.6	410.4	383.1	365.0	353.0	347.7
47.5°	411.7	364.4	333.0	312.8	298.8	288.5	285.6
50°	355.2	317.3	290.7	273.7	263.2	255.3	252.1
52.5°	308.5	277.9	257.5	243.5	233.6	228.6	225.9
55°	254.6	228.2	213.5	202.3	196.7	192.8	190.9
57.5°	208.2	189.1	178.4	170.7	165.5	163.0	162.1
60°	182.3	167.3	157.5	151.5	147.9	144.7	143.7
62.5°	159.3	147.5	140.0	134.6	131.2	129.8	129.2
65°	128.4	120.7	115.0	111.8	109.0	108.5	108.3
67.5°	102.0	97.5	94.5	91.2	90.2	88.6	88.2
70°	87.3	84.2	80.7	79.6	78.4	76.7	77.1
72.5°	74.0	71.0	68.6	67.1	66.7	65.9	66.6
75°	54.1	53.2	52.3	51.1	50.6	50.6	50.4
77.5°	38.7	37.9	36.9	36.2	36.0	35.0	35.3
80°	28.0	26.9	26.4	26.6	25.9	25.7	25.7
82.5°	20.7	20.3	19.8	19.9	19.7	19.5	19.7
85°	11.4	11.2	11.2	11.0	11.0	10.7	10.7
87.5°	5.9	6.2	5.9	5.8	5.9	6.1	6.3
90°	8.9	9.4	9.8	10.1	10.4	10.7	11.0
92.5°	19.6	20.3	20.7	20.9	21.1	21.4	21.6
95°	37.4	38.1	38.6	38.8	39.0	39.2	39.4
97.5°	58.2	58.8	59.2	59.3	59.5	59.6	59.7
100°	72.8	73.7	74.2	74.4	74.6	74.8	75.0
102.5°	87.7	88.7	89.3	89.6	89.9	90.2	90.5
105°	111.2	111.8	112.3	112.6	112.9	113.2	113.5
107.5°	136.7	137.0	137.2	137.2	137.1	137.1	137.1
110°	154.7	155.0	155.1	155.0	154.9	154.8	154.7



TEST NUMBER: P333641-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	172.5	172.7	172.7	172.5	172.3	172.1	171.9
115°	199.8	199.7	199.5	199.4	199.3	199.2	199.1
117.5°	227.3	227.4	227.3	226.9	226.5	226.0	225.6
120°	245.8	245.8	245.6	245.2	244.8	244.4	244.0
122.5°	263.9	263.8	263.6	263.3	263.0	262.6	262.3
125°	290.5	290.3	290.1	290.0	289.9	289.8	289.7
127.5°	317.2	317.1	316.9	316.7	316.5	316.3	316.1
130°	334.8	334.7	334.5	334.3	334.1	333.9	333.7
132.5°	351.5	351.4	351.3	351.0	350.7	350.4	350.1
135°	377.6	377.6	377.4	377.0	376.6	376.2	375.8
137.5°	402.9	403.1	402.9	402.4	401.9	401.3	400.8
140°	419.0	419.2	419.0	418.5	418.0	417.5	417.0
142.5°	434.4	434.5	434.3	433.8	433.3	432.8	432.3
145°	456.8	456.8	456.7	456.4	456.1	455.8	455.4
147.5°	477.9	478.1	477.9	477.2	476.5	475.7	475.1
150°	490.7	490.7	490.6	490.4	490.2	490.0	489.8
152.5°	503.1	503.3	503.3	502.9	502.6	502.2	501.8
155°	520.7	521.1	521.1	520.6	520.1	519.6	519.1
157.5°	535.8	536.2	536.1	535.4	534.7	534.1	533.4
160°	545.0	545.4	545.3	544.8	544.3	543.8	543.3
162.5°	553.6	554.1	554.1	553.5	552.9	552.3	551.7
165°	565.1	565.5	565.4	564.8	564.2	563.6	563.0
167.5°	573.9	574.5	574.5	573.8	573.2	572.6	572.0
170°	579.0	579.7	579.6	578.9	578.1	577.4	576.7
172.5°	582.7	583.3	583.3	582.6	582.0	581.4	580.8
175°	586.8	587.4	587.3	586.6	585.9	585.2	584.5
177.5°	588.5	589.1	589.0	588.4	587.8	587.2	586.7
180°	588.1	588.1	588.1	588.1	588.1	588.1	588.1

(END OF REPORT)