

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333645-840

Luminaire Tested: **S125RDIW-S375D770U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333645-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S375D770U840-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4162.9 lumens  
Efficiency: N/A  
Efficacy: 136.9 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	87	79	74	69	78	72	67	63	58	55	52	46	43	41	34	33	31	26
3	79	70	63	58	71	64	58	53	52	47	44	41	38	35	30	28	27	22
4	72	62	55	49	65	56	50	45	46	41	38	36	33	30	27	25	23	19
5	66	55	47	42	60	50	44	39	41	36	32	33	29	26	25	22	20	17
6	61	50	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	45	37	32	51	41	34	29	34	29	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22	24	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3672	3672	3672	3672
5°	4224	3676	3247	3676
10°	4845	3657	2865	3657
15°	5233	3620	2546	3620
20°	5770	3577	2351	3577
25°	6678	3518	2182	3518
30°	7267	3457	2071	3457
35°	6130	3387	1968	3387
40°	4281	3260	1881	3260
45°	3176	3088	1795	3088
50°	2533	2910	1721	2910
55°	2149	2688	1655	2688
60°	1856	2490	1550	2490
65°	1655	2275	1334	2275
70°	1456	2085	1216	2085
75°	1258	1804	1140	1804
80°	956	1517	956	1517
85°	793	1193	897	1193



TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.5	1.3
10°-20°	159.7	3.8
20°-30°	253.3	6.1
30°-40°	305.4	7.3
40°-50°	272.8	6.6
50°-60°	209.2	5.0
60°-70°	135.9	3.3
70°-80°	66.1	1.6
80°-90°	17.9	0.4
90°-100°	64.5	1.5
100°-110°	190.5	4.6
110°-120°	322.7	7.8
120°-130°	424.7	10.2
130°-140°	475.9	11.4
140°-150°	466.4	11.2
150°-160°	391.7	9.4
160°-170°	260.4	6.3
170°-180°	91.1	2.2
0°-30°	467.5	11.2
0°-40°	773.0	18.6
0°-60°	1254.9	30.1
0°-90°	1474.8	35.4
90°-120°	577.8	13.9
90°-150°	1944.8	46.7
90°-180°	2688.0	64.6
0°-180°	4162.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	568	568	568	568	568	
5°	652	567	501	567	652	65
15°	783	541	381	541	783	224
25°	937	494	306	494	937	430
35°	778	430	250	430	778	470
45°	348	338	196	338	348	277
55°	191	239	147	239	191	173
65°	108	149	87	149	108	108
75°	50	72	46	72	50	54
85°	11	16	12	16	11	13
90°	18	1	18	1	18	11
95°	64	49	64	49	64	66
105°	186	171	186	171	186	197
115°	326	323	326	323	326	323
125°	474	472	474	472	474	424
135°	616	613	616	613	616	475
145°	746	743	746	743	746	466
155°	850	850	850	850	850	391
165°	922	924	922	924	922	260
175°	957	961	957	961	957	91
180°	963	963	963	963	963	



TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	597.9	597.5	598.3	596.2	596.4	593.3	593.3	590.9	587.6	585.2	584.1
5°	651.5	652.0	651.1	647.5	645.2	641.7	637.7	630.8	624.9	619.2	614.9
7.5°	706.7	707.0	703.9	702.9	696.9	692.7	683.9	674.3	665.9	655.1	646.9
10°	738.8	738.5	735.3	732.7	727.6	721.0	712.4	701.3	690.7	679.0	667.8
12.5°	757.4	756.8	755.8	752.7	747.9	742.1	734.8	723.8	710.8	698.1	685.0
15°	782.6	781.0	778.0	774.0	767.2	760.4	752.3	742.6	730.1	715.7	703.6
17.5°	813.9	813.9	809.2	803.7	794.5	782.5	769.9	754.2	737.3	721.4	708.5
20°	839.6	838.9	834.2	823.4	812.9	798.0	783.6	764.2	743.7	722.9	706.8
22.5°	876.6	874.7	869.9	855.8	839.5	820.2	798.1	774.5	749.6	726.1	704.9
25°	937.2	935.7	926.1	909.8	887.0	857.3	828.4	796.0	760.2	729.2	703.6
27.5°	978.6	977.0	969.9	956.3	935.2	904.0	864.9	821.5	777.0	734.3	697.3
30°	974.4	978.0	977.0	970.7	954.8	926.9	890.7	841.9	788.9	738.8	694.7
32.5°	915.8	919.0	927.2	939.6	940.5	929.3	902.2	857.2	802.3	745.3	692.6
35°	777.5	781.7	797.6	822.5	855.3	882.5	888.1	863.8	814.6	753.3	689.5
37.5°	597.7	620.7	634.1	660.4	709.7	759.9	808.2	826.0	805.1	749.9	684.6
40°	507.8	513.3	537.1	566.8	608.3	660.6	729.4	779.1	780.7	742.6	676.7
42.5°	434.5	441.7	458.0	481.7	517.3	569.5	640.6	706.2	736.5	722.0	666.4
45°	347.7	353.0	365.0	383.1	410.4	453.6	514.7	590.6	650.8	674.4	638.9
47.5°	285.6	288.5	298.8	312.8	333.0	364.4	411.7	477.6	549.8	600.4	595.4
50°	252.1	255.3	263.2	273.7	290.7	317.3	355.2	410.0	484.4	546.2	558.7
52.5°	225.9	228.6	233.6	243.5	257.5	277.9	308.5	358.1	425.1	490.8	519.5
55°	190.9	192.8	196.7	202.3	213.5	228.2	254.6	288.9	343.1	409.3	451.3
57.5°	162.1	163.0	165.5	170.7	178.4	189.1	208.2	237.2	276.1	335.8	382.1
60°	143.7	144.7	147.9	151.5	157.5	167.3	182.3	202.6	239.8	289.1	336.0
62.5°	129.2	129.8	131.2	134.6	140.0	147.5	159.3	175.8	205.5	248.8	293.1
65°	108.3	108.5	109.0	111.8	115.0	120.7	128.4	140.0	162.4	195.1	234.3
67.5°	88.2	88.6	90.2	91.2	94.5	97.5	102.0	110.9	126.7	148.8	179.3
70°	77.1	76.7	78.4	79.6	80.7	84.2	87.3	94.5	104.3	121.1	146.5
72.5°	66.6	65.9	66.7	67.1	68.6	71.0	74.0	78.5	86.0	97.6	117.0
75°	50.4	50.6	50.6	51.1	52.3	53.2	54.1	56.5	60.7	68.4	78.9
77.5°	35.3	35.0	36.0	36.2	36.9	37.9	38.7	39.6	41.3	44.4	49.9
80°	25.7	25.7	25.9	26.6	26.4	26.9	28.0	29.0	31.0	32.9	34.7
82.5°	19.7	19.5	19.7	19.9	19.8	20.3	20.7	20.9	21.7	22.6	23.9
85°	10.7	10.7	11.0	11.0	11.2	11.2	11.4	11.4	11.4	11.7	11.9
87.5°	7.7	7.4	7.2	7.1	7.1	7.4	7.0	6.7	6.5	6.4	6.3
90°	18.0	17.5	17.0	16.5	16.0	15.3	14.5	13.6	12.8	12.0	10.8
92.5°	35.3	35.0	34.6	34.3	33.9	33.2	32.1	31.0	29.9	28.8	27.4
95°	64.4	64.1	63.8	63.5	63.1	62.4	61.2	60.1	58.9	57.8	56.0
97.5°	97.8	97.6	97.4	97.1	96.9	96.3	95.2	94.1	93.0	91.9	89.6
100°	122.9	122.6	122.3	122.0	121.6	120.7	119.2	117.6	116.2	114.7	112.5
102.5°	148.1	147.6	147.2	146.7	146.2	145.2	143.6	142.0	140.4	138.7	137.5
105°	185.9	185.4	184.9	184.4	183.9	183.2	182.2	181.2	180.2	179.2	178.1
107.5°	224.6	224.6	224.7	224.7	224.7	224.5	224.0	223.5	223.0	222.5	221.8
110°	253.4	253.6	253.7	253.9	254.1	253.9	253.4	252.9	252.4	251.9	251.4



TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	281.6	281.9	282.2	282.5	282.8	282.8	282.6	282.4	282.2	281.9	281.2
115°	326.1	326.3	326.5	326.6	326.8	326.9	327.1	327.3	327.4	327.6	327.3
117.5°	369.6	370.2	370.9	371.6	372.2	372.5	372.3	372.2	372.1	372.0	371.7
120°	399.6	400.2	400.9	401.6	402.2	402.5	402.5	402.5	402.5	402.5	402.4
122.5°	429.6	430.1	430.6	431.1	431.7	432.0	432.1	432.3	432.4	432.5	432.1
125°	474.5	474.7	474.8	475.0	475.2	475.4	475.7	476.2	476.5	476.8	476.7
127.5°	517.8	518.1	518.4	518.8	519.1	519.3	519.5	519.7	519.8	520.0	519.8
130°	546.5	546.8	547.1	547.5	547.9	548.1	548.3	548.5	548.6	548.8	548.5
132.5°	573.5	574.0	574.4	574.9	575.3	575.7	575.8	576.0	576.2	576.3	576.4
135°	615.5	616.1	616.8	617.4	618.1	618.4	618.4	618.4	618.4	618.4	618.3
137.5°	656.5	657.4	658.2	659.0	659.8	660.2	660.0	659.8	659.6	659.4	659.0
140°	683.0	683.8	684.6	685.5	686.3	686.5	686.2	685.9	685.5	685.2	684.7
142.5°	708.1	708.9	709.8	710.6	711.4	711.8	711.6	711.3	711.1	710.9	710.3
145°	745.9	746.4	746.9	747.4	747.9	748.2	748.2	748.2	748.2	748.2	747.7
147.5°	778.2	779.3	780.4	781.5	782.6	783.0	782.6	782.2	781.8	781.4	781.0
150°	802.1	802.4	802.8	803.1	803.4	803.7	803.7	803.7	803.7	803.7	802.9
152.5°	821.9	822.5	823.1	823.7	824.4	824.5	824.0	823.6	823.2	822.8	822.5
155°	850.1	850.9	851.8	852.6	853.4	853.5	852.8	852.2	851.5	850.9	850.7
157.5°	873.6	874.7	875.9	877.0	878.1	878.3	877.6	877.0	876.3	875.7	875.5
160°	889.9	890.7	891.5	892.3	893.2	893.2	892.6	891.9	891.3	890.6	890.4
162.5°	903.6	904.6	905.5	906.6	907.6	907.6	906.8	906.1	905.2	904.4	904.3
165°	922.1	923.1	924.1	925.1	926.0	926.2	925.6	924.9	924.2	923.6	923.4
167.5°	936.8	937.9	938.9	939.9	940.9	940.9	940.0	939.0	938.0	937.0	937.0
170°	944.6	945.7	947.0	948.1	949.3	949.4	948.4	947.4	946.3	945.3	945.3
172.5°	951.2	952.2	953.2	954.3	955.3	955.3	954.3	953.3	952.3	951.3	951.3
175°	957.4	958.5	959.7	960.8	962.0	962.1	961.1	960.1	959.1	958.1	958.1
177.5°	960.9	961.9	962.8	963.7	964.6	964.7	963.9	963.1	962.3	961.5	961.7
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	584.1	582.8	580.4	578.1	575.3	572.9	571.2	569.2	566.5	563.4	560.8
5°	610.0	604.8	598.0	592.2	584.7	579.0	572.9	567.0	561.2	553.7	547.1
7.5°	638.6	628.0	617.7	604.7	593.0	582.5	572.4	562.2	552.2	541.6	531.4
10°	656.2	643.3	629.1	612.8	597.8	583.6	570.6	557.6	544.1	532.3	519.5
12.5°	672.6	656.0	639.7	619.1	601.2	583.8	567.1	551.2	536.7	521.3	507.5
15°	687.4	671.1	652.9	627.7	602.7	581.7	562.1	541.4	523.4	506.1	490.7
17.5°	693.2	676.0	654.9	630.7	603.4	576.9	551.7	529.0	507.8	487.7	470.4
20°	690.9	674.4	652.7	629.5	600.4	572.9	545.5	520.4	496.8	475.5	457.2
22.5°	685.5	668.4	647.4	623.0	595.3	566.1	536.9	510.1	485.4	463.4	443.3
25°	677.4	654.1	632.6	608.7	582.4	553.5	523.4	493.7	467.4	444.9	423.0
27.5°	668.9	639.9	612.5	588.9	561.0	535.2	506.1	475.7	448.1	425.3	402.7
30°	661.3	628.6	598.5	571.7	545.3	520.8	493.3	463.6	435.2	411.6	388.8
32.5°	651.8	617.0	584.0	553.0	527.6	503.3	478.4	450.0	422.3	398.0	374.8
35°	639.9	595.5	559.6	526.6	498.5	474.8	452.4	429.6	401.8	376.6	354.0
37.5°	624.2	573.8	532.3	496.4	466.7	443.0	425.3	404.3	379.0	355.0	334.0
40°	614.6	558.2	512.7	477.2	446.0	420.9	404.3	386.7	363.6	340.9	319.9
42.5°	602.0	543.8	492.9	456.0	424.4	400.4	383.6	368.2	348.8	327.5	305.0
45°	577.0	515.9	462.5	422.8	391.1	367.5	351.8	338.1	323.5	303.8	284.2
47.5°	544.7	486.9	430.9	387.6	356.6	334.7	319.5	308.6	298.1	281.4	262.5
50°	518.8	462.9	408.4	366.4	333.3	312.5	298.2	289.6	280.0	264.9	248.9
52.5°	488.1	438.3	384.9	341.9	310.6	291.1	277.5	268.8	260.9	248.6	233.5
55°	439.9	396.2	347.2	308.2	279.5	259.9	246.9	238.7	234.1	223.6	211.7
57.5°	384.2	352.9	309.7	272.2	246.7	227.4	217.8	210.9	205.6	198.1	189.8
60°	345.4	323.5	284.7	248.9	225.6	207.2	198.5	192.8	187.8	181.6	175.0
62.5°	306.0	290.0	256.3	225.6	204.2	188.7	180.7	175.4	169.8	165.5	159.2
65°	253.2	238.9	215.6	191.6	171.8	159.4	153.5	148.9	145.4	140.7	136.2
67.5°	196.9	191.2	175.0	158.4	144.2	133.2	128.2	124.9	120.8	118.0	114.9
70°	162.4	159.6	148.1	137.2	123.9	116.4	111.8	110.4	105.2	102.4	100.4
72.5°	131.8	130.5	123.9	116.3	106.9	100.4	96.1	94.5	91.2	89.0	87.7
75°	90.3	90.8	89.6	84.7	81.2	77.1	73.3	72.3	70.0	68.2	67.0
77.5°	57.2	59.5	59.6	59.4	58.0	55.4	53.8	53.1	50.9	50.2	49.9
80°	39.2	41.8	44.1	43.8	43.4	42.7	41.5	40.8	39.7	39.0	38.5
82.5°	26.2	28.5	30.5	31.7	31.6	30.9	30.2	29.8	29.6	29.1	29.0
85°	12.3	12.8	13.5	15.1	16.4	16.6	16.4	16.1	15.5	15.7	15.9
87.5°	6.3	6.0	6.0	5.7	5.3	6.0	6.2	6.2	6.1	6.0	5.8
90°	9.7	8.5	7.4	6.1	4.7	3.4	2.1	0.7	2.1	3.4	4.7
92.5°	26.0	24.5	23.0	21.9	20.9	20.0	19.1	18.2	19.1	20.0	20.9
95°	54.4	52.7	51.1	50.1	49.7	49.4	49.1	48.8	49.1	49.4	49.7
97.5°	87.4	85.0	82.7	81.5	81.4	81.2	81.1	81.0	81.1	81.2	81.4
100°	110.4	108.2	106.0	104.9	104.9	104.9	104.9	104.9	104.9	104.9	104.9
102.5°	136.5	135.4	134.3	133.4	132.7	132.1	131.4	130.8	131.4	132.1	132.7
105°	177.1	176.2	175.2	174.3	173.4	172.6	171.8	171.0	171.8	172.6	173.4
107.5°	221.0	220.3	219.4	218.6	217.8	217.0	216.1	215.3	216.1	217.0	217.8
110°	250.9	250.3	249.8	249.2	248.4	247.5	246.7	245.9	246.7	247.5	248.4





TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	280.6	279.9	279.3	278.8	278.4	277.9	277.5	277.1	277.5	277.9	278.4
115°	326.9	326.6	326.3	325.8	325.1	324.5	323.8	323.2	323.8	324.5	325.1
117.5°	371.4	371.1	370.8	370.5	370.2	369.9	369.6	369.3	369.6	369.9	370.2
120°	402.2	402.0	401.9	401.4	400.6	399.7	398.9	398.1	398.9	399.7	400.6
122.5°	431.7	431.2	430.8	430.5	430.2	429.9	429.6	429.3	429.6	429.9	430.2
125°	476.5	476.3	476.2	475.5	474.5	473.5	472.5	471.5	472.5	473.5	474.5
127.5°	519.6	519.4	519.2	518.8	518.3	517.7	517.1	516.5	517.1	517.7	518.3
130°	548.1	547.8	547.4	546.8	546.0	545.2	544.3	543.5	544.3	545.2	546.0
132.5°	576.4	576.5	576.6	575.9	574.6	573.2	571.9	570.5	571.9	573.2	574.6
135°	618.1	617.9	617.8	617.2	616.2	615.2	614.2	613.2	614.2	615.2	616.2
137.5°	658.6	658.3	657.9	657.3	656.3	655.3	654.4	653.4	654.4	655.3	656.3
140°	684.2	683.7	683.2	682.6	681.7	680.9	680.0	679.2	680.0	680.9	681.7
142.5°	709.7	709.1	708.4	707.8	707.1	706.4	705.7	705.0	705.7	706.4	707.1
145°	747.2	746.7	746.2	745.6	744.9	744.3	743.6	743.0	743.6	744.3	744.9
147.5°	780.6	780.2	779.8	779.5	779.1	778.7	778.4	778.0	778.4	778.7	779.1
150°	802.3	801.6	801.0	800.7	800.9	801.0	801.2	801.4	801.2	801.0	800.9
152.5°	822.3	822.0	821.7	821.5	821.3	821.0	820.8	820.6	820.8	821.0	821.3
155°	850.5	850.4	850.2	850.1	850.1	850.1	850.1	850.1	850.1	850.1	850.1
157.5°	875.3	875.1	874.9	875.0	875.5	875.8	876.2	876.6	876.2	875.8	875.5
160°	890.3	890.1	889.9	890.1	890.6	891.1	891.6	892.1	891.6	891.1	890.6
162.5°	904.3	904.3	904.2	904.4	904.8	905.1	905.5	905.9	905.5	905.1	904.8
165°	923.2	923.1	922.9	923.0	923.3	923.7	924.0	924.3	924.0	923.7	923.3
167.5°	937.0	937.0	937.0	937.3	938.0	938.6	939.3	940.0	939.3	938.6	938.0
170°	945.3	945.3	945.3	945.6	946.3	947.0	947.7	948.4	947.7	947.0	946.3
172.5°	951.3	951.3	951.3	951.7	952.3	953.0	953.6	954.3	953.6	953.0	952.3
175°	958.1	958.1	958.1	958.4	959.1	959.8	960.4	961.1	960.4	959.8	959.1
177.5°	961.8	961.9	962.1	962.4	962.9	963.4	964.0	964.5	964.0	963.4	962.9
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	558.9	556.3	554.4	550.7	548.1	546.9	544.9	544.3	546.4	544.9	544.7
5°	542.3	535.5	530.2	524.8	519.0	515.2	509.6	508.7	507.3	505.2	504.7
7.5°	522.4	513.5	506.6	497.8	490.1	483.8	476.9	473.5	471.7	469.0	465.3
10°	509.0	498.5	489.1	480.2	470.7	462.9	456.0	450.6	447.1	443.8	442.4
12.5°	495.6	484.9	473.0	462.3	451.6	443.0	435.3	431.7	427.9	424.0	420.8
15°	475.0	460.9	447.8	435.5	426.4	417.0	409.5	404.3	398.6	396.9	390.6
17.5°	453.2	439.3	423.9	411.0	400.4	390.1	381.9	376.1	371.7	365.7	362.8
20°	439.6	423.0	408.1	396.2	384.6	372.4	364.1	359.1	355.0	350.0	347.7
22.5°	425.1	408.9	393.5	379.6	367.8	355.8	349.8	344.8	340.0	335.5	332.3
25°	403.6	387.4	371.2	356.8	344.5	335.8	328.8	323.0	320.4	316.0	312.7
27.5°	382.5	365.2	348.5	334.1	324.4	315.8	310.0	305.5	300.8	297.0	294.1
30°	368.9	351.2	333.0	321.5	311.2	303.2	296.8	292.4	288.9	285.4	283.3
32.5°	355.3	337.0	320.8	308.5	298.8	291.8	285.3	280.9	277.3	273.5	270.9
35°	333.5	314.8	301.7	289.6	280.0	273.5	269.0	263.0	259.9	257.1	254.6
37.5°	313.2	295.8	281.7	271.0	262.7	256.2	250.4	247.2	243.5	241.0	238.8
40°	298.2	282.4	269.5	258.3	252.3	245.0	239.6	235.4	232.7	229.3	227.0
42.5°	284.8	270.0	257.5	247.5	239.9	233.8	228.6	224.4	220.9	218.5	216.6
45°	265.8	251.1	238.9	229.6	222.6	216.8	211.4	209.3	204.6	201.9	200.9
47.5°	246.1	233.0	221.3	212.7	205.5	200.0	194.9	190.7	188.0	185.3	183.8
50°	232.9	220.3	209.3	200.9	193.9	187.8	183.2	180.4	176.8	174.3	172.5
52.5°	219.6	207.9	197.0	188.9	182.9	176.8	171.6	168.8	165.5	163.9	162.6
55°	200.7	188.3	178.9	171.1	164.7	159.2	154.2	151.5	149.4	147.7	147.2
57.5°	179.3	169.5	160.8	153.6	147.0	141.8	137.4	134.8	133.0	132.7	131.3
60°	165.2	156.3	148.5	140.7	135.1	130.2	126.4	123.4	121.6	121.4	120.9
62.5°	151.2	142.7	135.3	128.6	123.5	118.9	115.2	111.9	110.8	109.6	108.6
65°	130.5	122.7	116.6	111.3	105.9	102.0	98.5	96.3	93.8	92.4	89.9
67.5°	110.1	104.1	98.3	93.7	89.5	85.7	82.8	79.7	78.0	76.9	75.0
70°	96.6	91.9	86.1	81.2	78.0	74.9	72.6	69.1	67.9	67.0	66.0
72.5°	83.9	79.8	74.9	70.9	67.7	64.8	62.1	60.5	59.3	58.4	57.9
75°	66.0	62.1	57.9	55.0	52.7	50.4	49.0	47.9	47.4	47.2	46.3
77.5°	48.5	46.4	43.0	40.8	39.3	38.3	37.1	36.5	36.4	35.3	35.0
80°	37.1	36.0	33.1	32.2	31.0	30.1	29.4	28.3	27.1	26.6	25.9
82.5°	27.6	26.5	25.2	23.8	22.8	22.2	21.6	21.1	21.3	20.6	20.3
85°	14.7	13.5	13.0	12.8	12.3	12.8	12.6	12.3	12.1	11.9	12.1
87.5°	5.9	6.2	6.2	6.8	6.5	6.9	7.1	7.1	7.2	7.4	7.3
90°	6.1	7.4	8.5	9.7	10.8	12.0	12.8	13.6	14.5	15.3	16.0
92.5°	21.9	23.0	24.5	26.0	27.4	28.8	29.9	31.0	32.1	33.2	33.9
95°	50.1	51.1	52.7	54.4	56.0	57.8	58.9	60.1	61.2	62.4	63.1
97.5°	81.5	82.7	85.0	87.4	89.6	91.9	93.0	94.1	95.2	96.3	96.9
100°	104.9	106.0	108.2	110.4	112.5	114.7	116.2	117.6	119.2	120.7	121.6
102.5°	133.4	134.3	135.4	136.5	137.5	138.7	140.4	142.0	143.6	145.2	146.2
105°	174.3	175.2	176.2	177.1	178.1	179.2	180.2	181.2	182.2	183.2	183.9
107.5°	218.6	219.4	220.3	221.0	221.8	222.5	223.0	223.5	224.0	224.5	224.7
110°	249.2	249.8	250.3	250.9	251.4	251.9	252.4	252.9	253.4	253.9	254.1



TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	278.8	279.3	279.9	280.6	281.2	281.9	282.2	282.4	282.6	282.8	282.8
115°	325.8	326.3	326.6	326.9	327.3	327.6	327.4	327.3	327.1	326.9	326.8
117.5°	370.5	370.8	371.1	371.4	371.7	372.0	372.1	372.2	372.3	372.5	372.2
120°	401.4	401.9	402.0	402.2	402.4	402.5	402.5	402.5	402.5	402.5	402.2
122.5°	430.5	430.8	431.2	431.7	432.1	432.5	432.4	432.3	432.1	432.0	431.7
125°	475.5	476.2	476.3	476.5	476.7	476.8	476.5	476.2	475.7	475.4	475.2
127.5°	518.8	519.2	519.4	519.6	519.8	520.0	519.8	519.7	519.5	519.3	519.1
130°	546.8	547.4	547.8	548.1	548.5	548.8	548.6	548.5	548.3	548.1	547.9
132.5°	575.9	576.6	576.5	576.4	576.4	576.3	576.2	576.0	575.8	575.7	575.3
135°	617.2	617.8	617.9	618.1	618.3	618.4	618.4	618.4	618.4	618.4	618.1
137.5°	657.3	657.9	658.3	658.6	659.0	659.4	659.6	659.8	660.0	660.2	659.8
140°	682.6	683.2	683.7	684.2	684.7	685.2	685.5	685.9	686.2	686.5	686.3
142.5°	707.8	708.4	709.1	709.7	710.3	710.9	711.1	711.3	711.6	711.8	711.4
145°	745.6	746.2	746.7	747.2	747.7	748.2	748.2	748.2	748.2	748.2	747.9
147.5°	779.5	779.8	780.2	780.6	781.0	781.4	781.8	782.2	782.6	783.0	782.6
150°	800.7	801.0	801.6	802.3	802.9	803.7	803.7	803.7	803.7	803.7	803.4
152.5°	821.5	821.7	822.0	822.3	822.5	822.8	823.2	823.6	824.0	824.5	824.4
155°	850.1	850.2	850.4	850.5	850.7	850.9	851.5	852.2	852.8	853.5	853.4
157.5°	875.0	874.9	875.1	875.3	875.5	875.7	876.3	877.0	877.6	878.3	878.1
160°	890.1	889.9	890.1	890.3	890.4	890.6	891.3	891.9	892.6	893.2	893.2
162.5°	904.4	904.2	904.3	904.3	904.3	904.4	905.2	906.1	906.8	907.6	907.6
165°	923.0	922.9	923.1	923.2	923.4	923.6	924.2	924.9	925.6	926.2	926.0
167.5°	937.3	937.0	937.0	937.0	937.0	937.0	938.0	939.0	940.0	940.9	940.9
170°	945.6	945.3	945.3	945.3	945.3	945.3	946.3	947.4	948.4	949.4	949.3
172.5°	951.7	951.3	951.3	951.3	951.3	951.3	952.3	953.3	954.3	955.3	955.3
175°	958.4	958.1	958.1	958.1	958.1	958.1	959.1	960.1	961.1	962.1	962.0
177.5°	962.4	962.1	961.9	961.8	961.7	961.5	962.3	963.1	963.9	964.7	964.6
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	544.5	542.5	541.9	542.7	541.9	542.5	544.5	544.7	544.9	546.4	544.3
5°	502.4	500.1	501.2	500.8	501.2	500.1	502.4	504.7	505.2	507.3	508.7
7.5°	465.3	462.4	459.4	460.3	459.4	462.4	465.3	465.3	469.0	471.7	473.5
10°	439.4	437.1	435.7	436.9	435.7	437.1	439.4	442.4	443.8	447.1	450.6
12.5°	417.6	416.2	415.0	414.4	415.0	416.2	417.6	420.8	424.0	427.9	431.7
15°	387.8	385.1	383.8	380.8	383.8	385.1	387.8	390.6	396.9	398.6	404.3
17.5°	360.4	359.5	356.5	355.2	356.5	359.5	360.4	362.8	365.7	371.7	376.1
20°	344.2	343.3	340.2	342.0	340.2	343.3	344.2	347.7	350.0	355.0	359.1
22.5°	330.7	328.7	327.7	327.2	327.7	328.7	330.7	332.3	335.5	340.0	344.8
25°	311.7	308.7	307.5	306.2	307.5	308.7	311.7	312.7	316.0	320.4	323.0
27.5°	292.8	291.1	289.6	289.2	289.6	291.1	292.8	294.1	297.0	300.8	305.5
30°	280.4	278.8	277.7	277.7	277.7	278.8	280.4	283.3	285.4	288.9	292.4
32.5°	269.4	268.2	267.0	266.8	267.0	268.2	269.4	270.9	273.5	277.3	280.9
35°	253.4	251.6	251.1	249.6	251.1	251.6	253.4	254.6	257.1	259.9	263.0
37.5°	236.7	235.2	235.2	235.0	235.2	235.2	236.7	238.8	241.0	243.5	247.2
40°	226.1	224.9	224.7	223.1	224.7	224.9	226.1	227.0	229.3	232.7	235.4
42.5°	214.7	214.1	213.3	212.6	213.3	214.1	214.7	216.6	218.5	220.9	224.4
45°	199.2	197.6	197.6	196.5	197.6	197.6	199.2	200.9	201.9	204.6	209.3
47.5°	183.3	182.1	182.2	181.0	182.2	182.1	183.3	183.8	185.3	188.0	190.7
50°	172.7	172.0	171.8	171.3	171.8	172.0	172.7	172.5	174.3	176.8	180.4
52.5°	162.1	161.7	162.6	161.6	162.6	161.7	162.1	162.6	163.9	165.5	168.8
55°	147.7	147.0	148.5	147.0	148.5	147.0	147.7	147.2	147.7	149.4	151.5
57.5°	131.3	130.6	131.9	131.2	131.9	130.6	131.3	131.3	132.7	133.0	134.8
60°	120.4	119.0	119.7	120.0	119.7	119.0	120.4	120.9	121.4	121.6	123.4
62.5°	107.6	106.6	107.2	106.1	107.2	106.6	107.6	108.6	109.6	110.8	111.9
65°	89.4	88.7	87.8	87.3	87.8	88.7	89.4	89.9	92.4	93.8	96.3
67.5°	75.1	73.4	73.3	73.7	73.3	73.4	75.1	75.0	76.9	78.0	79.7
70°	64.6	64.6	64.4	64.4	64.4	64.6	64.6	66.0	67.0	67.9	69.1
72.5°	57.4	57.2	56.8	56.6	56.8	57.2	57.4	57.9	58.4	59.3	60.5
75°	46.3	46.5	45.9	45.7	45.9	46.5	46.3	46.3	47.2	47.4	47.9
77.5°	34.1	33.1	33.6	33.1	33.6	33.1	34.1	35.0	35.3	36.4	36.5
80°	25.9	25.7	26.4	25.7	26.4	25.7	25.9	25.9	26.6	27.1	28.3
82.5°	20.5	20.3	20.6	20.1	20.6	20.3	20.5	20.3	20.6	21.3	21.1
85°	12.3	12.1	11.9	12.1	11.9	12.1	12.3	12.1	11.9	12.1	12.3
87.5°	7.6	7.5	7.6	7.7	7.6	7.5	7.6	7.3	7.4	7.2	7.1
90°	16.5	17.0	17.5	18.0	17.5	17.0	16.5	16.0	15.3	14.5	13.6
92.5°	34.3	34.6	35.0	35.3	35.0	34.6	34.3	33.9	33.2	32.1	31.0
95°	63.5	63.8	64.1	64.4	64.1	63.8	63.5	63.1	62.4	61.2	60.1
97.5°	97.1	97.4	97.6	97.8	97.6	97.4	97.1	96.9	96.3	95.2	94.1
100°	122.0	122.3	122.6	122.9	122.6	122.3	122.0	121.6	120.7	119.2	117.6
102.5°	146.7	147.2	147.6	148.1	147.6	147.2	146.7	146.2	145.2	143.6	142.0
105°	184.4	184.9	185.4	185.9	185.4	184.9	184.4	183.9	183.2	182.2	181.2
107.5°	224.7	224.7	224.6	224.6	224.6	224.7	224.7	224.7	224.5	224.0	223.5
110°	253.9	253.7	253.6	253.4	253.6	253.7	253.9	254.1	253.9	253.4	252.9



TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	282.5	282.2	281.9	281.6	281.9	282.2	282.5	282.8	282.8	282.6	282.4
115°	326.6	326.5	326.3	326.1	326.3	326.5	326.6	326.8	326.9	327.1	327.3
117.5°	371.6	370.9	370.2	369.6	370.2	370.9	371.6	372.2	372.5	372.3	372.2
120°	401.6	400.9	400.2	399.6	400.2	400.9	401.6	402.2	402.5	402.5	402.5
122.5°	431.1	430.6	430.1	429.6	430.1	430.6	431.1	431.7	432.0	432.1	432.3
125°	475.0	474.8	474.7	474.5	474.7	474.8	475.0	475.2	475.4	475.7	476.2
127.5°	518.8	518.4	518.1	517.8	518.1	518.4	518.8	519.1	519.3	519.5	519.7
130°	547.5	547.1	546.8	546.5	546.8	547.1	547.5	547.9	548.1	548.3	548.5
132.5°	574.9	574.4	574.0	573.5	574.0	574.4	574.9	575.3	575.7	575.8	576.0
135°	617.4	616.8	616.1	615.5	616.1	616.8	617.4	618.1	618.4	618.4	618.4
137.5°	659.0	658.2	657.4	656.5	657.4	658.2	659.0	659.8	660.2	660.0	659.8
140°	685.5	684.6	683.8	683.0	683.8	684.6	685.5	686.3	686.5	686.2	685.9
142.5°	710.6	709.8	708.9	708.1	708.9	709.8	710.6	711.4	711.8	711.6	711.3
145°	747.4	746.9	746.4	745.9	746.4	746.9	747.4	747.9	748.2	748.2	748.2
147.5°	781.5	780.4	779.3	778.2	779.3	780.4	781.5	782.6	783.0	782.6	782.2
150°	803.1	802.8	802.4	802.1	802.4	802.8	803.1	803.4	803.7	803.7	803.7
152.5°	823.7	823.1	822.5	821.9	822.5	823.1	823.7	824.4	824.5	824.0	823.6
155°	852.6	851.8	850.9	850.1	850.9	851.8	852.6	853.4	853.5	852.8	852.2
157.5°	877.0	875.9	874.7	873.6	874.7	875.9	877.0	878.1	878.3	877.6	877.0
160°	892.3	891.5	890.7	889.9	890.7	891.5	892.3	893.2	893.2	892.6	891.9
162.5°	906.6	905.5	904.6	903.6	904.6	905.5	906.6	907.6	907.6	906.8	906.1
165°	925.1	924.1	923.1	922.1	923.1	924.1	925.1	926.0	926.2	925.6	924.9
167.5°	939.9	938.9	937.9	936.8	937.9	938.9	939.9	940.9	940.9	940.0	939.0
170°	948.1	947.0	945.7	944.6	945.7	947.0	948.1	949.3	949.4	948.4	947.4
172.5°	954.3	953.2	952.2	951.2	952.2	953.2	954.3	955.3	955.3	954.3	953.3
175°	960.8	959.7	958.5	957.4	958.5	959.7	960.8	962.0	962.1	961.1	960.1
177.5°	963.7	962.8	961.9	960.9	961.9	962.8	963.7	964.6	964.7	963.9	963.1
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	544.9	546.9	548.1	550.7	554.4	556.3	558.9	560.8	563.4	566.5	569.2
5°	509.6	515.2	519.0	524.8	530.2	535.5	542.3	547.1	553.7	561.2	567.0
7.5°	476.9	483.8	490.1	497.8	506.6	513.5	522.4	531.4	541.6	552.2	562.2
10°	456.0	462.9	470.7	480.2	489.1	498.5	509.0	519.5	532.3	544.1	557.6
12.5°	435.3	443.0	451.6	462.3	473.0	484.9	495.6	507.5	521.3	536.7	551.2
15°	409.5	417.0	426.4	435.5	447.8	460.9	475.0	490.7	506.1	523.4	541.4
17.5°	381.9	390.1	400.4	411.0	423.9	439.3	453.2	470.4	487.7	507.8	529.0
20°	364.1	372.4	384.6	396.2	408.1	423.0	439.6	457.2	475.5	496.8	520.4
22.5°	349.8	355.8	367.8	379.6	393.5	408.9	425.1	443.3	463.4	485.4	510.1
25°	328.8	335.8	344.5	356.8	371.2	387.4	403.6	423.0	444.9	467.4	493.7
27.5°	310.0	315.8	324.4	334.1	348.5	365.2	382.5	402.7	425.3	448.1	475.7
30°	296.8	303.2	311.2	321.5	333.0	351.2	368.9	388.8	411.6	435.2	463.6
32.5°	285.3	291.8	298.8	308.5	320.8	337.0	355.3	374.8	398.0	422.3	450.0
35°	269.0	273.5	280.0	289.6	301.7	314.8	333.5	354.0	376.6	401.8	429.6
37.5°	250.4	256.2	262.7	271.0	281.7	295.8	313.2	334.0	355.0	379.0	404.3
40°	239.6	245.0	252.3	258.3	269.5	282.4	298.2	319.9	340.9	363.6	386.7
42.5°	228.6	233.8	239.9	247.5	257.5	270.0	284.8	305.0	327.5	348.8	368.2
45°	211.4	216.8	222.6	229.6	238.9	251.1	265.8	284.2	303.8	323.5	338.1
47.5°	194.9	200.0	205.5	212.7	221.3	233.0	246.1	262.5	281.4	298.1	308.6
50°	183.2	187.8	193.9	200.9	209.3	220.3	232.9	248.9	264.9	280.0	289.6
52.5°	171.6	176.8	182.9	188.9	197.0	207.9	219.6	233.5	248.6	260.9	268.8
55°	154.2	159.2	164.7	171.1	178.9	188.3	200.7	211.7	223.6	234.1	238.7
57.5°	137.4	141.8	147.0	153.6	160.8	169.5	179.3	189.8	198.1	205.6	210.9
60°	126.4	130.2	135.1	140.7	148.5	156.3	165.2	175.0	181.6	187.8	192.8
62.5°	115.2	118.9	123.5	128.6	135.3	142.7	151.2	159.2	165.5	169.8	175.4
65°	98.5	102.0	105.9	111.3	116.6	122.7	130.5	136.2	140.7	145.4	148.9
67.5°	82.8	85.7	89.5	93.7	98.3	104.1	110.1	114.9	118.0	120.8	124.9
70°	72.6	74.9	78.0	81.2	86.1	91.9	96.6	100.4	102.4	105.2	110.4
72.5°	62.1	64.8	67.7	70.9	74.9	79.8	83.9	87.7	89.0	91.2	94.5
75°	49.0	50.4	52.7	55.0	57.9	62.1	66.0	67.0	68.2	70.0	72.3
77.5°	37.1	38.3	39.3	40.8	43.0	46.4	48.5	49.9	50.2	50.9	53.1
80°	29.4	30.1	31.0	32.2	33.1	36.0	37.1	38.5	39.0	39.7	40.8
82.5°	21.6	22.2	22.8	23.8	25.2	26.5	27.6	29.0	29.1	29.6	29.8
85°	12.6	12.8	12.3	12.8	13.0	13.5	14.7	15.9	15.7	15.5	16.1
87.5°	7.1	6.9	6.5	6.8	6.2	6.2	5.9	5.8	6.0	6.1	6.2
90°	12.8	12.0	10.8	9.7	8.5	7.4	6.1	4.7	3.4	2.1	0.7
92.5°	29.9	28.8	27.4	26.0	24.5	23.0	21.9	20.9	20.0	19.1	18.2
95°	58.9	57.8	56.0	54.4	52.7	51.1	50.1	49.7	49.4	49.1	48.8
97.5°	93.0	91.9	89.6	87.4	85.0	82.7	81.5	81.4	81.2	81.1	81.0
100°	116.2	114.7	112.5	110.4	108.2	106.0	104.9	104.9	104.9	104.9	104.9
102.5°	140.4	138.7	137.5	136.5	135.4	134.3	133.4	132.7	132.1	131.4	130.8
105°	180.2	179.2	178.1	177.1	176.2	175.2	174.3	173.4	172.6	171.8	171.0
107.5°	223.0	222.5	221.8	221.0	220.3	219.4	218.6	217.8	217.0	216.1	215.3
110°	252.4	251.9	251.4	250.9	250.3	249.8	249.2	248.4	247.5	246.7	245.9



TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	282.2	281.9	281.2	280.6	279.9	279.3	278.8	278.4	277.9	277.5	277.1
115°	327.4	327.6	327.3	326.9	326.6	326.3	325.8	325.1	324.5	323.8	323.2
117.5°	372.1	372.0	371.7	371.4	371.1	370.8	370.5	370.2	369.9	369.6	369.3
120°	402.5	402.5	402.4	402.2	402.0	401.9	401.4	400.6	399.7	398.9	398.1
122.5°	432.4	432.5	432.1	431.7	431.2	430.8	430.5	430.2	429.9	429.6	429.3
125°	476.5	476.8	476.7	476.5	476.3	476.2	475.5	474.5	473.5	472.5	471.5
127.5°	519.8	520.0	519.8	519.6	519.4	519.2	518.8	518.3	517.7	517.1	516.5
130°	548.6	548.8	548.5	548.1	547.8	547.4	546.8	546.0	545.2	544.3	543.5
132.5°	576.2	576.3	576.4	576.4	576.5	576.6	575.9	574.6	573.2	571.9	570.5
135°	618.4	618.4	618.3	618.1	617.9	617.8	617.2	616.2	615.2	614.2	613.2
137.5°	659.6	659.4	659.0	658.6	658.3	657.9	657.3	656.3	655.3	654.4	653.4
140°	685.5	685.2	684.7	684.2	683.7	683.2	682.6	681.7	680.9	680.0	679.2
142.5°	711.1	710.9	710.3	709.7	709.1	708.4	707.8	707.1	706.4	705.7	705.0
145°	748.2	748.2	747.7	747.2	746.7	746.2	745.6	744.9	744.3	743.6	743.0
147.5°	781.8	781.4	781.0	780.6	780.2	779.8	779.5	779.1	778.7	778.4	778.0
150°	803.7	803.7	802.9	802.3	801.6	801.0	800.7	800.9	801.0	801.2	801.4
152.5°	823.2	822.8	822.5	822.3	822.0	821.7	821.5	821.3	821.0	820.8	820.6
155°	851.5	850.9	850.7	850.5	850.4	850.2	850.1	850.1	850.1	850.1	850.1
157.5°	876.3	875.7	875.5	875.3	875.1	874.9	875.0	875.5	875.8	876.2	876.6
160°	891.3	890.6	890.4	890.3	890.1	889.9	890.1	890.6	891.1	891.6	892.1
162.5°	905.2	904.4	904.3	904.3	904.3	904.2	904.4	904.8	905.1	905.5	905.9
165°	924.2	923.6	923.4	923.2	923.1	922.9	923.0	923.3	923.7	924.0	924.3
167.5°	938.0	937.0	937.0	937.0	937.0	937.0	937.3	938.0	938.6	939.3	940.0
170°	946.3	945.3	945.3	945.3	945.3	945.3	945.6	946.3	947.0	947.7	948.4
172.5°	952.3	951.3	951.3	951.3	951.3	951.3	951.7	952.3	953.0	953.6	954.3
175°	959.1	958.1	958.1	958.1	958.1	958.1	958.4	959.1	959.8	960.4	961.1
177.5°	962.3	961.5	961.7	961.8	961.9	962.1	962.4	962.9	963.4	964.0	964.5
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	571.2	572.9	575.3	578.1	580.4	582.8	584.1	584.1	585.2	587.6	590.9
5°	572.9	579.0	584.7	592.2	598.0	604.8	610.0	614.9	619.2	624.9	630.8
7.5°	572.4	582.5	593.0	604.7	617.7	628.0	638.6	646.9	655.1	665.9	674.3
10°	570.6	583.6	597.8	612.8	629.1	643.3	656.2	667.8	679.0	690.7	701.3
12.5°	567.1	583.8	601.2	619.1	639.7	656.0	672.6	685.0	698.1	710.8	723.8
15°	562.1	581.7	602.7	627.7	652.9	671.1	687.4	703.6	715.7	730.1	742.6
17.5°	551.7	576.9	603.4	630.7	654.9	676.0	693.2	708.5	721.4	737.3	754.2
20°	545.5	572.9	600.4	629.5	652.7	674.4	690.9	706.8	722.9	743.7	764.2
22.5°	536.9	566.1	595.3	623.0	647.4	668.4	685.5	704.9	726.1	749.6	774.5
25°	523.4	553.5	582.4	608.7	632.6	654.1	677.4	703.6	729.2	760.2	796.0
27.5°	506.1	535.2	561.0	588.9	612.5	639.9	668.9	697.3	734.3	777.0	821.5
30°	493.3	520.8	545.3	571.7	598.5	628.6	661.3	694.7	738.8	788.9	841.9
32.5°	478.4	503.3	527.6	553.0	584.0	617.0	651.8	692.6	745.3	802.3	857.2
35°	452.4	474.8	498.5	526.6	559.6	595.5	639.9	689.5	753.3	814.6	863.8
37.5°	425.3	443.0	466.7	496.4	532.3	573.8	624.2	684.6	749.9	805.1	826.0
40°	404.3	420.9	446.0	477.2	512.7	558.2	614.6	676.7	742.6	780.7	779.1
42.5°	383.6	400.4	424.4	456.0	492.9	543.8	602.0	666.4	722.0	736.5	706.2
45°	351.8	367.5	391.1	422.8	462.5	515.9	577.0	638.9	674.4	650.8	590.6
47.5°	319.5	334.7	356.6	387.6	430.9	486.9	544.7	595.4	600.4	549.8	477.6
50°	298.2	312.5	333.3	366.4	408.4	462.9	518.8	558.7	546.2	484.4	410.0
52.5°	277.5	291.1	310.6	341.9	384.9	438.3	488.1	519.5	490.8	425.1	358.1
55°	246.9	259.9	279.5	308.2	347.2	396.2	439.9	451.3	409.3	343.1	288.9
57.5°	217.8	227.4	246.7	272.2	309.7	352.9	384.2	382.1	335.8	276.1	237.2
60°	198.5	207.2	225.6	248.9	284.7	323.5	345.4	336.0	289.1	239.8	202.6
62.5°	180.7	188.7	204.2	225.6	256.3	290.0	306.0	293.1	248.8	205.5	175.8
65°	153.5	159.4	171.8	191.6	215.6	238.9	253.2	234.3	195.1	162.4	140.0
67.5°	128.2	133.2	144.2	158.4	175.0	191.2	196.9	179.3	148.8	126.7	110.9
70°	111.8	116.4	123.9	137.2	148.1	159.6	162.4	146.5	121.1	104.3	94.5
72.5°	96.1	100.4	106.9	116.3	123.9	130.5	131.8	117.0	97.6	86.0	78.5
75°	73.3	77.1	81.2	84.7	89.6	90.8	90.3	78.9	68.4	60.7	56.5
77.5°	53.8	55.4	58.0	59.4	59.6	59.5	57.2	49.9	44.4	41.3	39.6
80°	41.5	42.7	43.4	43.8	44.1	41.8	39.2	34.7	32.9	31.0	29.0
82.5°	30.2	30.9	31.6	31.7	30.5	28.5	26.2	23.9	22.6	21.7	20.9
85°	16.4	16.6	16.4	15.1	13.5	12.8	12.3	11.9	11.7	11.4	11.4
87.5°	6.2	6.0	5.3	5.7	6.0	6.0	6.3	6.3	6.4	6.5	6.7
90°	2.1	3.4	4.7	6.1	7.4	8.5	9.7	10.8	12.0	12.8	13.6
92.5°	19.1	20.0	20.9	21.9	23.0	24.5	26.0	27.4	28.8	29.9	31.0
95°	49.1	49.4	49.7	50.1	51.1	52.7	54.4	56.0	57.8	58.9	60.1
97.5°	81.1	81.2	81.4	81.5	82.7	85.0	87.4	89.6	91.9	93.0	94.1
100°	104.9	104.9	104.9	104.9	106.0	108.2	110.4	112.5	114.7	116.2	117.6
102.5°	131.4	132.1	132.7	133.4	134.3	135.4	136.5	137.5	138.7	140.4	142.0
105°	171.8	172.6	173.4	174.3	175.2	176.2	177.1	178.1	179.2	180.2	181.2
107.5°	216.1	217.0	217.8	218.6	219.4	220.3	221.0	221.8	222.5	223.0	223.5
110°	246.7	247.5	248.4	249.2	249.8	250.3	250.9	251.4	251.9	252.4	252.9





TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	277.5	277.9	278.4	278.8	279.3	279.9	280.6	281.2	281.9	282.2	282.4
115°	323.8	324.5	325.1	325.8	326.3	326.6	326.9	327.3	327.6	327.4	327.3
117.5°	369.6	369.9	370.2	370.5	370.8	371.1	371.4	371.7	372.0	372.1	372.2
120°	398.9	399.7	400.6	401.4	401.9	402.0	402.2	402.4	402.5	402.5	402.5
122.5°	429.6	429.9	430.2	430.5	430.8	431.2	431.7	432.1	432.5	432.4	432.3
125°	472.5	473.5	474.5	475.5	476.2	476.3	476.5	476.7	476.8	476.5	476.2
127.5°	517.1	517.7	518.3	518.8	519.2	519.4	519.6	519.8	520.0	519.8	519.7
130°	544.3	545.2	546.0	546.8	547.4	547.8	548.1	548.5	548.8	548.6	548.5
132.5°	571.9	573.2	574.6	575.9	576.6	576.5	576.4	576.4	576.3	576.2	576.0
135°	614.2	615.2	616.2	617.2	617.8	617.9	618.1	618.3	618.4	618.4	618.4
137.5°	654.4	655.3	656.3	657.3	657.9	658.3	658.6	659.0	659.4	659.6	659.8
140°	680.0	680.9	681.7	682.6	683.2	683.7	684.2	684.7	685.2	685.5	685.9
142.5°	705.7	706.4	707.1	707.8	708.4	709.1	709.7	710.3	710.9	711.1	711.3
145°	743.6	744.3	744.9	745.6	746.2	746.7	747.2	747.7	748.2	748.2	748.2
147.5°	778.4	778.7	779.1	779.5	779.8	780.2	780.6	781.0	781.4	781.8	782.2
150°	801.2	801.0	800.9	800.7	801.0	801.6	802.3	802.9	803.7	803.7	803.7
152.5°	820.8	821.0	821.3	821.5	821.7	822.0	822.3	822.5	822.8	823.2	823.6
155°	850.1	850.1	850.1	850.1	850.2	850.4	850.5	850.7	850.9	851.5	852.2
157.5°	876.2	875.8	875.5	875.0	874.9	875.1	875.3	875.5	875.7	876.3	877.0
160°	891.6	891.1	890.6	890.1	889.9	890.1	890.3	890.4	890.6	891.3	891.9
162.5°	905.5	905.1	904.8	904.4	904.2	904.3	904.3	904.3	904.4	905.2	906.1
165°	924.0	923.7	923.3	923.0	922.9	923.1	923.2	923.4	923.6	924.2	924.9
167.5°	939.3	938.6	938.0	937.3	937.0	937.0	937.0	937.0	937.0	938.0	939.0
170°	947.7	947.0	946.3	945.6	945.3	945.3	945.3	945.3	945.3	946.3	947.4
172.5°	953.6	953.0	952.3	951.7	951.3	951.3	951.3	951.3	951.3	952.3	953.3
175°	960.4	959.8	959.1	958.4	958.1	958.1	958.1	958.1	958.1	959.1	960.1
177.5°	964.0	963.4	962.9	962.4	962.1	961.9	961.8	961.7	961.5	962.3	963.1
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	593.3	593.3	596.4	596.2	598.3	597.5	597.9
5°	637.7	641.7	645.2	647.5	651.1	652.0	651.5
7.5°	683.9	692.7	696.9	702.9	703.9	707.0	706.7
10°	712.4	721.0	727.6	732.7	735.3	738.5	738.8
12.5°	734.8	742.1	747.9	752.7	755.8	756.8	757.4
15°	752.3	760.4	767.2	774.0	778.0	781.0	782.6
17.5°	769.9	782.5	794.5	803.7	809.2	813.9	813.9
20°	783.6	798.0	812.9	823.4	834.2	838.9	839.6
22.5°	798.1	820.2	839.5	855.8	869.9	874.7	876.6
25°	828.4	857.3	887.0	909.8	926.1	935.7	937.2
27.5°	864.9	904.0	935.2	956.3	969.9	977.0	978.6
30°	890.7	926.9	954.8	970.7	977.0	978.0	974.4
32.5°	902.2	929.3	940.5	939.6	927.2	919.0	915.8
35°	888.1	882.5	855.3	822.5	797.6	781.7	777.5
37.5°	808.2	759.9	709.7	660.4	634.1	620.7	597.7
40°	729.4	660.6	608.3	566.8	537.1	513.3	507.8
42.5°	640.6	569.5	517.3	481.7	458.0	441.7	434.5
45°	514.7	453.6	410.4	383.1	365.0	353.0	347.7
47.5°	411.7	364.4	333.0	312.8	298.8	288.5	285.6
50°	355.2	317.3	290.7	273.7	263.2	255.3	252.1
52.5°	308.5	277.9	257.5	243.5	233.6	228.6	225.9
55°	254.6	228.2	213.5	202.3	196.7	192.8	190.9
57.5°	208.2	189.1	178.4	170.7	165.5	163.0	162.1
60°	182.3	167.3	157.5	151.5	147.9	144.7	143.7
62.5°	159.3	147.5	140.0	134.6	131.2	129.8	129.2
65°	128.4	120.7	115.0	111.8	109.0	108.5	108.3
67.5°	102.0	97.5	94.5	91.2	90.2	88.6	88.2
70°	87.3	84.2	80.7	79.6	78.4	76.7	77.1
72.5°	74.0	71.0	68.6	67.1	66.7	65.9	66.6
75°	54.1	53.2	52.3	51.1	50.6	50.6	50.4
77.5°	38.7	37.9	36.9	36.2	36.0	35.0	35.3
80°	28.0	26.9	26.4	26.6	25.9	25.7	25.7
82.5°	20.7	20.3	19.8	19.9	19.7	19.5	19.7
85°	11.4	11.2	11.2	11.0	11.0	10.7	10.7
87.5°	7.0	7.4	7.1	7.1	7.2	7.4	7.7
90°	14.5	15.3	16.0	16.5	17.0	17.5	18.0
92.5°	32.1	33.2	33.9	34.3	34.6	35.0	35.3
95°	61.2	62.4	63.1	63.5	63.8	64.1	64.4
97.5°	95.2	96.3	96.9	97.1	97.4	97.6	97.8
100°	119.2	120.7	121.6	122.0	122.3	122.6	122.9
102.5°	143.6	145.2	146.2	146.7	147.2	147.6	148.1
105°	182.2	183.2	183.9	184.4	184.9	185.4	185.9
107.5°	224.0	224.5	224.7	224.7	224.7	224.6	224.6
110°	253.4	253.9	254.1	253.9	253.7	253.6	253.4



TEST NUMBER: P333645-840

CATALOG NUMBER: S125RDIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	282.6	282.8	282.8	282.5	282.2	281.9	281.6
115°	327.1	326.9	326.8	326.6	326.5	326.3	326.1
117.5°	372.3	372.5	372.2	371.6	370.9	370.2	369.6
120°	402.5	402.5	402.2	401.6	400.9	400.2	399.6
122.5°	432.1	432.0	431.7	431.1	430.6	430.1	429.6
125°	475.7	475.4	475.2	475.0	474.8	474.7	474.5
127.5°	519.5	519.3	519.1	518.8	518.4	518.1	517.8
130°	548.3	548.1	547.9	547.5	547.1	546.8	546.5
132.5°	575.8	575.7	575.3	574.9	574.4	574.0	573.5
135°	618.4	618.4	618.1	617.4	616.8	616.1	615.5
137.5°	660.0	660.2	659.8	659.0	658.2	657.4	656.5
140°	686.2	686.5	686.3	685.5	684.6	683.8	683.0
142.5°	711.6	711.8	711.4	710.6	709.8	708.9	708.1
145°	748.2	748.2	747.9	747.4	746.9	746.4	745.9
147.5°	782.6	783.0	782.6	781.5	780.4	779.3	778.2
150°	803.7	803.7	803.4	803.1	802.8	802.4	802.1
152.5°	824.0	824.5	824.4	823.7	823.1	822.5	821.9
155°	852.8	853.5	853.4	852.6	851.8	850.9	850.1
157.5°	877.6	878.3	878.1	877.0	875.9	874.7	873.6
160°	892.6	893.2	893.2	892.3	891.5	890.7	889.9
162.5°	906.8	907.6	907.6	906.6	905.5	904.6	903.6
165°	925.6	926.2	926.0	925.1	924.1	923.1	922.1
167.5°	940.0	940.9	940.9	939.9	938.9	937.9	936.8
170°	948.4	949.4	949.3	948.1	947.0	945.7	944.6
172.5°	954.3	955.3	955.3	954.3	953.2	952.2	951.2
175°	961.1	962.1	962.0	960.8	959.7	958.5	957.4
177.5°	963.9	964.7	964.6	963.7	962.8	961.9	960.9
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3

(END OF REPORT)