

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333673-840

Luminaire Tested: **S125RDIW-S610D1340U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333673-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D1340U840-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7121.9 lumens
Efficiency: N/A
Efficacy: 132.4 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	95	90	87	83	85	82	79	76	66	64	62	51	49	48	37	36	36	29
2	86	79	73	68	78	72	67	63	58	54	51	45	43	41	33	32	30	25
3	79	70	63	57	71	63	57	53	51	47	43	40	37	35	29	28	26	21
4	72	62	54	49	65	56	50	45	45	41	37	36	32	30	26	24	23	19
5	66	55	47	42	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	22	19	17	14
7	56	44	37	31	51	41	34	29	33	28	25	26	23	20	20	17	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	11
9	48	37	29	25	44	34	27	23	28	23	19	22	18	16	17	14	13	10
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6035	6035	6035	6035
5°	6944	6043	5337	6043
10°	7965	6013	4709	6013
15°	8603	5951	4186	5951
20°	9487	5880	3865	5880
25°	10979	5784	3587	5784
30°	11946	5684	3404	5684
35°	10078	5568	3236	5568
40°	7038	5359	3092	5359
45°	5221	5076	2951	5076
50°	4163	4784	2829	4784
55°	3533	4418	2721	4418
60°	3052	4093	2547	4093
65°	2720	3741	2193	3741
70°	2391	3427	1998	3427
75°	2069	2969	1876	2969
80°	1570	2499	1570	2499
85°	1312	1964	1482	1964



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	1.3
10°-20°	262.6	3.7
20°-30°	416.4	5.8
30°-40°	502.1	7.1
40°-50°	448.4	6.3
50°-60°	343.9	4.8
60°-70°	223.5	3.1
70°-80°	108.6	1.5
80°-90°	29.6	0.4
90°-100°	112.7	1.6
100°-110°	332.9	4.7
110°-120°	563.9	7.9
120°-130°	742.1	10.4
130°-140°	831.6	11.7
140°-150°	815.0	11.4
150°-160°	684.5	9.6
160°-170°	455.0	6.4
170°-180°	159.2	2.2
0°-30°	768.6	10.8
0°-40°	1270.8	17.8
0°-60°	2063.1	29.0
0°-90°	2424.8	34.0
90°-120°	1009.6	14.2
90°-150°	3398.3	47.7
90°-180°	4697.0	66.0
0°-180°	7121.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	934	934	934	934	934	
5°	1071	932	823	932	1071	107
15°	1287	890	626	890	1287	369
25°	1541	812	503	812	1541	707
35°	1278	706	410	706	1278	772
45°	572	556	323	556	572	456
55°	314	392	242	392	314	285
65°	178	245	144	245	178	177
75°	83	119	75	119	83	88
85°	18	26	20	26	18	21
90°	31	1	31	1	31	19
95°	113	85	113	85	113	115
105°	325	299	325	299	325	344
115°	570	565	570	565	570	564
125°	829	824	829	824	829	740
135°	1076	1072	1076	1072	1076	830
145°	1303	1298	1303	1298	1303	814
155°	1486	1486	1486	1486	1486	684
165°	1611	1615	1611	1615	1611	454
175°	1673	1679	1673	1679	1673	159
180°	1683	1683	1683	1683	1683	



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	983.0	982.4	983.6	980.2	980.6	975.3	975.3	971.3	966.1	962.1	960.3
5°	1071.1	1071.9	1070.3	1064.5	1060.7	1054.9	1048.4	1036.9	1027.3	1018.1	1010.9
7.5°	1161.7	1162.3	1157.2	1155.5	1145.8	1138.7	1124.3	1108.6	1094.7	1077.0	1063.6
10°	1214.6	1214.2	1208.8	1204.6	1196.1	1185.4	1171.1	1152.8	1135.5	1116.3	1097.9
12.5°	1245.3	1244.3	1242.5	1237.4	1229.6	1220.0	1208.0	1189.9	1168.6	1147.6	1126.2
15°	1286.7	1283.9	1279.0	1272.4	1261.3	1250.2	1236.8	1220.7	1200.3	1176.6	1156.6
17.5°	1337.9	1338.0	1330.3	1321.3	1306.2	1286.5	1265.8	1239.8	1212.1	1186.0	1164.8
20°	1380.3	1379.1	1371.4	1353.8	1336.6	1312.0	1288.2	1256.4	1222.6	1188.4	1162.0
22.5°	1441.0	1438.0	1430.1	1406.8	1380.1	1348.5	1312.1	1273.2	1232.4	1193.7	1158.9
25°	1540.7	1538.3	1522.6	1495.7	1458.1	1409.4	1361.8	1308.5	1249.8	1198.8	1156.6
27.5°	1608.7	1606.2	1594.6	1572.3	1537.5	1486.3	1421.9	1350.7	1277.4	1207.2	1146.3
30°	1601.9	1607.7	1606.2	1595.9	1569.7	1523.7	1464.3	1384.1	1297.0	1214.6	1142.1
32.5°	1505.6	1510.8	1524.3	1544.6	1546.1	1527.7	1483.3	1409.3	1319.1	1225.3	1138.6
35°	1278.2	1285.2	1311.2	1352.2	1405.9	1450.9	1460.1	1420.2	1339.2	1238.3	1133.6
37.5°	982.7	1020.5	1042.4	1085.6	1166.7	1249.3	1328.7	1358.0	1323.5	1232.9	1125.4
40°	834.8	843.9	883.1	931.8	1000.1	1086.0	1199.2	1280.9	1283.5	1220.7	1112.5
42.5°	714.5	726.1	753.0	791.8	850.3	936.2	1053.1	1160.9	1210.8	1186.9	1095.6
45°	571.6	580.4	600.0	629.9	674.8	745.8	846.3	971.0	1070.0	1108.6	1050.4
47.5°	469.6	474.3	491.3	514.1	547.3	599.1	676.8	785.1	903.8	987.0	978.9
50°	414.3	419.7	432.7	450.0	478.0	521.7	583.9	674.0	796.4	898.1	918.4
52.5°	371.3	375.8	384.0	400.3	423.3	457.0	507.2	588.8	698.8	806.9	853.9
55°	313.8	316.9	323.4	332.5	351.0	375.2	418.5	474.9	563.9	672.9	741.9
57.5°	266.4	267.9	272.1	280.5	293.3	310.9	342.2	390.1	453.9	552.0	628.2
60°	236.3	237.8	243.2	248.9	258.9	275.1	299.6	333.0	394.4	475.3	552.4
62.5°	212.4	213.3	215.6	221.4	230.0	242.6	261.9	289.1	337.9	409.0	481.8
65°	178.0	178.3	179.2	183.8	189.1	198.3	211.0	230.1	267.0	320.7	385.2
67.5°	145.0	145.5	148.2	149.9	155.4	160.3	167.7	182.4	208.3	244.5	294.6
70°	126.6	126.2	128.9	130.8	132.7	138.5	143.5	155.3	171.5	199.1	241.0
72.5°	109.4	108.5	109.6	110.3	112.8	116.7	121.7	129.0	141.4	160.5	192.4
75°	82.9	83.2	83.2	84.0	85.9	87.5	89.0	92.8	99.8	112.4	129.7
77.5°	58.2	57.6	59.2	59.4	60.5	62.2	63.5	65.0	67.9	73.1	82.0
80°	42.2	42.2	42.6	43.7	43.3	44.1	46.0	47.6	51.0	54.1	57.2
82.5°	32.4	32.1	32.4	32.7	32.6	33.3	34.0	34.3	35.6	37.2	39.4
85°	17.7	17.7	18.1	18.1	18.4	18.4	18.8	18.8	18.8	19.2	19.6
87.5°	13.0	12.5	12.1	11.9	12.0	12.4	11.8	11.2	10.9	10.6	10.5
90°	31.4	30.6	29.7	28.8	28.0	26.8	25.3	23.8	22.4	21.0	18.9
92.5°	61.8	61.2	60.6	59.9	59.3	58.0	56.0	54.1	52.2	50.3	47.8
95°	112.7	112.1	111.5	110.9	110.3	109.1	106.9	104.9	102.9	100.9	98.0
97.5°	170.9	170.5	170.2	169.8	169.5	168.2	166.3	164.4	162.5	160.6	156.6
100°	214.8	214.3	213.7	213.1	212.5	210.9	208.2	205.7	203.1	200.5	196.6
102.5°	258.8	258.0	257.2	256.4	255.6	253.8	250.9	248.0	245.2	242.4	240.4
105°	324.9	324.0	323.2	322.2	321.3	320.0	318.3	316.6	314.9	313.1	311.3
107.5°	392.4	392.5	392.5	392.6	392.7	392.3	391.4	390.5	389.7	388.8	387.5
110°	442.7	443.0	443.3	443.6	443.9	443.6	442.7	441.9	441.0	440.1	439.3



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	492.0	492.5	493.1	493.6	494.1	494.1	493.7	493.3	492.9	492.5	491.4
115°	569.9	570.2	570.4	570.7	571.0	571.3	571.6	571.9	572.2	572.5	571.9
117.5°	645.8	647.0	648.1	649.3	650.5	651.0	650.7	650.5	650.3	650.1	649.4
120°	698.2	699.3	700.5	701.7	702.9	703.5	703.5	703.5	703.5	703.5	703.2
122.5°	750.6	751.5	752.5	753.4	754.4	754.9	755.2	755.4	755.6	755.9	755.1
125°	829.2	829.5	829.8	830.1	830.4	830.8	831.4	831.9	832.5	833.1	832.8
127.5°	904.6	905.2	905.8	906.5	907.0	907.5	907.7	908.0	908.3	908.6	908.3
130°	954.9	955.5	956.1	956.7	957.3	957.8	958.1	958.3	958.6	958.9	958.3
132.5°	1002.1	1002.9	1003.7	1004.6	1005.4	1005.9	1006.2	1006.5	1006.8	1007.1	1007.2
135°	1075.5	1076.6	1077.8	1078.9	1080.2	1080.8	1080.8	1080.8	1080.8	1080.8	1080.5
137.5°	1147.3	1148.7	1150.1	1151.7	1153.1	1153.7	1153.3	1153.0	1152.6	1152.3	1151.7
140°	1193.4	1194.9	1196.3	1197.7	1199.2	1199.6	1199.0	1198.5	1197.9	1197.3	1196.4
142.5°	1237.4	1238.8	1240.3	1241.7	1243.2	1243.7	1243.4	1243.0	1242.7	1242.3	1241.2
145°	1303.4	1304.2	1305.1	1306.1	1306.9	1307.4	1307.4	1307.4	1307.4	1307.4	1306.5
147.5°	1359.8	1361.7	1363.7	1365.6	1367.7	1368.3	1367.6	1366.9	1366.2	1365.5	1364.8
150°	1401.7	1402.2	1402.8	1403.4	1404.0	1404.3	1404.3	1404.3	1404.3	1404.3	1403.1
152.5°	1436.2	1437.2	1438.4	1439.4	1440.5	1440.6	1439.9	1439.2	1438.6	1437.8	1437.3
155°	1485.5	1486.9	1488.4	1489.9	1491.3	1491.5	1490.3	1489.1	1487.9	1486.8	1486.5
157.5°	1526.6	1528.5	1530.5	1532.4	1534.3	1534.7	1533.5	1532.4	1531.2	1530.0	1529.7
160°	1554.9	1556.4	1557.8	1559.3	1560.7	1560.8	1559.7	1558.5	1557.4	1556.2	1555.9
162.5°	1579.0	1580.7	1582.4	1584.1	1585.8	1585.9	1584.5	1583.2	1581.8	1580.3	1580.2
165°	1611.2	1613.0	1614.8	1616.5	1618.2	1618.5	1617.4	1616.2	1615.1	1613.9	1613.6
167.5°	1636.9	1638.7	1640.5	1642.3	1644.2	1644.2	1642.4	1640.7	1638.9	1637.2	1637.2
170°	1650.5	1652.5	1654.7	1656.7	1658.7	1658.8	1657.1	1655.4	1653.7	1651.8	1651.8
172.5°	1662.0	1663.9	1665.7	1667.5	1669.3	1669.3	1667.6	1665.9	1664.1	1662.3	1662.3
175°	1672.8	1674.9	1676.9	1678.9	1680.9	1681.1	1679.4	1677.6	1675.9	1674.2	1674.2
177.5°	1679.1	1680.7	1682.3	1683.9	1685.7	1685.8	1684.4	1682.9	1681.5	1680.1	1680.4
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	960.3	958.2	954.1	950.5	945.8	941.9	939.1	935.7	931.4	926.2	921.9
5°	1002.8	994.3	983.2	973.6	961.4	951.8	941.8	932.2	922.6	910.3	899.6
7.5°	1049.9	1032.5	1015.5	994.2	974.8	957.6	941.0	924.2	907.8	890.4	873.5
10°	1078.7	1057.6	1034.2	1007.3	982.8	959.5	938.0	916.9	894.6	875.0	853.9
12.5°	1105.7	1078.5	1051.8	1017.8	988.4	959.8	932.4	906.2	882.3	857.0	834.2
15°	1130.1	1103.3	1073.4	1032.0	990.9	956.3	924.1	890.0	860.5	832.0	806.8
17.5°	1139.5	1111.5	1076.6	1036.8	992.0	948.6	907.1	869.6	834.9	801.7	773.3
20°	1135.9	1108.6	1073.0	1035.0	987.0	941.8	896.9	855.5	816.7	781.8	751.5
22.5°	1127.0	1098.8	1064.4	1024.3	978.8	930.7	882.8	838.6	798.0	761.8	728.8
25°	1113.7	1075.3	1040.0	1000.9	957.6	910.0	860.5	811.7	768.4	731.5	695.5
27.5°	1099.7	1051.9	1007.0	968.1	922.3	879.9	832.1	782.2	736.6	699.1	662.2
30°	1087.2	1033.5	984.0	939.9	896.6	856.3	810.9	762.2	715.5	676.7	639.1
32.5°	1071.6	1014.4	960.1	909.2	867.4	827.4	786.4	739.8	694.3	654.3	616.1
35°	1051.9	979.0	919.9	865.9	819.4	780.6	743.9	706.2	660.6	619.1	582.0
37.5°	1026.1	943.4	875.0	816.1	767.2	728.2	699.2	664.8	623.2	583.5	549.0
40°	1010.5	917.7	842.8	784.5	733.1	692.1	664.8	635.6	597.6	560.5	525.9
42.5°	989.6	894.0	810.3	749.5	697.8	658.3	630.8	605.3	573.4	538.4	501.4
45°	948.7	848.2	760.3	695.1	643.0	604.2	578.5	555.8	531.7	499.5	467.3
47.5°	895.4	800.4	708.4	637.2	586.1	550.2	525.2	507.4	490.1	462.7	431.4
50°	852.8	761.1	671.4	602.3	547.9	513.6	490.3	476.1	460.3	435.5	409.3
52.5°	802.4	720.6	632.7	562.1	510.7	478.7	456.2	442.0	429.0	408.7	383.8
55°	723.2	651.4	570.8	506.8	459.6	427.4	405.9	392.4	384.8	367.5	347.9
57.5°	631.6	580.2	509.2	447.4	405.7	373.8	358.1	346.7	338.0	325.8	311.9
60°	567.7	531.7	468.0	409.3	370.9	340.6	326.5	316.9	308.8	298.4	287.7
62.5°	503.0	476.8	421.4	370.9	335.7	310.2	297.0	288.3	279.0	272.1	261.7
65°	416.3	392.8	354.5	315.0	282.4	262.1	252.5	244.8	239.0	231.4	224.0
67.5°	323.8	314.3	287.8	260.5	237.1	219.0	210.8	205.4	198.4	193.9	188.8
70°	267.0	262.4	243.6	225.6	203.7	191.5	183.8	181.5	173.0	168.4	164.9
72.5°	216.7	214.5	203.7	191.2	175.8	165.0	157.9	155.3	150.0	146.3	144.1
75°	148.5	149.3	147.3	139.3	133.5	126.6	120.5	119.0	115.1	112.0	110.1
77.5°	93.9	97.9	98.0	97.6	95.3	91.1	88.6	87.4	83.6	82.5	82.0
80°	64.4	68.7	72.5	72.1	71.4	70.2	68.3	67.2	65.2	64.0	63.3
82.5°	42.9	46.9	50.1	52.2	52.0	50.9	49.6	49.0	48.7	47.8	47.7
85°	20.3	21.1	22.2	24.9	26.9	27.3	26.9	26.5	25.3	25.8	26.1
87.5°	10.4	10.0	9.9	9.5	8.7	9.8	10.2	10.1	9.9	9.8	9.6
90°	16.9	14.8	12.8	10.6	8.3	6.0	3.6	1.3	3.6	6.0	8.3
92.5°	45.3	42.8	40.3	38.2	36.6	34.9	33.3	31.7	33.3	34.9	36.6
95°	95.0	92.1	89.3	87.5	86.8	86.3	85.7	85.1	85.7	86.3	86.8
97.5°	152.6	148.6	144.5	142.4	142.2	142.0	141.7	141.5	141.7	142.0	142.2
100°	192.9	189.0	185.3	183.4	183.4	183.4	183.4	183.4	183.4	183.4	183.4
102.5°	238.5	236.6	234.7	233.1	232.0	230.8	229.6	228.4	229.6	230.8	232.0
105°	309.6	307.8	306.1	304.5	303.1	301.5	300.1	298.7	300.1	301.5	303.1
107.5°	386.1	384.8	383.4	382.0	380.6	379.1	377.7	376.2	377.7	379.1	380.6
110°	438.4	437.6	436.7	435.5	434.0	432.6	431.1	429.7	431.1	432.6	434.0



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	490.3	489.2	488.2	487.2	486.5	485.6	484.9	484.1	484.9	485.6	486.5
115°	571.3	570.7	570.2	569.3	568.0	566.9	565.7	564.6	565.7	566.9	568.0
117.5°	648.9	648.4	647.9	647.4	646.8	646.3	645.8	645.3	645.8	646.3	646.8
120°	702.9	702.6	702.3	701.5	699.9	698.5	697.0	695.6	697.0	698.5	699.9
122.5°	754.4	753.6	752.9	752.1	751.6	751.1	750.6	750.1	750.6	751.1	751.6
125°	832.5	832.2	831.9	830.9	829.2	827.5	825.7	823.9	825.7	827.5	829.2
127.5°	907.9	907.6	907.2	906.6	905.5	904.5	903.5	902.5	903.5	904.5	905.5
130°	957.8	957.2	956.5	955.5	954.1	952.6	951.2	949.7	951.2	952.6	954.1
132.5°	1007.3	1007.4	1007.5	1006.4	1004.0	1001.7	999.3	996.8	999.3	1001.7	1004.0
135°	1080.2	1079.8	1079.5	1078.5	1076.8	1075.0	1073.3	1071.6	1073.3	1075.0	1076.8
137.5°	1150.9	1150.3	1149.6	1148.5	1146.8	1145.2	1143.5	1141.8	1143.5	1145.2	1146.8
140°	1195.6	1194.7	1193.8	1192.7	1191.2	1189.7	1188.3	1186.8	1188.3	1189.7	1191.2
142.5°	1240.1	1239.0	1237.9	1236.8	1235.6	1234.4	1233.1	1231.9	1233.1	1234.4	1235.6
145°	1305.6	1304.7	1303.8	1302.8	1301.6	1300.5	1299.3	1298.2	1299.3	1300.5	1301.6
147.5°	1364.1	1363.4	1362.7	1362.0	1361.4	1360.8	1360.1	1359.5	1360.1	1360.8	1361.4
150°	1402.0	1400.8	1399.6	1399.2	1399.5	1399.8	1400.1	1400.4	1400.1	1399.8	1399.5
152.5°	1436.8	1436.4	1435.9	1435.5	1435.1	1434.7	1434.3	1433.9	1434.3	1434.7	1435.1
155°	1486.2	1485.9	1485.6	1485.5	1485.5	1485.5	1485.5	1485.5	1485.5	1485.5	1485.5
157.5°	1529.4	1529.1	1528.8	1529.0	1529.6	1530.3	1531.0	1531.6	1531.0	1530.3	1529.6
160°	1555.7	1555.4	1555.1	1555.4	1556.2	1557.1	1558.0	1558.8	1558.0	1557.1	1556.2
162.5°	1580.2	1580.1	1580.1	1580.4	1581.0	1581.7	1582.4	1583.0	1582.4	1581.7	1581.0
165°	1613.3	1613.0	1612.8	1612.9	1613.5	1614.0	1614.6	1615.2	1614.6	1614.0	1613.5
167.5°	1637.2	1637.2	1637.2	1637.8	1638.9	1640.1	1641.2	1642.4	1641.2	1640.1	1638.9
170°	1651.8	1651.8	1651.8	1652.4	1653.7	1654.8	1656.0	1657.1	1656.0	1654.8	1653.7
172.5°	1662.3	1662.3	1662.3	1662.9	1664.1	1665.3	1666.4	1667.6	1666.4	1665.3	1664.1
175°	1674.2	1674.2	1674.2	1674.8	1675.9	1677.1	1678.2	1679.4	1678.2	1677.1	1675.9
177.5°	1680.6	1680.8	1681.1	1681.6	1682.6	1683.5	1684.5	1685.4	1684.5	1683.5	1682.6
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	918.9	914.5	911.5	905.3	901.0	899.2	895.9	894.9	898.3	895.9	895.5
5°	891.5	880.4	871.6	862.7	853.1	847.1	837.8	836.3	833.9	830.5	829.8
7.5°	858.8	844.2	832.9	818.3	805.7	795.5	784.0	778.5	775.5	771.0	765.1
10°	836.7	819.4	804.1	789.5	773.8	761.1	749.6	740.7	735.0	729.6	727.3
12.5°	814.9	797.3	777.7	760.0	742.5	728.2	715.5	709.7	703.4	697.1	691.8
15°	781.0	757.6	736.2	715.8	700.8	685.5	673.3	664.8	655.2	652.6	642.2
17.5°	745.2	722.2	697.0	675.6	658.3	641.4	627.9	618.3	611.1	601.2	596.4
20°	722.8	695.5	671.0	651.4	632.2	612.3	598.4	590.4	583.5	575.4	571.6
22.5°	698.8	672.2	647.0	624.1	604.6	584.9	575.1	566.7	559.0	551.5	546.4
25°	663.7	636.8	610.4	586.5	566.2	552.0	540.5	530.9	526.7	519.4	514.0
27.5°	628.9	600.4	572.9	549.2	533.2	519.2	509.8	502.2	494.5	488.2	483.5
30°	606.5	577.3	547.4	528.7	511.7	498.4	488.0	480.7	474.9	469.2	465.7
32.5°	584.1	554.0	527.5	507.2	491.2	479.6	469.0	461.9	455.9	449.5	445.5
35°	548.2	517.5	496.0	476.1	460.3	449.6	442.3	432.3	427.4	422.7	418.5
37.5°	514.8	486.3	463.0	445.6	431.9	421.2	411.8	406.4	400.3	396.2	392.6
40°	490.3	464.1	443.1	424.6	414.7	402.8	393.9	387.1	382.4	377.1	373.2
42.5°	468.2	443.9	423.4	406.9	394.5	384.4	375.9	369.0	363.1	359.3	356.1
45°	437.0	412.7	392.8	377.5	366.0	356.4	347.6	344.1	336.4	331.8	330.3
47.5°	404.7	383.0	363.8	349.6	337.8	328.7	320.4	313.5	309.2	304.7	302.3
50°	382.8	362.1	344.1	330.3	318.8	308.8	301.1	296.5	290.7	286.6	283.5
52.5°	361.0	341.8	323.9	310.6	300.6	290.7	282.2	277.5	272.1	269.3	267.2
55°	329.9	309.6	294.3	281.1	270.8	261.7	253.6	248.9	245.5	242.9	242.1
57.5°	294.6	278.5	264.3	252.5	241.8	233.1	226.0	221.7	218.6	218.2	215.9
60°	271.6	257.0	244.0	231.4	222.1	214.1	207.9	203.0	199.9	199.4	198.7
62.5°	248.6	234.6	222.5	211.4	203.1	195.3	189.6	183.9	182.1	180.2	178.4
65°	214.4	201.8	191.8	183.0	174.2	167.6	161.9	158.4	154.2	151.9	147.7
67.5°	180.9	171.1	161.5	154.1	147.1	141.0	136.2	131.1	128.3	126.3	123.3
70°	158.9	151.2	141.6	133.5	128.2	123.1	119.3	113.5	111.6	110.1	108.6
72.5°	137.9	131.2	123.1	116.6	111.3	106.5	102.1	99.5	97.6	95.9	95.0
75°	108.6	102.0	95.1	90.5	86.7	82.9	80.6	78.7	77.9	77.5	75.9
77.5°	79.7	76.2	70.7	67.1	64.5	63.0	60.9	59.9	59.9	58.2	57.7
80°	61.0	59.1	54.4	52.9	51.0	49.5	48.4	46.5	44.5	43.7	42.6
82.5°	45.3	43.4	41.6	39.1	37.6	36.6	35.4	34.7	34.9	33.9	33.3
85°	24.1	22.2	21.5	21.1	20.3	21.1	20.7	20.3	20.0	19.6	20.0
87.5°	9.8	10.2	10.3	11.3	10.8	11.5	11.8	11.8	12.1	12.4	12.3
90°	10.6	12.8	14.8	16.9	18.9	21.0	22.4	23.8	25.3	26.8	28.0
92.5°	38.2	40.3	42.8	45.3	47.8	50.3	52.2	54.1	56.0	58.0	59.3
95°	87.5	89.3	92.1	95.0	98.0	100.9	102.9	104.9	106.9	109.1	110.3
97.5°	142.4	144.5	148.6	152.6	156.6	160.6	162.5	164.4	166.3	168.2	169.5
100°	183.4	185.3	189.0	192.9	196.6	200.5	203.1	205.7	208.2	210.9	212.5
102.5°	233.1	234.7	236.6	238.5	240.4	242.4	245.2	248.0	250.9	253.8	255.6
105°	304.5	306.1	307.8	309.6	311.3	313.1	314.9	316.6	318.3	320.0	321.3
107.5°	382.0	383.4	384.8	386.1	387.5	388.8	389.7	390.5	391.4	392.3	392.7
110°	435.5	436.7	437.6	438.4	439.3	440.1	441.0	441.9	442.7	443.6	443.9



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	487.2	488.2	489.2	490.3	491.4	492.5	492.9	493.3	493.7	494.1	494.1
115°	569.3	570.2	570.7	571.3	571.9	572.5	572.2	571.9	571.6	571.3	571.0
117.5°	647.4	647.9	648.4	648.9	649.4	650.1	650.3	650.5	650.7	651.0	650.5
120°	701.5	702.3	702.6	702.9	703.2	703.5	703.5	703.5	703.5	703.5	702.9
122.5°	752.1	752.9	753.6	754.4	755.1	755.9	755.6	755.4	755.2	754.9	754.4
125°	830.9	831.9	832.2	832.5	832.8	833.1	832.5	831.9	831.4	830.8	830.4
127.5°	906.6	907.2	907.6	907.9	908.3	908.6	908.3	908.0	907.7	907.5	907.0
130°	955.5	956.5	957.2	957.8	958.3	958.9	958.6	958.3	958.1	957.8	957.3
132.5°	1006.4	1007.5	1007.4	1007.3	1007.2	1007.1	1006.8	1006.5	1006.2	1005.9	1005.4
135°	1078.5	1079.5	1079.8	1080.2	1080.5	1080.8	1080.8	1080.8	1080.8	1080.8	1080.2
137.5°	1148.5	1149.6	1150.3	1150.9	1151.7	1152.3	1152.6	1153.0	1153.3	1153.7	1153.1
140°	1192.7	1193.8	1194.7	1195.6	1196.4	1197.3	1197.9	1198.5	1199.0	1199.6	1199.2
142.5°	1236.8	1237.9	1239.0	1240.1	1241.2	1242.3	1242.7	1243.0	1243.4	1243.7	1243.2
145°	1302.8	1303.8	1304.7	1305.6	1306.5	1307.4	1307.4	1307.4	1307.4	1307.4	1306.9
147.5°	1362.0	1362.7	1363.4	1364.1	1364.8	1365.5	1366.2	1366.9	1367.6	1368.3	1367.7
150°	1399.2	1399.6	1400.8	1402.0	1403.1	1404.3	1404.3	1404.3	1404.3	1404.3	1404.0
152.5°	1435.5	1435.9	1436.4	1436.8	1437.3	1437.8	1438.6	1439.2	1439.9	1440.6	1440.5
155°	1485.5	1485.6	1485.9	1486.2	1486.5	1486.8	1487.9	1489.1	1490.3	1491.5	1491.3
157.5°	1529.0	1528.8	1529.1	1529.4	1529.7	1530.0	1531.2	1532.4	1533.5	1534.7	1534.3
160°	1555.4	1555.1	1555.4	1555.7	1555.9	1556.2	1557.4	1558.5	1559.7	1560.8	1560.7
162.5°	1580.4	1580.1	1580.1	1580.2	1580.2	1580.3	1581.8	1583.2	1584.5	1585.9	1585.8
165°	1612.9	1612.8	1613.0	1613.3	1613.6	1613.9	1615.1	1616.2	1617.4	1618.5	1618.2
167.5°	1637.8	1637.2	1637.2	1637.2	1637.2	1637.2	1638.9	1640.7	1642.4	1644.2	1644.2
170°	1652.4	1651.8	1651.8	1651.8	1651.8	1651.8	1653.7	1655.4	1657.1	1658.8	1658.7
172.5°	1662.9	1662.3	1662.3	1662.3	1662.3	1662.3	1664.1	1665.9	1667.6	1669.3	1669.3
175°	1674.8	1674.2	1674.2	1674.2	1674.2	1674.2	1675.9	1677.6	1679.4	1681.1	1680.9
177.5°	1681.6	1681.1	1680.8	1680.6	1680.4	1680.1	1681.5	1682.9	1684.4	1685.8	1685.7
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	895.2	891.8	890.9	892.1	890.9	891.8	895.2	895.5	895.9	898.3	894.9
5°	826.0	822.1	824.0	823.2	824.0	822.1	826.0	829.8	830.5	833.9	836.3
7.5°	765.0	760.2	755.2	756.8	755.2	760.2	765.0	765.1	771.0	775.5	778.5
10°	722.4	718.5	716.2	718.1	716.2	718.5	722.4	727.3	729.6	735.0	740.7
12.5°	686.4	684.2	682.2	681.4	682.2	684.2	686.4	691.8	697.1	703.4	709.7
15°	637.5	633.0	631.1	626.1	631.1	633.0	637.5	642.2	652.6	655.2	664.8
17.5°	592.5	591.0	586.0	583.9	586.0	591.0	592.5	596.4	601.2	611.1	618.3
20°	565.8	564.3	559.4	562.4	559.4	564.3	565.8	571.6	575.4	583.5	590.4
22.5°	543.7	540.4	538.8	537.9	538.8	540.4	543.7	546.4	551.5	559.0	566.7
25°	512.5	507.6	505.6	503.3	505.6	507.6	512.5	514.0	519.4	526.7	530.9
27.5°	481.4	478.7	476.2	475.5	476.2	478.7	481.4	483.5	488.2	494.5	502.2
30°	461.1	458.4	456.5	456.5	456.5	458.4	461.1	465.7	469.2	474.9	480.7
32.5°	443.0	440.9	439.0	438.7	439.0	440.9	443.0	445.5	449.5	455.9	461.9
35°	416.6	413.5	412.7	410.5	412.7	413.5	416.6	418.5	422.7	427.4	432.3
37.5°	389.2	386.7	386.6	386.4	386.6	386.7	389.2	392.6	396.2	400.3	406.4
40°	371.7	369.8	369.4	366.8	369.4	369.8	371.7	373.2	377.1	382.4	387.1
42.5°	353.0	352.0	350.7	349.5	350.7	352.0	353.0	356.1	359.3	363.1	369.0
45°	327.6	325.0	325.0	323.1	325.0	325.0	327.6	330.3	331.8	336.4	344.1
47.5°	301.3	299.3	299.5	297.5	299.5	299.3	301.3	302.3	304.7	309.2	313.5
50°	283.9	282.8	282.4	281.6	282.4	282.8	283.9	283.5	286.6	290.7	296.5
52.5°	266.4	265.9	267.3	265.6	267.3	265.9	266.4	267.2	269.3	272.1	277.5
55°	242.9	241.7	244.0	241.7	244.0	241.7	242.9	242.1	242.9	245.5	248.9
57.5°	215.7	214.7	216.7	215.6	216.7	214.7	215.7	215.9	218.2	218.6	221.7
60°	197.9	195.6	196.8	197.2	196.8	195.6	197.9	198.7	199.4	199.9	203.0
62.5°	176.7	175.4	176.2	174.5	176.2	175.4	176.7	178.4	180.2	182.1	183.9
65°	146.9	145.8	144.2	143.5	144.2	145.8	146.9	147.7	151.9	154.2	158.4
67.5°	123.4	120.7	120.6	121.2	120.6	120.7	123.4	123.3	126.3	128.3	131.1
70°	106.2	106.2	105.8	105.8	105.8	106.2	106.2	108.6	110.1	111.6	113.5
72.5°	94.3	94.0	93.3	93.0	93.3	94.0	94.3	95.0	95.9	97.6	99.5
75°	75.9	76.3	75.5	75.2	75.5	76.3	75.9	75.9	77.5	77.9	78.7
77.5°	56.0	54.4	55.3	54.4	55.3	54.4	56.0	57.7	58.2	59.9	59.9
80°	42.6	42.2	43.3	42.2	43.3	42.2	42.6	42.6	43.7	44.5	46.5
82.5°	33.7	33.3	33.8	33.0	33.8	33.3	33.7	33.3	33.9	34.9	34.7
85°	20.3	20.0	19.6	20.0	19.6	20.0	20.3	20.0	19.6	20.0	20.3
87.5°	12.8	12.7	12.8	13.0	12.8	12.7	12.8	12.3	12.4	12.1	11.8
90°	28.8	29.7	30.6	31.4	30.6	29.7	28.8	28.0	26.8	25.3	23.8
92.5°	59.9	60.6	61.2	61.8	61.2	60.6	59.9	59.3	58.0	56.0	54.1
95°	110.9	111.5	112.1	112.7	112.1	111.5	110.9	110.3	109.1	106.9	104.9
97.5°	169.8	170.2	170.5	170.9	170.5	170.2	169.8	169.5	168.2	166.3	164.4
100°	213.1	213.7	214.3	214.8	214.3	213.7	213.1	212.5	210.9	208.2	205.7
102.5°	256.4	257.2	258.0	258.8	258.0	257.2	256.4	255.6	253.8	250.9	248.0
105°	322.2	323.2	324.0	324.9	324.0	323.2	322.2	321.3	320.0	318.3	316.6
107.5°	392.6	392.5	392.5	392.4	392.5	392.5	392.6	392.7	392.3	391.4	390.5
110°	443.6	443.3	443.0	442.7	443.0	443.3	443.6	443.9	443.6	442.7	441.9



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	493.6	493.1	492.5	492.0	492.5	493.1	493.6	494.1	494.1	493.7	493.3
115°	570.7	570.4	570.2	569.9	570.2	570.4	570.7	571.0	571.3	571.6	571.9
117.5°	649.3	648.1	647.0	645.8	647.0	648.1	649.3	650.5	651.0	650.7	650.5
120°	701.7	700.5	699.3	698.2	699.3	700.5	701.7	702.9	703.5	703.5	703.5
122.5°	753.4	752.5	751.5	750.6	751.5	752.5	753.4	754.4	754.9	755.2	755.4
125°	830.1	829.8	829.5	829.2	829.5	829.8	830.1	830.4	830.8	831.4	831.9
127.5°	906.5	905.8	905.2	904.6	905.2	905.8	906.5	907.0	907.5	907.7	908.0
130°	956.7	956.1	955.5	954.9	955.5	956.1	956.7	957.3	957.8	958.1	958.3
132.5°	1004.6	1003.7	1002.9	1002.1	1002.9	1003.7	1004.6	1005.4	1005.9	1006.2	1006.5
135°	1078.9	1077.8	1076.6	1075.5	1076.6	1077.8	1078.9	1080.2	1080.8	1080.8	1080.8
137.5°	1151.7	1150.1	1148.7	1147.3	1148.7	1150.1	1151.7	1153.1	1153.7	1153.3	1153.0
140°	1197.7	1196.3	1194.9	1193.4	1194.9	1196.3	1197.7	1199.2	1199.6	1199.0	1198.5
142.5°	1241.7	1240.3	1238.8	1237.4	1238.8	1240.3	1241.7	1243.2	1243.7	1243.4	1243.0
145°	1306.1	1305.1	1304.2	1303.4	1304.2	1305.1	1306.1	1306.9	1307.4	1307.4	1307.4
147.5°	1365.6	1363.7	1361.7	1359.8	1361.7	1363.7	1365.6	1367.7	1368.3	1367.6	1366.9
150°	1403.4	1402.8	1402.2	1401.7	1402.2	1402.8	1403.4	1404.0	1404.3	1404.3	1404.3
152.5°	1439.4	1438.4	1437.2	1436.2	1437.2	1438.4	1439.4	1440.5	1440.6	1439.9	1439.2
155°	1489.9	1488.4	1486.9	1485.5	1486.9	1488.4	1489.9	1491.3	1491.5	1490.3	1489.1
157.5°	1532.4	1530.5	1528.5	1526.6	1528.5	1530.5	1532.4	1534.3	1534.7	1533.5	1532.4
160°	1559.3	1557.8	1556.4	1554.9	1556.4	1557.8	1559.3	1560.7	1560.8	1559.7	1558.5
162.5°	1584.1	1582.4	1580.7	1579.0	1580.7	1582.4	1584.1	1585.8	1585.9	1584.5	1583.2
165°	1616.5	1614.8	1613.0	1611.2	1613.0	1614.8	1616.5	1618.2	1618.5	1617.4	1616.2
167.5°	1642.3	1640.5	1638.7	1636.9	1638.7	1640.5	1642.3	1644.2	1644.2	1642.4	1640.7
170°	1656.7	1654.7	1652.5	1650.5	1652.5	1654.7	1656.7	1658.7	1658.8	1657.1	1655.4
172.5°	1667.5	1665.7	1663.9	1662.0	1663.9	1665.7	1667.5	1669.3	1669.3	1667.6	1665.9
175°	1678.9	1676.9	1674.9	1672.8	1674.9	1676.9	1678.9	1680.9	1681.1	1679.4	1677.6
177.5°	1683.9	1682.3	1680.7	1679.1	1680.7	1682.3	1683.9	1685.7	1685.8	1684.4	1682.9
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	895.9	899.2	901.0	905.3	911.5	914.5	918.9	921.9	926.2	931.4	935.7
5°	837.8	847.1	853.1	862.7	871.6	880.4	891.5	899.6	910.3	922.6	932.2
7.5°	784.0	795.5	805.7	818.3	832.9	844.2	858.8	873.5	890.4	907.8	924.2
10°	749.6	761.1	773.8	789.5	804.1	819.4	836.7	853.9	875.0	894.6	916.9
12.5°	715.5	728.2	742.5	760.0	777.7	797.3	814.9	834.2	857.0	882.3	906.2
15°	673.3	685.5	700.8	715.8	736.2	757.6	781.0	806.8	832.0	860.5	890.0
17.5°	627.9	641.4	658.3	675.6	697.0	722.2	745.2	773.3	801.7	834.9	869.6
20°	598.4	612.3	632.2	651.4	671.0	695.5	722.8	751.5	781.8	816.7	855.5
22.5°	575.1	584.9	604.6	624.1	647.0	672.2	698.8	728.8	761.8	798.0	838.6
25°	540.5	552.0	566.2	586.5	610.4	636.8	663.7	695.5	731.5	768.4	811.7
27.5°	509.8	519.2	533.2	549.2	572.9	600.4	628.9	662.2	699.1	736.6	782.2
30°	488.0	498.4	511.7	528.7	547.4	577.3	606.5	639.1	676.7	715.5	762.2
32.5°	469.0	479.6	491.2	507.2	527.5	554.0	584.1	616.1	654.3	694.3	739.8
35°	442.3	449.6	460.3	476.1	496.0	517.5	548.2	582.0	619.1	660.6	706.2
37.5°	411.8	421.2	431.9	445.6	463.0	486.3	514.8	549.0	583.5	623.2	664.8
40°	393.9	402.8	414.7	424.6	443.1	464.1	490.3	525.9	560.5	597.6	635.6
42.5°	375.9	384.4	394.5	406.9	423.4	443.9	468.2	501.4	538.4	573.4	605.3
45°	347.6	356.4	366.0	377.5	392.8	412.7	437.0	467.3	499.5	531.7	555.8
47.5°	320.4	328.7	337.8	349.6	363.8	383.0	404.7	431.4	462.7	490.1	507.4
50°	301.1	308.8	318.8	330.3	344.1	362.1	382.8	409.3	435.5	460.3	476.1
52.5°	282.2	290.7	300.6	310.6	323.9	341.8	361.0	383.8	408.7	429.0	442.0
55°	253.6	261.7	270.8	281.1	294.3	309.6	329.9	347.9	367.5	384.8	392.4
57.5°	226.0	233.1	241.8	252.5	264.3	278.5	294.6	311.9	325.8	338.0	346.7
60°	207.9	214.1	222.1	231.4	244.0	257.0	271.6	287.7	298.4	308.8	316.9
62.5°	189.6	195.3	203.1	211.4	222.5	234.6	248.6	261.7	272.1	279.0	288.3
65°	161.9	167.6	174.2	183.0	191.8	201.8	214.4	224.0	231.4	239.0	244.8
67.5°	136.2	141.0	147.1	154.1	161.5	171.1	180.9	188.8	193.9	198.4	205.4
70°	119.3	123.1	128.2	133.5	141.6	151.2	158.9	164.9	168.4	173.0	181.5
72.5°	102.1	106.5	111.3	116.6	123.1	131.2	137.9	144.1	146.3	150.0	155.3
75°	80.6	82.9	86.7	90.5	95.1	102.0	108.6	110.1	112.0	115.1	119.0
77.5°	60.9	63.0	64.5	67.1	70.7	76.2	79.7	82.0	82.5	83.6	87.4
80°	48.4	49.5	51.0	52.9	54.4	59.1	61.0	63.3	64.0	65.2	67.2
82.5°	35.4	36.6	37.6	39.1	41.6	43.4	45.3	47.7	47.8	48.7	49.0
85°	20.7	21.1	20.3	21.1	21.5	22.2	24.1	26.1	25.8	25.3	26.5
87.5°	11.8	11.5	10.8	11.3	10.3	10.2	9.8	9.6	9.8	9.9	10.1
90°	22.4	21.0	18.9	16.9	14.8	12.8	10.6	8.3	6.0	3.6	1.3
92.5°	52.2	50.3	47.8	45.3	42.8	40.3	38.2	36.6	34.9	33.3	31.7
95°	102.9	100.9	98.0	95.0	92.1	89.3	87.5	86.8	86.3	85.7	85.1
97.5°	162.5	160.6	156.6	152.6	148.6	144.5	142.4	142.2	142.0	141.7	141.5
100°	203.1	200.5	196.6	192.9	189.0	185.3	183.4	183.4	183.4	183.4	183.4
102.5°	245.2	242.4	240.4	238.5	236.6	234.7	233.1	232.0	230.8	229.6	228.4
105°	314.9	313.1	311.3	309.6	307.8	306.1	304.5	303.1	301.5	300.1	298.7
107.5°	389.7	388.8	387.5	386.1	384.8	383.4	382.0	380.6	379.1	377.7	376.2
110°	441.0	440.1	439.3	438.4	437.6	436.7	435.5	434.0	432.6	431.1	429.7



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	492.9	492.5	491.4	490.3	489.2	488.2	487.2	486.5	485.6	484.9	484.1
115°	572.2	572.5	571.9	571.3	570.7	570.2	569.3	568.0	566.9	565.7	564.6
117.5°	650.3	650.1	649.4	648.9	648.4	647.9	647.4	646.8	646.3	645.8	645.3
120°	703.5	703.5	703.2	702.9	702.6	702.3	701.5	699.9	698.5	697.0	695.6
122.5°	755.6	755.9	755.1	754.4	753.6	752.9	752.1	751.6	751.1	750.6	750.1
125°	832.5	833.1	832.8	832.5	832.2	831.9	830.9	829.2	827.5	825.7	823.9
127.5°	908.3	908.6	908.3	907.9	907.6	907.2	906.6	905.5	904.5	903.5	902.5
130°	958.6	958.9	958.3	957.8	957.2	956.5	955.5	954.1	952.6	951.2	949.7
132.5°	1006.8	1007.1	1007.2	1007.3	1007.4	1007.5	1006.4	1004.0	1001.7	999.3	996.8
135°	1080.8	1080.8	1080.5	1080.2	1079.8	1079.5	1078.5	1076.8	1075.0	1073.3	1071.6
137.5°	1152.6	1152.3	1151.7	1150.9	1150.3	1149.6	1148.5	1146.8	1145.2	1143.5	1141.8
140°	1197.9	1197.3	1196.4	1195.6	1194.7	1193.8	1192.7	1191.2	1189.7	1188.3	1186.8
142.5°	1242.7	1242.3	1241.2	1240.1	1239.0	1237.9	1236.8	1235.6	1234.4	1233.1	1231.9
145°	1307.4	1307.4	1306.5	1305.6	1304.7	1303.8	1302.8	1301.6	1300.5	1299.3	1298.2
147.5°	1366.2	1365.5	1364.8	1364.1	1363.4	1362.7	1362.0	1361.4	1360.8	1360.1	1359.5
150°	1404.3	1404.3	1403.1	1402.0	1400.8	1399.6	1399.2	1399.5	1399.8	1400.1	1400.4
152.5°	1438.6	1437.8	1437.3	1436.8	1436.4	1435.9	1435.5	1435.1	1434.7	1434.3	1433.9
155°	1487.9	1486.8	1486.5	1486.2	1485.9	1485.6	1485.5	1485.5	1485.5	1485.5	1485.5
157.5°	1531.2	1530.0	1529.7	1529.4	1529.1	1528.8	1529.0	1529.6	1530.3	1531.0	1531.6
160°	1557.4	1556.2	1555.9	1555.7	1555.4	1555.1	1555.4	1556.2	1557.1	1558.0	1558.8
162.5°	1581.8	1580.3	1580.2	1580.2	1580.1	1580.1	1580.4	1581.0	1581.7	1582.4	1583.0
165°	1615.1	1613.9	1613.6	1613.3	1613.0	1612.8	1612.9	1613.5	1614.0	1614.6	1615.2
167.5°	1638.9	1637.2	1637.2	1637.2	1637.2	1637.2	1637.8	1638.9	1640.1	1641.2	1642.4
170°	1653.7	1651.8	1651.8	1651.8	1651.8	1651.8	1652.4	1653.7	1654.8	1656.0	1657.1
172.5°	1664.1	1662.3	1662.3	1662.3	1662.3	1662.3	1662.9	1664.1	1665.3	1666.4	1667.6
175°	1675.9	1674.2	1674.2	1674.2	1674.2	1674.2	1674.8	1675.9	1677.1	1678.2	1679.4
177.5°	1681.5	1680.1	1680.4	1680.6	1680.8	1681.1	1681.6	1682.6	1683.5	1684.5	1685.4
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	939.1	941.9	945.8	950.5	954.1	958.2	960.3	960.3	962.1	966.1	971.3
5°	941.8	951.8	961.4	973.6	983.2	994.3	1002.8	1010.9	1018.1	1027.3	1036.9
7.5°	941.0	957.6	974.8	994.2	1015.5	1032.5	1049.9	1063.6	1077.0	1094.7	1108.6
10°	938.0	959.5	982.8	1007.3	1034.2	1057.6	1078.7	1097.9	1116.3	1135.5	1152.8
12.5°	932.4	959.8	988.4	1017.8	1051.8	1078.5	1105.7	1126.2	1147.6	1168.6	1189.9
15°	924.1	956.3	990.9	1032.0	1073.4	1103.3	1130.1	1156.6	1176.6	1200.3	1220.7
17.5°	907.1	948.6	992.0	1036.8	1076.6	1111.5	1139.5	1164.8	1186.0	1212.1	1239.8
20°	896.9	941.8	987.0	1035.0	1073.0	1108.6	1135.9	1162.0	1188.4	1222.6	1256.4
22.5°	882.8	930.7	978.8	1024.3	1064.4	1098.8	1127.0	1158.9	1193.7	1232.4	1273.2
25°	860.5	910.0	957.6	1000.9	1040.0	1075.3	1113.7	1156.6	1198.8	1249.8	1308.5
27.5°	832.1	879.9	922.3	968.1	1007.0	1051.9	1099.7	1146.3	1207.2	1277.4	1350.7
30°	810.9	856.3	896.6	939.9	984.0	1033.5	1087.2	1142.1	1214.6	1297.0	1384.1
32.5°	786.4	827.4	867.4	909.2	960.1	1014.4	1071.6	1138.6	1225.3	1319.1	1409.3
35°	743.9	780.6	819.4	865.9	919.9	979.0	1051.9	1133.6	1238.3	1339.2	1420.2
37.5°	699.2	728.2	767.2	816.1	875.0	943.4	1026.1	1125.4	1232.9	1323.5	1358.0
40°	664.8	692.1	733.1	784.5	842.8	917.7	1010.5	1112.5	1220.7	1283.5	1280.9
42.5°	630.8	658.3	697.8	749.5	810.3	894.0	989.6	1095.6	1186.9	1210.8	1160.9
45°	578.5	604.2	643.0	695.1	760.3	848.2	948.7	1050.4	1108.6	1070.0	971.0
47.5°	525.2	550.2	586.1	637.2	708.4	800.4	895.4	978.9	987.0	903.8	785.1
50°	490.3	513.6	547.9	602.3	671.4	761.1	852.8	918.4	898.1	796.4	674.0
52.5°	456.2	478.7	510.7	562.1	632.7	720.6	802.4	853.9	806.9	698.8	588.8
55°	405.9	427.4	459.6	506.8	570.8	651.4	723.2	741.9	672.9	563.9	474.9
57.5°	358.1	373.8	405.7	447.4	509.2	580.2	631.6	628.2	552.0	453.9	390.1
60°	326.5	340.6	370.9	409.3	468.0	531.7	567.7	552.4	475.3	394.4	333.0
62.5°	297.0	310.2	335.7	370.9	421.4	476.8	503.0	481.8	409.0	337.9	289.1
65°	252.5	262.1	282.4	315.0	354.5	392.8	416.3	385.2	320.7	267.0	230.1
67.5°	210.8	219.0	237.1	260.5	287.8	314.3	323.8	294.6	244.5	208.3	182.4
70°	183.8	191.5	203.7	225.6	243.6	262.4	267.0	241.0	199.1	171.5	155.3
72.5°	157.9	165.0	175.8	191.2	203.7	214.5	216.7	192.4	160.5	141.4	129.0
75°	120.5	126.6	133.5	139.3	147.3	149.3	148.5	129.7	112.4	99.8	92.8
77.5°	88.6	91.1	95.3	97.6	98.0	97.9	93.9	82.0	73.1	67.9	65.0
80°	68.3	70.2	71.4	72.1	72.5	68.7	64.4	57.2	54.1	51.0	47.6
82.5°	49.6	50.9	52.0	52.2	50.1	46.9	42.9	39.4	37.2	35.6	34.3
85°	26.9	27.3	26.9	24.9	22.2	21.1	20.3	19.6	19.2	18.8	18.8
87.5°	10.2	9.8	8.7	9.5	9.9	10.0	10.4	10.5	10.6	10.9	11.2
90°	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	21.0	22.4	23.8
92.5°	33.3	34.9	36.6	38.2	40.3	42.8	45.3	47.8	50.3	52.2	54.1
95°	85.7	86.3	86.8	87.5	89.3	92.1	95.0	98.0	100.9	102.9	104.9
97.5°	141.7	142.0	142.2	142.4	144.5	148.6	152.6	156.6	160.6	162.5	164.4
100°	183.4	183.4	183.4	183.4	185.3	189.0	192.9	196.6	200.5	203.1	205.7
102.5°	229.6	230.8	232.0	233.1	234.7	236.6	238.5	240.4	242.4	245.2	248.0
105°	300.1	301.5	303.1	304.5	306.1	307.8	309.6	311.3	313.1	314.9	316.6
107.5°	377.7	379.1	380.6	382.0	383.4	384.8	386.1	387.5	388.8	389.7	390.5
110°	431.1	432.6	434.0	435.5	436.7	437.6	438.4	439.3	440.1	441.0	441.9



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	484.9	485.6	486.5	487.2	488.2	489.2	490.3	491.4	492.5	492.9	493.3
115°	565.7	566.9	568.0	569.3	570.2	570.7	571.3	571.9	572.5	572.2	571.9
117.5°	645.8	646.3	646.8	647.4	647.9	648.4	648.9	649.4	650.1	650.3	650.5
120°	697.0	698.5	699.9	701.5	702.3	702.6	702.9	703.2	703.5	703.5	703.5
122.5°	750.6	751.1	751.6	752.1	752.9	753.6	754.4	755.1	755.9	755.6	755.4
125°	825.7	827.5	829.2	830.9	831.9	832.2	832.5	832.8	833.1	832.5	831.9
127.5°	903.5	904.5	905.5	906.6	907.2	907.6	907.9	908.3	908.6	908.3	908.0
130°	951.2	952.6	954.1	955.5	956.5	957.2	957.8	958.3	958.9	958.6	958.3
132.5°	999.3	1001.7	1004.0	1006.4	1007.5	1007.4	1007.3	1007.2	1007.1	1006.8	1006.5
135°	1073.3	1075.0	1076.8	1078.5	1079.5	1079.8	1080.2	1080.5	1080.8	1080.8	1080.8
137.5°	1143.5	1145.2	1146.8	1148.5	1149.6	1150.3	1150.9	1151.7	1152.3	1152.6	1153.0
140°	1188.3	1189.7	1191.2	1192.7	1193.8	1194.7	1195.6	1196.4	1197.3	1197.9	1198.5
142.5°	1233.1	1234.4	1235.6	1236.8	1237.9	1239.0	1240.1	1241.2	1242.3	1242.7	1243.0
145°	1299.3	1300.5	1301.6	1302.8	1303.8	1304.7	1305.6	1306.5	1307.4	1307.4	1307.4
147.5°	1360.1	1360.8	1361.4	1362.0	1362.7	1363.4	1364.1	1364.8	1365.5	1366.2	1366.9
150°	1400.1	1399.8	1399.5	1399.2	1399.6	1400.8	1402.0	1403.1	1404.3	1404.3	1404.3
152.5°	1434.3	1434.7	1435.1	1435.5	1435.9	1436.4	1436.8	1437.3	1437.8	1438.6	1439.2
155°	1485.5	1485.5	1485.5	1485.5	1485.6	1485.9	1486.2	1486.5	1486.8	1487.9	1489.1
157.5°	1531.0	1530.3	1529.6	1529.0	1528.8	1529.1	1529.4	1529.7	1530.0	1531.2	1532.4
160°	1558.0	1557.1	1556.2	1555.4	1555.1	1555.4	1555.7	1555.9	1556.2	1557.4	1558.5
162.5°	1582.4	1581.7	1581.0	1580.4	1580.1	1580.1	1580.2	1580.2	1580.3	1581.8	1583.2
165°	1614.6	1614.0	1613.5	1612.9	1612.8	1613.0	1613.3	1613.6	1613.9	1615.1	1616.2
167.5°	1641.2	1640.1	1638.9	1637.8	1637.2	1637.2	1637.2	1637.2	1637.2	1638.9	1640.7
170°	1656.0	1654.8	1653.7	1652.4	1651.8	1651.8	1651.8	1651.8	1651.8	1653.7	1655.4
172.5°	1666.4	1665.3	1664.1	1662.9	1662.3	1662.3	1662.3	1662.3	1662.3	1664.1	1665.9
175°	1678.2	1677.1	1675.9	1674.8	1674.2	1674.2	1674.2	1674.2	1674.2	1675.9	1677.6
177.5°	1684.5	1683.5	1682.6	1681.6	1681.1	1680.8	1680.6	1680.4	1680.1	1681.5	1682.9
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	975.3	975.3	980.6	980.2	983.6	982.4	983.0
5°	1048.4	1054.9	1060.7	1064.5	1070.3	1071.9	1071.1
7.5°	1124.3	1138.7	1145.8	1155.5	1157.2	1162.3	1161.7
10°	1171.1	1185.4	1196.1	1204.6	1208.8	1214.2	1214.6
12.5°	1208.0	1220.0	1229.6	1237.4	1242.5	1244.3	1245.3
15°	1236.8	1250.2	1261.3	1272.4	1279.0	1283.9	1286.7
17.5°	1265.8	1286.5	1306.2	1321.3	1330.3	1338.0	1337.9
20°	1288.2	1312.0	1336.6	1353.8	1371.4	1379.1	1380.3
22.5°	1312.1	1348.5	1380.1	1406.8	1430.1	1438.0	1441.0
25°	1361.8	1409.4	1458.1	1495.7	1522.6	1538.3	1540.7
27.5°	1421.9	1486.3	1537.5	1572.3	1594.6	1606.2	1608.7
30°	1464.3	1523.7	1569.7	1595.9	1606.2	1607.7	1601.9
32.5°	1483.3	1527.7	1546.1	1544.6	1524.3	1510.8	1505.6
35°	1460.1	1450.9	1405.9	1352.2	1311.2	1285.2	1278.2
37.5°	1328.7	1249.3	1166.7	1085.6	1042.4	1020.5	982.7
40°	1199.2	1086.0	1000.1	931.8	883.1	843.9	834.8
42.5°	1053.1	936.2	850.3	791.8	753.0	726.1	714.5
45°	846.3	745.8	674.8	629.9	600.0	580.4	571.6
47.5°	676.8	599.1	547.3	514.1	491.3	474.3	469.6
50°	583.9	521.7	478.0	450.0	432.7	419.7	414.3
52.5°	507.2	457.0	423.3	400.3	384.0	375.8	371.3
55°	418.5	375.2	351.0	332.5	323.4	316.9	313.8
57.5°	342.2	310.9	293.3	280.5	272.1	267.9	266.4
60°	299.6	275.1	258.9	248.9	243.2	237.8	236.3
62.5°	261.9	242.6	230.0	221.4	215.6	213.3	212.4
65°	211.0	198.3	189.1	183.8	179.2	178.3	178.0
67.5°	167.7	160.3	155.4	149.9	148.2	145.5	145.0
70°	143.5	138.5	132.7	130.8	128.9	126.2	126.6
72.5°	121.7	116.7	112.8	110.3	109.6	108.5	109.4
75°	89.0	87.5	85.9	84.0	83.2	83.2	82.9
77.5°	63.5	62.2	60.5	59.4	59.2	57.6	58.2
80°	46.0	44.1	43.3	43.7	42.6	42.2	42.2
82.5°	34.0	33.3	32.6	32.7	32.4	32.1	32.4
85°	18.8	18.4	18.4	18.1	18.1	17.7	17.7
87.5°	11.8	12.4	12.0	11.9	12.1	12.5	13.0
90°	25.3	26.8	28.0	28.8	29.7	30.6	31.4
92.5°	56.0	58.0	59.3	59.9	60.6	61.2	61.8
95°	106.9	109.1	110.3	110.9	111.5	112.1	112.7
97.5°	166.3	168.2	169.5	169.8	170.2	170.5	170.9
100°	208.2	210.9	212.5	213.1	213.7	214.3	214.8
102.5°	250.9	253.8	255.6	256.4	257.2	258.0	258.8
105°	318.3	320.0	321.3	322.2	323.2	324.0	324.9
107.5°	391.4	392.3	392.7	392.6	392.5	392.5	392.4
110°	442.7	443.6	443.9	443.6	443.3	443.0	442.7



TEST NUMBER: P333673-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	493.7	494.1	494.1	493.6	493.1	492.5	492.0
115°	571.6	571.3	571.0	570.7	570.4	570.2	569.9
117.5°	650.7	651.0	650.5	649.3	648.1	647.0	645.8
120°	703.5	703.5	702.9	701.7	700.5	699.3	698.2
122.5°	755.2	754.9	754.4	753.4	752.5	751.5	750.6
125°	831.4	830.8	830.4	830.1	829.8	829.5	829.2
127.5°	907.7	907.5	907.0	906.5	905.8	905.2	904.6
130°	958.1	957.8	957.3	956.7	956.1	955.5	954.9
132.5°	1006.2	1005.9	1005.4	1004.6	1003.7	1002.9	1002.1
135°	1080.8	1080.8	1080.2	1078.9	1077.8	1076.6	1075.5
137.5°	1153.3	1153.7	1153.1	1151.7	1150.1	1148.7	1147.3
140°	1199.0	1199.6	1199.2	1197.7	1196.3	1194.9	1193.4
142.5°	1243.4	1243.7	1243.2	1241.7	1240.3	1238.8	1237.4
145°	1307.4	1307.4	1306.9	1306.1	1305.1	1304.2	1303.4
147.5°	1367.6	1368.3	1367.7	1365.6	1363.7	1361.7	1359.8
150°	1404.3	1404.3	1404.0	1403.4	1402.8	1402.2	1401.7
152.5°	1439.9	1440.6	1440.5	1439.4	1438.4	1437.2	1436.2
155°	1490.3	1491.5	1491.3	1489.9	1488.4	1486.9	1485.5
157.5°	1533.5	1534.7	1534.3	1532.4	1530.5	1528.5	1526.6
160°	1559.7	1560.8	1560.7	1559.3	1557.8	1556.4	1554.9
162.5°	1584.5	1585.9	1585.8	1584.1	1582.4	1580.7	1579.0
165°	1617.4	1618.5	1618.2	1616.5	1614.8	1613.0	1611.2
167.5°	1642.4	1644.2	1644.2	1642.3	1640.5	1638.7	1636.9
170°	1657.1	1658.8	1658.7	1656.7	1654.7	1652.5	1650.5
172.5°	1667.6	1669.3	1669.3	1667.5	1665.7	1663.9	1662.0
175°	1679.4	1681.1	1680.9	1678.9	1676.9	1674.9	1672.8
177.5°	1684.4	1685.8	1685.7	1683.9	1682.3	1680.7	1679.1
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3

(END OF REPORT)