

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333660-840

Luminaire Tested: **S125RDIW-S610D470U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333660-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S610D470U840-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 470 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4314.9 lumens  
Efficiency: N/A  
Efficacy: 142.9 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 30.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	100	95	92	88	93	89	86	83	77	74	72	66	64	62	55	54	53	48
2	91	84	78	73	85	78	73	69	68	64	61	58	55	53	49	47	45	41
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39	35
4	76	66	58	52	71	62	55	49	54	48	44	46	42	39	40	37	34	31
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	36	32	30	27
6	65	53	45	39	60	50	42	37	44	38	34	38	33	30	33	29	26	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	44	36	31	52	41	34	29	36	30	26	32	27	24	27	24	21	19
9	52	40	32	27	48	38	31	26	33	28	24	29	25	21	25	22	19	17
10	49	37	29	25	45	34	28	23	31	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6035	6035	6035	6035
5°	6944	6043	5337	6043
10°	7965	6013	4709	6013
15°	8603	5951	4186	5951
20°	9487	5880	3865	5880
25°	10979	5784	3587	5784
30°	11946	5684	3404	5684
35°	10078	5568	3236	5568
40°	7038	5359	3092	5359
45°	5221	5076	2951	5076
50°	4163	4784	2829	4784
55°	3533	4418	2721	4418
60°	3052	4093	2547	4093
65°	2720	3741	2193	3741
70°	2391	3427	1998	3427
75°	2069	2969	1876	2969
80°	1570	2499	1570	2499
85°	1312	1964	1482	1964



TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.6	2.1
10°-20°	262.6	6.1
20°-30°	416.4	9.7
30°-40°	502.1	11.6
40°-50°	448.4	10.4
50°-60°	343.9	8.0
60°-70°	223.5	5.2
70°-80°	108.6	2.5
80°-90°	27.2	0.6
90°-100°	22.4	0.5
100°-110°	138.0	3.2
110°-120°	250.3	5.8
120°-130°	321.3	7.4
130°-140°	345.6	8.0
140°-150°	324.4	7.5
150°-160°	262.4	6.1
160°-170°	169.7	3.9
170°-180°	58.5	1.4
0°-30°	768.6	17.8
0°-40°	1270.8	29.5
0°-60°	2063.1	47.8
0°-90°	2422.4	56.1
90°-120°	410.7	9.5
90°-150°	1401.9	32.5
90°-180°	1893.0	43.9
0°-180°	4314.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	934	934	934	934	934	
5°	1071	932	823	932	1071	107
15°	1287	890	626	890	1287	369
25°	1541	812	503	812	1541	707
35°	1278	706	410	706	1278	772
45°	572	556	323	556	572	456
55°	314	392	242	392	314	285
65°	178	245	144	245	178	177
75°	83	119	75	119	83	88
85°	18	26	20	26	18	21
90°	11	0	11	0	11	6
95°	10	26	10	26	10	8
105°	136	134	136	134	136	123
115°	250	252	250	252	250	248
125°	359	359	359	359	359	319
135°	446	447	446	447	446	344
145°	517	519	517	519	517	323
155°	567	571	567	571	567	261
165°	599	603	599	603	599	169
175°	614	616	614	616	614	58
180°	616	616	616	616	616	



TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	983.0	982.4	983.6	980.2	980.6	975.3	975.3	971.3	966.1	962.1	960.3
5°	1071.1	1071.9	1070.3	1064.5	1060.7	1054.9	1048.4	1036.9	1027.3	1018.1	1010.9
7.5°	1161.7	1162.3	1157.2	1155.5	1145.8	1138.7	1124.3	1108.6	1094.7	1077.0	1063.6
10°	1214.6	1214.2	1208.8	1204.6	1196.1	1185.4	1171.1	1152.8	1135.5	1116.3	1097.9
12.5°	1245.3	1244.3	1242.5	1237.4	1229.6	1220.0	1208.0	1189.9	1168.6	1147.6	1126.2
15°	1286.7	1283.9	1279.0	1272.4	1261.3	1250.2	1236.8	1220.7	1200.3	1176.6	1156.6
17.5°	1337.9	1338.0	1330.3	1321.3	1306.2	1286.5	1265.8	1239.8	1212.1	1186.0	1164.8
20°	1380.3	1379.1	1371.4	1353.8	1336.6	1312.0	1288.2	1256.4	1222.6	1188.4	1162.0
22.5°	1441.0	1438.0	1430.1	1406.8	1380.1	1348.5	1312.1	1273.2	1232.4	1193.7	1158.9
25°	1540.7	1538.3	1522.6	1495.7	1458.1	1409.4	1361.8	1308.5	1249.8	1198.8	1156.6
27.5°	1608.7	1606.2	1594.6	1572.3	1537.5	1486.3	1421.9	1350.7	1277.4	1207.2	1146.3
30°	1601.9	1607.7	1606.2	1595.9	1569.7	1523.7	1464.3	1384.1	1297.0	1214.6	1142.1
32.5°	1505.6	1510.8	1524.3	1544.6	1546.1	1527.7	1483.3	1409.3	1319.1	1225.3	1138.6
35°	1278.2	1285.2	1311.2	1352.2	1405.9	1450.9	1460.1	1420.2	1339.2	1238.3	1133.6
37.5°	982.7	1020.5	1042.4	1085.6	1166.7	1249.3	1328.7	1358.0	1323.5	1232.9	1125.4
40°	834.8	843.9	883.1	931.8	1000.1	1086.0	1199.2	1280.9	1283.5	1220.7	1112.5
42.5°	714.5	726.1	753.0	791.8	850.3	936.2	1053.1	1160.9	1210.8	1186.9	1095.6
45°	571.6	580.4	600.0	629.9	674.8	745.8	846.3	971.0	1070.0	1108.6	1050.4
47.5°	469.6	474.3	491.3	514.1	547.3	599.1	676.8	785.1	903.8	987.0	978.9
50°	414.3	419.7	432.7	450.0	478.0	521.7	583.9	674.0	796.4	898.1	918.4
52.5°	371.3	375.8	384.0	400.3	423.3	457.0	507.2	588.8	698.8	806.9	853.9
55°	313.8	316.9	323.4	332.5	351.0	375.2	418.5	474.9	563.9	672.9	741.9
57.5°	266.4	267.9	272.1	280.5	293.3	310.9	342.2	390.1	453.9	552.0	628.2
60°	236.3	237.8	243.2	248.9	258.9	275.1	299.6	333.0	394.4	475.3	552.4
62.5°	212.4	213.3	215.6	221.4	230.0	242.6	261.9	289.1	337.9	409.0	481.8
65°	178.0	178.3	179.2	183.8	189.1	198.3	211.0	230.1	267.0	320.7	385.2
67.5°	145.0	145.5	148.2	149.9	155.4	160.3	167.7	182.4	208.3	244.5	294.6
70°	126.6	126.2	128.9	130.8	132.7	138.5	143.5	155.3	171.5	199.1	241.0
72.5°	109.4	108.5	109.6	110.3	112.8	116.7	121.7	129.0	141.4	160.5	192.4
75°	82.9	83.2	83.2	84.0	85.9	87.5	89.0	92.8	99.8	112.4	129.7
77.5°	58.2	57.6	59.2	59.4	60.5	62.2	63.5	65.0	67.9	73.1	82.0
80°	42.2	42.2	42.6	43.7	43.3	44.1	46.0	47.6	51.0	54.1	57.2
82.5°	32.4	32.1	32.4	32.7	32.6	33.3	34.0	34.3	35.6	37.2	39.4
85°	17.7	17.7	18.1	18.1	18.4	18.4	18.8	18.8	18.8	19.2	19.6
87.5°	9.0	8.6	8.2	8.2	8.4	8.9	8.5	8.1	8.0	7.9	8.1
90°	11.0	10.7	10.4	10.1	9.8	9.3	8.8	8.3	7.8	7.3	6.6
92.5°	10.2	10.1	10.0	9.8	9.7	9.3	8.8	8.3	7.8	7.3	6.7
95°	9.6	9.6	9.6	9.6	9.6	9.3	8.8	8.3	7.8	7.3	11.2
97.5°	9.6	9.6	9.6	9.6	9.6	11.0	13.9	16.8	19.6	22.5	30.1
100°	9.6	10.0	10.4	10.8	11.2	19.0	34.1	49.3	64.3	79.5	79.1
102.5°	57.5	64.3	71.3	78.2	85.1	90.0	92.8	95.7	98.6	101.4	101.2
105°	135.7	135.8	135.9	136.0	136.1	136.1	136.1	136.1	136.1	136.1	136.1
107.5°	171.1	171.4	171.7	172.0	172.3	172.4	172.4	172.4	172.4	172.3	172.1
110°	195.5	195.4	195.3	195.2	195.1	195.2	195.5	195.8	196.1	196.4	196.2



TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	217.4	217.6	217.7	217.9	218.0	218.3	218.6	219.0	219.4	219.8	219.7
115°	250.3	251.0	251.6	252.2	252.8	253.3	253.7	254.1	254.5	254.9	254.8
117.5°	285.5	285.7	286.0	286.2	286.5	286.9	287.4	287.9	288.5	289.0	288.6
120°	307.0	307.5	308.0	308.5	309.0	309.4	309.6	309.8	310.0	310.2	309.9
122.5°	327.5	328.1	328.6	329.2	329.8	330.2	330.4	330.6	330.8	331.0	330.9
125°	358.6	358.9	359.2	359.5	359.8	360.2	360.6	361.0	361.4	361.8	361.8
127.5°	384.9	385.6	386.4	387.1	387.9	388.4	388.6	388.8	389.0	389.2	389.3
130°	403.8	404.3	404.9	405.4	405.9	406.3	406.6	406.9	407.2	407.5	407.4
132.5°	421.4	421.9	422.4	422.9	423.4	423.7	423.7	423.8	423.9	423.9	424.1
135°	445.5	446.1	446.7	447.3	447.9	448.3	448.5	448.7	448.9	449.1	449.3
137.5°	469.6	470.1	470.6	471.1	471.7	471.9	471.9	471.8	471.8	471.7	471.9
140°	483.8	484.4	485.0	485.6	486.3	486.5	486.3	486.0	485.8	485.6	485.7
142.5°	497.4	498.0	498.6	499.2	499.8	500.1	500.0	500.0	499.9	499.9	499.8
145°	517.2	517.8	518.4	519.0	519.6	519.9	519.8	519.7	519.6	519.5	519.5
147.5°	533.5	534.2	535.0	535.7	536.4	536.7	536.6	536.5	536.3	536.2	536.1
150°	544.1	544.9	545.7	546.5	547.3	547.6	547.4	547.2	547.0	546.8	546.6
152.5°	554.0	554.7	555.4	556.1	556.9	557.1	556.9	556.7	556.5	556.3	556.1
155°	566.9	567.7	568.6	569.4	570.2	570.5	570.2	569.9	569.6	569.3	569.1
157.5°	577.8	578.7	579.5	580.3	581.1	581.3	581.0	580.7	580.4	580.1	580.0
160°	584.8	585.6	586.4	587.2	588.0	588.2	587.8	587.4	587.0	586.6	586.5
162.5°	591.0	591.9	592.8	593.7	594.6	594.7	594.2	593.6	593.0	592.5	592.4
165°	599.4	600.2	601.0	601.9	602.7	602.8	602.2	601.6	600.9	600.3	600.2
167.5°	605.2	606.1	607.0	607.9	608.9	608.9	608.2	607.5	606.8	606.0	605.9
170°	608.5	609.5	610.4	611.3	612.2	612.3	611.5	610.6	609.8	608.9	608.8
172.5°	610.8	611.7	612.6	613.5	614.4	614.5	613.7	613.0	612.3	611.6	611.4
175°	613.6	614.5	615.4	616.3	617.2	617.2	616.4	615.6	614.8	614.0	613.9
177.5°	615.2	615.8	616.5	617.1	617.8	617.8	617.2	616.7	616.1	615.6	615.5
180°	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3



TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	960.3	958.2	954.1	950.5	945.8	941.9	939.1	935.7	931.4	926.2	921.9
5°	1002.8	994.3	983.2	973.6	961.4	951.8	941.8	932.2	922.6	910.3	899.6
7.5°	1049.9	1032.5	1015.5	994.2	974.8	957.6	941.0	924.2	907.8	890.4	873.5
10°	1078.7	1057.6	1034.2	1007.3	982.8	959.5	938.0	916.9	894.6	875.0	853.9
12.5°	1105.7	1078.5	1051.8	1017.8	988.4	959.8	932.4	906.2	882.3	857.0	834.2
15°	1130.1	1103.3	1073.4	1032.0	990.9	956.3	924.1	890.0	860.5	832.0	806.8
17.5°	1139.5	1111.5	1076.6	1036.8	992.0	948.6	907.1	869.6	834.9	801.7	773.3
20°	1135.9	1108.6	1073.0	1035.0	987.0	941.8	896.9	855.5	816.7	781.8	751.5
22.5°	1127.0	1098.8	1064.4	1024.3	978.8	930.7	882.8	838.6	798.0	761.8	728.8
25°	1113.7	1075.3	1040.0	1000.9	957.6	910.0	860.5	811.7	768.4	731.5	695.5
27.5°	1099.7	1051.9	1007.0	968.1	922.3	879.9	832.1	782.2	736.6	699.1	662.2
30°	1087.2	1033.5	984.0	939.9	896.6	856.3	810.9	762.2	715.5	676.7	639.1
32.5°	1071.6	1014.4	960.1	909.2	867.4	827.4	786.4	739.8	694.3	654.3	616.1
35°	1051.9	979.0	919.9	865.9	819.4	780.6	743.9	706.2	660.6	619.1	582.0
37.5°	1026.1	943.4	875.0	816.1	767.2	728.2	699.2	664.8	623.2	583.5	549.0
40°	1010.5	917.7	842.8	784.5	733.1	692.1	664.8	635.6	597.6	560.5	525.9
42.5°	989.6	894.0	810.3	749.5	697.8	658.3	630.8	605.3	573.4	538.4	501.4
45°	948.7	848.2	760.3	695.1	643.0	604.2	578.5	555.8	531.7	499.5	467.3
47.5°	895.4	800.4	708.4	637.2	586.1	550.2	525.2	507.4	490.1	462.7	431.4
50°	852.8	761.1	671.4	602.3	547.9	513.6	490.3	476.1	460.3	435.5	409.3
52.5°	802.4	720.6	632.7	562.1	510.7	478.7	456.2	442.0	429.0	408.7	383.8
55°	723.2	651.4	570.8	506.8	459.6	427.4	405.9	392.4	384.8	367.5	347.9
57.5°	631.6	580.2	509.2	447.4	405.7	373.8	358.1	346.7	338.0	325.8	311.9
60°	567.7	531.7	468.0	409.3	370.9	340.6	326.5	316.9	308.8	298.4	287.7
62.5°	503.0	476.8	421.4	370.9	335.7	310.2	297.0	288.3	279.0	272.1	261.7
65°	416.3	392.8	354.5	315.0	282.4	262.1	252.5	244.8	239.0	231.4	224.0
67.5°	323.8	314.3	287.8	260.5	237.1	219.0	210.8	205.4	198.4	193.9	188.8
70°	267.0	262.4	243.6	225.6	203.7	191.5	183.8	181.5	173.0	168.4	164.9
72.5°	216.7	214.5	203.7	191.2	175.8	165.0	157.9	155.3	150.0	146.3	144.1
75°	148.5	149.3	147.3	139.3	133.5	126.6	120.5	119.0	115.1	112.0	110.1
77.5°	93.9	97.9	98.0	97.6	95.3	91.1	88.6	87.4	83.6	82.5	82.0
80°	64.4	68.7	72.5	72.1	71.4	70.2	68.3	67.2	65.2	64.0	63.3
82.5°	42.9	46.9	50.1	52.2	52.0	50.9	49.6	49.0	48.7	47.8	47.7
85°	20.3	21.1	22.2	24.9	26.9	27.3	26.9	26.5	25.3	25.8	26.1
87.5°	8.3	8.1	8.3	8.1	7.7	9.0	9.8	9.9	9.5	9.0	8.6
90°	5.9	5.2	4.4	3.7	2.9	2.1	1.3	0.5	1.3	2.1	2.9
92.5°	6.1	5.5	4.7	4.7	5.4	5.9	6.5	7.1	6.5	5.9	5.4
95°	15.0	18.9	22.7	24.8	25.1	25.4	25.8	26.1	25.8	25.4	25.1
97.5°	37.8	45.3	53.0	56.6	56.0	55.4	54.9	54.3	54.9	55.4	56.0
100°	78.7	78.3	77.9	77.6	77.3	77.0	76.6	76.2	76.6	77.0	77.3
102.5°	100.9	100.7	100.5	100.2	99.8	99.4	99.0	98.6	99.0	99.4	99.8
105°	136.1	136.1	136.1	135.9	135.5	135.1	134.7	134.3	134.7	135.1	135.5
107.5°	171.9	171.7	171.5	171.4	171.4	171.4	171.4	171.4	171.4	171.4	171.4
110°	196.0	195.8	195.6	195.5	195.5	195.5	195.5	195.5	195.5	195.5	195.5





TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	219.6	219.4	219.3	219.1	218.9	218.6	218.4	218.2	218.4	218.6	218.9
115°	254.7	254.6	254.5	254.2	253.7	253.2	252.7	252.2	252.7	253.2	253.7
117.5°	288.2	287.8	287.5	287.3	287.3	287.3	287.3	287.4	287.3	287.3	287.3
120°	309.6	309.3	309.0	308.9	309.0	309.1	309.2	309.3	309.2	309.1	309.0
122.5°	330.7	330.6	330.4	330.2	329.8	329.4	329.0	328.7	329.0	329.4	329.8
125°	361.8	361.8	361.8	361.4	360.7	360.0	359.3	358.6	359.3	360.0	360.7
127.5°	389.4	389.4	389.5	389.3	388.8	388.3	387.8	387.2	387.8	388.3	388.8
130°	407.3	407.2	407.1	406.8	406.3	405.8	405.3	404.8	405.3	405.8	406.3
132.5°	424.4	424.6	424.9	424.6	424.0	423.5	422.9	422.3	422.9	423.5	424.0
135°	449.5	449.7	449.9	449.7	449.1	448.5	447.9	447.3	447.9	448.5	449.1
137.5°	472.1	472.3	472.5	472.3	471.8	471.2	470.7	470.2	470.7	471.2	471.8
140°	485.8	485.9	486.0	485.9	485.7	485.5	485.3	485.1	485.3	485.5	485.7
142.5°	499.6	499.5	499.3	499.2	499.1	499.0	498.9	498.7	498.9	499.0	499.1
145°	519.5	519.5	519.5	519.4	519.2	519.0	518.8	518.6	518.8	519.0	519.2
147.5°	536.0	535.9	535.7	535.7	535.7	535.8	535.8	535.9	535.8	535.8	535.7
150°	546.4	546.2	546.0	546.0	546.2	546.4	546.6	546.8	546.6	546.4	546.2
152.5°	555.9	555.7	555.5	555.6	556.1	556.5	557.0	557.4	557.0	556.5	556.1
155°	568.9	568.7	568.5	568.7	569.3	569.9	570.5	571.1	570.5	569.9	569.3
157.5°	580.0	580.0	580.0	580.1	580.5	580.9	581.2	581.6	581.2	580.9	580.5
160°	586.4	586.3	586.2	586.4	587.0	587.6	588.2	588.9	588.2	587.6	587.0
162.5°	592.3	592.2	592.1	592.3	592.9	593.5	594.1	594.7	594.1	593.5	592.9
165°	600.1	600.0	599.9	600.2	600.8	601.4	602.0	602.6	602.0	601.4	600.8
167.5°	605.8	605.7	605.6	605.9	606.5	607.2	607.8	608.4	607.8	607.2	606.5
170°	608.7	608.6	608.5	608.8	609.6	610.3	611.1	611.8	611.1	610.3	609.6
172.5°	611.2	611.0	610.9	611.1	611.8	612.5	613.2	613.9	613.2	612.5	611.8
175°	613.8	613.7	613.6	613.9	614.5	615.1	615.7	616.3	615.7	615.1	614.5
177.5°	615.4	615.3	615.2	615.4	615.9	616.4	616.9	617.4	616.9	616.4	615.9
180°	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3



TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	918.9	914.5	911.5	905.3	901.0	899.2	895.9	894.9	898.3	895.9	895.5
5°	891.5	880.4	871.6	862.7	853.1	847.1	837.8	836.3	833.9	830.5	829.8
7.5°	858.8	844.2	832.9	818.3	805.7	795.5	784.0	778.5	775.5	771.0	765.1
10°	836.7	819.4	804.1	789.5	773.8	761.1	749.6	740.7	735.0	729.6	727.3
12.5°	814.9	797.3	777.7	760.0	742.5	728.2	715.5	709.7	703.4	697.1	691.8
15°	781.0	757.6	736.2	715.8	700.8	685.5	673.3	664.8	655.2	652.6	642.2
17.5°	745.2	722.2	697.0	675.6	658.3	641.4	627.9	618.3	611.1	601.2	596.4
20°	722.8	695.5	671.0	651.4	632.2	612.3	598.4	590.4	583.5	575.4	571.6
22.5°	698.8	672.2	647.0	624.1	604.6	584.9	575.1	566.7	559.0	551.5	546.4
25°	663.7	636.8	610.4	586.5	566.2	552.0	540.5	530.9	526.7	519.4	514.0
27.5°	628.9	600.4	572.9	549.2	533.2	519.2	509.8	502.2	494.5	488.2	483.5
30°	606.5	577.3	547.4	528.7	511.7	498.4	488.0	480.7	474.9	469.2	465.7
32.5°	584.1	554.0	527.5	507.2	491.2	479.6	469.0	461.9	455.9	449.5	445.5
35°	548.2	517.5	496.0	476.1	460.3	449.6	442.3	432.3	427.4	422.7	418.5
37.5°	514.8	486.3	463.0	445.6	431.9	421.2	411.8	406.4	400.3	396.2	392.6
40°	490.3	464.1	443.1	424.6	414.7	402.8	393.9	387.1	382.4	377.1	373.2
42.5°	468.2	443.9	423.4	406.9	394.5	384.4	375.9	369.0	363.1	359.3	356.1
45°	437.0	412.7	392.8	377.5	366.0	356.4	347.6	344.1	336.4	331.8	330.3
47.5°	404.7	383.0	363.8	349.6	337.8	328.7	320.4	313.5	309.2	304.7	302.3
50°	382.8	362.1	344.1	330.3	318.8	308.8	301.1	296.5	290.7	286.6	283.5
52.5°	361.0	341.8	323.9	310.6	300.6	290.7	282.2	277.5	272.1	269.3	267.2
55°	329.9	309.6	294.3	281.1	270.8	261.7	253.6	248.9	245.5	242.9	242.1
57.5°	294.6	278.5	264.3	252.5	241.8	233.1	226.0	221.7	218.6	218.2	215.9
60°	271.6	257.0	244.0	231.4	222.1	214.1	207.9	203.0	199.9	199.4	198.7
62.5°	248.6	234.6	222.5	211.4	203.1	195.3	189.6	183.9	182.1	180.2	178.4
65°	214.4	201.8	191.8	183.0	174.2	167.6	161.9	158.4	154.2	151.9	147.7
67.5°	180.9	171.1	161.5	154.1	147.1	141.0	136.2	131.1	128.3	126.3	123.3
70°	158.9	151.2	141.6	133.5	128.2	123.1	119.3	113.5	111.6	110.1	108.6
72.5°	137.9	131.2	123.1	116.6	111.3	106.5	102.1	99.5	97.6	95.9	95.0
75°	108.6	102.0	95.1	90.5	86.7	82.9	80.6	78.7	77.9	77.5	75.9
77.5°	79.7	76.2	70.7	67.1	64.5	63.0	60.9	59.9	59.9	58.2	57.7
80°	61.0	59.1	54.4	52.9	51.0	49.5	48.4	46.5	44.5	43.7	42.6
82.5°	45.3	43.4	41.6	39.1	37.6	36.6	35.4	34.7	34.9	33.9	33.3
85°	24.1	22.2	21.5	21.1	20.3	21.1	20.7	20.3	20.0	19.6	20.0
87.5°	8.4	8.6	8.4	9.2	8.4	8.8	8.9	8.7	8.8	8.9	8.7
90°	3.7	4.4	5.2	5.9	6.6	7.3	7.8	8.3	8.8	9.3	9.8
92.5°	4.7	4.7	5.5	6.1	6.7	7.3	7.8	8.3	8.8	9.3	9.7
95°	24.8	22.7	18.9	15.0	11.2	7.3	7.8	8.3	8.8	9.3	9.6
97.5°	56.6	53.0	45.3	37.8	30.1	22.5	19.6	16.8	13.9	11.0	9.6
100°	77.6	77.9	78.3	78.7	79.1	79.5	64.3	49.3	34.1	19.0	11.2
102.5°	100.2	100.5	100.7	100.9	101.2	101.4	98.6	95.7	92.8	90.0	85.1
105°	135.9	136.1	136.1	136.1	136.1	136.1	136.1	136.1	136.1	136.1	136.1
107.5°	171.4	171.5	171.7	171.9	172.1	172.3	172.4	172.4	172.4	172.4	172.3
110°	195.5	195.6	195.8	196.0	196.2	196.4	196.1	195.8	195.5	195.2	195.1



TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	219.1	219.3	219.4	219.6	219.7	219.8	219.4	219.0	218.6	218.3	218.0
115°	254.2	254.5	254.6	254.7	254.8	254.9	254.5	254.1	253.7	253.3	252.8
117.5°	287.3	287.5	287.8	288.2	288.6	289.0	288.5	287.9	287.4	286.9	286.5
120°	308.9	309.0	309.3	309.6	309.9	310.2	310.0	309.8	309.6	309.4	309.0
122.5°	330.2	330.4	330.6	330.7	330.9	331.0	330.8	330.6	330.4	330.2	329.8
125°	361.4	361.8	361.8	361.8	361.8	361.8	361.4	361.0	360.6	360.2	359.8
127.5°	389.3	389.5	389.4	389.4	389.3	389.2	389.0	388.8	388.6	388.4	387.9
130°	406.8	407.1	407.2	407.3	407.4	407.5	407.2	406.9	406.6	406.3	405.9
132.5°	424.6	424.9	424.6	424.4	424.1	423.9	423.9	423.8	423.7	423.7	423.4
135°	449.7	449.9	449.7	449.5	449.3	449.1	448.9	448.7	448.5	448.3	447.9
137.5°	472.3	472.5	472.3	472.1	471.9	471.7	471.8	471.8	471.9	471.9	471.7
140°	485.9	486.0	485.9	485.8	485.7	485.6	485.8	486.0	486.3	486.5	486.3
142.5°	499.2	499.3	499.5	499.6	499.8	499.9	499.9	500.0	500.0	500.1	499.8
145°	519.4	519.5	519.5	519.5	519.5	519.5	519.6	519.7	519.8	519.9	519.6
147.5°	535.7	535.7	535.9	536.0	536.1	536.2	536.3	536.5	536.6	536.7	536.4
150°	546.0	546.0	546.2	546.4	546.6	546.8	547.0	547.2	547.4	547.6	547.3
152.5°	555.6	555.5	555.7	555.9	556.1	556.3	556.5	556.7	556.9	557.1	556.9
155°	568.7	568.5	568.7	568.9	569.1	569.3	569.6	569.9	570.2	570.5	570.2
157.5°	580.1	580.0	580.0	580.0	580.0	580.1	580.4	580.7	581.0	581.3	581.1
160°	586.4	586.2	586.3	586.4	586.5	586.6	587.0	587.4	587.8	588.2	588.0
162.5°	592.3	592.1	592.2	592.3	592.4	592.5	593.0	593.6	594.2	594.7	594.6
165°	600.2	599.9	600.0	600.1	600.2	600.3	600.9	601.6	602.2	602.8	602.7
167.5°	605.9	605.6	605.7	605.8	605.9	606.0	606.8	607.5	608.2	608.9	608.9
170°	608.8	608.5	608.6	608.7	608.8	608.9	609.8	610.6	611.5	612.3	612.2
172.5°	611.1	610.9	611.0	611.2	611.4	611.6	612.3	613.0	613.7	614.5	614.4
175°	613.9	613.6	613.7	613.8	613.9	614.0	614.8	615.6	616.4	617.2	617.2
177.5°	615.4	615.2	615.3	615.4	615.5	615.6	616.1	616.7	617.2	617.8	617.8
180°	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3



TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	895.2	891.8	890.9	892.1	890.9	891.8	895.2	895.5	895.9	898.3	894.9
5°	826.0	822.1	824.0	823.2	824.0	822.1	826.0	829.8	830.5	833.9	836.3
7.5°	765.0	760.2	755.2	756.8	755.2	760.2	765.0	765.1	771.0	775.5	778.5
10°	722.4	718.5	716.2	718.1	716.2	718.5	722.4	727.3	729.6	735.0	740.7
12.5°	686.4	684.2	682.2	681.4	682.2	684.2	686.4	691.8	697.1	703.4	709.7
15°	637.5	633.0	631.1	626.1	631.1	633.0	637.5	642.2	652.6	655.2	664.8
17.5°	592.5	591.0	586.0	583.9	586.0	591.0	592.5	596.4	601.2	611.1	618.3
20°	565.8	564.3	559.4	562.4	559.4	564.3	565.8	571.6	575.4	583.5	590.4
22.5°	543.7	540.4	538.8	537.9	538.8	540.4	543.7	546.4	551.5	559.0	566.7
25°	512.5	507.6	505.6	503.3	505.6	507.6	512.5	514.0	519.4	526.7	530.9
27.5°	481.4	478.7	476.2	475.5	476.2	478.7	481.4	483.5	488.2	494.5	502.2
30°	461.1	458.4	456.5	456.5	456.5	458.4	461.1	465.7	469.2	474.9	480.7
32.5°	443.0	440.9	439.0	438.7	439.0	440.9	443.0	445.5	449.5	455.9	461.9
35°	416.6	413.5	412.7	410.5	412.7	413.5	416.6	418.5	422.7	427.4	432.3
37.5°	389.2	386.7	386.6	386.4	386.6	386.7	389.2	392.6	396.2	400.3	406.4
40°	371.7	369.8	369.4	366.8	369.4	369.8	371.7	373.2	377.1	382.4	387.1
42.5°	353.0	352.0	350.7	349.5	350.7	352.0	353.0	356.1	359.3	363.1	369.0
45°	327.6	325.0	325.0	323.1	325.0	325.0	327.6	330.3	331.8	336.4	344.1
47.5°	301.3	299.3	299.5	297.5	299.5	299.3	301.3	302.3	304.7	309.2	313.5
50°	283.9	282.8	282.4	281.6	282.4	282.8	283.9	283.5	286.6	290.7	296.5
52.5°	266.4	265.9	267.3	265.6	267.3	265.9	266.4	267.2	269.3	272.1	277.5
55°	242.9	241.7	244.0	241.7	244.0	241.7	242.9	242.1	242.9	245.5	248.9
57.5°	215.7	214.7	216.7	215.6	216.7	214.7	215.7	215.9	218.2	218.6	221.7
60°	197.9	195.6	196.8	197.2	196.8	195.6	197.9	198.7	199.4	199.9	203.0
62.5°	176.7	175.4	176.2	174.5	176.2	175.4	176.7	178.4	180.2	182.1	183.9
65°	146.9	145.8	144.2	143.5	144.2	145.8	146.9	147.7	151.9	154.2	158.4
67.5°	123.4	120.7	120.6	121.2	120.6	120.7	123.4	123.3	126.3	128.3	131.1
70°	106.2	106.2	105.8	105.8	105.8	106.2	106.2	108.6	110.1	111.6	113.5
72.5°	94.3	94.0	93.3	93.0	93.3	94.0	94.3	95.0	95.9	97.6	99.5
75°	75.9	76.3	75.5	75.2	75.5	76.3	75.9	75.9	77.5	77.9	78.7
77.5°	56.0	54.4	55.3	54.4	55.3	54.4	56.0	57.7	58.2	59.9	59.9
80°	42.6	42.2	43.3	42.2	43.3	42.2	42.6	42.6	43.7	44.5	46.5
82.5°	33.7	33.3	33.8	33.0	33.8	33.3	33.7	33.3	33.9	34.9	34.7
85°	20.3	20.0	19.6	20.0	19.6	20.0	20.3	20.0	19.6	20.0	20.3
87.5°	9.1	8.8	8.9	9.0	8.9	8.8	9.1	8.7	8.9	8.8	8.7
90°	10.1	10.4	10.7	11.0	10.7	10.4	10.1	9.8	9.3	8.8	8.3
92.5°	9.8	10.0	10.1	10.2	10.1	10.0	9.8	9.7	9.3	8.8	8.3
95°	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.3	8.8	8.3
97.5°	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	11.0	13.9	16.8
100°	10.8	10.4	10.0	9.6	10.0	10.4	10.8	11.2	19.0	34.1	49.3
102.5°	78.2	71.3	64.3	57.5	64.3	71.3	78.2	85.1	90.0	92.8	95.7
105°	136.0	135.9	135.8	135.7	135.8	135.9	136.0	136.1	136.1	136.1	136.1
107.5°	172.0	171.7	171.4	171.1	171.4	171.7	172.0	172.3	172.4	172.4	172.4
110°	195.2	195.3	195.4	195.5	195.4	195.3	195.2	195.1	195.2	195.5	195.8



TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	217.9	217.7	217.6	217.4	217.6	217.7	217.9	218.0	218.3	218.6	219.0
115°	252.2	251.6	251.0	250.3	251.0	251.6	252.2	252.8	253.3	253.7	254.1
117.5°	286.2	286.0	285.7	285.5	285.7	286.0	286.2	286.5	286.9	287.4	287.9
120°	308.5	308.0	307.5	307.0	307.5	308.0	308.5	309.0	309.4	309.6	309.8
122.5°	329.2	328.6	328.1	327.5	328.1	328.6	329.2	329.8	330.2	330.4	330.6
125°	359.5	359.2	358.9	358.6	358.9	359.2	359.5	359.8	360.2	360.6	361.0
127.5°	387.1	386.4	385.6	384.9	385.6	386.4	387.1	387.9	388.4	388.6	388.8
130°	405.4	404.9	404.3	403.8	404.3	404.9	405.4	405.9	406.3	406.6	406.9
132.5°	422.9	422.4	421.9	421.4	421.9	422.4	422.9	423.4	423.7	423.7	423.8
135°	447.3	446.7	446.1	445.5	446.1	446.7	447.3	447.9	448.3	448.5	448.7
137.5°	471.1	470.6	470.1	469.6	470.1	470.6	471.1	471.7	471.9	471.9	471.8
140°	485.6	485.0	484.4	483.8	484.4	485.0	485.6	486.3	486.5	486.3	486.0
142.5°	499.2	498.6	498.0	497.4	498.0	498.6	499.2	499.8	500.1	500.0	500.0
145°	519.0	518.4	517.8	517.2	517.8	518.4	519.0	519.6	519.9	519.8	519.7
147.5°	535.7	535.0	534.2	533.5	534.2	535.0	535.7	536.4	536.7	536.6	536.5
150°	546.5	545.7	544.9	544.1	544.9	545.7	546.5	547.3	547.6	547.4	547.2
152.5°	556.1	555.4	554.7	554.0	554.7	555.4	556.1	556.9	557.1	556.9	556.7
155°	569.4	568.6	567.7	566.9	567.7	568.6	569.4	570.2	570.5	570.2	569.9
157.5°	580.3	579.5	578.7	577.8	578.7	579.5	580.3	581.1	581.3	581.0	580.7
160°	587.2	586.4	585.6	584.8	585.6	586.4	587.2	588.0	588.2	587.8	587.4
162.5°	593.7	592.8	591.9	591.0	591.9	592.8	593.7	594.6	594.7	594.2	593.6
165°	601.9	601.0	600.2	599.4	600.2	601.0	601.9	602.7	602.8	602.2	601.6
167.5°	607.9	607.0	606.1	605.2	606.1	607.0	607.9	608.9	608.9	608.2	607.5
170°	611.3	610.4	609.5	608.5	609.5	610.4	611.3	612.2	612.3	611.5	610.6
172.5°	613.5	612.6	611.7	610.8	611.7	612.6	613.5	614.4	614.5	613.7	613.0
175°	616.3	615.4	614.5	613.6	614.5	615.4	616.3	617.2	617.2	616.4	615.6
177.5°	617.1	616.5	615.8	615.2	615.8	616.5	617.1	617.8	617.8	617.2	616.7
180°	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3



TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	895.9	899.2	901.0	905.3	911.5	914.5	918.9	921.9	926.2	931.4	935.7
5°	837.8	847.1	853.1	862.7	871.6	880.4	891.5	899.6	910.3	922.6	932.2
7.5°	784.0	795.5	805.7	818.3	832.9	844.2	858.8	873.5	890.4	907.8	924.2
10°	749.6	761.1	773.8	789.5	804.1	819.4	836.7	853.9	875.0	894.6	916.9
12.5°	715.5	728.2	742.5	760.0	777.7	797.3	814.9	834.2	857.0	882.3	906.2
15°	673.3	685.5	700.8	715.8	736.2	757.6	781.0	806.8	832.0	860.5	890.0
17.5°	627.9	641.4	658.3	675.6	697.0	722.2	745.2	773.3	801.7	834.9	869.6
20°	598.4	612.3	632.2	651.4	671.0	695.5	722.8	751.5	781.8	816.7	855.5
22.5°	575.1	584.9	604.6	624.1	647.0	672.2	698.8	728.8	761.8	798.0	838.6
25°	540.5	552.0	566.2	586.5	610.4	636.8	663.7	695.5	731.5	768.4	811.7
27.5°	509.8	519.2	533.2	549.2	572.9	600.4	628.9	662.2	699.1	736.6	782.2
30°	488.0	498.4	511.7	528.7	547.4	577.3	606.5	639.1	676.7	715.5	762.2
32.5°	469.0	479.6	491.2	507.2	527.5	554.0	584.1	616.1	654.3	694.3	739.8
35°	442.3	449.6	460.3	476.1	496.0	517.5	548.2	582.0	619.1	660.6	706.2
37.5°	411.8	421.2	431.9	445.6	463.0	486.3	514.8	549.0	583.5	623.2	664.8
40°	393.9	402.8	414.7	424.6	443.1	464.1	490.3	525.9	560.5	597.6	635.6
42.5°	375.9	384.4	394.5	406.9	423.4	443.9	468.2	501.4	538.4	573.4	605.3
45°	347.6	356.4	366.0	377.5	392.8	412.7	437.0	467.3	499.5	531.7	555.8
47.5°	320.4	328.7	337.8	349.6	363.8	383.0	404.7	431.4	462.7	490.1	507.4
50°	301.1	308.8	318.8	330.3	344.1	362.1	382.8	409.3	435.5	460.3	476.1
52.5°	282.2	290.7	300.6	310.6	323.9	341.8	361.0	383.8	408.7	429.0	442.0
55°	253.6	261.7	270.8	281.1	294.3	309.6	329.9	347.9	367.5	384.8	392.4
57.5°	226.0	233.1	241.8	252.5	264.3	278.5	294.6	311.9	325.8	338.0	346.7
60°	207.9	214.1	222.1	231.4	244.0	257.0	271.6	287.7	298.4	308.8	316.9
62.5°	189.6	195.3	203.1	211.4	222.5	234.6	248.6	261.7	272.1	279.0	288.3
65°	161.9	167.6	174.2	183.0	191.8	201.8	214.4	224.0	231.4	239.0	244.8
67.5°	136.2	141.0	147.1	154.1	161.5	171.1	180.9	188.8	193.9	198.4	205.4
70°	119.3	123.1	128.2	133.5	141.6	151.2	158.9	164.9	168.4	173.0	181.5
72.5°	102.1	106.5	111.3	116.6	123.1	131.2	137.9	144.1	146.3	150.0	155.3
75°	80.6	82.9	86.7	90.5	95.1	102.0	108.6	110.1	112.0	115.1	119.0
77.5°	60.9	63.0	64.5	67.1	70.7	76.2	79.7	82.0	82.5	83.6	87.4
80°	48.4	49.5	51.0	52.9	54.4	59.1	61.0	63.3	64.0	65.2	67.2
82.5°	35.4	36.6	37.6	39.1	41.6	43.4	45.3	47.7	47.8	48.7	49.0
85°	20.7	21.1	20.3	21.1	21.5	22.2	24.1	26.1	25.8	25.3	26.5
87.5°	8.9	8.8	8.4	9.2	8.4	8.6	8.4	8.6	9.0	9.5	9.9
90°	7.8	7.3	6.6	5.9	5.2	4.4	3.7	2.9	2.1	1.3	0.5
92.5°	7.8	7.3	6.7	6.1	5.5	4.7	4.7	5.4	5.9	6.5	7.1
95°	7.8	7.3	11.2	15.0	18.9	22.7	24.8	25.1	25.4	25.8	26.1
97.5°	19.6	22.5	30.1	37.8	45.3	53.0	56.6	56.0	55.4	54.9	54.3
100°	64.3	79.5	79.1	78.7	78.3	77.9	77.6	77.3	77.0	76.6	76.2
102.5°	98.6	101.4	101.2	100.9	100.7	100.5	100.2	99.8	99.4	99.0	98.6
105°	136.1	136.1	136.1	136.1	136.1	136.1	135.9	135.5	135.1	134.7	134.3
107.5°	172.4	172.3	172.1	171.9	171.7	171.5	171.4	171.4	171.4	171.4	171.4
110°	196.1	196.4	196.2	196.0	195.8	195.6	195.5	195.5	195.5	195.5	195.5



TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	219.4	219.8	219.7	219.6	219.4	219.3	219.1	218.9	218.6	218.4	218.2
115°	254.5	254.9	254.8	254.7	254.6	254.5	254.2	253.7	253.2	252.7	252.2
117.5°	288.5	289.0	288.6	288.2	287.8	287.5	287.3	287.3	287.3	287.3	287.4
120°	310.0	310.2	309.9	309.6	309.3	309.0	308.9	309.0	309.1	309.2	309.3
122.5°	330.8	331.0	330.9	330.7	330.6	330.4	330.2	329.8	329.4	329.0	328.7
125°	361.4	361.8	361.8	361.8	361.8	361.8	361.4	360.7	360.0	359.3	358.6
127.5°	389.0	389.2	389.3	389.4	389.4	389.5	389.3	388.8	388.3	387.8	387.2
130°	407.2	407.5	407.4	407.3	407.2	407.1	406.8	406.3	405.8	405.3	404.8
132.5°	423.9	423.9	424.1	424.4	424.6	424.9	424.6	424.0	423.5	422.9	422.3
135°	448.9	449.1	449.3	449.5	449.7	449.9	449.7	449.1	448.5	447.9	447.3
137.5°	471.8	471.7	471.9	472.1	472.3	472.5	472.3	471.8	471.2	470.7	470.2
140°	485.8	485.6	485.7	485.8	485.9	486.0	485.9	485.7	485.5	485.3	485.1
142.5°	499.9	499.9	499.8	499.6	499.5	499.3	499.2	499.1	499.0	498.9	498.7
145°	519.6	519.5	519.5	519.5	519.5	519.5	519.4	519.2	519.0	518.8	518.6
147.5°	536.3	536.2	536.1	536.0	535.9	535.7	535.7	535.7	535.8	535.8	535.9
150°	547.0	546.8	546.6	546.4	546.2	546.0	546.0	546.2	546.4	546.6	546.8
152.5°	556.5	556.3	556.1	555.9	555.7	555.5	555.6	556.1	556.5	557.0	557.4
155°	569.6	569.3	569.1	568.9	568.7	568.5	568.7	569.3	569.9	570.5	571.1
157.5°	580.4	580.1	580.0	580.0	580.0	580.0	580.1	580.5	580.9	581.2	581.6
160°	587.0	586.6	586.5	586.4	586.3	586.2	586.4	587.0	587.6	588.2	588.9
162.5°	593.0	592.5	592.4	592.3	592.2	592.1	592.3	592.9	593.5	594.1	594.7
165°	600.9	600.3	600.2	600.1	600.0	599.9	600.2	600.8	601.4	602.0	602.6
167.5°	606.8	606.0	605.9	605.8	605.7	605.6	605.9	606.5	607.2	607.8	608.4
170°	609.8	608.9	608.8	608.7	608.6	608.5	608.8	609.6	610.3	611.1	611.8
172.5°	612.3	611.6	611.4	611.2	611.0	610.9	611.1	611.8	612.5	613.2	613.9
175°	614.8	614.0	613.9	613.8	613.7	613.6	613.9	614.5	615.1	615.7	616.3
177.5°	616.1	615.6	615.5	615.4	615.3	615.2	615.4	615.9	616.4	616.9	617.4
180°	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3



TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	939.1	941.9	945.8	950.5	954.1	958.2	960.3	960.3	962.1	966.1	971.3
5°	941.8	951.8	961.4	973.6	983.2	994.3	1002.8	1010.9	1018.1	1027.3	1036.9
7.5°	941.0	957.6	974.8	994.2	1015.5	1032.5	1049.9	1063.6	1077.0	1094.7	1108.6
10°	938.0	959.5	982.8	1007.3	1034.2	1057.6	1078.7	1097.9	1116.3	1135.5	1152.8
12.5°	932.4	959.8	988.4	1017.8	1051.8	1078.5	1105.7	1126.2	1147.6	1168.6	1189.9
15°	924.1	956.3	990.9	1032.0	1073.4	1103.3	1130.1	1156.6	1176.6	1200.3	1220.7
17.5°	907.1	948.6	992.0	1036.8	1076.6	1111.5	1139.5	1164.8	1186.0	1212.1	1239.8
20°	896.9	941.8	987.0	1035.0	1073.0	1108.6	1135.9	1162.0	1188.4	1222.6	1256.4
22.5°	882.8	930.7	978.8	1024.3	1064.4	1098.8	1127.0	1158.9	1193.7	1232.4	1273.2
25°	860.5	910.0	957.6	1000.9	1040.0	1075.3	1113.7	1156.6	1198.8	1249.8	1308.5
27.5°	832.1	879.9	922.3	968.1	1007.0	1051.9	1099.7	1146.3	1207.2	1277.4	1350.7
30°	810.9	856.3	896.6	939.9	984.0	1033.5	1087.2	1142.1	1214.6	1297.0	1384.1
32.5°	786.4	827.4	867.4	909.2	960.1	1014.4	1071.6	1138.6	1225.3	1319.1	1409.3
35°	743.9	780.6	819.4	865.9	919.9	979.0	1051.9	1133.6	1238.3	1339.2	1420.2
37.5°	699.2	728.2	767.2	816.1	875.0	943.4	1026.1	1125.4	1232.9	1323.5	1358.0
40°	664.8	692.1	733.1	784.5	842.8	917.7	1010.5	1112.5	1220.7	1283.5	1280.9
42.5°	630.8	658.3	697.8	749.5	810.3	894.0	989.6	1095.6	1186.9	1210.8	1160.9
45°	578.5	604.2	643.0	695.1	760.3	848.2	948.7	1050.4	1108.6	1070.0	971.0
47.5°	525.2	550.2	586.1	637.2	708.4	800.4	895.4	978.9	987.0	903.8	785.1
50°	490.3	513.6	547.9	602.3	671.4	761.1	852.8	918.4	898.1	796.4	674.0
52.5°	456.2	478.7	510.7	562.1	632.7	720.6	802.4	853.9	806.9	698.8	588.8
55°	405.9	427.4	459.6	506.8	570.8	651.4	723.2	741.9	672.9	563.9	474.9
57.5°	358.1	373.8	405.7	447.4	509.2	580.2	631.6	628.2	552.0	453.9	390.1
60°	326.5	340.6	370.9	409.3	468.0	531.7	567.7	552.4	475.3	394.4	333.0
62.5°	297.0	310.2	335.7	370.9	421.4	476.8	503.0	481.8	409.0	337.9	289.1
65°	252.5	262.1	282.4	315.0	354.5	392.8	416.3	385.2	320.7	267.0	230.1
67.5°	210.8	219.0	237.1	260.5	287.8	314.3	323.8	294.6	244.5	208.3	182.4
70°	183.8	191.5	203.7	225.6	243.6	262.4	267.0	241.0	199.1	171.5	155.3
72.5°	157.9	165.0	175.8	191.2	203.7	214.5	216.7	192.4	160.5	141.4	129.0
75°	120.5	126.6	133.5	139.3	147.3	149.3	148.5	129.7	112.4	99.8	92.8
77.5°	88.6	91.1	95.3	97.6	98.0	97.9	93.9	82.0	73.1	67.9	65.0
80°	68.3	70.2	71.4	72.1	72.5	68.7	64.4	57.2	54.1	51.0	47.6
82.5°	49.6	50.9	52.0	52.2	50.1	46.9	42.9	39.4	37.2	35.6	34.3
85°	26.9	27.3	26.9	24.9	22.2	21.1	20.3	19.6	19.2	18.8	18.8
87.5°	9.8	9.0	7.7	8.1	8.3	8.1	8.3	8.1	7.9	8.0	8.1
90°	1.3	2.1	2.9	3.7	4.4	5.2	5.9	6.6	7.3	7.8	8.3
92.5°	6.5	5.9	5.4	4.7	4.7	5.5	6.1	6.7	7.3	7.8	8.3
95°	25.8	25.4	25.1	24.8	22.7	18.9	15.0	11.2	7.3	7.8	8.3
97.5°	54.9	55.4	56.0	56.6	53.0	45.3	37.8	30.1	22.5	19.6	16.8
100°	76.6	77.0	77.3	77.6	77.9	78.3	78.7	79.1	79.5	64.3	49.3
102.5°	99.0	99.4	99.8	100.2	100.5	100.7	100.9	101.2	101.4	98.6	95.7
105°	134.7	135.1	135.5	135.9	136.1	136.1	136.1	136.1	136.1	136.1	136.1
107.5°	171.4	171.4	171.4	171.4	171.5	171.7	171.9	172.1	172.3	172.4	172.4
110°	195.5	195.5	195.5	195.5	195.6	195.8	196.0	196.2	196.4	196.1	195.8





TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	218.4	218.6	218.9	219.1	219.3	219.4	219.6	219.7	219.8	219.4	219.0
115°	252.7	253.2	253.7	254.2	254.5	254.6	254.7	254.8	254.9	254.5	254.1
117.5°	287.3	287.3	287.3	287.3	287.5	287.8	288.2	288.6	289.0	288.5	287.9
120°	309.2	309.1	309.0	308.9	309.0	309.3	309.6	309.9	310.2	310.0	309.8
122.5°	329.0	329.4	329.8	330.2	330.4	330.6	330.7	330.9	331.0	330.8	330.6
125°	359.3	360.0	360.7	361.4	361.8	361.8	361.8	361.8	361.8	361.4	361.0
127.5°	387.8	388.3	388.8	389.3	389.5	389.4	389.4	389.3	389.2	389.0	388.8
130°	405.3	405.8	406.3	406.8	407.1	407.2	407.3	407.4	407.5	407.2	406.9
132.5°	422.9	423.5	424.0	424.6	424.9	424.6	424.4	424.1	423.9	423.9	423.8
135°	447.9	448.5	449.1	449.7	449.9	449.7	449.5	449.3	449.1	448.9	448.7
137.5°	470.7	471.2	471.8	472.3	472.5	472.3	472.1	471.9	471.7	471.8	471.8
140°	485.3	485.5	485.7	485.9	486.0	485.9	485.8	485.7	485.6	485.8	486.0
142.5°	498.9	499.0	499.1	499.2	499.3	499.5	499.6	499.8	499.9	499.9	500.0
145°	518.8	519.0	519.2	519.4	519.5	519.5	519.5	519.5	519.5	519.6	519.7
147.5°	535.8	535.8	535.7	535.7	535.7	535.9	536.0	536.1	536.2	536.3	536.5
150°	546.6	546.4	546.2	546.0	546.0	546.2	546.4	546.6	546.8	547.0	547.2
152.5°	557.0	556.5	556.1	555.6	555.5	555.7	555.9	556.1	556.3	556.5	556.7
155°	570.5	569.9	569.3	568.7	568.5	568.7	568.9	569.1	569.3	569.6	569.9
157.5°	581.2	580.9	580.5	580.1	580.0	580.0	580.0	580.0	580.1	580.4	580.7
160°	588.2	587.6	587.0	586.4	586.2	586.3	586.4	586.5	586.6	587.0	587.4
162.5°	594.1	593.5	592.9	592.3	592.1	592.2	592.3	592.4	592.5	593.0	593.6
165°	602.0	601.4	600.8	600.2	599.9	600.0	600.1	600.2	600.3	600.9	601.6
167.5°	607.8	607.2	606.5	605.9	605.6	605.7	605.8	605.9	606.0	606.8	607.5
170°	611.1	610.3	609.6	608.8	608.5	608.6	608.7	608.8	608.9	609.8	610.6
172.5°	613.2	612.5	611.8	611.1	610.9	611.0	611.2	611.4	611.6	612.3	613.0
175°	615.7	615.1	614.5	613.9	613.6	613.7	613.8	613.9	614.0	614.8	615.6
177.5°	616.9	616.4	615.9	615.4	615.2	615.3	615.4	615.5	615.6	616.1	616.7
180°	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3



TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	975.3	975.3	980.6	980.2	983.6	982.4	983.0
5°	1048.4	1054.9	1060.7	1064.5	1070.3	1071.9	1071.1
7.5°	1124.3	1138.7	1145.8	1155.5	1157.2	1162.3	1161.7
10°	1171.1	1185.4	1196.1	1204.6	1208.8	1214.2	1214.6
12.5°	1208.0	1220.0	1229.6	1237.4	1242.5	1244.3	1245.3
15°	1236.8	1250.2	1261.3	1272.4	1279.0	1283.9	1286.7
17.5°	1265.8	1286.5	1306.2	1321.3	1330.3	1338.0	1337.9
20°	1288.2	1312.0	1336.6	1353.8	1371.4	1379.1	1380.3
22.5°	1312.1	1348.5	1380.1	1406.8	1430.1	1438.0	1441.0
25°	1361.8	1409.4	1458.1	1495.7	1522.6	1538.3	1540.7
27.5°	1421.9	1486.3	1537.5	1572.3	1594.6	1606.2	1608.7
30°	1464.3	1523.7	1569.7	1595.9	1606.2	1607.7	1601.9
32.5°	1483.3	1527.7	1546.1	1544.6	1524.3	1510.8	1505.6
35°	1460.1	1450.9	1405.9	1352.2	1311.2	1285.2	1278.2
37.5°	1328.7	1249.3	1166.7	1085.6	1042.4	1020.5	982.7
40°	1199.2	1086.0	1000.1	931.8	883.1	843.9	834.8
42.5°	1053.1	936.2	850.3	791.8	753.0	726.1	714.5
45°	846.3	745.8	674.8	629.9	600.0	580.4	571.6
47.5°	676.8	599.1	547.3	514.1	491.3	474.3	469.6
50°	583.9	521.7	478.0	450.0	432.7	419.7	414.3
52.5°	507.2	457.0	423.3	400.3	384.0	375.8	371.3
55°	418.5	375.2	351.0	332.5	323.4	316.9	313.8
57.5°	342.2	310.9	293.3	280.5	272.1	267.9	266.4
60°	299.6	275.1	258.9	248.9	243.2	237.8	236.3
62.5°	261.9	242.6	230.0	221.4	215.6	213.3	212.4
65°	211.0	198.3	189.1	183.8	179.2	178.3	178.0
67.5°	167.7	160.3	155.4	149.9	148.2	145.5	145.0
70°	143.5	138.5	132.7	130.8	128.9	126.2	126.6
72.5°	121.7	116.7	112.8	110.3	109.6	108.5	109.4
75°	89.0	87.5	85.9	84.0	83.2	83.2	82.9
77.5°	63.5	62.2	60.5	59.4	59.2	57.6	58.2
80°	46.0	44.1	43.3	43.7	42.6	42.2	42.2
82.5°	34.0	33.3	32.6	32.7	32.4	32.1	32.4
85°	18.8	18.4	18.4	18.1	18.1	17.7	17.7
87.5°	8.5	8.9	8.4	8.2	8.2	8.6	9.0
90°	8.8	9.3	9.8	10.1	10.4	10.7	11.0
92.5°	8.8	9.3	9.7	9.8	10.0	10.1	10.2
95°	8.8	9.3	9.6	9.6	9.6	9.6	9.6
97.5°	13.9	11.0	9.6	9.6	9.6	9.6	9.6
100°	34.1	19.0	11.2	10.8	10.4	10.0	9.6
102.5°	92.8	90.0	85.1	78.2	71.3	64.3	57.5
105°	136.1	136.1	136.1	136.0	135.9	135.8	135.7
107.5°	172.4	172.4	172.3	172.0	171.7	171.4	171.1
110°	195.5	195.2	195.1	195.2	195.3	195.4	195.5



TEST NUMBER: P333660-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	218.6	218.3	218.0	217.9	217.7	217.6	217.4
115°	253.7	253.3	252.8	252.2	251.6	251.0	250.3
117.5°	287.4	286.9	286.5	286.2	286.0	285.7	285.5
120°	309.6	309.4	309.0	308.5	308.0	307.5	307.0
122.5°	330.4	330.2	329.8	329.2	328.6	328.1	327.5
125°	360.6	360.2	359.8	359.5	359.2	358.9	358.6
127.5°	388.6	388.4	387.9	387.1	386.4	385.6	384.9
130°	406.6	406.3	405.9	405.4	404.9	404.3	403.8
132.5°	423.7	423.7	423.4	422.9	422.4	421.9	421.4
135°	448.5	448.3	447.9	447.3	446.7	446.1	445.5
137.5°	471.9	471.9	471.7	471.1	470.6	470.1	469.6
140°	486.3	486.5	486.3	485.6	485.0	484.4	483.8
142.5°	500.0	500.1	499.8	499.2	498.6	498.0	497.4
145°	519.8	519.9	519.6	519.0	518.4	517.8	517.2
147.5°	536.6	536.7	536.4	535.7	535.0	534.2	533.5
150°	547.4	547.6	547.3	546.5	545.7	544.9	544.1
152.5°	556.9	557.1	556.9	556.1	555.4	554.7	554.0
155°	570.2	570.5	570.2	569.4	568.6	567.7	566.9
157.5°	581.0	581.3	581.1	580.3	579.5	578.7	577.8
160°	587.8	588.2	588.0	587.2	586.4	585.6	584.8
162.5°	594.2	594.7	594.6	593.7	592.8	591.9	591.0
165°	602.2	602.8	602.7	601.9	601.0	600.2	599.4
167.5°	608.2	608.9	608.9	607.9	607.0	606.1	605.2
170°	611.5	612.3	612.2	611.3	610.4	609.5	608.5
172.5°	613.7	614.5	614.4	613.5	612.6	611.7	610.8
175°	616.4	617.2	617.2	616.3	615.4	614.5	613.6
177.5°	617.2	617.8	617.8	617.1	616.5	615.8	615.2
180°	616.3	616.3	616.3	616.3	616.3	616.3	616.3

(END OF REPORT)