

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333682-840

Luminaire Tested: **S125RDIW-S850D470U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333682-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S850D470U840-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 470 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5174.3 lumens  
Efficiency: N/A  
Efficacy: 137.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333682-840

CATALOG NUMBER: S125RDIW-S850D470U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333682-840

CATALOG NUMBER: S125RDIW-S850D470U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	68	68	68	63
1	101	97	93	89	95	91	88	85	80	78	75	70	68	67	61	60	58	54
2	92	85	79	74	86	80	74	70	71	66	63	62	59	56	54	52	50	46
3	84	75	67	62	79	71	64	59	62	57	53	55	51	48	48	45	43	39
4	77	66	58	52	72	63	56	50	56	50	46	49	45	41	43	40	37	34
5	71	59	51	45	67	56	49	43	50	44	39	44	40	36	39	35	32	29
6	66	53	45	39	61	51	43	38	45	39	35	40	35	32	35	32	29	26
7	61	48	40	35	57	46	39	33	41	35	31	37	32	28	32	28	25	23
8	57	44	36	31	53	42	35	30	38	32	27	34	29	25	30	26	23	21
9	53	40	33	28	50	38	31	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8969	8969	8969
5°	8989	8887	8941
10°	8921	8804	8804
15°	8815	8625	8555
20°	8678	8376	8276
25°	8521	8131	7952
30°	8322	7845	7594
35°	8121	7550	7194
40°	7932	7242	6800
45°	7701	6898	6370
50°	7471	6523	5923
55°	7203	6164	5444
60°	6935	5730	4930
65°	6619	5225	4343
70°	6258	4594	3743
75°	5759	3873	3114
80°	5069	3042	2615
85°	4276	2482	2334



TEST NUMBER: P333682-840

CATALOG NUMBER: S125RDIW-S850D470U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	130.6	2.5
10°-20°	364.9	7.1
20°-30°	529.2	10.2
30°-40°	603.1	11.7
40°-50°	587.8	11.4
50°-60°	494.8	9.6
60°-70°	346.9	6.7
70°-80°	178.3	3.4
80°-90°	46.3	0.9
90°-100°	22.4	0.4
100°-110°	138.0	2.7
110°-120°	250.3	4.8
120°-130°	321.3	6.2
130°-140°	345.6	6.7
140°-150°	324.4	6.3
150°-160°	262.4	5.1
160°-170°	169.7	3.3
170°-180°	58.5	1.1
0°-30°	1024.6	19.8
0°-40°	1627.7	31.5
0°-60°	2710.4	52.4
0°-90°	3281.8	63.4
90°-120°	410.7	7.9
90°-150°	1401.9	27.1
90°-180°	1893.0	36.6
0°-180°	5174.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1386	1382	1371	1381	1379	131
15°	1318	1311	1290	1289	1280	371
25°	1196	1179	1141	1128	1116	550
35°	1030	1004	958	928	912	645
45°	843	811	755	715	697	650
55°	640	605	547	502	484	572
65°	433	396	342	301	284	429
75°	231	199	155	133	125	244
85°	58	40	34	32	32	65
90°	0	4	7	10	11	4
95°	26	24	7	9	10	33
105°	134	136	136	136	136	142
115°	252	254	255	253	250	250
125°	359	362	362	360	359	320
135°	447	450	449	448	446	345
145°	519	519	520	520	517	324
155°	571	569	569	570	567	263
165°	603	600	600	603	599	170
175°	616	614	614	617	614	59
180°	616	616	616	616	616	



TEST NUMBER: P333682-840

CATALOG NUMBER: S125RDIW-S850D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1391.1	1390.6	1390.0	1389.5	1388.9	1387.7	1385.8	1383.9	1382.1	1380.2	1382.1
5°	1386.5	1385.6	1384.6	1383.7	1382.8	1381.1	1378.5	1375.9	1373.3	1370.8	1373.1
7.5°	1372.9	1372.0	1371.1	1370.2	1369.4	1367.4	1364.3	1361.2	1358.2	1355.0	1356.7
10°	1360.3	1359.6	1358.9	1358.2	1357.5	1355.5	1352.3	1349.0	1345.7	1342.5	1343.1
12.5°	1346.0	1345.1	1344.2	1343.4	1342.5	1339.9	1335.4	1331.1	1326.8	1322.3	1322.8
15°	1318.4	1317.0	1315.6	1314.1	1312.7	1309.6	1304.7	1299.8	1294.9	1290.0	1289.8
17.5°	1287.1	1285.0	1282.8	1280.7	1278.5	1274.3	1268.2	1262.0	1255.9	1249.7	1248.6
20°	1262.7	1260.4	1258.1	1255.8	1253.4	1248.5	1241.1	1233.7	1226.2	1218.7	1217.6
22.5°	1235.9	1233.6	1231.2	1228.9	1226.6	1221.5	1213.7	1205.9	1198.0	1190.2	1187.9
25°	1195.7	1192.1	1188.6	1185.2	1181.6	1175.6	1167.0	1158.3	1149.7	1141.1	1138.1
27.5°	1149.5	1145.3	1141.0	1136.8	1132.6	1125.8	1116.6	1107.3	1098.1	1088.8	1084.6
30°	1115.9	1111.5	1107.1	1102.7	1098.2	1091.1	1081.4	1071.6	1061.8	1052.0	1046.6
32.5°	1083.2	1078.0	1072.9	1067.7	1062.5	1054.9	1045.0	1035.0	1025.0	1015.0	1009.2
35°	1030.0	1024.3	1018.8	1013.1	1007.5	999.5	989.1	978.6	968.1	957.6	950.8
37.5°	977.7	970.9	964.1	957.3	950.5	941.7	930.9	920.0	909.2	898.4	890.3
40°	940.8	933.8	926.8	919.8	912.8	903.7	892.5	881.3	870.2	859.0	850.1
42.5°	902.2	895.0	887.9	880.6	873.4	864.1	852.5	841.0	829.4	817.9	809.4
45°	843.2	836.5	829.7	822.9	816.2	806.4	793.6	780.8	768.0	755.2	745.8
47.5°	782.2	775.1	767.9	760.8	753.7	743.7	730.7	717.8	704.9	692.0	682.4
50°	743.6	735.9	728.2	720.5	712.9	702.4	689.0	675.8	662.5	649.2	639.4
52.5°	701.7	693.8	685.9	678.0	670.1	659.9	647.4	634.9	622.3	609.8	599.3
55°	639.7	632.3	624.9	617.4	610.0	599.7	586.6	573.6	560.6	547.4	536.9
57.5°	577.2	569.3	561.3	553.3	545.4	535.1	522.5	509.9	497.4	484.7	474.5
60°	536.9	528.9	520.7	512.5	504.3	494.0	481.4	468.8	456.3	443.6	433.4
62.5°	494.2	486.5	478.7	470.8	463.0	452.8	440.0	427.3	414.4	401.7	392.2
65°	433.1	425.3	417.3	409.4	401.4	391.3	379.0	366.6	354.3	341.9	332.5
67.5°	372.5	364.6	356.7	348.8	340.8	330.9	319.1	307.3	295.5	283.6	275.1
70°	331.4	323.5	315.6	307.6	299.7	289.9	278.3	266.6	255.0	243.3	236.1
72.5°	291.1	283.4	275.7	267.9	260.2	250.9	239.9	229.0	218.1	207.2	200.6
75°	230.8	223.8	216.7	209.7	202.8	194.4	184.6	174.8	165.0	155.2	150.1
77.5°	170.8	165.1	159.6	154.0	148.3	141.7	133.8	126.0	118.2	110.4	106.7
80°	136.3	130.8	125.1	119.6	114.0	108.0	101.4	94.8	88.4	81.8	79.7
82.5°	102.8	97.8	92.7	87.7	82.6	77.9	73.4	69.0	64.4	60.0	59.0
85°	57.7	53.5	49.3	45.1	40.9	38.2	37.1	35.9	34.7	33.5	33.3
87.5°	19.4	18.3	17.1	16.0	14.8	14.2	14.1	14.1	14.1	14.0	14.1
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.2	5.9	6.6	7.3	7.8
92.5°	7.1	6.5	5.9	5.4	4.7	4.7	5.5	6.1	6.7	7.3	7.8
95°	26.1	25.8	25.4	25.1	24.8	22.7	18.9	15.0	11.2	7.3	7.8
97.5°	54.3	54.9	55.4	56.0	56.6	53.0	45.3	37.8	30.1	22.5	19.6
100°	76.2	76.6	77.0	77.3	77.6	77.9	78.3	78.7	79.1	79.5	64.3
102.5°	98.6	99.0	99.4	99.8	100.2	100.5	100.7	100.9	101.2	101.4	98.6
105°	134.3	134.7	135.1	135.5	135.9	136.1	136.1	136.1	136.1	136.1	136.1
107.5°	171.4	171.4	171.4	171.4	171.4	171.5	171.7	171.9	172.1	172.3	172.4
110°	195.5	195.5	195.5	195.5	195.5	195.6	195.8	196.0	196.2	196.4	196.1



TEST NUMBER: P333682-840

CATALOG NUMBER: S125RDIW-S850D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	218.2	218.4	218.6	218.9	219.1	219.3	219.4	219.6	219.7	219.8	219.4
115°	252.2	252.7	253.2	253.7	254.2	254.5	254.6	254.7	254.8	254.9	254.5
117.5°	287.4	287.3	287.3	287.3	287.3	287.5	287.8	288.2	288.6	289.0	288.5
120°	309.3	309.2	309.1	309.0	308.9	309.0	309.3	309.6	309.9	310.2	310.0
122.5°	328.7	329.0	329.4	329.8	330.2	330.4	330.6	330.7	330.9	331.0	330.8
125°	358.6	359.3	360.0	360.7	361.4	361.8	361.8	361.8	361.8	361.8	361.4
127.5°	387.2	387.8	388.3	388.8	389.3	389.5	389.4	389.4	389.3	389.2	389.0
130°	404.8	405.3	405.8	406.3	406.8	407.1	407.2	407.3	407.4	407.5	407.2
132.5°	422.3	422.9	423.5	424.0	424.6	424.9	424.6	424.4	424.1	423.9	423.9
135°	447.3	447.9	448.5	449.1	449.7	449.9	449.7	449.5	449.3	449.1	448.9
137.5°	470.2	470.7	471.2	471.8	472.3	472.5	472.3	472.1	471.9	471.7	471.8
140°	485.1	485.3	485.5	485.7	485.9	486.0	485.9	485.8	485.7	485.6	485.8
142.5°	498.7	498.9	499.0	499.1	499.2	499.3	499.5	499.6	499.8	499.9	499.9
145°	518.6	518.8	519.0	519.2	519.4	519.5	519.5	519.5	519.5	519.5	519.6
147.5°	535.9	535.8	535.8	535.7	535.7	535.7	535.9	536.0	536.1	536.2	536.3
150°	546.8	546.6	546.4	546.2	546.0	546.0	546.2	546.4	546.6	546.8	547.0
152.5°	557.4	557.0	556.5	556.1	555.6	555.5	555.7	555.9	556.1	556.3	556.5
155°	571.1	570.5	569.9	569.3	568.7	568.5	568.7	568.9	569.1	569.3	569.6
157.5°	581.6	581.2	580.9	580.5	580.1	580.0	580.0	580.0	580.0	580.1	580.4
160°	588.9	588.2	587.6	587.0	586.4	586.2	586.3	586.4	586.5	586.6	587.0
162.5°	594.7	594.1	593.5	592.9	592.3	592.1	592.2	592.3	592.4	592.5	593.0
165°	602.6	602.0	601.4	600.8	600.2	599.9	600.0	600.1	600.2	600.3	600.9
167.5°	608.4	607.8	607.2	606.5	605.9	605.6	605.7	605.8	605.9	606.0	606.8
170°	611.8	611.1	610.3	609.6	608.8	608.5	608.6	608.7	608.8	608.9	609.8
172.5°	613.9	613.2	612.5	611.8	611.1	610.9	611.0	611.2	611.4	611.6	612.3
175°	616.3	615.7	615.1	614.5	613.9	613.6	613.7	613.8	613.9	614.0	614.8
177.5°	617.4	616.9	616.4	615.9	615.4	615.2	615.3	615.4	615.5	615.6	616.1
180°	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3



TEST NUMBER: P333682-840

CATALOG NUMBER: S125RDIW-S850D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1383.9	1385.8	1387.7	1388.6	1388.4	1388.2	1388.0	1387.8
5°	1375.4	1377.8	1380.1	1381.1	1380.6	1380.1	1379.7	1379.2
7.5°	1358.4	1360.0	1361.6	1362.1	1361.6	1361.1	1360.6	1360.1
10°	1343.8	1344.5	1345.2	1345.2	1344.5	1343.8	1343.1	1342.5
12.5°	1323.3	1323.8	1324.3	1324.1	1323.0	1321.9	1320.9	1319.8
15°	1289.6	1289.3	1289.1	1288.0	1285.9	1283.7	1281.6	1279.5
17.5°	1247.4	1246.3	1245.1	1243.6	1241.9	1240.2	1238.5	1236.8
20°	1216.4	1215.2	1214.1	1212.4	1210.3	1208.2	1206.1	1204.1
22.5°	1185.6	1183.4	1181.0	1179.0	1177.3	1175.6	1173.9	1172.2
25°	1135.1	1132.1	1129.0	1126.2	1123.6	1121.1	1118.5	1115.9
27.5°	1080.4	1076.1	1071.9	1068.5	1066.1	1063.6	1061.2	1058.6
30°	1041.3	1035.9	1030.5	1026.8	1024.7	1022.6	1020.5	1018.3
32.5°	1003.2	997.2	991.4	987.0	984.4	981.8	979.1	976.4
35°	944.0	937.3	930.5	925.5	922.2	919.0	915.7	912.4
37.5°	882.2	874.0	866.0	860.3	857.2	853.9	850.8	847.7
40°	841.2	832.4	823.5	817.7	815.0	812.1	809.3	806.6
42.5°	800.9	792.4	784.0	777.6	773.6	769.4	765.3	761.2
45°	736.5	727.2	717.8	711.4	707.9	704.5	700.9	697.4
47.5°	672.8	663.2	653.6	646.8	643.0	639.1	635.2	631.4
50°	629.7	619.9	610.1	603.4	600.0	596.4	592.9	589.5
52.5°	588.8	578.1	567.6	560.6	557.1	553.6	550.2	546.6
55°	526.5	516.0	505.5	498.4	494.7	491.0	487.3	483.5
57.5°	464.2	454.0	443.7	437.0	433.6	430.3	427.1	423.7
60°	423.1	412.8	402.6	395.8	392.2	388.8	385.3	381.7
62.5°	382.6	373.1	363.7	357.2	353.7	350.1	346.7	343.2
65°	323.3	314.0	304.6	298.2	294.7	291.2	287.7	284.2
67.5°	266.5	258.0	249.4	243.8	241.1	238.2	235.4	232.7
70°	228.8	221.7	214.4	209.4	206.6	203.8	201.1	198.2
72.5°	193.9	187.2	180.6	176.3	174.4	172.6	170.8	168.8
75°	145.0	139.9	134.7	131.4	129.7	128.1	126.4	124.8
77.5°	103.1	99.6	95.9	93.6	92.4	91.2	90.0	88.8
80°	77.7	75.5	73.4	72.1	71.7	71.2	70.7	70.3
82.5°	58.1	57.1	56.0	55.4	55.1	54.9	54.6	54.3
85°	33.1	32.8	32.6	32.4	32.1	31.9	31.7	31.5
87.5°	14.2	14.3	14.4	14.4	14.3	14.2	14.0	13.9
90°	8.3	8.8	9.3	9.8	10.1	10.4	10.7	11.0
92.5°	8.3	8.8	9.3	9.7	9.8	10.0	10.1	10.2
95°	8.3	8.8	9.3	9.6	9.6	9.6	9.6	9.6
97.5°	16.8	13.9	11.0	9.6	9.6	9.6	9.6	9.6
100°	49.3	34.1	19.0	11.2	10.8	10.4	10.0	9.6
102.5°	95.7	92.8	90.0	85.1	78.2	71.3	64.3	57.5
105°	136.1	136.1	136.1	136.1	136.0	135.9	135.8	135.7
107.5°	172.4	172.4	172.4	172.3	172.0	171.7	171.4	171.1
110°	195.8	195.5	195.2	195.1	195.2	195.3	195.4	195.5





TEST NUMBER: P333682-840

CATALOG NUMBER: S125RDIW-S850D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	219.0	218.6	218.3	218.0	217.9	217.7	217.6	217.4
115°	254.1	253.7	253.3	252.8	252.2	251.6	251.0	250.3
117.5°	287.9	287.4	286.9	286.5	286.2	286.0	285.7	285.5
120°	309.8	309.6	309.4	309.0	308.5	308.0	307.5	307.0
122.5°	330.6	330.4	330.2	329.8	329.2	328.6	328.1	327.5
125°	361.0	360.6	360.2	359.8	359.5	359.2	358.9	358.6
127.5°	388.8	388.6	388.4	387.9	387.1	386.4	385.6	384.9
130°	406.9	406.6	406.3	405.9	405.4	404.9	404.3	403.8
132.5°	423.8	423.7	423.7	423.4	422.9	422.4	421.9	421.4
135°	448.7	448.5	448.3	447.9	447.3	446.7	446.1	445.5
137.5°	471.8	471.9	471.9	471.7	471.1	470.6	470.1	469.6
140°	486.0	486.3	486.5	486.3	485.6	485.0	484.4	483.8
142.5°	500.0	500.0	500.1	499.8	499.2	498.6	498.0	497.4
145°	519.7	519.8	519.9	519.6	519.0	518.4	517.8	517.2
147.5°	536.5	536.6	536.7	536.4	535.7	535.0	534.2	533.5
150°	547.2	547.4	547.6	547.3	546.5	545.7	544.9	544.1
152.5°	556.7	556.9	557.1	556.9	556.1	555.4	554.7	554.0
155°	569.9	570.2	570.5	570.2	569.4	568.6	567.7	566.9
157.5°	580.7	581.0	581.3	581.1	580.3	579.5	578.7	577.8
160°	587.4	587.8	588.2	588.0	587.2	586.4	585.6	584.8
162.5°	593.6	594.2	594.7	594.6	593.7	592.8	591.9	591.0
165°	601.6	602.2	602.8	602.7	601.9	601.0	600.2	599.4
167.5°	607.5	608.2	608.9	608.9	607.9	607.0	606.1	605.2
170°	610.6	611.5	612.3	612.2	611.3	610.4	609.5	608.5
172.5°	613.0	613.7	614.5	614.4	613.5	612.6	611.7	610.8
175°	615.6	616.4	617.2	617.2	616.3	615.4	614.5	613.6
177.5°	616.7	617.2	617.8	617.8	617.1	616.5	615.8	615.2
180°	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3

(END OF REPORT)