

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333435-940

Luminaire Tested: **S125DIW-S1090D470U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333435-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1090D470U940-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5409.7 lumens  
Efficiency: N/A  
Efficacy: 117.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333435-940

CATALOG NUMBER: S125DIW-S1090D470U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333435-940

CATALOG NUMBER: S125DIW-S1090D470U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	97	94	90	87	84	82	79	76	74	72	68	67	65	61
2	94	86	79	74	89	82	76	71	74	69	65	67	63	60	60	57	55	51
3	85	76	68	62	81	72	65	59	65	60	55	59	55	51	53	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	32
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31	28
7	62	49	40	35	58	47	39	34	43	36	31	39	34	29	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	37	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9827	9827	9827
5°	9849	9756	9818
10°	9789	9686	9742
15°	9682	9570	9610
20°	9531	9407	9423
25°	9368	9213	9204
30°	9165	9004	8959
35°	8949	8779	8656
40°	8728	8535	8413
45°	8488	8312	8147
50°	8225	8043	7801
55°	7970	7739	7523
60°	7665	7432	7167
65°	7303	7065	6825
70°	6956	6637	6411
75°	6338	6128	5916
80°	5642	5553	5415
85°	4905	4994	4728



TEST NUMBER: P333435-940

CATALOG NUMBER: S125DIW-S1090D470U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.5	2.7
10°-20°	405.3	7.5
20°-30°	598.4	11.1
30°-40°	698.2	12.9
40°-50°	701.3	13.0
50°-60°	615.6	11.4
60°-70°	458.7	8.5
70°-80°	262.3	4.8
80°-90°	77.4	1.4
90°-100°	34.8	0.6
100°-110°	102.7	1.9
110°-120°	174.0	3.2
120°-130°	229.0	4.2
130°-140°	256.6	4.7
140°-150°	251.5	4.6
150°-160°	211.2	3.9
160°-170°	140.4	2.6
170°-180°	49.1	0.9
0°-30°	1147.1	21.2
0°-40°	1845.3	34.1
0°-60°	3162.2	58.5
0°-90°	3960.5	73.2
90°-120°	311.5	5.8
90°-150°	1048.5	19.4
90°-180°	1449.0	26.8
0°-180°	5409.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1522	1522	1522	1522	1522	
5°	1519	1516	1505	1515	1514	144
15°	1448	1444	1431	1437	1437	408
25°	1315	1308	1293	1295	1292	605
35°	1135	1130	1114	1107	1098	710
45°	929	924	910	896	892	716
55°	708	703	687	677	668	632
65°	478	475	462	452	447	474
75°	254	251	246	242	237	271
85°	66	67	67	66	64	74
90°	0	4	6	8	10	5
95°	26	27	31	34	35	28
105°	92	94	97	99	100	98
115°	174	176	177	176	176	172
125°	254	257	257	256	256	228
135°	331	333	333	333	332	255
145°	401	402	403	403	402	250
155°	458	458	459	460	458	211
165°	498	498	498	499	497	141
175°	518	517	516	519	516	49
180°	519	519	519	519	519	



TEST NUMBER: P333435-940

CATALOG NUMBER: S125DIW-S1090D470U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6
2.5°	1525.4	1524.8	1524.1	1523.5	1522.9	1521.4	1519.3	1517.2	1515.0	1512.9	1515.0
5°	1519.2	1518.7	1518.1	1517.6	1517.1	1515.5	1512.8	1510.1	1507.4	1504.8	1507.2
7.5°	1505.2	1504.7	1504.1	1503.6	1503.1	1501.3	1498.3	1495.4	1492.5	1489.5	1491.9
10°	1492.7	1492.2	1491.7	1491.1	1490.6	1488.8	1485.9	1482.9	1480.0	1477.0	1479.2
12.5°	1477.3	1476.3	1475.3	1474.4	1473.5	1471.6	1468.8	1466.2	1463.4	1460.6	1462.4
15°	1448.1	1447.3	1446.5	1445.7	1444.9	1443.1	1440.1	1437.2	1434.2	1431.3	1432.6
17.5°	1414.7	1413.5	1412.3	1411.1	1410.0	1407.8	1404.8	1401.8	1398.7	1395.6	1397.3
20°	1386.8	1386.3	1385.7	1385.2	1384.6	1382.6	1379.1	1375.6	1372.2	1368.7	1370.6
22.5°	1358.8	1357.9	1356.9	1355.9	1355.0	1352.8	1349.6	1346.3	1343.1	1339.8	1341.0
25°	1314.6	1313.2	1311.9	1310.5	1309.2	1306.8	1303.3	1299.8	1296.4	1292.9	1293.4
27.5°	1262.8	1261.9	1261.1	1260.3	1259.5	1257.4	1253.7	1250.2	1246.6	1243.0	1243.1
30°	1229.0	1228.2	1227.4	1226.6	1225.8	1223.4	1219.4	1215.4	1211.4	1207.4	1206.8
32.5°	1192.5	1191.2	1190.0	1188.7	1187.6	1185.2	1181.5	1177.9	1174.4	1170.8	1169.8
35°	1135.1	1134.1	1133.0	1131.9	1130.9	1128.5	1124.7	1121.0	1117.2	1113.5	1112.1
37.5°	1075.7	1074.3	1073.0	1071.7	1070.3	1067.9	1064.3	1060.9	1057.3	1053.8	1051.8
40°	1035.3	1033.9	1032.6	1031.3	1029.9	1027.3	1023.6	1019.8	1016.1	1012.4	1010.0
42.5°	991.9	990.8	989.7	988.6	987.4	985.0	981.2	977.5	973.7	970.0	967.8
45°	929.3	928.3	927.2	926.1	925.1	922.9	919.7	916.5	913.3	910.1	906.9
47.5°	861.9	861.9	862.0	862.1	862.1	860.2	856.4	852.5	848.6	844.8	841.5
50°	818.6	817.8	817.0	816.2	815.4	813.3	810.1	806.9	803.7	800.5	797.0
52.5°	774.3	773.6	773.1	772.5	772.0	769.9	766.5	763.0	759.6	756.2	753.1
55°	707.8	707.0	706.2	705.4	704.6	702.3	698.6	694.8	691.1	687.3	684.9
57.5°	637.8	637.3	636.9	636.5	636.1	634.3	631.1	627.9	624.8	621.6	618.5
60°	593.4	592.4	591.3	590.2	589.2	587.2	584.2	581.3	578.4	575.4	572.7
62.5°	547.2	546.4	545.5	544.7	543.9	542.2	539.6	537.1	534.6	532.1	529.1
65°	477.9	477.3	476.8	476.3	475.7	474.0	471.1	468.1	465.2	462.3	459.9
67.5°	410.7	409.6	408.5	407.3	406.3	404.6	402.3	400.2	398.0	395.8	393.8
70°	368.4	367.0	365.7	364.4	363.0	361.1	358.7	356.3	353.9	351.5	349.9
72.5°	322.2	321.2	320.3	319.4	318.5	317.3	315.8	314.1	312.6	311.0	309.2
75°	254.0	253.4	252.9	252.4	251.8	250.9	249.6	248.3	246.9	245.6	244.8
77.5°	191.2	190.9	190.7	190.6	190.3	189.8	189.0	188.3	187.6	186.8	186.4
80°	151.7	151.7	151.7	151.7	151.7	151.4	150.9	150.3	149.8	149.3	149.0
82.5°	117.0	116.5	116.2	115.7	115.3	115.0	114.9	114.9	114.7	114.6	114.1
85°	66.2	66.4	66.7	67.0	67.2	67.4	67.4	67.4	67.4	67.4	67.1
87.5°	26.0	26.2	26.4	26.5	26.7	26.7	26.6	26.5	26.4	26.3	26.4
90°	0.4	1.2	1.9	2.6	3.3	3.9	4.5	5.2	5.8	6.5	7.0
92.5°	9.8	10.3	10.8	11.3	11.8	12.4	13.2	14.0	14.7	15.5	16.1
95°	26.3	26.5	26.7	26.8	27.0	27.6	28.4	29.3	30.2	31.1	31.7
97.5°	43.6	43.7	43.8	43.9	44.0	44.6	45.8	47.1	48.3	49.6	50.1
100°	56.6	56.6	56.6	56.6	56.6	57.2	58.3	59.5	60.6	61.8	62.7
102.5°	70.4	70.8	71.2	71.6	72.0	72.4	73.0	73.6	74.2	74.7	75.6
105°	92.1	92.6	93.0	93.5	94.0	94.4	95.0	95.5	96.0	96.6	97.1
107.5°	116.1	116.5	117.0	117.4	117.9	118.3	118.7	119.1	119.6	119.9	120.2
110°	132.6	133.0	133.5	133.9	134.4	134.7	135.0	135.3	135.5	135.8	136.1



TEST NUMBER: P333435-940

CATALOG NUMBER: S125DIW-S1090D470U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	149.4	149.6	149.8	150.1	150.3	150.6	151.0	151.3	151.6	151.9	152.1
115°	174.2	174.5	175.0	175.3	175.7	175.9	176.1	176.3	176.5	176.6	176.6
117.5°	199.1	199.2	199.4	199.6	199.7	199.9	200.1	200.2	200.4	200.5	200.6
120°	214.6	215.1	215.5	216.0	216.4	216.7	216.8	216.9	217.0	217.0	217.0
122.5°	231.4	231.6	231.8	231.9	232.0	232.3	232.5	232.7	233.0	233.2	233.1
125°	254.2	254.8	255.3	255.8	256.4	256.7	256.8	256.9	257.0	257.1	256.9
127.5°	278.5	278.7	279.1	279.4	279.7	279.9	280.0	280.1	280.2	280.4	280.3
130°	293.0	293.5	293.9	294.4	294.8	295.2	295.3	295.5	295.7	295.9	295.8
132.5°	307.6	308.3	309.1	309.8	310.5	310.9	310.9	310.8	310.8	310.7	310.6
135°	330.6	331.2	331.7	332.3	332.8	333.1	333.1	333.2	333.3	333.4	333.4
137.5°	352.2	352.8	353.3	353.8	354.4	354.7	354.9	355.1	355.3	355.5	355.6
140°	366.1	366.6	367.0	367.5	367.9	368.4	368.6	368.9	369.2	369.4	369.6
142.5°	380.0	380.4	380.8	381.2	381.6	381.9	382.3	382.6	383.0	383.3	383.4
145°	400.6	400.9	401.3	401.6	402.0	402.3	402.5	402.8	403.1	403.3	403.3
147.5°	419.5	419.6	419.8	420.0	420.3	420.4	420.6	420.9	421.1	421.3	421.5
150°	432.0	431.9	431.9	431.8	431.7	431.9	432.2	432.6	432.9	433.3	433.3
152.5°	442.4	442.6	442.6	442.7	442.9	443.0	443.2	443.4	443.4	443.6	443.8
155°	458.3	458.3	458.3	458.3	458.3	458.3	458.4	458.5	458.6	458.7	459.1
157.5°	472.5	472.3	472.2	472.0	471.7	471.7	471.8	471.9	472.0	472.1	472.4
160°	481.0	480.7	480.4	480.1	479.8	479.7	479.8	479.9	480.0	480.1	480.5
162.5°	488.4	488.2	488.0	487.8	487.6	487.5	487.5	487.5	487.6	487.6	488.0
165°	498.3	498.1	497.9	497.8	497.6	497.6	497.7	497.8	497.8	497.9	498.3
167.5°	506.8	506.4	506.0	505.7	505.3	505.2	505.2	505.2	505.2	505.2	505.7
170°	511.2	510.9	510.5	510.1	509.8	509.6	509.6	509.6	509.6	509.6	510.1
172.5°	514.5	514.2	513.8	513.4	513.1	512.9	512.9	512.9	512.9	512.9	513.4
175°	518.2	517.7	517.4	517.0	516.7	516.5	516.5	516.5	516.5	516.5	517.0
177.5°	520.0	519.7	519.4	519.2	518.8	518.6	518.6	518.5	518.4	518.4	518.8
180°	519.3	519.3	519.3	519.3	519.3	519.3	519.3	519.3	519.3	519.3	519.3



TEST NUMBER: P333435-940

CATALOG NUMBER: S125DIW-S1090D470U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6
2.5°	1517.2	1519.3	1521.4	1522.4	1522.2	1522.0	1521.8	1521.6
5°	1509.6	1512.0	1514.4	1515.5	1515.2	1514.9	1514.7	1514.4
7.5°	1494.2	1496.6	1499.0	1500.0	1499.8	1499.5	1499.2	1499.0
10°	1481.3	1483.5	1485.6	1486.6	1486.3	1486.0	1485.8	1485.5
12.5°	1464.1	1465.8	1467.5	1468.4	1468.3	1468.2	1468.2	1468.1
15°	1434.0	1435.3	1436.6	1437.3	1437.3	1437.3	1437.3	1437.3
17.5°	1399.0	1400.6	1402.3	1402.5	1401.1	1399.8	1398.5	1397.1
20°	1372.4	1374.3	1376.2	1376.4	1375.1	1373.8	1372.4	1371.1
22.5°	1342.3	1343.5	1344.7	1344.9	1344.0	1343.1	1342.2	1341.2
25°	1294.0	1294.5	1295.0	1294.9	1294.1	1293.2	1292.4	1291.6
27.5°	1243.2	1243.3	1243.5	1243.1	1242.3	1241.5	1240.7	1239.9
30°	1206.3	1205.8	1205.2	1204.6	1203.8	1203.0	1202.2	1201.4
32.5°	1168.9	1167.9	1167.0	1165.7	1164.3	1162.9	1161.4	1159.9
35°	1110.8	1109.5	1108.1	1106.4	1104.3	1102.2	1100.0	1097.9
37.5°	1049.8	1047.8	1045.9	1044.3	1043.0	1041.8	1040.5	1039.4
40°	1007.5	1005.1	1002.7	1001.1	1000.3	999.5	998.7	997.9
42.5°	965.6	963.4	961.3	959.5	958.3	957.1	955.8	954.6
45°	903.7	900.4	897.2	895.2	894.4	893.6	892.8	892.0
47.5°	838.3	835.0	831.8	829.2	827.3	825.5	823.6	821.7
50°	793.5	790.1	786.6	783.9	782.0	780.2	778.3	776.4
52.5°	750.1	747.1	744.0	741.5	739.3	737.3	735.2	733.1
55°	682.5	680.1	677.7	675.6	673.7	671.8	669.9	668.1
57.5°	615.5	612.3	609.2	607.2	606.2	605.1	604.1	603.1
60°	570.1	567.4	564.7	562.4	560.5	558.7	556.8	554.9
62.5°	526.3	523.4	520.5	518.4	516.9	515.5	514.0	512.6
65°	457.4	455.0	452.6	450.8	449.8	448.7	447.6	446.6
67.5°	391.7	389.7	387.6	386.3	385.7	385.0	384.4	383.8
70°	348.3	346.7	345.1	343.8	342.7	341.6	340.5	339.5
72.5°	307.5	305.6	303.8	302.4	301.3	300.2	299.2	298.1
75°	244.0	243.2	242.4	241.4	240.3	239.2	238.2	237.1
77.5°	185.8	185.4	184.9	184.3	183.5	182.8	182.0	181.3
80°	148.7	148.5	148.2	147.8	147.2	146.7	146.2	145.6
82.5°	113.6	113.2	112.7	112.4	112.3	112.2	112.1	111.9
85°	66.9	66.6	66.3	65.9	65.4	64.8	64.3	63.8
87.5°	26.5	26.6	26.7	26.6	26.2	25.8	25.4	25.1
90°	7.4	7.8	8.3	8.6	8.9	9.2	9.5	9.7
92.5°	16.7	17.3	17.9	18.3	18.5	18.6	18.9	19.1
95°	32.4	33.0	33.6	34.1	34.2	34.4	34.6	34.8
97.5°	50.7	51.4	51.9	52.3	52.3	52.5	52.6	52.7
100°	63.5	64.3	65.1	65.5	65.7	65.9	66.1	66.3
102.5°	76.5	77.4	78.3	78.8	79.1	79.4	79.6	79.9
105°	97.6	98.2	98.7	99.2	99.4	99.7	100.0	100.2
107.5°	120.5	120.7	121.0	121.2	121.2	121.1	121.1	121.1
110°	136.3	136.6	136.9	137.0	136.9	136.8	136.7	136.6





TEST NUMBER: P333435-940

CATALOG NUMBER: S125DIW-S1090D470U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	152.2	152.3	152.5	152.5	152.3	152.1	151.9	151.8
115°	176.5	176.4	176.3	176.2	176.1	176.0	175.9	175.8
117.5°	200.7	200.7	200.8	200.7	200.4	200.0	199.6	199.2
120°	217.0	217.0	217.0	216.9	216.5	216.2	215.8	215.4
122.5°	233.1	233.0	232.9	232.7	232.5	232.2	231.8	231.6
125°	256.7	256.5	256.4	256.2	256.1	256.0	255.9	255.8
127.5°	280.2	280.1	280.0	279.8	279.6	279.5	279.3	279.1
130°	295.7	295.6	295.5	295.3	295.2	295.0	294.8	294.6
132.5°	310.5	310.4	310.3	310.2	310.0	309.7	309.4	309.2
135°	333.4	333.4	333.4	333.2	332.9	332.5	332.2	331.8
137.5°	355.7	355.8	356.0	355.8	355.3	354.9	354.4	353.9
140°	369.8	370.0	370.1	370.0	369.5	369.1	368.6	368.2
142.5°	383.5	383.6	383.7	383.5	383.1	382.6	382.2	381.7
145°	403.3	403.3	403.3	403.2	403.0	402.7	402.4	402.2
147.5°	421.7	422.0	422.1	422.0	421.3	420.7	420.1	419.5
150°	433.3	433.3	433.3	433.2	433.0	432.8	432.7	432.5
152.5°	444.1	444.3	444.4	444.4	444.1	443.8	443.4	443.1
155°	459.4	459.8	460.1	460.1	459.7	459.2	458.8	458.3
157.5°	472.8	473.1	473.5	473.4	472.8	472.2	471.6	471.0
160°	480.9	481.3	481.6	481.5	481.1	480.6	480.2	479.7
162.5°	488.5	488.8	489.3	489.3	488.7	488.2	487.7	487.1
165°	498.6	499.0	499.4	499.3	498.7	498.2	497.7	497.1
167.5°	506.2	506.8	507.3	507.3	506.7	506.1	505.6	505.1
170°	510.7	511.2	511.8	511.8	511.1	510.5	509.9	509.3
172.5°	514.0	514.5	515.1	515.1	514.4	513.9	513.4	512.8
175°	517.5	518.2	518.7	518.6	518.0	517.4	516.7	516.1
177.5°	519.2	519.7	520.1	520.0	519.6	519.1	518.5	518.1
180°	519.3	519.3	519.3	519.3	519.3	519.3	519.3	519.3

(END OF REPORT)