

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333464-940

Luminaire Tested: **S125DIW-S1270D470U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333464-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1270D470U940-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 470 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6245.1 lumens  
Efficiency: N/A  
Efficacy: 119.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333464-940

CATALOG NUMBER: S125DIW-S1270D470U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333464-940

CATALOG NUMBER: S125DIW-S1270D470U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65	62
2	94	86	79	74	89	82	76	71	74	69	65	67	63	60	60	57	55	51
3	85	76	68	62	81	72	65	59	65	60	55	59	55	51	53	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	32
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31	28
7	62	49	40	35	58	47	39	34	43	36	31	39	34	29	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	37	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11349	11349	11349
5°	11374	11267	11339
10°	11305	11187	11252
15°	11183	11053	11099
20°	11008	10864	10883
25°	10819	10641	10630
30°	10586	10399	10347
35°	10336	10139	9996
40°	10080	9857	9716
45°	9803	9600	9409
50°	9499	9289	9010
55°	9205	8939	8688
60°	8853	8584	8280
65°	8436	8159	7882
70°	8033	7666	7404
75°	7321	7079	6832
80°	6512	6412	6259
85°	5669	5765	5461



TEST NUMBER: P333464-940

CATALOG NUMBER: S125DIW-S1270D470U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	165.7	2.7
10°-20°	468.1	7.5
20°-30°	691.1	11.1
30°-40°	806.4	12.9
40°-50°	809.9	13.0
50°-60°	710.9	11.4
60°-70°	529.7	8.5
70°-80°	302.9	4.9
80°-90°	89.3	1.4
90°-100°	19.8	0.3
100°-110°	121.9	2.0
110°-120°	221.0	3.5
120°-130°	283.7	4.5
130°-140°	305.1	4.9
140°-150°	286.4	4.6
150°-160°	231.7	3.7
160°-170°	149.8	2.4
170°-180°	51.7	0.8
0°-30°	1324.8	21.2
0°-40°	2131.2	34.1
0°-60°	3652.1	58.5
0°-90°	4574.0	73.2
90°-120°	362.7	5.8
90°-150°	1237.9	19.8
90°-180°	1671.0	26.8
0°-180°	6245.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1757	1757	1757	1757	1757	
5°	1754	1751	1738	1750	1749	166
15°	1672	1668	1653	1660	1660	471
25°	1518	1511	1493	1496	1492	698
35°	1311	1305	1286	1279	1268	820
45°	1073	1067	1051	1035	1030	827
55°	818	812	794	781	772	730
65°	552	548	534	522	516	548
75°	293	290	284	279	274	313
85°	76	78	78	76	74	85
90°	0	4	6	8	10	5
95°	23	21	6	8	8	29
105°	119	120	120	120	120	126
115°	223	225	225	223	221	221
125°	317	319	320	318	317	283
135°	395	397	396	396	393	304
145°	458	459	459	459	457	286
155°	504	502	503	504	501	232
165°	532	530	530	532	529	150
175°	544	542	542	545	542	52
180°	544	544	544	544	544	



TEST NUMBER: P333464-940

CATALOG NUMBER: S125DIW-S1270D470U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3
2.5°	1761.8	1761.0	1760.3	1759.5	1758.8	1757.2	1754.7	1752.2	1749.8	1747.3	1749.8
5°	1754.5	1753.9	1753.3	1752.7	1752.0	1750.2	1747.1	1744.0	1741.0	1737.9	1740.6
7.5°	1738.4	1737.8	1737.1	1736.5	1735.9	1733.9	1730.5	1727.2	1723.8	1720.4	1723.1
10°	1723.9	1723.3	1722.7	1722.1	1721.4	1719.5	1716.1	1712.7	1709.2	1705.8	1708.3
12.5°	1706.1	1705.0	1704.0	1702.8	1701.7	1699.6	1696.4	1693.3	1690.1	1686.9	1689.0
15°	1672.5	1671.6	1670.6	1669.7	1668.8	1666.6	1663.2	1659.8	1656.4	1653.1	1654.6
17.5°	1633.9	1632.5	1631.1	1629.8	1628.4	1625.9	1622.5	1618.9	1615.4	1611.9	1613.8
20°	1601.6	1601.0	1600.4	1599.7	1599.1	1596.8	1592.8	1588.8	1584.7	1580.7	1582.9
22.5°	1569.3	1568.3	1567.1	1566.0	1564.9	1562.5	1558.7	1555.0	1551.1	1547.4	1548.8
25°	1518.2	1516.6	1515.1	1513.6	1512.0	1509.2	1505.2	1501.2	1497.2	1493.2	1493.8
27.5°	1458.4	1457.5	1456.5	1455.6	1454.7	1452.2	1448.0	1443.9	1439.8	1435.6	1435.7
30°	1419.5	1418.5	1417.6	1416.7	1415.8	1413.0	1408.4	1403.7	1399.1	1394.5	1393.8
32.5°	1377.2	1375.8	1374.4	1373.0	1371.5	1368.8	1364.6	1360.5	1356.3	1352.2	1351.1
35°	1311.0	1309.8	1308.6	1307.3	1306.1	1303.3	1299.0	1294.7	1290.3	1286.0	1284.5
37.5°	1242.3	1240.8	1239.3	1237.7	1236.2	1233.3	1229.3	1225.2	1221.1	1217.1	1214.8
40°	1195.6	1194.1	1192.6	1191.0	1189.5	1186.5	1182.2	1177.9	1173.6	1169.2	1166.4
42.5°	1145.6	1144.3	1143.0	1141.7	1140.4	1137.6	1133.3	1128.9	1124.6	1120.3	1117.8
45°	1073.3	1072.1	1070.9	1069.6	1068.4	1065.9	1062.2	1058.5	1054.8	1051.1	1047.3
47.5°	995.4	995.5	995.6	995.6	995.7	993.5	989.1	984.6	980.2	975.7	972.0
50°	945.4	944.5	943.5	942.6	941.6	939.3	935.7	931.9	928.3	924.5	920.5
52.5°	894.2	893.6	892.9	892.2	891.5	889.2	885.2	881.3	877.4	873.3	869.9
55°	817.5	816.5	815.6	814.7	813.8	811.2	806.8	802.5	798.2	793.9	791.0
57.5°	736.6	736.1	735.6	735.1	734.6	732.5	728.9	725.2	721.6	717.9	714.3
60°	685.4	684.2	683.0	681.7	680.5	678.1	674.8	671.4	668.0	664.6	661.5
62.5°	632.0	631.1	630.1	629.0	628.0	626.2	623.2	620.3	617.4	614.5	611.2
65°	552.0	551.3	550.7	550.1	549.5	547.4	544.0	540.6	537.3	533.9	531.1
67.5°	474.4	473.1	471.8	470.5	469.2	467.3	464.8	462.2	459.7	457.1	454.8
70°	425.4	423.9	422.3	420.8	419.3	417.1	414.3	411.5	408.8	406.0	404.1
72.5°	372.0	371.0	370.0	368.9	367.8	366.4	364.6	362.8	361.1	359.3	357.1
75°	293.4	292.7	292.1	291.5	290.9	289.8	288.3	286.7	285.2	283.7	282.7
77.5°	220.8	220.5	220.3	220.1	219.8	219.3	218.4	217.5	216.6	215.8	215.3
80°	175.1	175.1	175.1	175.1	175.1	174.9	174.2	173.6	173.0	172.4	172.1
82.5°	135.1	134.6	134.1	133.7	133.1	132.9	132.7	132.6	132.5	132.3	131.8
85°	76.5	76.8	77.0	77.4	77.7	77.8	77.8	77.8	77.8	77.8	77.6
87.5°	30.1	30.2	30.4	30.5	30.7	30.7	30.6	30.5	30.3	30.2	30.3
90°	0.4	1.2	1.9	2.6	3.3	3.9	4.5	5.2	5.8	6.4	6.9
92.5°	6.2	5.7	5.2	4.7	4.2	4.2	4.8	5.4	5.9	6.4	6.9
95°	23.0	22.7	22.5	22.2	21.9	20.1	16.7	13.3	9.9	6.4	6.9
97.5°	48.0	48.5	49.0	49.5	49.9	46.8	40.0	33.3	26.6	19.9	17.3
100°	67.3	67.7	67.9	68.2	68.5	68.8	69.1	69.5	69.8	70.2	56.8
102.5°	87.0	87.4	87.7	88.1	88.5	88.7	88.9	89.1	89.3	89.5	87.0
105°	118.6	119.0	119.3	119.7	120.0	120.2	120.2	120.2	120.2	120.2	120.2
107.5°	151.3	151.3	151.3	151.3	151.3	151.4	151.6	151.8	151.9	152.1	152.2
110°	172.6	172.6	172.6	172.6	172.6	172.7	172.9	173.1	173.3	173.4	173.2



TEST NUMBER: P333464-940

CATALOG NUMBER: S125DIW-S1270D470U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	192.7	192.9	193.1	193.3	193.5	193.7	193.8	193.9	194.0	194.1	193.8
115°	222.7	223.1	223.6	224.0	224.4	224.7	224.8	224.9	225.0	225.1	224.7
117.5°	253.8	253.7	253.7	253.7	253.7	253.9	254.1	254.5	254.9	255.2	254.8
120°	273.1	273.0	273.0	272.9	272.8	272.9	273.1	273.4	273.7	273.9	273.8
122.5°	290.3	290.5	290.9	291.2	291.6	291.8	291.9	292.0	292.2	292.3	292.1
125°	316.6	317.3	317.9	318.5	319.1	319.5	319.5	319.5	319.5	319.5	319.1
127.5°	341.9	342.4	342.9	343.3	343.8	343.9	343.8	343.8	343.8	343.7	343.5
130°	357.4	357.8	358.3	358.7	359.2	359.4	359.5	359.6	359.7	359.8	359.5
132.5°	372.9	373.4	374.0	374.4	375.0	375.1	375.0	374.8	374.5	374.3	374.3
135°	394.9	395.5	396.0	396.5	397.1	397.3	397.1	396.9	396.7	396.5	396.4
137.5°	415.2	415.6	416.1	416.6	417.1	417.2	417.1	416.9	416.7	416.5	416.6
140°	428.4	428.6	428.7	428.9	429.1	429.2	429.1	429.0	428.9	428.8	429.0
142.5°	440.3	440.5	440.6	440.7	440.8	440.9	441.0	441.1	441.3	441.4	441.4
145°	457.9	458.1	458.3	458.4	458.6	458.7	458.7	458.7	458.7	458.7	458.8
147.5°	473.2	473.1	473.1	473.1	473.1	473.1	473.2	473.3	473.4	473.5	473.6
150°	482.9	482.7	482.5	482.3	482.1	482.1	482.3	482.5	482.7	482.9	483.0
152.5°	492.2	491.9	491.4	491.1	490.6	490.5	490.7	490.9	491.1	491.2	491.4
155°	504.3	503.7	503.2	502.7	502.1	501.9	502.1	502.3	502.5	502.7	502.9
157.5°	513.5	513.2	512.9	512.6	512.2	512.1	512.1	512.1	512.1	512.2	512.5
160°	520.0	519.4	518.9	518.4	517.8	517.6	517.7	517.8	517.9	518.0	518.4
162.5°	525.1	524.6	524.1	523.5	523.0	522.8	522.9	523.0	523.1	523.2	523.6
165°	532.1	531.5	531.0	530.5	529.9	529.7	529.8	529.9	529.9	530.0	530.6
167.5°	537.3	536.7	536.2	535.6	535.0	534.8	534.8	534.9	535.0	535.1	535.8
170°	540.2	539.6	538.9	538.2	537.6	537.3	537.4	537.5	537.6	537.7	538.4
172.5°	542.1	541.4	540.8	540.2	539.6	539.4	539.5	539.7	539.8	540.0	540.6
175°	544.2	543.7	543.1	542.6	542.1	541.8	541.9	542.0	542.1	542.2	542.9
177.5°	545.2	544.7	544.3	543.9	543.4	543.2	543.3	543.4	543.5	543.6	544.0
180°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2



TEST NUMBER: P333464-940

CATALOG NUMBER: S125DIW-S1270D470U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3
2.5°	1752.2	1754.7	1757.2	1758.3	1758.1	1757.8	1757.6	1757.3
5°	1743.4	1746.2	1749.0	1750.2	1749.9	1749.6	1749.3	1749.0
7.5°	1725.7	1728.5	1731.2	1732.4	1732.1	1731.8	1731.5	1731.2
10°	1710.8	1713.3	1715.7	1716.8	1716.5	1716.2	1715.9	1715.7
12.5°	1691.0	1692.9	1694.9	1695.9	1695.8	1695.7	1695.7	1695.6
15°	1656.2	1657.7	1659.2	1660.0	1660.0	1660.0	1660.0	1660.0
17.5°	1615.7	1617.7	1619.5	1619.7	1618.2	1616.7	1615.1	1613.6
20°	1585.1	1587.2	1589.4	1589.7	1588.1	1586.6	1585.1	1583.5
22.5°	1550.2	1551.7	1553.1	1553.3	1552.2	1551.1	1550.1	1549.1
25°	1494.4	1495.0	1495.7	1495.5	1494.6	1493.6	1492.7	1491.7
27.5°	1435.8	1436.0	1436.1	1435.7	1434.8	1433.9	1432.9	1432.0
30°	1393.2	1392.6	1392.0	1391.2	1390.3	1389.4	1388.4	1387.5
32.5°	1350.0	1348.9	1347.7	1346.3	1344.7	1343.0	1341.3	1339.7
35°	1282.9	1281.4	1279.9	1277.8	1275.3	1272.9	1270.4	1267.9
37.5°	1212.5	1210.2	1207.9	1206.0	1204.6	1203.2	1201.8	1200.3
40°	1163.7	1160.9	1158.1	1156.3	1155.3	1154.4	1153.4	1152.5
42.5°	1115.3	1112.7	1110.2	1108.2	1106.8	1105.4	1103.9	1102.5
45°	1043.7	1039.9	1036.3	1033.9	1033.0	1032.1	1031.1	1030.2
47.5°	968.1	964.4	960.6	957.7	955.5	953.3	951.2	949.0
50°	916.5	912.5	908.5	905.4	903.2	901.1	898.9	896.7
52.5°	866.3	862.8	859.3	856.3	853.9	851.5	849.1	846.7
55°	788.3	785.5	782.7	780.2	778.1	776.0	773.7	771.6
57.5°	710.8	707.2	703.6	701.2	700.1	698.9	697.7	696.5
60°	658.4	655.3	652.2	649.6	647.4	645.2	643.1	641.0
62.5°	607.8	604.5	601.2	598.7	597.0	595.3	593.6	592.0
65°	528.3	525.5	522.7	520.8	519.5	518.3	517.0	515.8
67.5°	452.5	450.0	447.7	446.2	445.4	444.7	444.0	443.2
70°	402.3	400.4	398.5	397.0	395.7	394.5	393.3	392.1
72.5°	355.1	352.9	350.9	349.2	347.9	346.7	345.4	344.2
75°	281.8	280.8	279.9	278.8	277.6	276.3	275.1	273.8
77.5°	214.6	214.1	213.6	212.9	212.0	211.1	210.3	209.4
80°	171.7	171.5	171.1	170.7	170.0	169.4	168.8	168.3
82.5°	131.3	130.7	130.1	129.8	129.7	129.6	129.4	129.3
85°	77.2	77.0	76.6	76.2	75.5	74.9	74.3	73.7
87.5°	30.4	30.5	30.6	30.4	30.0	29.5	29.1	28.6
90°	7.3	7.8	8.2	8.6	8.9	9.2	9.5	9.7
92.5°	7.3	7.8	8.2	8.6	8.6	8.8	8.9	9.0
95°	7.3	7.8	8.2	8.5	8.5	8.5	8.5	8.5
97.5°	14.8	12.3	9.7	8.5	8.5	8.5	8.5	8.5
100°	43.5	30.1	16.8	9.9	9.5	9.2	8.8	8.5
102.5°	84.5	81.9	79.5	75.2	69.0	63.0	56.8	50.7
105°	120.2	120.2	120.2	120.2	120.1	120.0	119.9	119.8
107.5°	152.2	152.2	152.2	152.1	151.9	151.6	151.3	151.1
110°	172.9	172.6	172.4	172.3	172.4	172.5	172.5	172.6





TEST NUMBER: P333464-940

CATALOG NUMBER: S125DIW-S1270D470U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	193.4	193.1	192.8	192.5	192.4	192.3	192.2	192.0
115°	224.4	224.0	223.6	223.2	222.7	222.1	221.6	221.1
117.5°	254.2	253.8	253.3	253.0	252.7	252.5	252.3	252.1
120°	273.6	273.4	273.2	272.9	272.4	272.0	271.5	271.1
122.5°	291.9	291.8	291.6	291.2	290.7	290.2	289.7	289.2
125°	318.8	318.4	318.1	317.7	317.4	317.2	316.9	316.6
127.5°	343.3	343.1	343.0	342.5	341.8	341.2	340.5	339.8
130°	359.3	359.0	358.7	358.4	357.9	357.5	357.0	356.6
132.5°	374.3	374.2	374.2	373.9	373.4	373.0	372.6	372.1
135°	396.2	396.0	395.8	395.5	394.9	394.4	393.9	393.3
137.5°	416.6	416.7	416.7	416.5	416.0	415.5	415.1	414.6
140°	429.2	429.4	429.5	429.4	428.8	428.3	427.8	427.2
142.5°	441.5	441.5	441.6	441.3	440.8	440.2	439.7	439.2
145°	458.9	459.0	459.1	458.8	458.3	457.7	457.2	456.6
147.5°	473.8	473.9	473.9	473.7	473.1	472.4	471.7	471.1
150°	483.2	483.4	483.6	483.3	482.6	481.9	481.2	480.5
152.5°	491.6	491.8	492.0	491.8	491.1	490.4	489.8	489.2
155°	503.2	503.5	503.7	503.5	502.7	502.0	501.3	500.6
157.5°	512.7	513.0	513.3	513.1	512.4	511.7	511.0	510.2
160°	518.7	519.1	519.4	519.2	518.5	517.8	517.1	516.4
162.5°	524.1	524.7	525.1	525.0	524.2	523.4	522.6	521.8
165°	531.2	531.7	532.3	532.2	531.5	530.7	529.9	529.2
167.5°	536.5	537.1	537.7	537.7	536.8	536.0	535.2	534.4
170°	539.1	539.9	540.6	540.6	539.8	539.0	538.1	537.3
172.5°	541.3	541.9	542.6	542.5	541.7	540.9	540.1	539.3
175°	543.6	544.3	545.0	545.0	544.2	543.4	542.6	541.8
177.5°	544.6	545.0	545.5	545.5	544.9	544.4	543.8	543.2
180°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2

(END OF REPORT)