

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333399-940

Luminaire Tested: **S125DIW-S610D1560U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333399-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1560U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7054.4 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333399-940

CATALOG NUMBER: S125DIW-S610D1560U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333399-940

CATALOG NUMBER: S125DIW-S610D1560U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32								
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33	27								
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28	22								
3	78	68	61	56	70	62	56	51	49	45	41	38	35	32	27	25	24	19								
4	71	60	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16								
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14								
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	15	12								
7	55	43	36	30	49	39	33	28	32	27	23	25	21	18	18	16	14	11								
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	10								
9	48	36	28	23	43	32	26	22	26	21	18	21	17	15	15	13	11	9								
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	8								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5531	5531	5531
5°	5544	5490	5525
10°	5509	5452	5483
15°	5449	5386	5409
20°	5364	5294	5304
25°	5273	5185	5181
30°	5158	5068	5043
35°	5037	4941	4872
40°	4912	4804	4736
45°	4778	4678	4585
50°	4629	4527	4391
55°	4486	4355	4234
60°	4314	4184	4035
65°	4109	3976	3842
70°	3914	3737	3609
75°	3566	3449	3331
80°	3172	3124	3046
85°	2764	2808	2660



TEST NUMBER: P333399-940

CATALOG NUMBER: S125DIW-S610D1560U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.7	1.1
10°-20°	228.1	3.2
20°-30°	336.8	4.8
30°-40°	393.0	5.6
40°-50°	394.7	5.6
50°-60°	346.5	4.9
60°-70°	258.2	3.7
70°-80°	147.6	2.1
80°-90°	46.7	0.7
90°-100°	115.7	1.6
100°-110°	341.8	4.8
110°-120°	578.9	8.2
120°-130°	761.9	10.8
130°-140°	853.7	12.1
140°-150°	836.7	11.9
150°-160°	702.8	10.0
160°-170°	467.2	6.6
170°-180°	163.5	2.3
0°-30°	645.6	9.2
0°-40°	1038.6	14.7
0°-60°	1779.7	25.2
0°-90°	2232.2	31.6
90°-120°	1036.5	14.7
90°-150°	3488.8	49.5
90°-180°	4822.0	68.4
0°-180°	7054.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	856	856	856	856	856	
5°	855	853	847	853	852	81
15°	815	813	806	809	809	230
25°	740	736	728	729	727	340
35°	639	636	627	623	618	399
45°	523	520	512	504	502	403
55°	398	396	387	381	376	356
65°	269	267	260	254	251	267
75°	143	142	138	136	134	152
85°	37	38	38	37	36	42
90°	1	12	22	28	32	7
95°	87	91	104	113	116	93
105°	307	313	322	329	334	327
115°	580	585	588	586	585	573
125°	846	854	855	853	851	757
135°	1100	1108	1110	1109	1104	848
145°	1333	1338	1342	1342	1338	833
155°	1525	1525	1526	1531	1525	702
165°	1658	1656	1657	1661	1654	468
175°	1724	1719	1719	1726	1717	164
180°	1728	1728	1728	1728	1728	



TEST NUMBER: P333399-940

CATALOG NUMBER: S125DIW-S610D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	858.5	858.2	857.8	857.5	857.1	856.3	855.2	853.9	852.7	851.5	852.7
5°	855.1	854.7	854.4	854.1	853.8	852.9	851.4	849.9	848.4	846.9	848.3
7.5°	847.1	846.9	846.6	846.2	846.0	845.0	843.3	841.7	840.0	838.4	839.6
10°	840.1	839.8	839.5	839.2	838.9	837.9	836.2	834.6	832.9	831.3	832.5
12.5°	831.4	830.9	830.4	829.8	829.3	828.2	826.7	825.2	823.6	822.1	823.0
15°	815.0	814.6	814.1	813.7	813.2	812.2	810.6	808.9	807.2	805.6	806.3
17.5°	796.2	795.6	794.9	794.2	793.5	792.4	790.7	788.9	787.2	785.5	786.4
20°	780.5	780.2	779.9	779.6	779.3	778.2	776.2	774.3	772.3	770.3	771.4
22.5°	764.7	764.2	763.7	763.1	762.6	761.4	759.6	757.8	755.9	754.0	754.7
25°	739.9	739.0	738.3	737.6	736.8	735.5	733.5	731.6	729.6	727.6	728.0
27.5°	710.7	710.2	709.8	709.4	708.9	707.7	705.6	703.6	701.6	699.6	699.6
30°	691.7	691.3	690.8	690.4	689.9	688.6	686.3	684.0	681.8	679.6	679.2
32.5°	671.1	670.5	669.8	669.1	668.3	667.0	665.0	663.0	660.9	659.0	658.4
35°	638.9	638.3	637.7	637.1	636.5	635.2	633.0	630.9	628.8	626.7	626.0
37.5°	605.4	604.7	604.0	603.2	602.4	601.0	599.1	597.1	595.0	593.1	592.0
40°	582.6	581.9	581.1	580.4	579.6	578.2	576.1	574.0	571.9	569.8	568.5
42.5°	558.3	557.7	557.0	556.3	555.7	554.4	552.2	550.2	548.0	545.9	544.7
45°	523.1	522.5	521.8	521.2	520.7	519.4	517.6	515.9	514.0	512.2	510.4
47.5°	485.1	485.1	485.2	485.2	485.2	484.1	482.0	479.8	477.7	475.5	473.7
50°	460.7	460.2	459.8	459.3	458.9	457.8	455.9	454.1	452.4	450.6	448.6
52.5°	435.8	435.4	435.2	434.8	434.4	433.3	431.4	429.4	427.6	425.6	423.9
55°	398.4	397.9	397.4	397.0	396.5	395.3	393.2	391.1	389.0	386.8	385.5
57.5°	358.9	358.7	358.5	358.2	358.0	357.0	355.2	353.4	351.6	349.9	348.1
60°	334.0	333.4	332.8	332.2	331.6	330.5	328.9	327.2	325.5	323.9	322.4
62.5°	308.0	307.6	307.0	306.6	306.0	305.1	303.7	302.3	300.9	299.4	297.8
65°	268.9	268.7	268.4	268.0	267.8	266.8	265.1	263.5	261.8	260.2	258.8
67.5°	231.1	230.5	229.9	229.3	228.6	227.7	226.5	225.2	224.0	222.7	221.6
70°	207.3	206.6	205.8	205.1	204.3	203.2	201.9	200.5	199.2	197.9	196.9
72.5°	181.3	180.7	180.3	179.8	179.2	178.5	177.7	176.8	175.9	175.0	174.1
75°	142.9	142.7	142.3	142.0	141.8	141.2	140.4	139.7	138.9	138.2	137.8
77.5°	107.6	107.5	107.4	107.2	107.1	106.8	106.4	106.0	105.6	105.1	104.9
80°	85.3	85.3	85.3	85.3	85.3	85.2	84.9	84.6	84.4	84.0	83.8
82.5°	65.9	65.6	65.4	65.1	64.9	64.7	64.6	64.6	64.6	64.5	64.2
85°	37.3	37.5	37.5	37.7	37.9	37.9	37.9	37.9	37.9	37.9	37.8
87.5°	14.9	15.3	15.9	16.3	16.9	17.2	17.5	17.8	18.1	18.4	18.7
90°	1.3	3.7	6.2	8.6	10.9	13.1	15.2	17.3	19.4	21.5	23.0
92.5°	32.5	34.2	35.9	37.5	39.2	41.4	44.0	46.5	49.0	51.6	53.6
95°	87.4	88.0	88.6	89.2	89.8	91.6	94.6	97.6	100.6	103.5	105.7
97.5°	145.3	145.4	145.7	146.0	146.2	148.4	152.5	156.7	160.8	164.9	166.8
100°	188.2	188.2	188.2	188.2	188.2	190.2	194.1	198.0	201.9	205.7	208.5
102.5°	234.5	235.8	236.9	238.1	239.3	240.9	242.9	244.9	246.8	248.8	251.7
105°	306.7	308.1	309.6	311.1	312.6	314.2	316.0	317.8	319.6	321.5	323.2
107.5°	386.2	387.7	389.2	390.7	392.2	393.7	395.0	396.4	397.8	399.1	400.0
110°	441.1	442.6	444.1	445.6	447.1	448.3	449.2	450.0	450.9	451.8	452.7



TEST NUMBER: P333399-940

CATALOG NUMBER: S125DIW-S610D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	497.0	497.8	498.6	499.4	500.2	501.1	502.2	503.4	504.5	505.7	506.0
115°	579.6	580.9	582.0	583.2	584.4	585.3	585.9	586.5	587.1	587.7	587.4
117.5°	662.5	663.0	663.5	664.1	664.6	665.1	665.7	666.2	666.7	667.4	667.5
120°	714.1	715.6	717.1	718.6	720.1	720.9	721.3	721.6	721.8	722.2	722.2
122.5°	770.1	770.6	771.2	771.7	772.2	772.8	773.6	774.5	775.2	776.0	775.7
125°	845.9	847.7	849.5	851.3	853.1	854.2	854.4	854.7	855.1	855.3	854.7
127.5°	926.6	927.6	928.6	929.6	930.7	931.4	931.7	932.1	932.5	932.8	932.5
130°	975.0	976.5	978.0	979.5	981.0	982.0	982.7	983.2	983.8	984.4	984.1
132.5°	1023.4	1025.9	1028.3	1030.8	1033.2	1034.4	1034.3	1034.1	1034.0	1033.9	1033.6
135°	1100.1	1101.9	1103.7	1105.5	1107.2	1108.3	1108.6	1108.9	1109.2	1109.5	1109.5
137.5°	1172.2	1173.9	1175.6	1177.3	1179.1	1180.3	1181.0	1181.6	1182.2	1182.9	1183.3
140°	1218.4	1219.9	1221.4	1222.9	1224.4	1225.6	1226.5	1227.4	1228.3	1229.2	1229.8
142.5°	1264.7	1266.0	1267.2	1268.5	1269.7	1270.9	1272.0	1273.2	1274.3	1275.4	1275.8
145°	1332.8	1333.9	1335.2	1336.3	1337.6	1338.5	1339.4	1340.3	1341.2	1342.1	1342.1
147.5°	1395.7	1396.3	1397.0	1397.7	1398.3	1399.0	1399.7	1400.4	1401.1	1401.9	1402.6
150°	1437.6	1437.3	1437.1	1436.7	1436.5	1436.9	1438.1	1439.3	1440.5	1441.7	1441.7
152.5°	1472.0	1472.5	1472.9	1473.3	1473.7	1474.2	1474.7	1475.2	1475.6	1476.1	1476.9
155°	1525.1	1525.1	1525.1	1525.1	1525.1	1525.2	1525.5	1525.8	1526.1	1526.4	1527.6
157.5°	1572.4	1571.7	1571.1	1570.4	1569.8	1569.6	1569.9	1570.2	1570.5	1570.7	1572.0
160°	1600.4	1599.5	1598.6	1597.7	1596.8	1596.5	1596.8	1597.1	1597.4	1597.7	1598.8
162.5°	1625.1	1624.4	1623.8	1623.2	1622.5	1622.2	1622.2	1622.3	1622.4	1622.4	1623.9
165°	1658.2	1657.6	1657.0	1656.4	1655.8	1655.6	1656.0	1656.3	1656.5	1656.9	1658.0
167.5°	1686.1	1685.0	1683.8	1682.6	1681.4	1680.8	1680.8	1680.8	1680.8	1680.8	1682.6
170°	1701.2	1700.0	1698.8	1697.6	1696.5	1695.9	1695.9	1695.9	1695.9	1695.9	1697.6
172.5°	1712.0	1710.8	1709.6	1708.4	1707.2	1706.6	1706.6	1706.6	1706.6	1706.6	1708.4
175°	1724.1	1722.9	1721.7	1720.5	1719.3	1718.7	1718.7	1718.7	1718.7	1718.7	1720.5
177.5°	1730.3	1729.3	1728.4	1727.4	1726.4	1725.8	1725.6	1725.4	1725.1	1724.9	1726.4
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333399-940

CATALOG NUMBER: S125DIW-S610D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	853.9	855.2	856.3	856.8	856.8	856.6	856.5	856.4
5°	849.6	851.0	852.3	852.9	852.7	852.7	852.5	852.3
7.5°	841.0	842.3	843.6	844.3	844.1	843.9	843.8	843.6
10°	833.7	834.9	836.2	836.7	836.5	836.3	836.2	836.1
12.5°	824.0	825.0	825.9	826.4	826.3	826.3	826.3	826.3
15°	807.1	807.8	808.6	809.0	809.0	809.0	809.0	809.0
17.5°	787.4	788.3	789.3	789.3	788.5	787.8	787.1	786.3
20°	772.4	773.5	774.5	774.7	773.9	773.2	772.4	771.7
22.5°	755.5	756.2	756.9	757.0	756.4	755.9	755.4	754.9
25°	728.3	728.5	728.9	728.8	728.3	727.9	727.5	727.0
27.5°	699.7	699.8	699.8	699.6	699.2	698.7	698.3	697.9
30°	678.9	678.7	678.3	678.0	677.5	677.1	676.6	676.2
32.5°	657.9	657.3	656.7	656.1	655.3	654.5	653.6	652.8
35°	625.2	624.5	623.7	622.7	621.5	620.3	619.1	617.9
37.5°	590.8	589.8	588.6	587.7	587.0	586.4	585.7	585.0
40°	567.0	565.7	564.4	563.5	563.0	562.6	562.1	561.7
42.5°	543.5	542.2	541.0	540.0	539.3	538.7	538.0	537.3
45°	508.5	506.8	505.0	503.8	503.4	502.9	502.5	502.0
47.5°	471.8	469.9	468.1	466.7	465.7	464.6	463.5	462.4
50°	446.7	444.7	442.7	441.2	440.1	439.1	438.0	437.0
52.5°	422.1	420.4	418.7	417.3	416.2	414.9	413.8	412.6
55°	384.1	382.8	381.5	380.2	379.2	378.1	377.1	376.0
57.5°	346.3	344.6	342.9	341.7	341.2	340.5	340.0	339.5
60°	320.8	319.3	317.8	316.6	315.5	314.4	313.3	312.4
62.5°	296.2	294.6	292.9	291.8	291.0	290.1	289.3	288.5
65°	257.4	256.1	254.8	253.8	253.2	252.5	252.0	251.4
67.5°	220.5	219.4	218.2	217.4	217.0	216.7	216.3	216.0
70°	196.0	195.1	194.2	193.5	192.9	192.3	191.6	191.1
72.5°	173.0	172.0	170.9	170.1	169.5	169.0	168.4	167.7
75°	137.3	136.9	136.4	135.9	135.3	134.6	134.1	133.5
77.5°	104.6	104.3	104.1	103.7	103.3	102.9	102.5	102.0
80°	83.7	83.6	83.4	83.2	82.8	82.6	82.3	81.9
82.5°	63.9	63.7	63.4	63.2	63.2	63.1	63.0	63.0
85°	37.6	37.5	37.4	37.1	36.8	36.5	36.2	35.9
87.5°	19.0	19.3	19.6	19.7	19.6	19.6	19.5	19.4
90°	24.5	26.0	27.5	28.7	29.6	30.5	31.4	32.3
92.5°	55.6	57.5	59.6	60.8	61.5	62.2	62.8	63.5
95°	107.7	109.9	111.9	113.2	113.9	114.5	115.0	115.7
97.5°	168.8	170.8	172.7	174.0	174.3	174.7	175.0	175.4
100°	211.2	213.8	216.5	218.2	218.7	219.4	220.0	220.5
102.5°	254.7	257.6	260.5	262.4	263.2	264.0	264.9	265.7
105°	325.0	326.8	328.6	329.9	330.8	331.7	332.6	333.5
107.5°	400.9	401.8	402.7	403.1	403.1	403.1	403.0	402.9
110°	453.7	454.6	455.5	455.8	455.5	455.1	454.9	454.6



TEST NUMBER: P333399-940

CATALOG NUMBER: S125DIW-S610D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	506.5	506.9	507.3	507.3	506.8	506.2	505.7	505.2
115°	587.1	586.8	586.5	586.2	585.9	585.6	585.3	585.1
117.5°	667.8	668.1	668.2	667.8	666.6	665.4	664.2	663.0
120°	722.2	722.2	722.2	721.6	720.4	719.2	718.0	716.8
122.5°	775.5	775.3	775.0	774.5	773.5	772.5	771.5	770.6
125°	854.2	853.5	852.9	852.5	852.2	851.9	851.6	851.3
127.5°	932.2	931.9	931.6	931.1	930.5	930.0	929.3	928.7
130°	983.8	983.6	983.2	982.8	982.2	981.6	981.0	980.4
132.5°	1033.3	1033.0	1032.7	1032.2	1031.4	1030.5	1029.7	1028.8
135°	1109.5	1109.5	1109.5	1108.9	1107.7	1106.5	1105.3	1104.1
137.5°	1183.7	1184.0	1184.4	1183.8	1182.3	1180.8	1179.3	1177.8
140°	1230.4	1231.0	1231.5	1231.1	1229.7	1228.2	1226.6	1225.1
142.5°	1276.1	1276.5	1276.9	1276.3	1274.8	1273.4	1271.8	1270.3
145°	1342.1	1342.1	1342.1	1341.7	1340.8	1339.9	1339.0	1338.1
147.5°	1403.3	1404.0	1404.7	1404.1	1402.0	1400.0	1398.0	1396.0
150°	1441.7	1441.7	1441.7	1441.4	1440.7	1440.2	1439.6	1439.0
152.5°	1477.6	1478.3	1479.0	1478.8	1477.7	1476.7	1475.6	1474.5
155°	1528.7	1530.0	1531.2	1531.1	1529.6	1528.0	1526.5	1525.1
157.5°	1573.2	1574.4	1575.6	1575.2	1573.2	1571.2	1569.2	1567.3
160°	1600.1	1601.2	1602.5	1602.3	1600.8	1599.3	1597.9	1596.3
162.5°	1625.3	1626.7	1628.2	1628.0	1626.3	1624.5	1622.8	1621.0
165°	1659.2	1660.5	1661.6	1661.3	1659.6	1657.8	1656.0	1654.1
167.5°	1684.4	1686.1	1687.9	1687.9	1686.0	1684.3	1682.4	1680.5
170°	1699.4	1701.2	1703.0	1702.9	1700.8	1698.7	1696.6	1694.5
172.5°	1710.2	1712.0	1713.8	1713.8	1711.9	1710.0	1708.2	1706.4
175°	1722.3	1724.1	1725.9	1725.7	1723.7	1721.5	1719.5	1717.3
177.5°	1727.8	1729.2	1730.6	1730.5	1728.8	1727.2	1725.5	1723.9
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1

(END OF REPORT)