

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333729-940

Luminaire Tested: **S125RDIW-S1270D1050U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333729-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7629.3 lumens  
Efficiency: N/A  
Efficacy: 113.2 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - · - 135°-315°



TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63	58
1	100	96	92	89	93	89	86	83	78	75	73	67	65	63	57	55	54	49
2	91	84	78	73	85	79	74	69	68	65	61	59	56	54	50	48	46	42
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	45	42	40	36
4	77	66	58	52	71	62	55	50	54	49	45	47	43	40	40	37	35	31
5	71	59	51	45	66	55	48	43	49	43	39	42	38	35	37	33	30	27
6	65	53	45	39	61	50	43	38	44	38	34	38	34	30	33	30	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	24	22	19
9	52	40	33	27	49	38	31	26	34	28	24	30	25	22	26	22	20	17
10	49	37	29	25	46	35	28	24	31	25	22	27	23	20	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10936	10936	10936	10936
5°	12582	10950	9671	10950
10°	14432	10895	8533	10895
15°	15588	10783	7585	10783
20°	17189	10654	7003	10654
25°	19892	10481	6499	10481
30°	21647	10300	6169	10300
35°	18260	10089	5864	10089
40°	12752	9711	5602	9711
45°	9460	9199	5345	9199
50°	7543	8667	5126	8667
55°	6402	8007	4931	8007
60°	5531	7417	4615	7417
65°	4928	6776	3972	6776
70°	4330	6209	3622	6209
75°	3748	5375	3401	5375
80°	2841	4523	2841	4523
85°	2371	3557	2675	3557



TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.4	2.1
10°-20°	475.9	6.2
20°-30°	754.5	9.9
30°-40°	909.8	11.9
40°-50°	812.5	10.7
50°-60°	623.1	8.2
60°-70°	404.9	5.3
70°-80°	196.9	2.6
80°-90°	49.5	0.6
90°-100°	77.8	1.0
100°-110°	229.6	3.0
110°-120°	388.9	5.1
120°-130°	511.9	6.7
130°-140°	573.6	7.5
140°-150°	562.1	7.4
150°-160°	472.2	6.2
160°-170°	313.9	4.1
170°-180°	109.8	1.4
0°-30°	1392.7	18.3
0°-40°	2302.6	30.2
0°-60°	3738.2	49.0
0°-90°	4389.5	57.5
90°-120°	696.4	9.1
90°-150°	2344.0	30.7
90°-180°	3240.0	42.5
0°-180°	7629.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1693	1693	1693	1693	1693	
5°	1941	1689	1492	1689	1941	194
15°	2331	1613	1134	1613	2331	668
25°	2792	1471	912	1471	2792	1282
35°	2316	1280	744	1280	2316	1399
45°	1036	1007	585	1007	1036	826
55°	569	711	438	711	569	516
65°	322	443	260	443	322	321
75°	150	215	136	215	150	160
85°	32	48	36	48	32	37
90°	22	1	22	1	22	14
95°	78	59	78	59	78	79
105°	224	206	224	206	224	237
115°	393	389	393	389	393	389
125°	572	568	572	568	572	511
135°	742	739	742	739	742	572
145°	899	895	899	895	899	561
155°	1025	1025	1025	1025	1025	471
165°	1111	1114	1111	1114	1111	313
175°	1154	1158	1154	1158	1154	110
180°	1161	1161	1161	1161	1161	



TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1781.1	1780.0	1782.3	1776.1	1776.6	1767.2	1767.2	1760.0	1750.5	1743.3	1740.0
5°	1940.7	1942.1	1939.3	1928.9	1922.0	1911.6	1899.7	1878.8	1861.4	1844.8	1831.6
7.5°	2105.1	2106.0	2096.9	2093.6	2076.1	2063.3	2037.0	2008.7	1983.5	1951.6	1927.1
10°	2200.7	2200.0	2190.2	2182.6	2167.3	2147.9	2122.2	2088.7	2057.5	2022.8	1989.4
12.5°	2256.3	2254.5	2251.4	2242.1	2227.9	2210.7	2188.9	2156.1	2117.5	2079.5	2040.5
15°	2331.4	2326.5	2317.5	2305.6	2285.5	2265.3	2241.0	2211.8	2175.0	2131.9	2095.7
17.5°	2424.2	2424.4	2410.5	2394.1	2366.7	2331.1	2293.6	2246.4	2196.4	2148.9	2110.5
20°	2501.0	2498.8	2485.0	2453.0	2421.7	2377.2	2334.1	2276.4	2215.3	2153.4	2105.4
22.5°	2611.1	2605.7	2591.2	2549.2	2500.7	2443.4	2377.5	2307.0	2233.1	2162.8	2099.9
25°	2791.5	2787.3	2758.9	2710.2	2642.0	2553.8	2467.6	2371.0	2264.7	2172.2	2095.7
27.5°	2915.0	2910.4	2889.2	2848.8	2786.0	2693.1	2576.4	2447.3	2314.5	2187.4	2077.1
30°	2902.7	2913.1	2910.4	2891.6	2844.4	2760.9	2653.2	2507.9	2350.1	2200.7	2069.3
32.5°	2728.1	2737.5	2761.9	2798.7	2801.5	2768.1	2687.7	2553.5	2390.1	2220.2	2063.2
35°	2316.0	2328.6	2375.9	2450.2	2547.5	2628.9	2645.5	2573.3	2426.6	2243.8	2054.1
37.5°	1780.6	1849.0	1888.7	1967.0	2114.1	2263.7	2407.5	2460.5	2398.1	2234.1	2039.2
40°	1512.5	1529.2	1600.1	1688.4	1812.1	1967.8	2172.9	2320.9	2325.8	2211.8	2015.8
42.5°	1294.6	1315.7	1364.3	1434.9	1540.8	1696.5	1908.2	2103.5	2194.1	2150.6	1985.2
45°	1035.7	1051.7	1087.2	1141.4	1222.7	1351.3	1533.4	1759.3	1938.7	2008.8	1903.2
47.5°	850.8	859.4	890.3	931.6	991.8	1085.5	1226.5	1422.5	1637.6	1788.5	1773.6
50°	750.7	760.5	784.1	815.4	866.1	945.3	1057.9	1221.3	1443.1	1627.2	1664.1
52.5°	672.9	680.9	695.6	725.2	767.1	828.0	918.9	1066.7	1266.2	1462.0	1547.3
55°	568.6	574.2	585.9	602.6	636.1	679.8	758.3	860.5	1021.8	1219.2	1344.3
57.5°	482.7	485.4	492.9	508.4	531.5	563.5	620.2	706.8	822.4	1000.2	1138.3
60°	428.2	431.0	440.7	451.1	469.2	498.4	542.9	603.3	714.5	861.2	1000.9
62.5°	384.8	386.5	390.7	401.1	417.0	439.4	474.5	523.8	612.2	741.1	873.1
65°	322.5	323.2	324.6	333.0	342.7	359.4	382.3	417.1	483.8	581.1	697.9
67.5°	262.8	263.7	268.6	271.5	281.7	290.4	303.9	330.5	377.5	443.1	533.9
70°	229.3	228.7	233.5	237.0	240.5	250.9	259.9	281.5	310.7	360.8	436.5
72.5°	198.2	196.4	198.5	199.7	204.4	211.4	220.5	233.7	256.2	290.7	348.7
75°	150.2	150.9	150.9	152.2	155.7	158.5	161.2	168.2	180.7	203.7	235.0
77.5°	105.4	104.2	107.2	107.6	109.7	112.7	115.1	117.9	123.1	132.5	148.6
80°	76.4	76.4	77.1	79.3	78.6	79.9	83.4	86.2	92.5	98.0	103.5
82.5°	58.7	58.1	58.8	59.2	59.1	60.5	61.7	62.2	64.6	67.4	71.3
85°	32.0	32.0	32.6	32.6	33.3	33.3	34.1	34.1	34.1	34.8	35.5
87.5°	16.6	15.9	15.2	15.1	15.5	16.5	15.7	15.0	14.8	14.5	14.8
90°	21.7	21.0	20.5	19.9	19.3	18.5	17.5	16.5	15.4	14.4	13.0
92.5°	42.6	42.2	41.7	41.3	40.8	40.0	38.7	37.4	36.0	34.7	33.0
95°	77.7	77.3	76.9	76.5	76.1	75.2	73.7	72.4	71.0	69.6	67.6
97.5°	117.8	117.6	117.3	117.1	116.8	116.1	114.8	113.4	112.1	110.8	108.0
100°	148.2	147.8	147.4	147.0	146.6	145.4	143.7	141.9	140.1	138.2	135.6
102.5°	178.5	178.0	177.5	176.8	176.3	175.0	173.1	171.1	169.2	167.2	165.9
105°	224.1	223.5	222.8	222.3	221.7	220.8	219.5	218.4	217.1	216.0	214.7
107.5°	270.7	270.7	270.8	270.8	270.9	270.5	270.0	269.4	268.8	268.1	267.2
110°	305.4	305.6	305.8	306.0	306.2	306.0	305.4	304.8	304.2	303.6	303.0



TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	339.4	339.7	340.1	340.5	340.8	340.8	340.5	340.3	340.0	339.7	338.9
115°	393.1	393.2	393.4	393.6	393.9	394.0	394.2	394.4	394.7	394.8	394.4
117.5°	445.4	446.2	447.0	447.8	448.6	449.0	448.8	448.6	448.5	448.4	448.0
120°	481.6	482.4	483.2	484.0	484.8	485.2	485.2	485.2	485.2	485.2	485.0
122.5°	517.7	518.4	519.0	519.7	520.3	520.7	520.8	521.0	521.2	521.4	520.8
125°	571.9	572.1	572.3	572.6	572.7	573.0	573.5	573.8	574.3	574.6	574.4
127.5°	624.0	624.4	624.8	625.2	625.6	625.9	626.1	626.2	626.5	626.7	626.4
130°	658.7	659.1	659.5	659.9	660.3	660.6	660.8	661.0	661.2	661.4	661.0
132.5°	691.2	691.8	692.3	692.9	693.5	693.8	694.0	694.2	694.5	694.6	694.7
135°	741.8	742.6	743.4	744.2	745.0	745.4	745.4	745.4	745.4	745.4	745.2
137.5°	791.3	792.3	793.4	794.3	795.3	795.7	795.5	795.2	795.0	794.8	794.3
140°	823.1	824.1	825.1	826.2	827.2	827.4	827.1	826.6	826.3	825.8	825.2
142.5°	853.5	854.5	855.5	856.5	857.5	857.9	857.6	857.4	857.1	856.9	856.1
145°	899.0	899.6	900.2	900.8	901.4	901.7	901.7	901.7	901.7	901.7	901.2
147.5°	937.9	939.2	940.6	942.0	943.3	943.8	943.3	942.8	942.4	941.8	941.4
150°	966.8	967.1	967.6	968.0	968.4	968.6	968.6	968.6	968.6	968.6	967.8
152.5°	990.6	991.3	992.1	992.8	993.5	993.6	993.2	992.7	992.2	991.8	991.4
155°	1024.6	1025.6	1026.6	1027.6	1028.6	1028.8	1028.0	1027.2	1026.4	1025.6	1025.3
157.5°	1053.0	1054.3	1055.6	1056.9	1058.3	1058.5	1057.7	1056.9	1056.1	1055.3	1055.2
160°	1072.5	1073.5	1074.5	1075.5	1076.5	1076.7	1075.8	1075.0	1074.2	1073.4	1073.2
162.5°	1089.1	1090.3	1091.5	1092.6	1093.8	1093.9	1092.9	1092.0	1091.0	1090.0	1090.0
165°	1111.3	1112.6	1113.7	1115.0	1116.2	1116.3	1115.5	1114.7	1113.9	1113.1	1112.9
167.5°	1129.1	1130.3	1131.6	1132.8	1134.1	1134.1	1132.8	1131.7	1130.4	1129.3	1129.3
170°	1138.4	1139.9	1141.3	1142.6	1144.1	1144.2	1143.0	1141.7	1140.6	1139.3	1139.3
172.5°	1146.4	1147.6	1148.9	1150.1	1151.4	1151.4	1150.2	1149.0	1147.8	1146.6	1146.6
175°	1153.8	1155.2	1156.6	1158.1	1159.4	1159.6	1158.3	1157.1	1155.9	1154.7	1154.7
177.5°	1158.2	1159.3	1160.4	1161.5	1162.6	1162.7	1161.8	1160.8	1159.8	1158.9	1159.0
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0



TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1740.0	1736.1	1728.8	1722.2	1713.9	1706.6	1701.6	1695.5	1687.7	1678.3	1670.4
5°	1816.9	1801.7	1781.5	1764.2	1742.0	1724.6	1706.5	1689.1	1671.7	1649.5	1630.0
7.5°	1902.4	1870.8	1840.0	1801.4	1766.4	1735.1	1705.0	1674.6	1644.8	1613.3	1582.9
10°	1954.6	1916.4	1874.0	1825.3	1780.8	1738.5	1699.5	1661.3	1621.0	1585.6	1547.3
12.5°	2003.6	1954.2	1905.7	1844.2	1790.8	1739.0	1689.5	1641.8	1598.7	1552.7	1511.7
15°	2047.7	1999.1	1944.9	1869.8	1795.5	1732.9	1674.5	1612.7	1559.1	1507.7	1461.8
17.5°	2064.8	2013.8	1950.9	1878.7	1797.4	1718.7	1643.5	1575.7	1512.7	1452.8	1401.1
20°	2058.2	2008.8	1944.2	1875.4	1788.5	1706.5	1625.1	1550.1	1479.9	1416.6	1361.7
22.5°	2042.1	1991.0	1928.6	1855.9	1773.4	1686.5	1599.6	1519.5	1445.9	1380.5	1320.5
25°	2017.9	1948.4	1884.5	1813.5	1735.0	1648.8	1559.1	1470.8	1392.3	1325.5	1260.3
27.5°	1992.7	1905.9	1824.6	1754.2	1671.2	1594.3	1507.8	1417.3	1334.7	1266.8	1199.7
30°	1969.9	1872.6	1782.9	1703.0	1624.4	1551.5	1469.5	1381.2	1296.4	1226.2	1158.1
32.5°	1941.5	1838.1	1739.5	1647.3	1571.6	1499.2	1425.0	1340.6	1258.0	1185.5	1116.3
35°	1905.9	1773.9	1666.9	1568.9	1484.7	1414.5	1347.8	1279.7	1196.9	1121.9	1054.4
37.5°	1859.2	1709.4	1585.6	1478.7	1390.1	1319.6	1266.9	1204.6	1129.1	1057.2	994.7
40°	1830.9	1662.7	1527.1	1421.5	1328.3	1253.9	1204.6	1151.8	1083.0	1015.6	953.0
42.5°	1793.1	1619.9	1468.2	1358.1	1264.4	1192.8	1142.9	1096.7	1039.0	975.5	908.5
45°	1719.0	1536.9	1377.7	1259.5	1165.0	1094.8	1048.2	1007.2	963.4	905.0	846.6
47.5°	1622.5	1450.3	1283.7	1154.7	1062.1	996.9	951.7	919.4	888.1	838.4	781.7
50°	1545.2	1379.1	1216.4	1091.3	992.6	930.8	888.3	862.6	834.1	788.9	741.6
52.5°	1454.0	1305.6	1146.4	1018.4	925.3	867.4	826.6	800.9	777.4	740.6	695.5
55°	1310.3	1180.3	1034.3	918.2	832.8	774.4	735.4	711.1	697.2	665.9	630.4
57.5°	1144.4	1051.2	922.6	810.7	735.0	677.3	648.8	628.1	612.4	590.3	565.3
60°	1028.8	963.4	848.0	741.6	672.2	617.2	591.6	574.2	559.5	540.8	521.3
62.5°	911.4	863.9	763.5	672.2	608.2	562.2	538.1	522.5	505.6	492.9	474.0
65°	754.2	711.8	642.3	570.7	511.6	474.7	457.4	443.4	433.0	419.1	405.9
67.5°	586.7	569.4	521.5	472.1	429.7	396.9	381.9	372.2	359.6	351.3	342.2
70°	483.8	475.5	441.4	408.8	369.1	346.9	333.0	328.8	313.5	305.1	298.9
72.5°	392.6	388.7	369.1	346.4	318.5	299.0	286.2	281.5	271.8	265.1	261.1
75°	269.0	270.4	266.9	252.4	241.9	229.3	218.3	215.4	208.6	203.0	199.5
77.5°	170.1	177.3	177.5	176.8	172.6	165.1	160.4	158.4	151.5	149.5	148.6
80°	116.8	124.4	131.3	130.6	129.3	127.2	123.8	121.6	118.2	116.1	114.7
82.5°	77.8	85.0	90.8	94.5	94.3	92.2	89.8	88.8	88.1	86.6	86.3
85°	36.8	38.3	40.3	45.2	48.7	49.3	48.7	48.0	45.8	46.5	47.3
87.5°	15.2	14.8	15.1	14.8	13.9	16.4	17.7	18.0	17.2	16.4	15.6
90°	11.7	10.3	8.8	7.3	5.7	4.1	2.5	0.9	2.5	4.1	5.7
92.5°	31.2	29.5	27.8	26.4	25.2	24.1	23.0	21.8	23.0	24.1	25.2
95°	65.5	63.6	61.5	60.4	59.9	59.6	59.1	58.8	59.1	59.6	59.9
97.5°	105.2	102.5	99.7	98.3	98.1	97.9	97.7	97.6	97.7	97.9	98.1
100°	133.0	130.4	127.8	126.5	126.5	126.5	126.5	126.5	126.5	126.5	126.5
102.5°	164.5	163.2	161.8	160.8	160.0	159.2	158.4	157.6	158.4	159.2	160.0
105°	213.6	212.3	211.2	210.0	209.0	208.0	207.0	206.0	207.0	208.0	209.0
107.5°	266.4	265.4	264.5	263.5	262.5	261.5	260.5	259.5	260.5	261.5	262.5
110°	302.4	301.8	301.2	300.4	299.3	298.4	297.4	296.3	297.4	298.4	299.3





TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	338.2	337.4	336.7	336.0	335.6	335.0	334.5	333.9	334.5	335.0	335.6
115°	394.0	393.6	393.2	392.6	391.8	391.0	390.2	389.4	390.2	391.0	391.8
117.5°	447.6	447.3	446.9	446.6	446.1	445.8	445.4	445.1	445.4	445.8	446.1
120°	484.8	484.6	484.4	483.8	482.8	481.8	480.8	479.7	480.8	481.8	482.8
122.5°	520.3	519.8	519.2	518.8	518.4	518.1	517.7	517.4	517.7	518.1	518.4
125°	574.3	574.1	573.8	573.1	571.9	570.7	569.5	568.3	569.5	570.7	571.9
127.5°	626.2	626.0	625.7	625.3	624.6	623.9	623.2	622.5	623.2	623.9	624.6
130°	660.6	660.2	659.8	659.1	658.1	657.1	656.0	655.1	656.0	657.1	658.1
132.5°	694.8	694.9	695.0	694.2	692.5	690.9	689.2	687.6	689.2	690.9	692.5
135°	745.0	744.8	744.6	744.0	742.7	741.5	740.3	739.0	740.3	741.5	742.7
137.5°	793.9	793.4	793.0	792.2	791.0	789.9	788.7	787.6	788.7	789.9	791.0
140°	824.7	824.0	823.4	822.6	821.6	820.6	819.6	818.6	819.6	820.6	821.6
142.5°	855.4	854.6	853.9	853.1	852.2	851.4	850.5	849.7	850.5	851.4	852.2
145°	900.5	899.9	899.3	898.6	897.8	897.0	896.2	895.4	896.2	897.0	897.8
147.5°	940.8	940.4	940.0	939.4	939.0	938.6	938.2	937.7	938.2	938.6	939.0
150°	967.0	966.2	965.4	965.1	965.3	965.5	965.7	965.9	965.7	965.5	965.3
152.5°	991.0	990.8	990.4	990.2	989.9	989.5	989.3	989.0	989.3	989.5	989.9
155°	1025.1	1024.9	1024.7	1024.6	1024.6	1024.6	1024.6	1024.6	1024.6	1024.6	1024.6
157.5°	1054.9	1054.7	1054.5	1054.6	1055.1	1055.5	1056.0	1056.4	1056.0	1055.5	1055.1
160°	1073.0	1072.8	1072.6	1072.8	1073.4	1074.0	1074.6	1075.2	1074.6	1074.0	1073.4
162.5°	1089.9	1089.9	1089.8	1090.0	1090.5	1090.9	1091.4	1091.8	1091.4	1090.9	1090.5
165°	1112.8	1112.6	1112.3	1112.4	1112.9	1113.2	1113.7	1114.1	1113.7	1113.2	1112.9
167.5°	1129.3	1129.3	1129.3	1129.6	1130.4	1131.2	1132.0	1132.8	1132.0	1131.2	1130.4
170°	1139.3	1139.3	1139.3	1139.8	1140.6	1141.4	1142.2	1143.0	1142.2	1141.4	1140.6
172.5°	1146.6	1146.6	1146.6	1147.0	1147.8	1148.6	1149.4	1150.2	1149.4	1148.6	1147.8
175°	1154.7	1154.7	1154.7	1155.1	1155.9	1156.7	1157.5	1158.3	1157.5	1156.7	1155.9
177.5°	1159.2	1159.3	1159.5	1159.9	1160.6	1161.2	1161.8	1162.5	1161.8	1161.2	1160.6
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0



TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1664.9	1657.2	1651.5	1640.4	1632.6	1629.3	1623.2	1621.5	1627.6	1623.2	1622.6
5°	1615.4	1595.3	1579.3	1563.3	1545.9	1534.8	1518.1	1515.3	1511.2	1504.9	1503.5
7.5°	1556.0	1529.8	1509.2	1482.8	1459.8	1441.4	1420.5	1410.6	1405.2	1397.1	1386.3
10°	1516.0	1484.7	1457.0	1430.5	1402.0	1379.1	1358.3	1342.2	1331.8	1322.1	1317.9
12.5°	1476.5	1444.7	1409.1	1377.2	1345.3	1319.6	1296.5	1286.1	1274.5	1263.1	1253.4
15°	1415.2	1372.8	1333.9	1297.1	1270.0	1242.2	1219.9	1204.6	1187.2	1182.4	1163.6
17.5°	1350.1	1308.6	1263.0	1224.2	1192.8	1162.2	1137.7	1120.3	1107.3	1089.4	1080.8
20°	1309.6	1260.3	1215.8	1180.3	1145.5	1109.4	1084.3	1069.8	1057.2	1042.7	1035.7
22.5°	1266.2	1218.0	1172.3	1130.8	1095.5	1059.9	1042.1	1027.0	1012.7	999.3	990.1
25°	1202.6	1153.9	1105.9	1062.8	1026.0	1000.2	979.4	962.0	954.4	941.2	931.4
27.5°	1139.5	1087.8	1038.0	995.1	966.2	940.8	923.6	909.9	896.1	884.6	876.1
30°	1098.9	1046.2	991.9	957.9	927.3	902.9	884.1	870.9	860.5	850.1	843.8
32.5°	1058.4	1003.9	955.7	918.9	890.0	869.0	849.7	837.0	826.1	814.5	807.2
35°	993.3	937.7	898.8	862.6	834.1	814.7	801.5	783.4	774.4	766.0	758.3
37.5°	932.8	881.1	839.0	807.3	782.6	763.2	746.1	736.4	725.2	717.7	711.4
40°	888.3	841.1	802.8	769.5	751.4	729.9	713.9	701.3	693.0	683.3	676.4
42.5°	848.3	804.4	767.2	737.3	714.7	696.5	681.1	668.5	658.0	651.0	645.2
45°	791.8	748.0	711.8	683.9	663.2	645.8	629.7	623.5	609.6	601.3	598.5
47.5°	733.2	694.0	659.1	633.5	612.1	595.7	580.7	567.9	560.3	552.1	547.6
50°	693.8	656.2	623.5	598.5	577.7	559.5	545.6	537.3	526.9	519.2	513.7
52.5°	654.2	619.5	586.8	562.8	544.8	526.7	511.2	502.8	492.9	488.1	484.2
55°	597.8	561.0	533.2	509.5	490.7	474.0	459.5	451.1	444.9	440.0	438.6
57.5°	533.9	504.6	478.8	457.5	438.0	422.3	409.6	401.6	396.1	395.4	391.2
60°	492.1	465.7	442.1	419.1	402.4	387.9	376.7	367.7	362.1	361.4	360.1
62.5°	450.4	425.1	403.1	383.0	368.0	353.9	343.4	333.2	329.9	326.5	323.3
65°	388.5	365.6	347.6	331.5	315.6	303.7	293.4	287.0	279.5	275.3	267.6
67.5°	327.8	310.0	292.7	279.2	266.6	255.4	246.7	237.5	232.3	229.0	223.4
70°	287.8	273.8	256.5	241.9	232.2	223.1	216.2	205.7	202.2	199.5	196.7
72.5°	249.9	237.7	223.1	211.3	201.6	193.1	185.0	180.1	176.7	173.9	172.3
75°	196.7	184.9	172.4	164.1	157.1	150.2	146.0	142.5	141.1	140.4	137.6
77.5°	144.5	138.2	128.1	121.5	116.9	114.1	110.4	108.6	108.4	105.4	104.4
80°	110.5	107.0	98.7	95.9	92.5	89.7	87.6	84.1	80.6	79.3	77.1
82.5°	82.1	78.6	75.3	70.9	67.9	66.3	64.2	63.0	63.4	61.4	60.5
85°	43.8	40.3	39.0	38.3	36.8	38.3	37.5	36.8	36.1	35.5	36.1
87.5°	15.3	15.7	15.4	16.8	15.4	16.2	16.4	16.1	16.3	16.5	16.1
90°	7.3	8.8	10.3	11.7	13.0	14.4	15.4	16.5	17.5	18.5	19.3
92.5°	26.4	27.8	29.5	31.2	33.0	34.7	36.0	37.4	38.7	40.0	40.8
95°	60.4	61.5	63.6	65.5	67.6	69.6	71.0	72.4	73.7	75.2	76.1
97.5°	98.3	99.7	102.5	105.2	108.0	110.8	112.1	113.4	114.8	116.1	116.8
100°	126.5	127.8	130.4	133.0	135.6	138.2	140.1	141.9	143.7	145.4	146.6
102.5°	160.8	161.8	163.2	164.5	165.9	167.2	169.2	171.1	173.1	175.0	176.3
105°	210.0	211.2	212.3	213.6	214.7	216.0	217.1	218.4	219.5	220.8	221.7
107.5°	263.5	264.5	265.4	266.4	267.2	268.1	268.8	269.4	270.0	270.5	270.9
110°	300.4	301.2	301.8	302.4	303.0	303.6	304.2	304.8	305.4	306.0	306.2



TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	336.0	336.7	337.4	338.2	338.9	339.7	340.0	340.3	340.5	340.8	340.8
115°	392.6	393.2	393.6	394.0	394.4	394.8	394.7	394.4	394.2	394.0	393.9
117.5°	446.6	446.9	447.3	447.6	448.0	448.4	448.5	448.6	448.8	449.0	448.6
120°	483.8	484.4	484.6	484.8	485.0	485.2	485.2	485.2	485.2	485.2	484.8
122.5°	518.8	519.2	519.8	520.3	520.8	521.4	521.2	521.0	520.8	520.7	520.3
125°	573.1	573.8	574.1	574.3	574.4	574.6	574.3	573.8	573.5	573.0	572.7
127.5°	625.3	625.7	626.0	626.2	626.4	626.7	626.5	626.2	626.1	625.9	625.6
130°	659.1	659.8	660.2	660.6	661.0	661.4	661.2	661.0	660.8	660.6	660.3
132.5°	694.2	695.0	694.9	694.8	694.7	694.6	694.5	694.2	694.0	693.8	693.5
135°	744.0	744.6	744.8	745.0	745.2	745.4	745.4	745.4	745.4	745.4	745.0
137.5°	792.2	793.0	793.4	793.9	794.3	794.8	795.0	795.2	795.5	795.7	795.3
140°	822.6	823.4	824.0	824.7	825.2	825.8	826.3	826.6	827.1	827.4	827.2
142.5°	853.1	853.9	854.6	855.4	856.1	856.9	857.1	857.4	857.6	857.9	857.5
145°	898.6	899.3	899.9	900.5	901.2	901.7	901.7	901.7	901.7	901.7	901.4
147.5°	939.4	940.0	940.4	940.8	941.4	941.8	942.4	942.8	943.3	943.8	943.3
150°	965.1	965.4	966.2	967.0	967.8	968.6	968.6	968.6	968.6	968.6	968.4
152.5°	990.2	990.4	990.8	991.0	991.4	991.8	992.2	992.7	993.2	993.6	993.5
155°	1024.6	1024.7	1024.9	1025.1	1025.3	1025.6	1026.4	1027.2	1028.0	1028.8	1028.6
157.5°	1054.6	1054.5	1054.7	1054.9	1055.2	1055.3	1056.1	1056.9	1057.7	1058.5	1058.3
160°	1072.8	1072.6	1072.8	1073.0	1073.2	1073.4	1074.2	1075.0	1075.8	1076.7	1076.5
162.5°	1090.0	1089.8	1089.9	1089.9	1090.0	1090.0	1091.0	1092.0	1092.9	1093.9	1093.8
165°	1112.4	1112.3	1112.6	1112.8	1112.9	1113.1	1113.9	1114.7	1115.5	1116.3	1116.2
167.5°	1129.6	1129.3	1129.3	1129.3	1129.3	1129.3	1130.4	1131.7	1132.8	1134.1	1134.1
170°	1139.8	1139.3	1139.3	1139.3	1139.3	1139.3	1140.6	1141.7	1143.0	1144.2	1144.1
172.5°	1147.0	1146.6	1146.6	1146.6	1146.6	1146.6	1147.8	1149.0	1150.2	1151.4	1151.4
175°	1155.1	1154.7	1154.7	1154.7	1154.7	1154.7	1155.9	1157.1	1158.3	1159.6	1159.4
177.5°	1159.9	1159.5	1159.3	1159.2	1159.0	1158.9	1159.8	1160.8	1161.8	1162.7	1162.6
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0



TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1622.1	1616.0	1614.3	1616.5	1614.3	1616.0	1622.1	1622.6	1623.2	1627.6	1621.5
5°	1496.6	1489.6	1493.1	1491.7	1493.1	1489.6	1496.6	1503.5	1504.9	1511.2	1515.3
7.5°	1386.2	1377.5	1368.3	1371.3	1368.3	1377.5	1386.2	1386.3	1397.1	1405.2	1410.6
10°	1308.9	1301.9	1297.7	1301.2	1297.7	1301.9	1308.9	1317.9	1322.1	1331.8	1342.2
12.5°	1243.8	1239.7	1236.0	1234.5	1236.0	1239.7	1243.8	1253.4	1263.1	1274.5	1286.1
15°	1155.2	1146.9	1143.4	1134.4	1143.4	1146.9	1155.2	1163.6	1182.4	1187.2	1204.6
17.5°	1073.6	1070.9	1061.8	1057.9	1061.8	1070.9	1073.6	1080.8	1089.4	1107.3	1120.3
20°	1025.3	1022.5	1013.4	1019.0	1013.4	1022.5	1025.3	1035.7	1042.7	1057.2	1069.8
22.5°	985.3	979.1	976.2	974.6	976.2	979.1	985.3	990.1	999.3	1012.7	1027.0
25°	928.6	919.6	916.1	912.0	916.1	919.6	928.6	931.4	941.2	954.4	962.0
27.5°	872.2	867.4	862.7	861.7	862.7	867.4	872.2	876.1	884.6	896.1	909.9
30°	835.5	830.6	827.2	827.2	827.2	830.6	835.5	843.8	850.1	860.5	870.9
32.5°	802.7	799.0	795.5	795.0	795.5	799.0	802.7	807.2	814.5	826.1	837.0
35°	754.9	749.3	748.0	743.8	748.0	749.3	754.9	758.3	766.0	774.4	783.4
37.5°	705.3	700.6	700.5	700.1	700.5	700.6	705.3	711.4	717.7	725.2	736.4
40°	673.5	670.0	669.4	664.5	669.4	670.0	673.5	676.4	683.3	693.0	701.3
42.5°	639.6	637.8	635.4	633.4	635.4	637.8	639.6	645.2	651.0	658.0	668.5
45°	593.6	588.7	588.7	585.2	588.7	588.7	593.6	598.5	601.3	609.6	623.5
47.5°	546.1	542.3	542.7	539.1	542.7	542.3	546.1	547.6	552.1	560.3	567.9
50°	514.3	512.3	511.6	510.2	511.6	512.3	514.3	513.7	519.2	526.9	537.3
52.5°	482.7	481.7	484.4	481.3	484.4	481.7	482.7	484.2	488.1	492.9	502.8
55°	440.0	437.9	442.1	437.9	442.1	437.9	440.0	438.6	440.0	444.9	451.1
57.5°	390.9	389.0	392.7	390.7	392.7	389.0	390.9	391.2	395.4	396.1	401.6
60°	358.6	354.5	356.6	357.3	356.6	354.5	358.6	360.1	361.4	362.1	367.7
62.5°	320.3	317.8	319.3	316.1	319.3	317.8	320.3	323.3	326.5	329.9	333.2
65°	266.3	264.1	261.4	259.9	261.4	264.1	266.3	267.6	275.3	279.5	287.0
67.5°	223.6	218.6	218.6	219.6	218.6	218.6	223.6	223.4	229.0	232.3	237.5
70°	192.5	192.5	191.8	191.8	191.8	192.5	192.5	196.7	199.5	202.2	205.7
72.5°	170.9	170.3	169.1	168.5	169.1	170.3	170.9	172.3	173.9	176.7	180.1
75°	137.6	138.3	137.0	136.3	137.0	138.3	137.6	137.6	140.4	141.1	142.5
77.5°	101.7	98.7	100.2	98.7	100.2	98.7	101.7	104.4	105.4	108.4	108.6
80°	77.1	76.4	78.6	76.4	78.6	76.4	77.1	77.1	79.3	80.6	84.1
82.5°	61.0	60.4	61.3	59.7	61.3	60.4	61.0	60.5	61.4	63.4	63.0
85°	36.8	36.1	35.5	36.1	35.5	36.1	36.8	36.1	35.5	36.1	36.8
87.5°	16.8	16.3	16.4	16.6	16.4	16.3	16.8	16.1	16.5	16.3	16.1
90°	19.9	20.5	21.0	21.7	21.0	20.5	19.9	19.3	18.5	17.5	16.5
92.5°	41.3	41.7	42.2	42.6	42.2	41.7	41.3	40.8	40.0	38.7	37.4
95°	76.5	76.9	77.3	77.7	77.3	76.9	76.5	76.1	75.2	73.7	72.4
97.5°	117.1	117.3	117.6	117.8	117.6	117.3	117.1	116.8	116.1	114.8	113.4
100°	147.0	147.4	147.8	148.2	147.8	147.4	147.0	146.6	145.4	143.7	141.9
102.5°	176.8	177.5	178.0	178.5	178.0	177.5	176.8	176.3	175.0	173.1	171.1
105°	222.3	222.8	223.5	224.1	223.5	222.8	222.3	221.7	220.8	219.5	218.4
107.5°	270.8	270.8	270.7	270.7	270.7	270.8	270.8	270.9	270.5	270.0	269.4
110°	306.0	305.8	305.6	305.4	305.6	305.8	306.0	306.2	306.0	305.4	304.8



TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	340.5	340.1	339.7	339.4	339.7	340.1	340.5	340.8	340.8	340.5	340.3
115°	393.6	393.4	393.2	393.1	393.2	393.4	393.6	393.9	394.0	394.2	394.4
117.5°	447.8	447.0	446.2	445.4	446.2	447.0	447.8	448.6	449.0	448.8	448.6
120°	484.0	483.2	482.4	481.6	482.4	483.2	484.0	484.8	485.2	485.2	485.2
122.5°	519.7	519.0	518.4	517.7	518.4	519.0	519.7	520.3	520.7	520.8	521.0
125°	572.6	572.3	572.1	571.9	572.1	572.3	572.6	572.7	573.0	573.5	573.8
127.5°	625.2	624.8	624.4	624.0	624.4	624.8	625.2	625.6	625.9	626.1	626.2
130°	659.9	659.5	659.1	658.7	659.1	659.5	659.9	660.3	660.6	660.8	661.0
132.5°	692.9	692.3	691.8	691.2	691.8	692.3	692.9	693.5	693.8	694.0	694.2
135°	744.2	743.4	742.6	741.8	742.6	743.4	744.2	745.0	745.4	745.4	745.4
137.5°	794.3	793.4	792.3	791.3	792.3	793.4	794.3	795.3	795.7	795.5	795.2
140°	826.2	825.1	824.1	823.1	824.1	825.1	826.2	827.2	827.4	827.1	826.6
142.5°	856.5	855.5	854.5	853.5	854.5	855.5	856.5	857.5	857.9	857.6	857.4
145°	900.8	900.2	899.6	899.0	899.6	900.2	900.8	901.4	901.7	901.7	901.7
147.5°	942.0	940.6	939.2	937.9	939.2	940.6	942.0	943.3	943.8	943.3	942.8
150°	968.0	967.6	967.1	966.8	967.1	967.6	968.0	968.4	968.6	968.6	968.6
152.5°	992.8	992.1	991.3	990.6	991.3	992.1	992.8	993.5	993.6	993.2	992.7
155°	1027.6	1026.6	1025.6	1024.6	1025.6	1026.6	1027.6	1028.6	1028.8	1028.0	1027.2
157.5°	1056.9	1055.6	1054.3	1053.0	1054.3	1055.6	1056.9	1058.3	1058.5	1057.7	1056.9
160°	1075.5	1074.5	1073.5	1072.5	1073.5	1074.5	1075.5	1076.5	1076.7	1075.8	1075.0
162.5°	1092.6	1091.5	1090.3	1089.1	1090.3	1091.5	1092.6	1093.8	1093.9	1092.9	1092.0
165°	1115.0	1113.7	1112.6	1111.3	1112.6	1113.7	1115.0	1116.2	1116.3	1115.5	1114.7
167.5°	1132.8	1131.6	1130.3	1129.1	1130.3	1131.6	1132.8	1134.1	1134.1	1132.8	1131.7
170°	1142.6	1141.3	1139.9	1138.4	1139.9	1141.3	1142.6	1144.1	1144.2	1143.0	1141.7
172.5°	1150.1	1148.9	1147.6	1146.4	1147.6	1148.9	1150.1	1151.4	1151.4	1150.2	1149.0
175°	1158.1	1156.6	1155.2	1153.8	1155.2	1156.6	1158.1	1159.4	1159.6	1158.3	1157.1
177.5°	1161.5	1160.4	1159.3	1158.2	1159.3	1160.4	1161.5	1162.6	1162.7	1161.8	1160.8
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0



TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1623.2	1629.3	1632.6	1640.4	1651.5	1657.2	1664.9	1670.4	1678.3	1687.7	1695.5
5°	1518.1	1534.8	1545.9	1563.3	1579.3	1595.3	1615.4	1630.0	1649.5	1671.7	1689.1
7.5°	1420.5	1441.4	1459.8	1482.8	1509.2	1529.8	1556.0	1582.9	1613.3	1644.8	1674.6
10°	1358.3	1379.1	1402.0	1430.5	1457.0	1484.7	1516.0	1547.3	1585.6	1621.0	1661.3
12.5°	1296.5	1319.6	1345.3	1377.2	1409.1	1444.7	1476.5	1511.7	1552.7	1598.7	1641.8
15°	1219.9	1242.2	1270.0	1297.1	1333.9	1372.8	1415.2	1461.8	1507.7	1559.1	1612.7
17.5°	1137.7	1162.2	1192.8	1224.2	1263.0	1308.6	1350.1	1401.1	1452.8	1512.7	1575.7
20°	1084.3	1109.4	1145.5	1180.3	1215.8	1260.3	1309.6	1361.7	1416.6	1479.9	1550.1
22.5°	1042.1	1059.9	1095.5	1130.8	1172.3	1218.0	1266.2	1320.5	1380.5	1445.9	1519.5
25°	979.4	1000.2	1026.0	1062.8	1105.9	1153.9	1202.6	1260.3	1325.5	1392.3	1470.8
27.5°	923.6	940.8	966.2	995.1	1038.0	1087.8	1139.5	1199.7	1266.8	1334.7	1417.3
30°	884.1	902.9	927.3	957.9	991.9	1046.2	1098.9	1158.1	1226.2	1296.4	1381.2
32.5°	849.7	869.0	890.0	918.9	955.7	1003.9	1058.4	1116.3	1185.5	1258.0	1340.6
35°	801.5	814.7	834.1	862.6	898.8	937.7	993.3	1054.4	1121.9	1196.9	1279.7
37.5°	746.1	763.2	782.6	807.3	839.0	881.1	932.8	994.7	1057.2	1129.1	1204.6
40°	713.9	729.9	751.4	769.5	802.8	841.1	888.3	953.0	1015.6	1083.0	1151.8
42.5°	681.1	696.5	714.7	737.3	767.2	804.4	848.3	908.5	975.5	1039.0	1096.7
45°	629.7	645.8	663.2	683.9	711.8	748.0	791.8	846.6	905.0	963.4	1007.2
47.5°	580.7	595.7	612.1	633.5	659.1	694.0	733.2	781.7	838.4	888.1	919.4
50°	545.6	559.5	577.7	598.5	623.5	656.2	693.8	741.6	788.9	834.1	862.6
52.5°	511.2	526.7	544.8	562.8	586.8	619.5	654.2	695.5	740.6	777.4	800.9
55°	459.5	474.0	490.7	509.5	533.2	561.0	597.8	630.4	665.9	697.2	711.1
57.5°	409.6	422.3	438.0	457.5	478.8	504.6	533.9	565.3	590.3	612.4	628.1
60°	376.7	387.9	402.4	419.1	442.1	465.7	492.1	521.3	540.8	559.5	574.2
62.5°	343.4	353.9	368.0	383.0	403.1	425.1	450.4	474.0	492.9	505.6	522.5
65°	293.4	303.7	315.6	331.5	347.6	365.6	388.5	405.9	419.1	433.0	443.4
67.5°	246.7	255.4	266.6	279.2	292.7	310.0	327.8	342.2	351.3	359.6	372.2
70°	216.2	223.1	232.2	241.9	256.5	273.8	287.8	298.9	305.1	313.5	328.8
72.5°	185.0	193.1	201.6	211.3	223.1	237.7	249.9	261.1	265.1	271.8	281.5
75°	146.0	150.2	157.1	164.1	172.4	184.9	196.7	199.5	203.0	208.6	215.4
77.5°	110.4	114.1	116.9	121.5	128.1	138.2	144.5	148.6	149.5	151.5	158.4
80°	87.6	89.7	92.5	95.9	98.7	107.0	110.5	114.7	116.1	118.2	121.6
82.5°	64.2	66.3	67.9	70.9	75.3	78.6	82.1	86.3	86.6	88.1	88.8
85°	37.5	38.3	36.8	38.3	39.0	40.3	43.8	47.3	46.5	45.8	48.0
87.5°	16.4	16.2	15.4	16.8	15.4	15.7	15.3	15.6	16.4	17.2	18.0
90°	15.4	14.4	13.0	11.7	10.3	8.8	7.3	5.7	4.1	2.5	0.9
92.5°	36.0	34.7	33.0	31.2	29.5	27.8	26.4	25.2	24.1	23.0	21.8
95°	71.0	69.6	67.6	65.5	63.6	61.5	60.4	59.9	59.6	59.1	58.8
97.5°	112.1	110.8	108.0	105.2	102.5	99.7	98.3	98.1	97.9	97.7	97.6
100°	140.1	138.2	135.6	133.0	130.4	127.8	126.5	126.5	126.5	126.5	126.5
102.5°	169.2	167.2	165.9	164.5	163.2	161.8	160.8	160.0	159.2	158.4	157.6
105°	217.1	216.0	214.7	213.6	212.3	211.2	210.0	209.0	208.0	207.0	206.0
107.5°	268.8	268.1	267.2	266.4	265.4	264.5	263.5	262.5	261.5	260.5	259.5
110°	304.2	303.6	303.0	302.4	301.8	301.2	300.4	299.3	298.4	297.4	296.3



TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	340.0	339.7	338.9	338.2	337.4	336.7	336.0	335.6	335.0	334.5	333.9
115°	394.7	394.8	394.4	394.0	393.6	393.2	392.6	391.8	391.0	390.2	389.4
117.5°	448.5	448.4	448.0	447.6	447.3	446.9	446.6	446.1	445.8	445.4	445.1
120°	485.2	485.2	485.0	484.8	484.6	484.4	483.8	482.8	481.8	480.8	479.7
122.5°	521.2	521.4	520.8	520.3	519.8	519.2	518.8	518.4	518.1	517.7	517.4
125°	574.3	574.6	574.4	574.3	574.1	573.8	573.1	571.9	570.7	569.5	568.3
127.5°	626.5	626.7	626.4	626.2	626.0	625.7	625.3	624.6	623.9	623.2	622.5
130°	661.2	661.4	661.0	660.6	660.2	659.8	659.1	658.1	657.1	656.0	655.1
132.5°	694.5	694.6	694.7	694.8	694.9	695.0	694.2	692.5	690.9	689.2	687.6
135°	745.4	745.4	745.2	745.0	744.8	744.6	744.0	742.7	741.5	740.3	739.0
137.5°	795.0	794.8	794.3	793.9	793.4	793.0	792.2	791.0	789.9	788.7	787.6
140°	826.3	825.8	825.2	824.7	824.0	823.4	822.6	821.6	820.6	819.6	818.6
142.5°	857.1	856.9	856.1	855.4	854.6	853.9	853.1	852.2	851.4	850.5	849.7
145°	901.7	901.7	901.2	900.5	899.9	899.3	898.6	897.8	897.0	896.2	895.4
147.5°	942.4	941.8	941.4	940.8	940.4	940.0	939.4	939.0	938.6	938.2	937.7
150°	968.6	968.6	967.8	967.0	966.2	965.4	965.1	965.3	965.5	965.7	965.9
152.5°	992.2	991.8	991.4	991.0	990.8	990.4	990.2	989.9	989.5	989.3	989.0
155°	1026.4	1025.6	1025.3	1025.1	1024.9	1024.7	1024.6	1024.6	1024.6	1024.6	1024.6
157.5°	1056.1	1055.3	1055.2	1054.9	1054.7	1054.5	1054.6	1055.1	1055.5	1056.0	1056.4
160°	1074.2	1073.4	1073.2	1073.0	1072.8	1072.6	1072.8	1073.4	1074.0	1074.6	1075.2
162.5°	1091.0	1090.0	1090.0	1089.9	1089.9	1089.8	1090.0	1090.5	1090.9	1091.4	1091.8
165°	1113.9	1113.1	1112.9	1112.8	1112.6	1112.3	1112.4	1112.9	1113.2	1113.7	1114.1
167.5°	1130.4	1129.3	1129.3	1129.3	1129.3	1129.3	1129.6	1130.4	1131.2	1132.0	1132.8
170°	1140.6	1139.3	1139.3	1139.3	1139.3	1139.3	1139.8	1140.6	1141.4	1142.2	1143.0
172.5°	1147.8	1146.6	1146.6	1146.6	1146.6	1146.6	1147.0	1147.8	1148.6	1149.4	1150.2
175°	1155.9	1154.7	1154.7	1154.7	1154.7	1154.7	1155.1	1155.9	1156.7	1157.5	1158.3
177.5°	1159.8	1158.9	1159.0	1159.2	1159.3	1159.5	1159.9	1160.6	1161.2	1161.8	1162.5
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0



TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1701.6	1706.6	1713.9	1722.2	1728.8	1736.1	1740.0	1740.0	1743.3	1750.5	1760.0
5°	1706.5	1724.6	1742.0	1764.2	1781.5	1801.7	1816.9	1831.6	1844.8	1861.4	1878.8
7.5°	1705.0	1735.1	1766.4	1801.4	1840.0	1870.8	1902.4	1927.1	1951.6	1983.5	2008.7
10°	1699.5	1738.5	1780.8	1825.3	1874.0	1916.4	1954.6	1989.4	2022.8	2057.5	2088.7
12.5°	1689.5	1739.0	1790.8	1844.2	1905.7	1954.2	2003.6	2040.5	2079.5	2117.5	2156.1
15°	1674.5	1732.9	1795.5	1869.8	1944.9	1999.1	2047.7	2095.7	2131.9	2175.0	2211.8
17.5°	1643.5	1718.7	1797.4	1878.7	1950.9	2013.8	2064.8	2110.5	2148.9	2196.4	2246.4
20°	1625.1	1706.5	1788.5	1875.4	1944.2	2008.8	2058.2	2105.4	2153.4	2215.3	2276.4
22.5°	1599.6	1686.5	1773.4	1855.9	1928.6	1991.0	2042.1	2099.9	2162.8	2233.1	2307.0
25°	1559.1	1648.8	1735.0	1813.5	1884.5	1948.4	2017.9	2095.7	2172.2	2264.7	2371.0
27.5°	1507.8	1594.3	1671.2	1754.2	1824.6	1905.9	1992.7	2077.1	2187.4	2314.5	2447.3
30°	1469.5	1551.5	1624.4	1703.0	1782.9	1872.6	1969.9	2069.3	2200.7	2350.1	2507.9
32.5°	1425.0	1499.2	1571.6	1647.3	1739.5	1838.1	1941.5	2063.2	2220.2	2390.1	2553.5
35°	1347.8	1414.5	1484.7	1568.9	1666.9	1773.9	1905.9	2054.1	2243.8	2426.6	2573.3
37.5°	1266.9	1319.6	1390.1	1478.7	1585.6	1709.4	1859.2	2039.2	2234.1	2398.1	2460.5
40°	1204.6	1253.9	1328.3	1421.5	1527.1	1662.7	1830.9	2015.8	2211.8	2325.8	2320.9
42.5°	1142.9	1192.8	1264.4	1358.1	1468.2	1619.9	1793.1	1985.2	2150.6	2194.1	2103.5
45°	1048.2	1094.8	1165.0	1259.5	1377.7	1536.9	1719.0	1903.2	2008.8	1938.7	1759.3
47.5°	951.7	996.9	1062.1	1154.7	1283.7	1450.3	1622.5	1773.6	1788.5	1637.6	1422.5
50°	888.3	930.8	992.6	1091.3	1216.4	1379.1	1545.2	1664.1	1627.2	1443.1	1221.3
52.5°	826.6	867.4	925.3	1018.4	1146.4	1305.6	1454.0	1547.3	1462.0	1266.2	1066.7
55°	735.4	774.4	832.8	918.2	1034.3	1180.3	1310.3	1344.3	1219.2	1021.8	860.5
57.5°	648.8	677.3	735.0	810.7	922.6	1051.2	1144.4	1138.3	1000.2	822.4	706.8
60°	591.6	617.2	672.2	741.6	848.0	963.4	1028.8	1000.9	861.2	714.5	603.3
62.5°	538.1	562.2	608.2	672.2	763.5	863.9	911.4	873.1	741.1	612.2	523.8
65°	457.4	474.7	511.6	570.7	642.3	711.8	754.2	697.9	581.1	483.8	417.1
67.5°	381.9	396.9	429.7	472.1	521.5	569.4	586.7	533.9	443.1	377.5	330.5
70°	333.0	346.9	369.1	408.8	441.4	475.5	483.8	436.5	360.8	310.7	281.5
72.5°	286.2	299.0	318.5	346.4	369.1	388.7	392.6	348.7	290.7	256.2	233.7
75°	218.3	229.3	241.9	252.4	266.9	270.4	269.0	235.0	203.7	180.7	168.2
77.5°	160.4	165.1	172.6	176.8	177.5	177.3	170.1	148.6	132.5	123.1	117.9
80°	123.8	127.2	129.3	130.6	131.3	124.4	116.8	103.5	98.0	92.5	86.2
82.5°	89.8	92.2	94.3	94.5	90.8	85.0	77.8	71.3	67.4	64.6	62.2
85°	48.7	49.3	48.7	45.2	40.3	38.3	36.8	35.5	34.8	34.1	34.1
87.5°	17.7	16.4	13.9	14.8	15.1	14.8	15.2	14.8	14.5	14.8	15.0
90°	2.5	4.1	5.7	7.3	8.8	10.3	11.7	13.0	14.4	15.4	16.5
92.5°	23.0	24.1	25.2	26.4	27.8	29.5	31.2	33.0	34.7	36.0	37.4
95°	59.1	59.6	59.9	60.4	61.5	63.6	65.5	67.6	69.6	71.0	72.4
97.5°	97.7	97.9	98.1	98.3	99.7	102.5	105.2	108.0	110.8	112.1	113.4
100°	126.5	126.5	126.5	126.5	127.8	130.4	133.0	135.6	138.2	140.1	141.9
102.5°	158.4	159.2	160.0	160.8	161.8	163.2	164.5	165.9	167.2	169.2	171.1
105°	207.0	208.0	209.0	210.0	211.2	212.3	213.6	214.7	216.0	217.1	218.4
107.5°	260.5	261.5	262.5	263.5	264.5	265.4	266.4	267.2	268.1	268.8	269.4
110°	297.4	298.4	299.3	300.4	301.2	301.8	302.4	303.0	303.6	304.2	304.8





TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	334.5	335.0	335.6	336.0	336.7	337.4	338.2	338.9	339.7	340.0	340.3
115°	390.2	391.0	391.8	392.6	393.2	393.6	394.0	394.4	394.8	394.7	394.4
117.5°	445.4	445.8	446.1	446.6	446.9	447.3	447.6	448.0	448.4	448.5	448.6
120°	480.8	481.8	482.8	483.8	484.4	484.6	484.8	485.0	485.2	485.2	485.2
122.5°	517.7	518.1	518.4	518.8	519.2	519.8	520.3	520.8	521.4	521.2	521.0
125°	569.5	570.7	571.9	573.1	573.8	574.1	574.3	574.4	574.6	574.3	573.8
127.5°	623.2	623.9	624.6	625.3	625.7	626.0	626.2	626.4	626.7	626.5	626.2
130°	656.0	657.1	658.1	659.1	659.8	660.2	660.6	661.0	661.4	661.2	661.0
132.5°	689.2	690.9	692.5	694.2	695.0	694.9	694.8	694.7	694.6	694.5	694.2
135°	740.3	741.5	742.7	744.0	744.6	744.8	745.0	745.2	745.4	745.4	745.4
137.5°	788.7	789.9	791.0	792.2	793.0	793.4	793.9	794.3	794.8	795.0	795.2
140°	819.6	820.6	821.6	822.6	823.4	824.0	824.7	825.2	825.8	826.3	826.6
142.5°	850.5	851.4	852.2	853.1	853.9	854.6	855.4	856.1	856.9	857.1	857.4
145°	896.2	897.0	897.8	898.6	899.3	899.9	900.5	901.2	901.7	901.7	901.7
147.5°	938.2	938.6	939.0	939.4	940.0	940.4	940.8	941.4	941.8	942.4	942.8
150°	965.7	965.5	965.3	965.1	965.4	966.2	967.0	967.8	968.6	968.6	968.6
152.5°	989.3	989.5	989.9	990.2	990.4	990.8	991.0	991.4	991.8	992.2	992.7
155°	1024.6	1024.6	1024.6	1024.6	1024.7	1024.9	1025.1	1025.3	1025.6	1026.4	1027.2
157.5°	1056.0	1055.5	1055.1	1054.6	1054.5	1054.7	1054.9	1055.2	1055.3	1056.1	1056.9
160°	1074.6	1074.0	1073.4	1072.8	1072.6	1072.8	1073.0	1073.2	1073.4	1074.2	1075.0
162.5°	1091.4	1090.9	1090.5	1090.0	1089.8	1089.9	1089.9	1090.0	1090.0	1091.0	1092.0
165°	1113.7	1113.2	1112.9	1112.4	1112.3	1112.6	1112.8	1112.9	1113.1	1113.9	1114.7
167.5°	1132.0	1131.2	1130.4	1129.6	1129.3	1129.3	1129.3	1129.3	1129.3	1130.4	1131.7
170°	1142.2	1141.4	1140.6	1139.8	1139.3	1139.3	1139.3	1139.3	1139.3	1140.6	1141.7
172.5°	1149.4	1148.6	1147.8	1147.0	1146.6	1146.6	1146.6	1146.6	1146.6	1147.8	1149.0
175°	1157.5	1156.7	1155.9	1155.1	1154.7	1154.7	1154.7	1154.7	1154.7	1155.9	1157.1
177.5°	1161.8	1161.2	1160.6	1159.9	1159.5	1159.3	1159.2	1159.0	1158.9	1159.8	1160.8
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0



TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1767.2	1767.2	1776.6	1776.1	1782.3	1780.0	1781.1
5°	1899.7	1911.6	1922.0	1928.9	1939.3	1942.1	1940.7
7.5°	2037.0	2063.3	2076.1	2093.6	2096.9	2106.0	2105.1
10°	2122.2	2147.9	2167.3	2182.6	2190.2	2200.0	2200.7
12.5°	2188.9	2210.7	2227.9	2242.1	2251.4	2254.5	2256.3
15°	2241.0	2265.3	2285.5	2305.6	2317.5	2326.5	2331.4
17.5°	2293.6	2331.1	2366.7	2394.1	2410.5	2424.4	2424.2
20°	2334.1	2377.2	2421.7	2453.0	2485.0	2498.8	2501.0
22.5°	2377.5	2443.4	2500.7	2549.2	2591.2	2605.7	2611.1
25°	2467.6	2553.8	2642.0	2710.2	2758.9	2787.3	2791.5
27.5°	2576.4	2693.1	2786.0	2848.8	2889.2	2910.4	2915.0
30°	2653.2	2760.9	2844.4	2891.6	2910.4	2913.1	2902.7
32.5°	2687.7	2768.1	2801.5	2798.7	2761.9	2737.5	2728.1
35°	2645.5	2628.9	2547.5	2450.2	2375.9	2328.6	2316.0
37.5°	2407.5	2263.7	2114.1	1967.0	1888.7	1849.0	1780.6
40°	2172.9	1967.8	1812.1	1688.4	1600.1	1529.2	1512.5
42.5°	1908.2	1696.5	1540.8	1434.9	1364.3	1315.7	1294.6
45°	1533.4	1351.3	1222.7	1141.4	1087.2	1051.7	1035.7
47.5°	1226.5	1085.5	991.8	931.6	890.3	859.4	850.8
50°	1057.9	945.3	866.1	815.4	784.1	760.5	750.7
52.5°	918.9	828.0	767.1	725.2	695.6	680.9	672.9
55°	758.3	679.8	636.1	602.6	585.9	574.2	568.6
57.5°	620.2	563.5	531.5	508.4	492.9	485.4	482.7
60°	542.9	498.4	469.2	451.1	440.7	431.0	428.2
62.5°	474.5	439.4	417.0	401.1	390.7	386.5	384.8
65°	382.3	359.4	342.7	333.0	324.6	323.2	322.5
67.5°	303.9	290.4	281.7	271.5	268.6	263.7	262.8
70°	259.9	250.9	240.5	237.0	233.5	228.7	229.3
72.5°	220.5	211.4	204.4	199.7	198.5	196.4	198.2
75°	161.2	158.5	155.7	152.2	150.9	150.9	150.2
77.5°	115.1	112.7	109.7	107.6	107.2	104.2	105.4
80°	83.4	79.9	78.6	79.3	77.1	76.4	76.4
82.5°	61.7	60.5	59.1	59.2	58.8	58.1	58.7
85°	34.1	33.3	33.3	32.6	32.6	32.0	32.0
87.5°	15.7	16.5	15.5	15.1	15.2	15.9	16.6
90°	17.5	18.5	19.3	19.9	20.5	21.0	21.7
92.5°	38.7	40.0	40.8	41.3	41.7	42.2	42.6
95°	73.7	75.2	76.1	76.5	76.9	77.3	77.7
97.5°	114.8	116.1	116.8	117.1	117.3	117.6	117.8
100°	143.7	145.4	146.6	147.0	147.4	147.8	148.2
102.5°	173.1	175.0	176.3	176.8	177.5	178.0	178.5
105°	219.5	220.8	221.7	222.3	222.8	223.5	224.1
107.5°	270.0	270.5	270.9	270.8	270.8	270.7	270.7
110°	305.4	306.0	306.2	306.0	305.8	305.6	305.4



TEST NUMBER: P333729-940

CATALOG NUMBER: S125RDIW-S1270D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	340.5	340.8	340.8	340.5	340.1	339.7	339.4
115°	394.2	394.0	393.9	393.6	393.4	393.2	393.1
117.5°	448.8	449.0	448.6	447.8	447.0	446.2	445.4
120°	485.2	485.2	484.8	484.0	483.2	482.4	481.6
122.5°	520.8	520.7	520.3	519.7	519.0	518.4	517.7
125°	573.5	573.0	572.7	572.6	572.3	572.1	571.9
127.5°	626.1	625.9	625.6	625.2	624.8	624.4	624.0
130°	660.8	660.6	660.3	659.9	659.5	659.1	658.7
132.5°	694.0	693.8	693.5	692.9	692.3	691.8	691.2
135°	745.4	745.4	745.0	744.2	743.4	742.6	741.8
137.5°	795.5	795.7	795.3	794.3	793.4	792.3	791.3
140°	827.1	827.4	827.2	826.2	825.1	824.1	823.1
142.5°	857.6	857.9	857.5	856.5	855.5	854.5	853.5
145°	901.7	901.7	901.4	900.8	900.2	899.6	899.0
147.5°	943.3	943.8	943.3	942.0	940.6	939.2	937.9
150°	968.6	968.6	968.4	968.0	967.6	967.1	966.8
152.5°	993.2	993.6	993.5	992.8	992.1	991.3	990.6
155°	1028.0	1028.8	1028.6	1027.6	1026.6	1025.6	1024.6
157.5°	1057.7	1058.5	1058.3	1056.9	1055.6	1054.3	1053.0
160°	1075.8	1076.7	1076.5	1075.5	1074.5	1073.5	1072.5
162.5°	1092.9	1093.9	1093.8	1092.6	1091.5	1090.3	1089.1
165°	1115.5	1116.3	1116.2	1115.0	1113.7	1112.6	1111.3
167.5°	1132.8	1134.1	1134.1	1132.8	1131.6	1130.3	1129.1
170°	1143.0	1144.2	1144.1	1142.6	1141.3	1139.9	1138.4
172.5°	1150.2	1151.4	1151.4	1150.1	1148.9	1147.6	1146.4
175°	1158.3	1159.6	1159.4	1158.1	1156.6	1155.2	1153.8
177.5°	1161.8	1162.7	1162.6	1161.5	1160.4	1159.3	1158.2
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0

(END OF REPORT)