

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333723-940

Luminaire Tested: **S125RDIW-S1270D470U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333723-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D470U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5799.0 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333723-940

CATALOG NUMBER: S125RDIW-S1270D470U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333723-940

CATALOG NUMBER: S125RDIW-S1270D470U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75																				
1	104	99	95	92	99	95	91	88	86	83	81	78	76	74	70	69	68	64																				
2	95	87	81	76	90	83	78	73	76	71	67	69	65	62	62	60	57	54																				
3	87	77	69	63	82	74	67	61	67	62	57	61	57	53	56	52	49	46																				
4	80	68	60	54	75	65	58	52	60	54	49	55	50	46	50	46	43	40																				
5	73	61	53	47	69	59	51	45	54	47	43	49	44	40	45	41	37	35																				
6	68	55	47	41	64	53	45	40	49	42	37	45	39	35	41	37	33	31																				
7	63	50	42	36	60	48	41	35	44	38	33	41	35	31	38	33	30	27																				
8	58	46	38	32	55	44	37	31	41	34	30	38	32	28	35	30	27	24																				
9	55	42	34	29	52	40	33	28	37	31	27	35	29	25	32	27	24	22																				
10	51	39	31	26	49	37	30	26	35	29	24	32	27	23	30	25	22	20																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11889	11889	11889
5°	11916	11780	11852
10°	11825	11671	11671
15°	11685	11433	11340
20°	11504	11103	10970
25°	11294	10779	10541
30°	11032	10399	10068
35°	10764	10008	9536
40°	10514	9599	9014
45°	10209	9143	8444
50°	9904	8647	7850
55°	9549	8172	7218
60°	9195	7596	6536
65°	8775	6927	5757
70°	8295	6090	4962
75°	7633	5133	4127
80°	6721	4032	3466
85°	5669	3298	3090



TEST NUMBER: P333723-940

CATALOG NUMBER: S125RDIW-S1270D470U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.1	3.0
10°-20°	483.7	8.3
20°-30°	701.4	12.1
30°-40°	799.4	13.8
40°-50°	779.2	13.4
50°-60°	655.9	11.3
60°-70°	459.8	7.9
70°-80°	236.3	4.1
80°-90°	60.8	1.0
90°-100°	34.8	0.6
100°-110°	102.7	1.8
110°-120°	174.0	3.0
120°-130°	229.0	3.9
130°-140°	256.6	4.4
140°-150°	251.5	4.3
150°-160°	211.2	3.6
160°-170°	140.4	2.4
170°-180°	49.1	0.8
0°-30°	1358.2	23.4
0°-40°	2157.6	37.2
0°-60°	3592.8	62.0
0°-90°	4349.8	75.0
90°-120°	311.5	5.4
90°-150°	1048.5	18.1
90°-180°	1449.0	25.0
0°-180°	5799.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1841	1841	1841	1841	1841	
5°	1838	1832	1817	1830	1828	174
15°	1748	1738	1710	1708	1696	492
25°	1585	1562	1513	1495	1479	729
35°	1365	1330	1269	1230	1210	854
45°	1118	1075	1001	947	924	862
55°	848	802	726	665	641	758
65°	574	525	453	400	377	569
75°	306	263	206	176	165	324
85°	76	52	44	43	42	86
90°	0	4	6	8	10	5
95°	26	27	31	34	35	28
105°	92	94	97	99	100	98
115°	174	176	177	176	176	172
125°	254	257	257	256	256	228
135°	331	333	333	333	332	255
145°	401	402	403	403	402	250
155°	458	458	459	460	458	211
165°	498	498	498	499	497	141
175°	518	517	516	519	516	49
180°	519	519	519	519	519	



TEST NUMBER: P333723-940

CATALOG NUMBER: S125RDIW-S1270D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8
2.5°	1844.1	1843.3	1842.5	1841.8	1841.1	1839.5	1837.0	1834.5	1832.1	1829.6	1832.1
5°	1838.0	1836.7	1835.5	1834.2	1833.0	1830.7	1827.3	1823.9	1820.5	1817.1	1820.2
7.5°	1819.9	1818.7	1817.6	1816.3	1815.2	1812.6	1808.5	1804.4	1800.4	1796.3	1798.4
10°	1803.2	1802.2	1801.3	1800.5	1799.5	1796.9	1792.5	1788.2	1783.9	1779.6	1780.5
12.5°	1784.3	1783.2	1781.9	1780.7	1779.6	1776.1	1770.3	1764.5	1758.6	1752.8	1753.5
15°	1747.6	1745.7	1743.9	1742.0	1740.2	1736.0	1729.5	1723.1	1716.5	1710.0	1709.8
17.5°	1706.1	1703.3	1700.5	1697.6	1694.8	1689.3	1681.1	1672.9	1664.8	1656.6	1655.1
20°	1673.9	1670.8	1667.7	1664.6	1661.5	1655.0	1645.2	1635.3	1625.4	1615.5	1614.0
22.5°	1638.3	1635.2	1632.1	1629.1	1625.9	1619.3	1608.8	1598.5	1588.0	1577.7	1574.7
25°	1584.9	1580.3	1575.7	1571.0	1566.4	1558.4	1546.9	1535.5	1524.0	1512.6	1508.6
27.5°	1523.8	1518.1	1512.5	1506.9	1501.3	1492.4	1480.1	1467.8	1455.6	1443.4	1437.8
30°	1479.3	1473.4	1467.5	1461.7	1455.8	1446.4	1433.3	1420.4	1407.4	1394.5	1387.3
32.5°	1435.9	1429.1	1422.2	1415.3	1408.5	1398.4	1385.2	1372.0	1358.7	1345.5	1337.7
35°	1365.3	1357.8	1350.4	1343.0	1335.6	1324.9	1311.0	1297.2	1283.3	1269.4	1260.3
37.5°	1296.0	1287.0	1278.0	1269.0	1259.9	1248.2	1233.9	1219.6	1205.2	1190.9	1180.2
40°	1247.1	1237.8	1228.5	1219.2	1210.1	1197.9	1183.1	1168.3	1153.4	1138.6	1126.9
42.5°	1196.0	1186.4	1176.9	1167.3	1157.9	1145.4	1130.2	1114.8	1099.5	1084.1	1072.9
45°	1117.8	1108.8	1099.8	1090.9	1081.9	1069.0	1052.0	1035.0	1018.0	1001.0	988.6
47.5°	1036.9	1027.4	1018.0	1008.5	999.1	985.8	968.7	951.5	934.4	917.3	904.6
50°	985.7	975.5	965.3	955.1	944.9	931.0	913.4	895.8	878.2	860.6	847.6
52.5°	930.1	919.6	909.2	898.8	888.3	874.8	858.2	841.6	824.9	808.3	794.3
55°	848.1	838.2	828.3	818.4	808.5	795.0	777.7	760.4	743.1	725.8	711.9
57.5°	765.2	754.7	744.0	733.5	722.9	709.4	692.7	675.9	659.2	642.6	629.0
60°	711.9	701.0	690.2	679.4	668.6	654.8	638.1	621.4	604.8	588.1	574.5
62.5°	655.1	644.8	634.5	624.1	613.9	600.2	583.3	566.3	549.4	532.4	519.9
65°	574.2	563.7	553.2	542.7	532.2	518.7	502.4	486.0	469.6	453.3	440.9
67.5°	493.8	483.3	472.8	462.4	451.8	438.7	423.0	407.3	391.6	375.9	364.6
70°	439.3	428.8	418.3	407.8	397.3	384.3	368.9	353.5	338.0	322.5	313.0
72.5°	385.9	375.7	365.4	355.2	344.9	332.5	318.1	303.6	289.2	274.7	265.9
75°	305.9	296.6	287.3	278.0	268.8	257.7	244.7	231.8	218.7	205.7	198.9
77.5°	226.3	218.9	211.5	204.1	196.7	187.8	177.4	167.0	156.7	146.2	141.5
80°	180.7	173.3	165.9	158.5	151.1	143.0	134.4	125.7	117.1	108.4	105.7
82.5°	136.3	129.6	122.9	116.2	109.6	103.3	97.3	91.4	85.4	79.5	78.2
85°	76.5	70.9	65.4	59.7	54.2	50.6	49.1	47.6	46.0	44.5	44.1
87.5°	25.7	24.1	22.5	20.9	19.4	18.5	18.4	18.2	18.1	18.0	18.1
90°	0.4	1.2	1.9	2.6	3.3	3.9	4.5	5.2	5.8	6.5	7.0
92.5°	9.8	10.3	10.8	11.3	11.8	12.4	13.2	14.0	14.7	15.5	16.1
95°	26.3	26.5	26.7	26.8	27.0	27.6	28.4	29.3	30.2	31.1	31.7
97.5°	43.6	43.7	43.8	43.9	44.0	44.6	45.8	47.1	48.3	49.6	50.1
100°	56.6	56.6	56.6	56.6	56.6	57.2	58.3	59.5	60.6	61.8	62.7
102.5°	70.4	70.8	71.2	71.6	72.0	72.4	73.0	73.6	74.2	74.7	75.6
105°	92.1	92.6	93.0	93.5	94.0	94.4	95.0	95.5	96.0	96.6	97.1
107.5°	116.1	116.5	117.0	117.4	117.9	118.3	118.7	119.1	119.6	119.9	120.2
110°	132.6	133.0	133.5	133.9	134.4	134.7	135.0	135.3	135.5	135.8	136.1



TEST NUMBER: P333723-940

CATALOG NUMBER: S125RDIW-S1270D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	149.4	149.6	149.8	150.1	150.3	150.6	151.0	151.3	151.6	151.9	152.1
115°	174.2	174.5	175.0	175.3	175.7	175.9	176.1	176.3	176.5	176.6	176.6
117.5°	199.1	199.2	199.4	199.6	199.7	199.9	200.1	200.2	200.4	200.5	200.6
120°	214.6	215.1	215.5	216.0	216.4	216.7	216.8	216.9	217.0	217.0	217.0
122.5°	231.4	231.6	231.8	231.9	232.0	232.3	232.5	232.7	233.0	233.2	233.1
125°	254.2	254.8	255.3	255.8	256.4	256.7	256.8	256.9	257.0	257.1	256.9
127.5°	278.5	278.7	279.1	279.4	279.7	279.9	280.0	280.1	280.2	280.4	280.3
130°	293.0	293.5	293.9	294.4	294.8	295.2	295.3	295.5	295.7	295.9	295.8
132.5°	307.6	308.3	309.1	309.8	310.5	310.9	310.9	310.8	310.8	310.7	310.6
135°	330.6	331.2	331.7	332.3	332.8	333.1	333.1	333.2	333.3	333.4	333.4
137.5°	352.2	352.8	353.3	353.8	354.4	354.7	354.9	355.1	355.3	355.5	355.6
140°	366.1	366.6	367.0	367.5	367.9	368.4	368.6	368.9	369.2	369.4	369.6
142.5°	380.0	380.4	380.8	381.2	381.6	381.9	382.3	382.6	383.0	383.3	383.4
145°	400.6	400.9	401.3	401.6	402.0	402.3	402.5	402.8	403.1	403.3	403.3
147.5°	419.5	419.6	419.8	420.0	420.3	420.4	420.6	420.9	421.1	421.3	421.5
150°	432.0	431.9	431.9	431.8	431.7	431.9	432.2	432.6	432.9	433.3	433.3
152.5°	442.4	442.6	442.6	442.7	442.9	443.0	443.2	443.4	443.4	443.6	443.8
155°	458.3	458.3	458.3	458.3	458.3	458.3	458.4	458.5	458.6	458.7	459.1
157.5°	472.5	472.3	472.2	472.0	471.7	471.7	471.8	471.9	472.0	472.1	472.4
160°	481.0	480.7	480.4	480.1	479.8	479.7	479.8	479.9	480.0	480.1	480.5
162.5°	488.4	488.2	488.0	487.8	487.6	487.5	487.5	487.5	487.6	487.6	488.0
165°	498.3	498.1	497.9	497.8	497.6	497.6	497.7	497.8	497.8	497.9	498.3
167.5°	506.8	506.4	506.0	505.7	505.3	505.2	505.2	505.2	505.2	505.2	505.7
170°	511.2	510.9	510.5	510.1	509.8	509.6	509.6	509.6	509.6	509.6	510.1
172.5°	514.5	514.2	513.8	513.4	513.1	512.9	512.9	512.9	512.9	512.9	513.4
175°	518.2	517.7	517.4	517.0	516.7	516.5	516.5	516.5	516.5	516.5	517.0
177.5°	520.0	519.7	519.4	519.2	518.8	518.6	518.6	518.5	518.4	518.4	518.8
180°	519.3	519.3	519.3	519.3	519.3	519.3	519.3	519.3	519.3	519.3	519.3



TEST NUMBER: P333723-940

CATALOG NUMBER: S125RDIW-S1270D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8
2.5°	1834.5	1837.0	1839.5	1840.6	1840.4	1840.1	1839.9	1839.6
5°	1823.3	1826.4	1829.4	1830.7	1830.1	1829.4	1828.8	1828.2
7.5°	1800.5	1802.8	1804.9	1805.6	1804.9	1804.3	1803.6	1803.0
10°	1781.4	1782.4	1783.2	1783.2	1782.4	1781.4	1780.5	1779.6
12.5°	1754.3	1754.9	1755.6	1755.2	1753.8	1752.4	1751.0	1749.5
15°	1709.4	1709.1	1708.8	1707.3	1704.5	1701.7	1698.9	1696.1
17.5°	1653.6	1652.0	1650.5	1648.6	1646.3	1644.0	1641.7	1639.4
20°	1612.4	1610.9	1609.4	1607.1	1604.4	1601.6	1598.8	1596.1
22.5°	1571.6	1568.6	1565.6	1562.9	1560.7	1558.4	1556.0	1553.8
25°	1504.6	1500.6	1496.6	1492.8	1489.4	1486.0	1482.6	1479.3
27.5°	1432.2	1426.6	1420.9	1416.5	1413.2	1409.9	1406.6	1403.4
30°	1380.3	1373.1	1366.0	1361.1	1358.3	1355.5	1352.7	1350.0
32.5°	1329.8	1322.0	1314.1	1308.4	1304.9	1301.4	1297.9	1294.3
35°	1251.4	1242.4	1233.5	1226.8	1222.5	1218.2	1213.9	1209.5
37.5°	1169.4	1158.7	1147.9	1140.4	1136.2	1132.0	1127.8	1123.6
40°	1115.2	1103.4	1091.7	1084.0	1080.2	1076.6	1072.8	1069.2
42.5°	1061.7	1050.4	1039.2	1030.8	1025.4	1019.9	1014.5	1009.1
45°	976.2	963.9	951.5	943.1	938.4	933.8	929.2	924.5
47.5°	891.9	879.1	866.4	857.5	852.3	847.2	842.0	837.0
50°	834.6	821.6	808.7	799.9	795.2	790.6	786.0	781.3
52.5°	780.3	766.4	752.4	743.2	738.5	733.9	729.2	724.6
55°	697.9	684.0	670.1	660.7	655.8	650.8	645.9	641.0
57.5°	615.4	601.8	588.2	579.3	574.8	570.4	566.1	561.7
60°	560.9	547.3	533.7	524.6	520.0	515.3	510.7	506.0
62.5°	507.3	494.6	482.1	473.4	468.8	464.1	459.5	454.9
65°	428.6	416.2	403.8	395.3	390.7	386.0	381.4	376.7
67.5°	353.3	342.0	330.7	323.2	319.5	315.8	312.1	308.4
70°	303.4	293.8	284.3	277.6	273.8	270.2	266.4	262.8
72.5°	257.1	248.3	239.3	233.7	231.2	228.8	226.3	223.8
75°	192.2	185.4	178.6	174.1	171.9	169.8	167.6	165.4
77.5°	136.7	132.0	127.2	124.0	122.4	120.8	119.2	117.6
80°	102.9	100.1	97.3	95.6	95.0	94.3	93.8	93.2
82.5°	77.0	75.6	74.4	73.5	73.1	72.8	72.4	72.1
85°	43.9	43.6	43.2	43.0	42.6	42.4	42.0	41.7
87.5°	18.2	18.3	18.4	18.3	18.1	17.9	17.7	17.5
90°	7.4	7.8	8.3	8.6	8.9	9.2	9.5	9.7
92.5°	16.7	17.3	17.9	18.3	18.5	18.6	18.9	19.1
95°	32.4	33.0	33.6	34.1	34.2	34.4	34.6	34.8
97.5°	50.7	51.4	51.9	52.3	52.3	52.5	52.6	52.7
100°	63.5	64.3	65.1	65.5	65.7	65.9	66.1	66.3
102.5°	76.5	77.4	78.3	78.8	79.1	79.4	79.6	79.9
105°	97.6	98.2	98.7	99.2	99.4	99.7	100.0	100.2
107.5°	120.5	120.7	121.0	121.2	121.2	121.1	121.1	121.1
110°	136.3	136.6	136.9	137.0	136.9	136.8	136.7	136.6



TEST NUMBER: P333723-940

CATALOG NUMBER: S125RDIW-S1270D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	152.2	152.3	152.5	152.5	152.3	152.1	151.9	151.8
115°	176.5	176.4	176.3	176.2	176.1	176.0	175.9	175.8
117.5°	200.7	200.7	200.8	200.7	200.4	200.0	199.6	199.2
120°	217.0	217.0	217.0	216.9	216.5	216.2	215.8	215.4
122.5°	233.1	233.0	232.9	232.7	232.5	232.2	231.8	231.6
125°	256.7	256.5	256.4	256.2	256.1	256.0	255.9	255.8
127.5°	280.2	280.1	280.0	279.8	279.6	279.5	279.3	279.1
130°	295.7	295.6	295.5	295.3	295.2	295.0	294.8	294.6
132.5°	310.5	310.4	310.3	310.2	310.0	309.7	309.4	309.2
135°	333.4	333.4	333.4	333.2	332.9	332.5	332.2	331.8
137.5°	355.7	355.8	356.0	355.8	355.3	354.9	354.4	353.9
140°	369.8	370.0	370.1	370.0	369.5	369.1	368.6	368.2
142.5°	383.5	383.6	383.7	383.5	383.1	382.6	382.2	381.7
145°	403.3	403.3	403.3	403.2	403.0	402.7	402.4	402.2
147.5°	421.7	422.0	422.1	422.0	421.3	420.7	420.1	419.5
150°	433.3	433.3	433.3	433.2	433.0	432.8	432.7	432.5
152.5°	444.1	444.3	444.4	444.4	444.1	443.8	443.4	443.1
155°	459.4	459.8	460.1	460.1	459.7	459.2	458.8	458.3
157.5°	472.8	473.1	473.5	473.4	472.8	472.2	471.6	471.0
160°	480.9	481.3	481.6	481.5	481.1	480.6	480.2	479.7
162.5°	488.5	488.8	489.3	489.3	488.7	488.2	487.7	487.1
165°	498.6	499.0	499.4	499.3	498.7	498.2	497.7	497.1
167.5°	506.2	506.8	507.3	507.3	506.7	506.1	505.6	505.1
170°	510.7	511.2	511.8	511.8	511.1	510.5	509.9	509.3
172.5°	514.0	514.5	515.1	515.1	514.4	513.9	513.4	512.8
175°	517.5	518.2	518.7	518.6	518.0	517.4	516.7	516.1
177.5°	519.2	519.7	520.1	520.0	519.6	519.1	518.5	518.1
180°	519.3	519.3	519.3	519.3	519.3	519.3	519.3	519.3

(END OF REPORT)