

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333657-940

Luminaire Tested: **S125RDIW-S375D1560U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333657-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S375D1560U940-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6126.4 lumens  
Efficiency: N/A  
Efficacy: 114.7 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	92	87	84	81	81	78	75	72	59	57	55	42	41	40	26	26	25	18
2	83	76	71	66	74	68	63	59	52	49	46	37	35	34	24	23	22	16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	28	21	20	19	13
4	70	59	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	12
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	9
7	54	42	35	30	48	38	32	27	29	25	22	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	29	23	19	22	18	15	16	14	11	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3241	3241	3241	3241
5°	3729	3246	2867	3246
10°	4278	3229	2530	3229
15°	4621	3196	2249	3196
20°	5096	3158	2076	3158
25°	5897	3107	1927	3107
30°	6416	3053	1829	3053
35°	5412	2990	1738	2990
40°	3780	2878	1661	2878
45°	2804	2726	1585	2726
50°	2237	2569	1519	2569
55°	1897	2374	1462	2374
60°	1639	2198	1368	2198
65°	1461	2008	1177	2008
70°	1284	1841	1074	1841
75°	1110	1592	1008	1592
80°	841	1339	841	1339
85°	704	1052	793	1052



TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.1	0.8
10°-20°	141.1	2.3
20°-30°	223.6	3.7
30°-40°	269.7	4.4
40°-50°	240.9	3.9
50°-60°	184.7	3.0
60°-70°	120.0	2.0
70°-80°	58.3	1.0
80°-90°	17.7	0.3
90°-100°	115.7	1.9
100°-110°	341.8	5.6
110°-120°	578.9	9.4
120°-130°	761.9	12.4
130°-140°	853.7	13.9
140°-150°	836.7	13.7
150°-160°	702.8	11.5
160°-170°	467.2	7.6
170°-180°	163.5	2.7
0°-30°	412.8	6.7
0°-40°	682.5	11.1
0°-60°	1108.1	18.1
0°-90°	1304.2	21.3
90°-120°	1036.5	16.9
90°-150°	3488.8	56.9
90°-180°	4822.0	78.7
0°-180°	6126.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	502	502	502	502	502	
5°	575	501	442	501	575	57
15°	691	478	336	478	691	198
25°	828	436	270	436	828	380
35°	686	379	220	379	686	415
45°	307	298	174	298	307	245
55°	168	211	130	211	168	153
65°	96	131	77	131	96	95
75°	44	64	40	64	44	47
85°	10	14	11	14	10	12
90°	32	1	32	1	32	19
95°	116	87	116	87	116	118
105°	334	307	334	307	334	353
115°	585	580	585	580	585	579
125°	851	846	851	846	851	760
135°	1104	1100	1104	1100	1104	852
145°	1338	1333	1338	1333	1338	835
155°	1525	1525	1525	1525	1525	702
165°	1654	1658	1654	1658	1654	466
175°	1717	1724	1717	1724	1717	163
180°	1728	1728	1728	1728	1728	



TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	528.0	527.6	528.3	526.5	526.6	523.9	523.9	521.7	518.9	516.7	515.8
5°	575.2	575.7	574.9	571.8	569.7	566.6	563.1	557.0	551.8	546.8	543.0
7.5°	624.0	624.3	621.5	620.6	615.4	611.6	603.9	595.4	588.0	578.5	571.2
10°	652.4	652.1	649.3	646.9	642.5	636.7	629.0	619.2	609.9	599.6	589.7
12.5°	668.8	668.2	667.4	664.6	660.4	655.3	648.8	639.1	627.7	616.4	604.8
15°	691.1	689.6	687.0	683.4	677.4	671.5	664.3	655.7	644.7	632.0	621.3
17.5°	718.6	718.6	714.5	709.6	701.5	691.0	679.8	665.9	651.0	637.0	625.6
20°	741.4	740.7	736.6	727.1	717.8	704.6	691.9	674.8	656.7	638.3	624.1
22.5°	774.0	772.4	768.1	755.6	741.3	724.2	704.7	683.9	661.9	641.1	622.4
25°	827.5	826.3	817.8	803.3	783.2	757.0	731.5	702.8	671.3	643.9	621.3
27.5°	864.1	862.7	856.4	844.5	825.8	798.3	763.8	725.4	686.1	648.4	615.7
30°	860.4	863.5	862.7	857.1	843.1	818.4	786.5	743.4	696.6	652.4	613.4
32.5°	808.7	811.5	818.7	829.6	830.5	820.6	796.7	756.9	708.5	658.1	611.5
35°	686.5	690.3	704.3	726.3	755.2	779.3	784.2	762.8	719.3	665.1	608.9
37.5°	527.8	548.0	559.9	583.1	626.7	671.0	713.6	729.3	710.9	662.2	604.5
40°	448.4	453.3	474.3	500.5	537.2	583.3	644.1	688.0	689.4	655.7	597.5
42.5°	383.7	390.0	404.4	425.3	456.7	502.8	565.6	623.6	650.3	637.5	588.4
45°	307.0	311.7	322.3	338.3	362.4	400.6	454.5	521.5	574.6	595.5	564.2
47.5°	252.2	254.8	263.9	276.2	294.0	321.7	363.6	421.7	485.4	530.1	525.8
50°	222.6	225.4	232.4	241.7	256.7	280.2	313.6	362.0	427.8	482.3	493.3
52.5°	199.5	201.9	206.3	215.0	227.4	245.4	272.4	316.2	375.3	433.4	458.7
55°	168.5	170.2	173.7	178.6	188.5	201.5	224.8	255.1	302.9	361.4	398.5
57.5°	143.1	143.9	146.2	150.7	157.6	167.0	183.9	209.5	243.8	296.5	337.4
60°	126.9	127.8	130.6	133.8	139.1	147.8	161.0	178.9	211.8	255.3	296.7
62.5°	114.0	114.6	115.8	118.9	123.6	130.3	140.6	155.2	181.5	219.7	258.8
65°	95.6	95.8	96.2	98.7	101.6	106.6	113.3	123.6	143.4	172.3	206.9
67.5°	77.8	78.2	79.6	80.5	83.5	86.1	90.1	97.9	111.9	131.3	158.3
70°	68.0	67.8	69.2	70.3	71.2	74.4	77.0	83.5	92.1	106.9	129.4
72.5°	58.8	58.2	58.9	59.2	60.5	62.7	65.4	69.3	76.0	86.1	103.3
75°	44.5	44.7	44.7	45.1	46.2	47.0	47.8	49.8	53.6	60.4	69.6
77.5°	31.2	30.9	31.7	31.9	32.5	33.4	34.2	35.0	36.5	39.2	44.1
80°	22.6	22.6	22.8	23.5	23.3	23.7	24.7	25.6	27.4	29.1	30.7
82.5°	17.4	17.2	17.4	17.6	17.5	17.9	18.3	18.5	19.2	20.0	21.1
85°	9.5	9.5	9.7	9.7	9.9	9.9	10.1	10.1	10.1	10.3	10.5
87.5°	10.1	9.7	9.4	9.2	9.2	9.3	8.8	8.4	8.0	7.8	7.5
90°	32.3	31.4	30.5	29.6	28.7	27.5	26.0	24.5	23.0	21.5	19.4
92.5°	63.5	62.8	62.2	61.5	60.8	59.6	57.5	55.6	53.6	51.6	49.0
95°	115.7	115.0	114.5	113.9	113.2	111.9	109.9	107.7	105.7	103.5	100.6
97.5°	175.4	175.0	174.7	174.3	174.0	172.7	170.8	168.8	166.8	164.9	160.8
100°	220.5	220.0	219.4	218.7	218.2	216.5	213.8	211.2	208.5	205.7	201.9
102.5°	265.7	264.9	264.0	263.2	262.4	260.5	257.6	254.7	251.7	248.8	246.8
105°	333.5	332.6	331.7	330.8	329.9	328.6	326.8	325.0	323.2	321.5	319.6
107.5°	402.9	403.0	403.1	403.1	403.1	402.7	401.8	400.9	400.0	399.1	397.8
110°	454.6	454.9	455.1	455.5	455.8	455.5	454.6	453.7	452.7	451.8	450.9



TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	505.2	505.7	506.2	506.8	507.3	507.3	506.9	506.5	506.0	505.7	504.5
115°	585.1	585.3	585.6	585.9	586.2	586.5	586.8	587.1	587.4	587.7	587.1
117.5°	663.0	664.2	665.4	666.6	667.8	668.2	668.1	667.8	667.5	667.4	666.7
120°	716.8	718.0	719.2	720.4	721.6	722.2	722.2	722.2	722.2	722.2	721.8
122.5°	770.6	771.5	772.5	773.5	774.5	775.0	775.3	775.5	775.7	776.0	775.2
125°	851.3	851.6	851.9	852.2	852.5	852.9	853.5	854.2	854.7	855.3	855.1
127.5°	928.7	929.3	930.0	930.5	931.1	931.6	931.9	932.2	932.5	932.8	932.5
130°	980.4	981.0	981.6	982.2	982.8	983.2	983.6	983.8	984.1	984.4	983.8
132.5°	1028.8	1029.7	1030.5	1031.4	1032.2	1032.7	1033.0	1033.3	1033.6	1033.9	1034.0
135°	1104.1	1105.3	1106.5	1107.7	1108.9	1109.5	1109.5	1109.5	1109.5	1109.5	1109.2
137.5°	1177.8	1179.3	1180.8	1182.3	1183.8	1184.4	1184.0	1183.7	1183.3	1182.9	1182.2
140°	1225.1	1226.6	1228.2	1229.7	1231.1	1231.5	1231.0	1230.4	1229.8	1229.2	1228.3
142.5°	1270.3	1271.8	1273.4	1274.8	1276.3	1276.9	1276.5	1276.1	1275.8	1275.4	1274.3
145°	1338.1	1339.0	1339.9	1340.8	1341.7	1342.1	1342.1	1342.1	1342.1	1342.1	1341.2
147.5°	1396.0	1398.0	1400.0	1402.0	1404.1	1404.7	1404.0	1403.3	1402.6	1401.9	1401.1
150°	1439.0	1439.6	1440.2	1440.7	1441.4	1441.7	1441.7	1441.7	1441.7	1441.7	1440.5
152.5°	1474.5	1475.6	1476.7	1477.7	1478.8	1479.0	1478.3	1477.6	1476.9	1476.1	1475.6
155°	1525.1	1526.5	1528.0	1529.6	1531.1	1531.2	1530.0	1528.7	1527.6	1526.4	1526.1
157.5°	1567.3	1569.2	1571.2	1573.2	1575.2	1575.6	1574.4	1573.2	1572.0	1570.7	1570.5
160°	1596.3	1597.9	1599.3	1600.8	1602.3	1602.5	1601.2	1600.1	1598.8	1597.7	1597.4
162.5°	1621.0	1622.8	1624.5	1626.3	1628.0	1628.2	1626.7	1625.3	1623.9	1622.4	1622.4
165°	1654.1	1656.0	1657.8	1659.6	1661.3	1661.6	1660.5	1659.2	1658.0	1656.9	1656.5
167.5°	1680.5	1682.4	1684.3	1686.0	1687.9	1687.9	1686.1	1684.4	1682.6	1680.8	1680.8
170°	1694.5	1696.6	1698.7	1700.8	1702.9	1703.0	1701.2	1699.4	1697.6	1695.9	1695.9
172.5°	1706.4	1708.2	1710.0	1711.9	1713.8	1713.8	1712.0	1710.2	1708.4	1706.6	1706.6
175°	1717.3	1719.5	1721.5	1723.7	1725.7	1725.9	1724.1	1722.3	1720.5	1718.7	1718.7
177.5°	1723.9	1725.5	1727.2	1728.8	1730.5	1730.6	1729.2	1727.8	1726.4	1724.9	1725.1
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	515.8	514.6	512.5	510.5	508.0	505.9	504.4	502.6	500.2	497.5	495.2
5°	538.6	534.0	528.1	522.9	516.3	511.2	505.9	500.7	495.5	488.9	483.1
7.5°	563.9	554.6	545.5	534.0	523.6	514.3	505.4	496.4	487.6	478.2	469.2
10°	579.4	568.0	555.5	541.1	527.9	515.3	503.8	492.4	480.5	470.0	458.7
12.5°	593.9	579.3	564.9	546.7	530.8	515.5	500.8	486.7	473.9	460.3	448.1
15°	607.0	592.5	576.5	554.3	532.2	513.6	496.3	478.0	462.2	446.9	433.3
17.5°	612.1	596.9	578.3	556.9	532.8	509.4	487.1	467.1	448.4	430.6	415.4
20°	610.1	595.5	576.3	555.9	530.1	505.9	481.7	459.5	438.6	419.9	403.7
22.5°	605.3	590.2	571.7	550.1	525.7	499.9	474.1	450.4	428.6	409.2	391.5
25°	598.2	577.6	558.6	537.5	514.2	488.7	462.2	436.0	412.7	392.9	373.5
27.5°	590.7	565.0	540.8	520.0	495.3	472.6	446.9	420.1	395.7	375.5	355.6
30°	583.9	555.1	528.5	504.8	481.5	459.9	435.6	409.4	384.2	363.5	343.3
32.5°	575.5	544.8	515.7	488.3	465.8	444.4	422.4	397.3	372.9	351.4	330.9
35°	565.0	525.8	494.1	465.0	440.1	419.3	399.5	379.3	354.8	332.5	312.5
37.5°	551.2	506.7	470.0	438.4	412.1	391.2	375.5	357.0	334.7	313.4	294.9
40°	542.7	492.8	452.7	421.3	393.8	371.7	357.0	341.4	321.0	301.0	282.5
42.5°	531.5	480.2	435.2	402.6	374.8	353.6	338.8	325.1	308.0	289.2	269.3
45°	509.5	455.6	408.4	373.4	345.4	324.5	310.7	298.5	285.6	268.2	250.9
47.5°	481.0	429.9	380.5	342.2	314.9	295.5	282.1	272.5	263.2	248.5	231.8
50°	458.1	408.8	360.6	323.5	294.3	275.9	263.3	255.7	247.3	233.9	219.8
52.5°	431.0	387.0	339.8	301.9	274.3	257.1	245.0	237.4	230.4	219.5	206.2
55°	388.4	349.8	306.6	272.2	246.8	229.5	218.0	210.8	206.7	197.4	186.9
57.5°	339.2	311.7	273.5	240.3	217.8	200.8	192.3	186.2	181.6	175.0	167.6
60°	305.0	285.6	251.4	219.8	199.2	183.0	175.3	170.2	165.9	160.3	154.5
62.5°	270.2	256.1	226.3	199.2	180.3	166.7	159.5	154.9	149.9	146.2	140.5
65°	223.6	211.0	190.4	169.2	151.7	140.7	135.5	131.4	128.4	124.2	120.3
67.5°	173.9	168.8	154.5	139.9	127.3	117.6	113.2	110.3	106.6	104.2	101.5
70°	143.4	140.9	130.8	121.2	109.4	102.8	98.7	97.5	92.9	90.4	88.6
72.5°	116.4	115.2	109.4	102.7	94.4	88.6	84.9	83.5	80.5	78.6	77.4
75°	79.7	80.2	79.1	74.8	71.7	68.0	64.7	63.8	61.8	60.2	59.1
77.5°	50.5	52.5	52.6	52.4	51.2	49.0	47.5	46.9	44.9	44.3	44.1
80°	34.6	36.9	39.0	38.7	38.3	37.7	36.6	36.0	35.0	34.4	34.0
82.5°	23.1	25.1	26.9	28.0	27.9	27.3	26.7	26.3	26.1	25.7	25.6
85°	10.9	11.3	11.9	13.4	14.4	14.6	14.4	14.2	13.6	13.8	14.0
87.5°	7.2	6.9	6.6	6.2	5.5	5.8	5.9	5.5	5.7	5.8	6.0
90°	17.3	15.2	13.1	10.9	8.6	6.2	3.7	1.3	3.7	6.2	8.6
92.5°	46.5	44.0	41.4	39.2	37.5	35.9	34.2	32.5	34.2	35.9	37.5
95°	97.6	94.6	91.6	89.8	89.2	88.6	88.0	87.4	88.0	88.6	89.2
97.5°	156.7	152.5	148.4	146.2	146.0	145.7	145.4	145.3	145.4	145.7	146.0
100°	198.0	194.1	190.2	188.2	188.2	188.2	188.2	188.2	188.2	188.2	188.2
102.5°	244.9	242.9	240.9	239.3	238.1	236.9	235.8	234.5	235.8	236.9	238.1
105°	317.8	316.0	314.2	312.6	311.1	309.6	308.1	306.7	308.1	309.6	311.1
107.5°	396.4	395.0	393.7	392.2	390.7	389.2	387.7	386.2	387.7	389.2	390.7
110°	450.0	449.2	448.3	447.1	445.6	444.1	442.6	441.1	442.6	444.1	445.6





TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	503.4	502.2	501.1	500.2	499.4	498.6	497.8	497.0	497.8	498.6	499.4
115°	586.5	585.9	585.3	584.4	583.2	582.0	580.9	579.6	580.9	582.0	583.2
117.5°	666.2	665.7	665.1	664.6	664.1	663.5	663.0	662.5	663.0	663.5	664.1
120°	721.6	721.3	720.9	720.1	718.6	717.1	715.6	714.1	715.6	717.1	718.6
122.5°	774.5	773.6	772.8	772.2	771.7	771.2	770.6	770.1	770.6	771.2	771.7
125°	854.7	854.4	854.2	853.1	851.3	849.5	847.7	845.9	847.7	849.5	851.3
127.5°	932.1	931.7	931.4	930.7	929.6	928.6	927.6	926.6	927.6	928.6	929.6
130°	983.2	982.7	982.0	981.0	979.5	978.0	976.5	975.0	976.5	978.0	979.5
132.5°	1034.1	1034.3	1034.4	1033.2	1030.8	1028.3	1025.9	1023.4	1025.9	1028.3	1030.8
135°	1108.9	1108.6	1108.3	1107.2	1105.5	1103.7	1101.9	1100.1	1101.9	1103.7	1105.5
137.5°	1181.6	1181.0	1180.3	1179.1	1177.3	1175.6	1173.9	1172.2	1173.9	1175.6	1177.3
140°	1227.4	1226.5	1225.6	1224.4	1222.9	1221.4	1219.9	1218.4	1219.9	1221.4	1222.9
142.5°	1273.2	1272.0	1270.9	1269.7	1268.5	1267.2	1266.0	1264.7	1266.0	1267.2	1268.5
145°	1340.3	1339.4	1338.5	1337.6	1336.3	1335.2	1333.9	1332.8	1333.9	1335.2	1336.3
147.5°	1400.4	1399.7	1399.0	1398.3	1397.7	1397.0	1396.3	1395.7	1396.3	1397.0	1397.7
150°	1439.3	1438.1	1436.9	1436.5	1436.7	1437.1	1437.3	1437.6	1437.3	1437.1	1436.7
152.5°	1475.2	1474.7	1474.2	1473.7	1473.3	1472.9	1472.5	1472.0	1472.5	1472.9	1473.3
155°	1525.8	1525.5	1525.2	1525.1	1525.1	1525.1	1525.1	1525.1	1525.1	1525.1	1525.1
157.5°	1570.2	1569.9	1569.6	1569.8	1570.4	1571.1	1571.7	1572.4	1571.7	1571.1	1570.4
160°	1597.1	1596.8	1596.5	1596.8	1597.7	1598.6	1599.5	1600.4	1599.5	1598.6	1597.7
162.5°	1622.3	1622.2	1622.2	1622.5	1623.2	1623.8	1624.4	1625.1	1624.4	1623.8	1623.2
165°	1656.3	1656.0	1655.6	1655.8	1656.4	1657.0	1657.6	1658.2	1657.6	1657.0	1656.4
167.5°	1680.8	1680.8	1680.8	1681.4	1682.6	1683.8	1685.0	1686.1	1685.0	1683.8	1682.6
170°	1695.9	1695.9	1695.9	1696.5	1697.6	1698.8	1700.0	1701.2	1700.0	1698.8	1697.6
172.5°	1706.6	1706.6	1706.6	1707.2	1708.4	1709.6	1710.8	1712.0	1710.8	1709.6	1708.4
175°	1718.7	1718.7	1718.7	1719.3	1720.5	1721.7	1722.9	1724.1	1722.9	1721.7	1720.5
177.5°	1725.4	1725.6	1725.8	1726.4	1727.4	1728.4	1729.3	1730.3	1729.3	1728.4	1727.4
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	493.5	491.2	489.5	486.2	483.9	483.0	481.2	480.6	482.5	481.2	481.0
5°	478.8	472.9	468.1	463.4	458.3	455.0	450.0	449.2	447.9	446.1	445.7
7.5°	461.3	453.4	447.4	439.5	432.7	427.2	421.1	418.1	416.5	414.1	410.9
10°	449.4	440.1	431.9	424.0	415.6	408.8	402.6	397.9	394.8	391.9	390.7
12.5°	437.7	428.2	417.7	408.2	398.8	391.2	384.3	381.2	377.8	374.4	371.6
15°	419.5	407.0	395.4	384.5	376.5	368.2	361.6	357.0	352.0	350.4	344.9
17.5°	400.2	387.9	374.3	362.9	353.6	344.5	337.2	332.1	328.2	322.9	320.4
20°	388.2	373.5	360.3	349.8	339.6	328.9	321.5	317.1	313.4	309.1	307.0
22.5°	375.3	361.1	347.5	335.2	324.8	314.1	308.9	304.4	300.2	296.2	293.5
25°	356.4	342.1	327.8	315.0	304.2	296.5	290.3	285.2	282.9	279.0	276.1
27.5°	337.8	322.4	307.7	295.0	286.4	278.8	273.8	269.7	265.6	262.3	259.7
30°	325.7	310.1	294.0	283.9	274.8	267.7	262.1	258.2	255.1	252.0	250.1
32.5°	313.7	297.6	283.3	272.4	263.9	257.6	251.9	248.1	244.9	241.5	239.2
35°	294.4	277.9	266.4	255.7	247.3	241.5	237.6	232.2	229.5	227.0	224.8
37.5°	276.5	261.2	248.7	239.3	231.9	226.2	221.1	218.3	215.0	212.8	210.9
40°	263.3	249.3	238.0	228.1	222.7	216.3	211.6	207.9	205.5	202.5	200.5
42.5°	251.5	238.4	227.4	218.6	211.9	206.4	201.9	198.1	195.0	193.0	191.3
45°	234.7	221.7	211.0	202.8	196.5	191.5	186.6	184.9	180.7	178.3	177.4
47.5°	217.3	205.7	195.4	187.8	181.5	176.6	172.1	168.4	166.0	163.6	162.3
50°	205.6	194.5	184.9	177.4	171.2	165.9	161.8	159.3	156.1	153.9	152.3
52.5°	193.9	183.6	174.0	166.8	161.5	156.1	151.5	149.1	146.2	144.7	143.6
55°	177.2	166.3	158.0	151.1	145.4	140.5	136.2	133.8	131.9	130.5	130.0
57.5°	158.3	149.6	142.0	135.6	129.8	125.2	121.4	119.0	117.4	117.2	115.9
60°	145.9	138.0	131.1	124.2	119.3	114.9	111.6	109.0	107.4	107.2	106.7
62.5°	133.5	126.0	119.5	113.5	109.1	105.0	101.7	98.8	97.8	96.8	95.9
65°	115.2	108.3	103.0	98.3	93.5	90.1	86.9	85.1	82.8	81.6	79.4
67.5°	97.2	91.9	86.8	82.8	79.0	75.7	73.1	70.4	68.8	67.9	66.3
70°	85.3	81.1	76.1	71.7	68.8	66.2	64.1	61.0	59.9	59.1	58.3
72.5°	74.1	70.4	66.2	62.6	59.7	57.2	54.8	53.4	52.3	51.5	51.1
75°	58.3	54.8	51.1	48.6	46.5	44.5	43.2	42.3	41.8	41.6	40.8
77.5°	42.8	40.9	38.0	36.0	34.7	33.8	32.7	32.2	32.1	31.2	30.9
80°	32.7	31.7	29.2	28.4	27.4	26.6	25.9	25.0	23.9	23.5	22.8
82.5°	24.3	23.4	22.3	21.0	20.2	19.6	19.1	18.6	18.8	18.2	17.9
85°	13.0	11.9	11.5	11.3	10.9	11.3	11.1	10.9	10.7	10.5	10.7
87.5°	6.3	6.8	7.0	7.8	7.7	8.3	8.6	8.6	9.0	9.3	9.4
90°	10.9	13.1	15.2	17.3	19.4	21.5	23.0	24.5	26.0	27.5	28.7
92.5°	39.2	41.4	44.0	46.5	49.0	51.6	53.6	55.6	57.5	59.6	60.8
95°	89.8	91.6	94.6	97.6	100.6	103.5	105.7	107.7	109.9	111.9	113.2
97.5°	146.2	148.4	152.5	156.7	160.8	164.9	166.8	168.8	170.8	172.7	174.0
100°	188.2	190.2	194.1	198.0	201.9	205.7	208.5	211.2	213.8	216.5	218.2
102.5°	239.3	240.9	242.9	244.9	246.8	248.8	251.7	254.7	257.6	260.5	262.4
105°	312.6	314.2	316.0	317.8	319.6	321.5	323.2	325.0	326.8	328.6	329.9
107.5°	392.2	393.7	395.0	396.4	397.8	399.1	400.0	400.9	401.8	402.7	403.1
110°	447.1	448.3	449.2	450.0	450.9	451.8	452.7	453.7	454.6	455.5	455.8



TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	500.2	501.1	502.2	503.4	504.5	505.7	506.0	506.5	506.9	507.3	507.3
115°	584.4	585.3	585.9	586.5	587.1	587.7	587.4	587.1	586.8	586.5	586.2
117.5°	664.6	665.1	665.7	666.2	666.7	667.4	667.5	667.8	668.1	668.2	667.8
120°	720.1	720.9	721.3	721.6	721.8	722.2	722.2	722.2	722.2	722.2	721.6
122.5°	772.2	772.8	773.6	774.5	775.2	776.0	775.7	775.5	775.3	775.0	774.5
125°	853.1	854.2	854.4	854.7	855.1	855.3	854.7	854.2	853.5	852.9	852.5
127.5°	930.7	931.4	931.7	932.1	932.5	932.8	932.5	932.2	931.9	931.6	931.1
130°	981.0	982.0	982.7	983.2	983.8	984.4	984.1	983.8	983.6	983.2	982.8
132.5°	1033.2	1034.4	1034.3	1034.1	1034.0	1033.9	1033.6	1033.3	1033.0	1032.7	1032.2
135°	1107.2	1108.3	1108.6	1108.9	1109.2	1109.5	1109.5	1109.5	1109.5	1109.5	1108.9
137.5°	1179.1	1180.3	1181.0	1181.6	1182.2	1182.9	1183.3	1183.7	1184.0	1184.4	1183.8
140°	1224.4	1225.6	1226.5	1227.4	1228.3	1229.2	1229.8	1230.4	1231.0	1231.5	1231.1
142.5°	1269.7	1270.9	1272.0	1273.2	1274.3	1275.4	1275.8	1276.1	1276.5	1276.9	1276.3
145°	1337.6	1338.5	1339.4	1340.3	1341.2	1342.1	1342.1	1342.1	1342.1	1342.1	1341.7
147.5°	1398.3	1399.0	1399.7	1400.4	1401.1	1401.9	1402.6	1403.3	1404.0	1404.7	1404.1
150°	1436.5	1436.9	1438.1	1439.3	1440.5	1441.7	1441.7	1441.7	1441.7	1441.7	1441.4
152.5°	1473.7	1474.2	1474.7	1475.2	1475.6	1476.1	1476.9	1477.6	1478.3	1479.0	1478.8
155°	1525.1	1525.2	1525.5	1525.8	1526.1	1526.4	1527.6	1528.7	1530.0	1531.2	1531.1
157.5°	1569.8	1569.6	1569.9	1570.2	1570.5	1570.7	1572.0	1573.2	1574.4	1575.6	1575.2
160°	1596.8	1596.5	1596.8	1597.1	1597.4	1597.7	1598.8	1600.1	1601.2	1602.5	1602.3
162.5°	1622.5	1622.2	1622.2	1622.3	1622.4	1622.4	1623.9	1625.3	1626.7	1628.2	1628.0
165°	1655.8	1655.6	1656.0	1656.3	1656.5	1656.9	1658.0	1659.2	1660.5	1661.6	1661.3
167.5°	1681.4	1680.8	1680.8	1680.8	1680.8	1680.8	1682.6	1684.4	1686.1	1687.9	1687.9
170°	1696.5	1695.9	1695.9	1695.9	1695.9	1695.9	1697.6	1699.4	1701.2	1703.0	1702.9
172.5°	1707.2	1706.6	1706.6	1706.6	1706.6	1706.6	1708.4	1710.2	1712.0	1713.8	1713.8
175°	1719.3	1718.7	1718.7	1718.7	1718.7	1718.7	1720.5	1722.3	1724.1	1725.9	1725.7
177.5°	1726.4	1725.8	1725.6	1725.4	1725.1	1724.9	1726.4	1727.8	1729.2	1730.6	1730.5
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	480.8	479.0	478.5	479.2	478.5	479.0	480.8	481.0	481.2	482.5	480.6
5°	443.6	441.6	442.6	442.2	442.6	441.6	443.6	445.7	446.1	447.9	449.2
7.5°	410.9	408.3	405.6	406.4	405.6	408.3	410.9	410.9	414.1	416.5	418.1
10°	388.0	385.9	384.7	385.8	384.7	385.9	388.0	390.7	391.9	394.8	397.9
12.5°	368.7	367.5	366.4	366.0	366.4	367.5	368.7	371.6	374.4	377.8	381.2
15°	342.4	340.0	338.9	336.3	338.9	340.0	342.4	344.9	350.4	352.0	357.0
17.5°	318.3	317.4	314.8	313.6	314.8	317.4	318.3	320.4	322.9	328.2	332.1
20°	303.9	303.1	300.4	302.0	300.4	303.1	303.9	307.0	309.1	313.4	317.1
22.5°	292.0	290.3	289.4	288.9	289.4	290.3	292.0	293.5	296.2	300.2	304.4
25°	275.3	272.6	271.5	270.4	271.5	272.6	275.3	276.1	279.0	282.9	285.2
27.5°	258.5	257.1	255.7	255.4	255.7	257.1	258.5	259.7	262.3	265.6	269.7
30°	247.6	246.2	245.2	245.2	245.2	246.2	247.6	250.1	252.0	255.1	258.2
32.5°	237.9	236.8	235.8	235.6	235.8	236.8	237.9	239.2	241.5	244.9	248.1
35°	223.7	222.1	221.7	220.4	221.7	222.1	223.7	224.8	227.0	229.5	232.2
37.5°	209.0	207.7	207.7	207.5	207.7	207.7	209.0	210.9	212.8	215.0	218.3
40°	199.7	198.6	198.4	197.0	198.4	198.6	199.7	200.5	202.5	205.5	207.9
42.5°	189.6	189.0	188.3	187.7	188.3	189.0	189.6	191.3	193.0	195.0	198.1
45°	175.9	174.5	174.5	173.5	174.5	174.5	175.9	177.4	178.3	180.7	184.9
47.5°	161.8	160.8	160.9	159.8	160.9	160.8	161.8	162.3	163.6	166.0	168.4
50°	152.5	151.9	151.7	151.2	151.7	151.9	152.5	152.3	153.9	156.1	159.3
52.5°	143.1	142.8	143.6	142.7	143.6	142.8	143.1	143.6	144.7	146.2	149.1
55°	130.5	129.8	131.1	129.8	131.1	129.8	130.5	130.0	130.5	131.9	133.8
57.5°	115.9	115.3	116.5	115.8	116.5	115.3	115.9	115.9	117.2	117.4	119.0
60°	106.3	105.0	105.7	105.9	105.7	105.0	106.3	106.7	107.2	107.4	109.0
62.5°	95.0	94.2	94.7	93.7	94.7	94.2	95.0	95.9	96.8	97.8	98.8
65°	78.9	78.3	77.5	77.0	77.5	78.3	78.9	79.4	81.6	82.8	85.1
67.5°	66.3	64.8	64.7	65.1	64.7	64.8	66.3	66.3	67.9	68.8	70.4
70°	57.1	57.1	56.9	56.9	56.9	57.1	57.1	58.3	59.1	59.9	61.0
72.5°	50.6	50.5	50.1	49.9	50.1	50.5	50.6	51.1	51.5	52.3	53.4
75°	40.8	41.0	40.6	40.4	40.6	41.0	40.8	40.8	41.6	41.8	42.3
77.5°	30.1	29.2	29.7	29.2	29.7	29.2	30.1	30.9	31.2	32.1	32.2
80°	22.8	22.6	23.3	22.6	23.3	22.6	22.8	22.8	23.5	23.9	25.0
82.5°	18.1	17.9	18.2	17.7	18.2	17.9	18.1	17.9	18.2	18.8	18.6
85°	10.9	10.7	10.5	10.7	10.5	10.7	10.9	10.7	10.5	10.7	10.9
87.5°	9.7	9.7	9.9	10.1	9.9	9.7	9.7	9.4	9.3	9.0	8.6
90°	29.6	30.5	31.4	32.3	31.4	30.5	29.6	28.7	27.5	26.0	24.5
92.5°	61.5	62.2	62.8	63.5	62.8	62.2	61.5	60.8	59.6	57.5	55.6
95°	113.9	114.5	115.0	115.7	115.0	114.5	113.9	113.2	111.9	109.9	107.7
97.5°	174.3	174.7	175.0	175.4	175.0	174.7	174.3	174.0	172.7	170.8	168.8
100°	218.7	219.4	220.0	220.5	220.0	219.4	218.7	218.2	216.5	213.8	211.2
102.5°	263.2	264.0	264.9	265.7	264.9	264.0	263.2	262.4	260.5	257.6	254.7
105°	330.8	331.7	332.6	333.5	332.6	331.7	330.8	329.9	328.6	326.8	325.0
107.5°	403.1	403.1	403.0	402.9	403.0	403.1	403.1	403.1	402.7	401.8	400.9
110°	455.5	455.1	454.9	454.6	454.9	455.1	455.5	455.8	455.5	454.6	453.7



TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	506.8	506.2	505.7	505.2	505.7	506.2	506.8	507.3	507.3	506.9	506.5
115°	585.9	585.6	585.3	585.1	585.3	585.6	585.9	586.2	586.5	586.8	587.1
117.5°	666.6	665.4	664.2	663.0	664.2	665.4	666.6	667.8	668.2	668.1	667.8
120°	720.4	719.2	718.0	716.8	718.0	719.2	720.4	721.6	722.2	722.2	722.2
122.5°	773.5	772.5	771.5	770.6	771.5	772.5	773.5	774.5	775.0	775.3	775.5
125°	852.2	851.9	851.6	851.3	851.6	851.9	852.2	852.5	852.9	853.5	854.2
127.5°	930.5	930.0	929.3	928.7	929.3	930.0	930.5	931.1	931.6	931.9	932.2
130°	982.2	981.6	981.0	980.4	981.0	981.6	982.2	982.8	983.2	983.6	983.8
132.5°	1031.4	1030.5	1029.7	1028.8	1029.7	1030.5	1031.4	1032.2	1032.7	1033.0	1033.3
135°	1107.7	1106.5	1105.3	1104.1	1105.3	1106.5	1107.7	1108.9	1109.5	1109.5	1109.5
137.5°	1182.3	1180.8	1179.3	1177.8	1179.3	1180.8	1182.3	1183.8	1184.4	1184.0	1183.7
140°	1229.7	1228.2	1226.6	1225.1	1226.6	1228.2	1229.7	1231.1	1231.5	1231.0	1230.4
142.5°	1274.8	1273.4	1271.8	1270.3	1271.8	1273.4	1274.8	1276.3	1276.9	1276.5	1276.1
145°	1340.8	1339.9	1339.0	1338.1	1339.0	1339.9	1340.8	1341.7	1342.1	1342.1	1342.1
147.5°	1402.0	1400.0	1398.0	1396.0	1398.0	1400.0	1402.0	1404.1	1404.7	1404.0	1403.3
150°	1440.7	1440.2	1439.6	1439.0	1439.6	1440.2	1440.7	1441.4	1441.7	1441.7	1441.7
152.5°	1477.7	1476.7	1475.6	1474.5	1475.6	1476.7	1477.7	1478.8	1479.0	1478.3	1477.6
155°	1529.6	1528.0	1526.5	1525.1	1526.5	1528.0	1529.6	1531.1	1531.2	1530.0	1528.7
157.5°	1573.2	1571.2	1569.2	1567.3	1569.2	1571.2	1573.2	1575.2	1575.6	1574.4	1573.2
160°	1600.8	1599.3	1597.9	1596.3	1597.9	1599.3	1600.8	1602.3	1602.5	1601.2	1600.1
162.5°	1626.3	1624.5	1622.8	1621.0	1622.8	1624.5	1626.3	1628.0	1628.2	1626.7	1625.3
165°	1659.6	1657.8	1656.0	1654.1	1656.0	1657.8	1659.6	1661.3	1661.6	1660.5	1659.2
167.5°	1686.0	1684.3	1682.4	1680.5	1682.4	1684.3	1686.0	1687.9	1687.9	1686.1	1684.4
170°	1700.8	1698.7	1696.6	1694.5	1696.6	1698.7	1700.8	1702.9	1703.0	1701.2	1699.4
172.5°	1711.9	1710.0	1708.2	1706.4	1708.2	1710.0	1711.9	1713.8	1713.8	1712.0	1710.2
175°	1723.7	1721.5	1719.5	1717.3	1719.5	1721.5	1723.7	1725.7	1725.9	1724.1	1722.3
177.5°	1728.8	1727.2	1725.5	1723.9	1725.5	1727.2	1728.8	1730.5	1730.6	1729.2	1727.8
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	481.2	483.0	483.9	486.2	489.5	491.2	493.5	495.2	497.5	500.2	502.6
5°	450.0	455.0	458.3	463.4	468.1	472.9	478.8	483.1	488.9	495.5	500.7
7.5°	421.1	427.2	432.7	439.5	447.4	453.4	461.3	469.2	478.2	487.6	496.4
10°	402.6	408.8	415.6	424.0	431.9	440.1	449.4	458.7	470.0	480.5	492.4
12.5°	384.3	391.2	398.8	408.2	417.7	428.2	437.7	448.1	460.3	473.9	486.7
15°	361.6	368.2	376.5	384.5	395.4	407.0	419.5	433.3	446.9	462.2	478.0
17.5°	337.2	344.5	353.6	362.9	374.3	387.9	400.2	415.4	430.6	448.4	467.1
20°	321.5	328.9	339.6	349.8	360.3	373.5	388.2	403.7	419.9	438.6	459.5
22.5°	308.9	314.1	324.8	335.2	347.5	361.1	375.3	391.5	409.2	428.6	450.4
25°	290.3	296.5	304.2	315.0	327.8	342.1	356.4	373.5	392.9	412.7	436.0
27.5°	273.8	278.8	286.4	295.0	307.7	322.4	337.8	355.6	375.5	395.7	420.1
30°	262.1	267.7	274.8	283.9	294.0	310.1	325.7	343.3	363.5	384.2	409.4
32.5°	251.9	257.6	263.9	272.4	283.3	297.6	313.7	330.9	351.4	372.9	397.3
35°	237.6	241.5	247.3	255.7	266.4	277.9	294.4	312.5	332.5	354.8	379.3
37.5°	221.1	226.2	231.9	239.3	248.7	261.2	276.5	294.9	313.4	334.7	357.0
40°	211.6	216.3	222.7	228.1	238.0	249.3	263.3	282.5	301.0	321.0	341.4
42.5°	201.9	206.4	211.9	218.6	227.4	238.4	251.5	269.3	289.2	308.0	325.1
45°	186.6	191.5	196.5	202.8	211.0	221.7	234.7	250.9	268.2	285.6	298.5
47.5°	172.1	176.6	181.5	187.8	195.4	205.7	217.3	231.8	248.5	263.2	272.5
50°	161.8	165.9	171.2	177.4	184.9	194.5	205.6	219.8	233.9	247.3	255.7
52.5°	151.5	156.1	161.5	166.8	174.0	183.6	193.9	206.2	219.5	230.4	237.4
55°	136.2	140.5	145.4	151.1	158.0	166.3	177.2	186.9	197.4	206.7	210.8
57.5°	121.4	125.2	129.8	135.6	142.0	149.6	158.3	167.6	175.0	181.6	186.2
60°	111.6	114.9	119.3	124.2	131.1	138.0	145.9	154.5	160.3	165.9	170.2
62.5°	101.7	105.0	109.1	113.5	119.5	126.0	133.5	140.5	146.2	149.9	154.9
65°	86.9	90.1	93.5	98.3	103.0	108.3	115.2	120.3	124.2	128.4	131.4
67.5°	73.1	75.7	79.0	82.8	86.8	91.9	97.2	101.5	104.2	106.6	110.3
70°	64.1	66.2	68.8	71.7	76.1	81.1	85.3	88.6	90.4	92.9	97.5
72.5°	54.8	57.2	59.7	62.6	66.2	70.4	74.1	77.4	78.6	80.5	83.5
75°	43.2	44.5	46.5	48.6	51.1	54.8	58.3	59.1	60.2	61.8	63.8
77.5°	32.7	33.8	34.7	36.0	38.0	40.9	42.8	44.1	44.3	44.9	46.9
80°	25.9	26.6	27.4	28.4	29.2	31.7	32.7	34.0	34.4	35.0	36.0
82.5°	19.1	19.6	20.2	21.0	22.3	23.4	24.3	25.6	25.7	26.1	26.3
85°	11.1	11.3	10.9	11.3	11.5	11.9	13.0	14.0	13.8	13.6	14.2
87.5°	8.6	8.3	7.7	7.8	7.0	6.8	6.3	6.0	5.8	5.7	5.5
90°	23.0	21.5	19.4	17.3	15.2	13.1	10.9	8.6	6.2	3.7	1.3
92.5°	53.6	51.6	49.0	46.5	44.0	41.4	39.2	37.5	35.9	34.2	32.5
95°	105.7	103.5	100.6	97.6	94.6	91.6	89.8	89.2	88.6	88.0	87.4
97.5°	166.8	164.9	160.8	156.7	152.5	148.4	146.2	146.0	145.7	145.4	145.3
100°	208.5	205.7	201.9	198.0	194.1	190.2	188.2	188.2	188.2	188.2	188.2
102.5°	251.7	248.8	246.8	244.9	242.9	240.9	239.3	238.1	236.9	235.8	234.5
105°	323.2	321.5	319.6	317.8	316.0	314.2	312.6	311.1	309.6	308.1	306.7
107.5°	400.0	399.1	397.8	396.4	395.0	393.7	392.2	390.7	389.2	387.7	386.2
110°	452.7	451.8	450.9	450.0	449.2	448.3	447.1	445.6	444.1	442.6	441.1



TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	506.0	505.7	504.5	503.4	502.2	501.1	500.2	499.4	498.6	497.8	497.0
115°	587.4	587.7	587.1	586.5	585.9	585.3	584.4	583.2	582.0	580.9	579.6
117.5°	667.5	667.4	666.7	666.2	665.7	665.1	664.6	664.1	663.5	663.0	662.5
120°	722.2	722.2	721.8	721.6	721.3	720.9	720.1	718.6	717.1	715.6	714.1
122.5°	775.7	776.0	775.2	774.5	773.6	772.8	772.2	771.7	771.2	770.6	770.1
125°	854.7	855.3	855.1	854.7	854.4	854.2	853.1	851.3	849.5	847.7	845.9
127.5°	932.5	932.8	932.5	932.1	931.7	931.4	930.7	929.6	928.6	927.6	926.6
130°	984.1	984.4	983.8	983.2	982.7	982.0	981.0	979.5	978.0	976.5	975.0
132.5°	1033.6	1033.9	1034.0	1034.1	1034.3	1034.4	1033.2	1030.8	1028.3	1025.9	1023.4
135°	1109.5	1109.5	1109.2	1108.9	1108.6	1108.3	1107.2	1105.5	1103.7	1101.9	1100.1
137.5°	1183.3	1182.9	1182.2	1181.6	1181.0	1180.3	1179.1	1177.3	1175.6	1173.9	1172.2
140°	1229.8	1229.2	1228.3	1227.4	1226.5	1225.6	1224.4	1222.9	1221.4	1219.9	1218.4
142.5°	1275.8	1275.4	1274.3	1273.2	1272.0	1270.9	1269.7	1268.5	1267.2	1266.0	1264.7
145°	1342.1	1342.1	1341.2	1340.3	1339.4	1338.5	1337.6	1336.3	1335.2	1333.9	1332.8
147.5°	1402.6	1401.9	1401.1	1400.4	1399.7	1399.0	1398.3	1397.7	1397.0	1396.3	1395.7
150°	1441.7	1441.7	1440.5	1439.3	1438.1	1436.9	1436.5	1436.7	1437.1	1437.3	1437.6
152.5°	1476.9	1476.1	1475.6	1475.2	1474.7	1474.2	1473.7	1473.3	1472.9	1472.5	1472.0
155°	1527.6	1526.4	1526.1	1525.8	1525.5	1525.2	1525.1	1525.1	1525.1	1525.1	1525.1
157.5°	1572.0	1570.7	1570.5	1570.2	1569.9	1569.6	1569.8	1570.4	1571.1	1571.7	1572.4
160°	1598.8	1597.7	1597.4	1597.1	1596.8	1596.5	1596.8	1597.7	1598.6	1599.5	1600.4
162.5°	1623.9	1622.4	1622.4	1622.3	1622.2	1622.2	1622.5	1623.2	1623.8	1624.4	1625.1
165°	1658.0	1656.9	1656.5	1656.3	1656.0	1655.6	1655.8	1656.4	1657.0	1657.6	1658.2
167.5°	1682.6	1680.8	1680.8	1680.8	1680.8	1680.8	1681.4	1682.6	1683.8	1685.0	1686.1
170°	1697.6	1695.9	1695.9	1695.9	1695.9	1695.9	1696.5	1697.6	1698.8	1700.0	1701.2
172.5°	1708.4	1706.6	1706.6	1706.6	1706.6	1706.6	1707.2	1708.4	1709.6	1710.8	1712.0
175°	1720.5	1718.7	1718.7	1718.7	1718.7	1718.7	1719.3	1720.5	1721.7	1722.9	1724.1
177.5°	1726.4	1724.9	1725.1	1725.4	1725.6	1725.8	1726.4	1727.4	1728.4	1729.3	1730.3
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	504.4	505.9	508.0	510.5	512.5	514.6	515.8	515.8	516.7	518.9	521.7
5°	505.9	511.2	516.3	522.9	528.1	534.0	538.6	543.0	546.8	551.8	557.0
7.5°	505.4	514.3	523.6	534.0	545.5	554.6	563.9	571.2	578.5	588.0	595.4
10°	503.8	515.3	527.9	541.1	555.5	568.0	579.4	589.7	599.6	609.9	619.2
12.5°	500.8	515.5	530.8	546.7	564.9	579.3	593.9	604.8	616.4	627.7	639.1
15°	496.3	513.6	532.2	554.3	576.5	592.5	607.0	621.3	632.0	644.7	655.7
17.5°	487.1	509.4	532.8	556.9	578.3	596.9	612.1	625.6	637.0	651.0	665.9
20°	481.7	505.9	530.1	555.9	576.3	595.5	610.1	624.1	638.3	656.7	674.8
22.5°	474.1	499.9	525.7	550.1	571.7	590.2	605.3	622.4	641.1	661.9	683.9
25°	462.2	488.7	514.2	537.5	558.6	577.6	598.2	621.3	643.9	671.3	702.8
27.5°	446.9	472.6	495.3	520.0	540.8	565.0	590.7	615.7	648.4	686.1	725.4
30°	435.6	459.9	481.5	504.8	528.5	555.1	583.9	613.4	652.4	696.6	743.4
32.5°	422.4	444.4	465.8	488.3	515.7	544.8	575.5	611.5	658.1	708.5	756.9
35°	399.5	419.3	440.1	465.0	494.1	525.8	565.0	608.9	665.1	719.3	762.8
37.5°	375.5	391.2	412.1	438.4	470.0	506.7	551.2	604.5	662.2	710.9	729.3
40°	357.0	371.7	393.8	421.3	452.7	492.8	542.7	597.5	655.7	689.4	688.0
42.5°	338.8	353.6	374.8	402.6	435.2	480.2	531.5	588.4	637.5	650.3	623.6
45°	310.7	324.5	345.4	373.4	408.4	455.6	509.5	564.2	595.5	574.6	521.5
47.5°	282.1	295.5	314.9	342.2	380.5	429.9	481.0	525.8	530.1	485.4	421.7
50°	263.3	275.9	294.3	323.5	360.6	408.8	458.1	493.3	482.3	427.8	362.0
52.5°	245.0	257.1	274.3	301.9	339.8	387.0	431.0	458.7	433.4	375.3	316.2
55°	218.0	229.5	246.8	272.2	306.6	349.8	388.4	398.5	361.4	302.9	255.1
57.5°	192.3	200.8	217.8	240.3	273.5	311.7	339.2	337.4	296.5	243.8	209.5
60°	175.3	183.0	199.2	219.8	251.4	285.6	305.0	296.7	255.3	211.8	178.9
62.5°	159.5	166.7	180.3	199.2	226.3	256.1	270.2	258.8	219.7	181.5	155.2
65°	135.5	140.7	151.7	169.2	190.4	211.0	223.6	206.9	172.3	143.4	123.6
67.5°	113.2	117.6	127.3	139.9	154.5	168.8	173.9	158.3	131.3	111.9	97.9
70°	98.7	102.8	109.4	121.2	130.8	140.9	143.4	129.4	106.9	92.1	83.5
72.5°	84.9	88.6	94.4	102.7	109.4	115.2	116.4	103.3	86.1	76.0	69.3
75°	64.7	68.0	71.7	74.8	79.1	80.2	79.7	69.6	60.4	53.6	49.8
77.5°	47.5	49.0	51.2	52.4	52.6	52.5	50.5	44.1	39.2	36.5	35.0
80°	36.6	37.7	38.3	38.7	39.0	36.9	34.6	30.7	29.1	27.4	25.6
82.5°	26.7	27.3	27.9	28.0	26.9	25.1	23.1	21.1	20.0	19.2	18.5
85°	14.4	14.6	14.4	13.4	11.9	11.3	10.9	10.5	10.3	10.1	10.1
87.5°	5.9	5.8	5.5	6.2	6.6	6.9	7.2	7.5	7.8	8.0	8.4
90°	3.7	6.2	8.6	10.9	13.1	15.2	17.3	19.4	21.5	23.0	24.5
92.5°	34.2	35.9	37.5	39.2	41.4	44.0	46.5	49.0	51.6	53.6	55.6
95°	88.0	88.6	89.2	89.8	91.6	94.6	97.6	100.6	103.5	105.7	107.7
97.5°	145.4	145.7	146.0	146.2	148.4	152.5	156.7	160.8	164.9	166.8	168.8
100°	188.2	188.2	188.2	188.2	190.2	194.1	198.0	201.9	205.7	208.5	211.2
102.5°	235.8	236.9	238.1	239.3	240.9	242.9	244.9	246.8	248.8	251.7	254.7
105°	308.1	309.6	311.1	312.6	314.2	316.0	317.8	319.6	321.5	323.2	325.0
107.5°	387.7	389.2	390.7	392.2	393.7	395.0	396.4	397.8	399.1	400.0	400.9
110°	442.6	444.1	445.6	447.1	448.3	449.2	450.0	450.9	451.8	452.7	453.7





TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	497.8	498.6	499.4	500.2	501.1	502.2	503.4	504.5	505.7	506.0	506.5
115°	580.9	582.0	583.2	584.4	585.3	585.9	586.5	587.1	587.7	587.4	587.1
117.5°	663.0	663.5	664.1	664.6	665.1	665.7	666.2	666.7	667.4	667.5	667.8
120°	715.6	717.1	718.6	720.1	720.9	721.3	721.6	721.8	722.2	722.2	722.2
122.5°	770.6	771.2	771.7	772.2	772.8	773.6	774.5	775.2	776.0	775.7	775.5
125°	847.7	849.5	851.3	853.1	854.2	854.4	854.7	855.1	855.3	854.7	854.2
127.5°	927.6	928.6	929.6	930.7	931.4	931.7	932.1	932.5	932.8	932.5	932.2
130°	976.5	978.0	979.5	981.0	982.0	982.7	983.2	983.8	984.4	984.1	983.8
132.5°	1025.9	1028.3	1030.8	1033.2	1034.4	1034.3	1034.1	1034.0	1033.9	1033.6	1033.3
135°	1101.9	1103.7	1105.5	1107.2	1108.3	1108.6	1108.9	1109.2	1109.5	1109.5	1109.5
137.5°	1173.9	1175.6	1177.3	1179.1	1180.3	1181.0	1181.6	1182.2	1182.9	1183.3	1183.7
140°	1219.9	1221.4	1222.9	1224.4	1225.6	1226.5	1227.4	1228.3	1229.2	1229.8	1230.4
142.5°	1266.0	1267.2	1268.5	1269.7	1270.9	1272.0	1273.2	1274.3	1275.4	1275.8	1276.1
145°	1333.9	1335.2	1336.3	1337.6	1338.5	1339.4	1340.3	1341.2	1342.1	1342.1	1342.1
147.5°	1396.3	1397.0	1397.7	1398.3	1399.0	1399.7	1400.4	1401.1	1401.9	1402.6	1403.3
150°	1437.3	1437.1	1436.7	1436.5	1436.9	1438.1	1439.3	1440.5	1441.7	1441.7	1441.7
152.5°	1472.5	1472.9	1473.3	1473.7	1474.2	1474.7	1475.2	1475.6	1476.1	1476.9	1477.6
155°	1525.1	1525.1	1525.1	1525.1	1525.2	1525.5	1525.8	1526.1	1526.4	1527.6	1528.7
157.5°	1571.7	1571.1	1570.4	1569.8	1569.6	1569.9	1570.2	1570.5	1570.7	1572.0	1573.2
160°	1599.5	1598.6	1597.7	1596.8	1596.5	1596.8	1597.1	1597.4	1597.7	1598.8	1600.1
162.5°	1624.4	1623.8	1623.2	1622.5	1622.2	1622.2	1622.3	1622.4	1622.4	1623.9	1625.3
165°	1657.6	1657.0	1656.4	1655.8	1655.6	1656.0	1656.3	1656.5	1656.9	1658.0	1659.2
167.5°	1685.0	1683.8	1682.6	1681.4	1680.8	1680.8	1680.8	1680.8	1680.8	1682.6	1684.4
170°	1700.0	1698.8	1697.6	1696.5	1695.9	1695.9	1695.9	1695.9	1695.9	1697.6	1699.4
172.5°	1710.8	1709.6	1708.4	1707.2	1706.6	1706.6	1706.6	1706.6	1706.6	1708.4	1710.2
175°	1722.9	1721.7	1720.5	1719.3	1718.7	1718.7	1718.7	1718.7	1718.7	1720.5	1722.3
177.5°	1729.3	1728.4	1727.4	1726.4	1725.8	1725.6	1725.4	1725.1	1724.9	1726.4	1727.8
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	523.9	523.9	526.6	526.5	528.3	527.6	528.0
5°	563.1	566.6	569.7	571.8	574.9	575.7	575.2
7.5°	603.9	611.6	615.4	620.6	621.5	624.3	624.0
10°	629.0	636.7	642.5	646.9	649.3	652.1	652.4
12.5°	648.8	655.3	660.4	664.6	667.4	668.2	668.8
15°	664.3	671.5	677.4	683.4	687.0	689.6	691.1
17.5°	679.8	691.0	701.5	709.6	714.5	718.6	718.6
20°	691.9	704.6	717.8	727.1	736.6	740.7	741.4
22.5°	704.7	724.2	741.3	755.6	768.1	772.4	774.0
25°	731.5	757.0	783.2	803.3	817.8	826.3	827.5
27.5°	763.8	798.3	825.8	844.5	856.4	862.7	864.1
30°	786.5	818.4	843.1	857.1	862.7	863.5	860.4
32.5°	796.7	820.6	830.5	829.6	818.7	811.5	808.7
35°	784.2	779.3	755.2	726.3	704.3	690.3	686.5
37.5°	713.6	671.0	626.7	583.1	559.9	548.0	527.8
40°	644.1	583.3	537.2	500.5	474.3	453.3	448.4
42.5°	565.6	502.8	456.7	425.3	404.4	390.0	383.7
45°	454.5	400.6	362.4	338.3	322.3	311.7	307.0
47.5°	363.6	321.7	294.0	276.2	263.9	254.8	252.2
50°	313.6	280.2	256.7	241.7	232.4	225.4	222.6
52.5°	272.4	245.4	227.4	215.0	206.3	201.9	199.5
55°	224.8	201.5	188.5	178.6	173.7	170.2	168.5
57.5°	183.9	167.0	157.6	150.7	146.2	143.9	143.1
60°	161.0	147.8	139.1	133.8	130.6	127.8	126.9
62.5°	140.6	130.3	123.6	118.9	115.8	114.6	114.0
65°	113.3	106.6	101.6	98.7	96.2	95.8	95.6
67.5°	90.1	86.1	83.5	80.5	79.6	78.2	77.8
70°	77.0	74.4	71.2	70.3	69.2	67.8	68.0
72.5°	65.4	62.7	60.5	59.2	58.9	58.2	58.8
75°	47.8	47.0	46.2	45.1	44.7	44.7	44.5
77.5°	34.2	33.4	32.5	31.9	31.7	30.9	31.2
80°	24.7	23.7	23.3	23.5	22.8	22.6	22.6
82.5°	18.3	17.9	17.5	17.6	17.4	17.2	17.4
85°	10.1	9.9	9.9	9.7	9.7	9.5	9.5
87.5°	8.8	9.3	9.2	9.2	9.4	9.7	10.1
90°	26.0	27.5	28.7	29.6	30.5	31.4	32.3
92.5°	57.5	59.6	60.8	61.5	62.2	62.8	63.5
95°	109.9	111.9	113.2	113.9	114.5	115.0	115.7
97.5°	170.8	172.7	174.0	174.3	174.7	175.0	175.4
100°	213.8	216.5	218.2	218.7	219.4	220.0	220.5
102.5°	257.6	260.5	262.4	263.2	264.0	264.9	265.7
105°	326.8	328.6	329.9	330.8	331.7	332.6	333.5
107.5°	401.8	402.7	403.1	403.1	403.1	403.0	402.9
110°	454.6	455.5	455.8	455.5	455.1	454.9	454.6



TEST NUMBER: P333657-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	506.9	507.3	507.3	506.8	506.2	505.7	505.2
115°	586.8	586.5	586.2	585.9	585.6	585.3	585.1
117.5°	668.1	668.2	667.8	666.6	665.4	664.2	663.0
120°	722.2	722.2	721.6	720.4	719.2	718.0	716.8
122.5°	775.3	775.0	774.5	773.5	772.5	771.5	770.6
125°	853.5	852.9	852.5	852.2	851.9	851.6	851.3
127.5°	931.9	931.6	931.1	930.5	930.0	929.3	928.7
130°	983.6	983.2	982.8	982.2	981.6	981.0	980.4
132.5°	1033.0	1032.7	1032.2	1031.4	1030.5	1029.7	1028.8
135°	1109.5	1109.5	1108.9	1107.7	1106.5	1105.3	1104.1
137.5°	1184.0	1184.4	1183.8	1182.3	1180.8	1179.3	1177.8
140°	1231.0	1231.5	1231.1	1229.7	1228.2	1226.6	1225.1
142.5°	1276.5	1276.9	1276.3	1274.8	1273.4	1271.8	1270.3
145°	1342.1	1342.1	1341.7	1340.8	1339.9	1339.0	1338.1
147.5°	1404.0	1404.7	1404.1	1402.0	1400.0	1398.0	1396.0
150°	1441.7	1441.7	1441.4	1440.7	1440.2	1439.6	1439.0
152.5°	1478.3	1479.0	1478.8	1477.7	1476.7	1475.6	1474.5
155°	1530.0	1531.2	1531.1	1529.6	1528.0	1526.5	1525.1
157.5°	1574.4	1575.6	1575.2	1573.2	1571.2	1569.2	1567.3
160°	1601.2	1602.5	1602.3	1600.8	1599.3	1597.9	1596.3
162.5°	1626.7	1628.2	1628.0	1626.3	1624.5	1622.8	1621.0
165°	1660.5	1661.6	1661.3	1659.6	1657.8	1656.0	1654.1
167.5°	1686.1	1687.9	1687.9	1686.0	1684.3	1682.4	1680.5
170°	1701.2	1703.0	1702.9	1700.8	1698.7	1696.6	1694.5
172.5°	1712.0	1713.8	1713.8	1711.9	1710.0	1708.2	1706.4
175°	1724.1	1725.9	1725.7	1723.7	1721.5	1719.5	1717.3
177.5°	1729.2	1730.6	1730.5	1728.8	1727.2	1725.5	1723.9
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1

(END OF REPORT)