

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333664-940

Luminaire Tested: **S125RDIW-S610D770U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333664-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D770U940-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4876.8 lumens
Efficiency: N/A
Efficacy: 129.7 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50	44
1	97	93	89	86	88	85	82	79	71	68	66	57	56	55	45	44	43	38
2	88	81	75	70	81	75	70	65	62	59	55	51	48	46	40	39	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	26	24	21	18
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	15	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5329	5329	5329	5329
5°	6131	5336	4713	5336
10°	7033	5309	4158	5309
15°	7596	5255	3697	5255
20°	8377	5192	3413	5192
25°	9694	5108	3167	5108
30°	10549	5020	3006	5020
35°	8898	4917	2858	4917
40°	6214	4731	2731	4731
45°	4610	4483	2606	4483
50°	3676	4224	2498	4224
55°	3120	3902	2403	3902
60°	2696	3614	2250	3614
65°	2402	3304	1936	3304
70°	2111	3025	1766	3025
75°	1827	2620	1657	2620
80°	1387	2205	1387	2205
85°	1156	1734	1312	1734



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.6
10°-20°	231.9	4.8
20°-30°	367.7	7.5
30°-40°	443.4	9.1
40°-50°	396.0	8.1
50°-60°	303.6	6.2
60°-70°	197.3	4.0
70°-80°	95.9	2.0
80°-90°	24.7	0.5
90°-100°	32.4	0.7
100°-110°	199.6	4.1
110°-120°	362.0	7.4
120°-130°	464.6	9.5
130°-140°	499.8	10.2
140°-150°	469.1	9.6
150°-160°	379.5	7.8
160°-170°	245.4	5.0
170°-180°	84.6	1.7
0°-30°	678.7	13.9
0°-40°	1122.1	23.0
0°-60°	1821.7	37.4
0°-90°	2139.7	43.9
90°-120°	594.1	12.2
90°-150°	2027.6	41.6
90°-180°	2737.0	56.1
0°-180°	4876.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	825	825	825	825	825	
5°	946	823	727	823	946	94
15°	1136	786	553	786	1136	326
25°	1360	717	444	717	1360	625
35°	1129	624	362	624	1129	682
45°	505	491	285	491	505	403
55°	277	346	213	346	277	251
65°	157	216	127	216	157	156
75°	73	105	66	105	73	78
85°	16	23	18	23	16	18
90°	16	1	16	1	16	8
95°	14	38	14	38	14	11
105°	196	194	196	194	196	177
115°	362	365	362	365	362	359
125°	519	519	519	519	519	461
135°	644	647	644	647	644	497
145°	748	750	748	750	748	467
155°	820	826	820	826	820	378
165°	867	872	867	872	867	245
175°	887	891	887	891	887	84
180°	891	891	891	891	891	



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	868.0	867.5	868.5	865.5	865.9	861.2	861.2	857.6	853.1	849.5	847.9
5°	945.7	946.5	945.0	940.0	936.6	931.5	925.8	915.6	907.1	899.0	892.6
7.5°	1025.8	1026.3	1021.8	1020.3	1011.7	1005.5	992.7	978.9	966.6	951.0	939.1
10°	1072.5	1072.1	1067.4	1063.6	1056.1	1046.7	1034.1	1017.9	1002.6	985.7	969.5
12.5°	1099.6	1098.7	1097.2	1092.6	1085.7	1077.3	1066.7	1050.7	1031.9	1013.3	994.4
15°	1136.1	1133.7	1129.4	1123.6	1113.7	1103.9	1092.1	1077.9	1059.9	1038.9	1021.3
17.5°	1181.3	1181.4	1174.7	1166.7	1153.3	1136.0	1117.7	1094.8	1070.3	1047.2	1028.5
20°	1218.8	1217.7	1210.9	1195.4	1180.2	1158.5	1137.5	1109.4	1079.6	1049.4	1026.0
22.5°	1272.4	1269.8	1262.8	1242.2	1218.6	1190.7	1158.6	1124.3	1088.2	1054.0	1023.3
25°	1360.4	1358.3	1344.4	1320.7	1287.5	1244.5	1202.5	1155.4	1103.6	1058.5	1021.3
27.5°	1420.5	1418.3	1408.0	1388.3	1357.6	1312.4	1255.5	1192.7	1127.9	1066.0	1012.2
30°	1414.5	1419.6	1418.3	1409.2	1386.1	1345.4	1293.0	1222.2	1145.2	1072.5	1008.4
32.5°	1329.5	1334.0	1345.9	1363.9	1365.2	1349.0	1309.7	1244.4	1164.8	1081.9	1005.4
35°	1128.6	1134.8	1157.8	1194.0	1241.4	1281.1	1289.2	1254.0	1182.5	1093.4	1000.9
37.5°	867.7	901.1	920.4	958.6	1030.2	1103.1	1173.2	1199.1	1168.7	1088.7	993.7
40°	737.1	745.2	779.8	822.8	883.1	958.9	1058.9	1131.0	1133.4	1077.9	982.3
42.5°	630.9	641.1	664.9	699.2	750.8	826.7	929.9	1025.1	1069.2	1048.0	967.4
45°	504.7	512.5	529.8	556.2	595.8	658.5	747.3	857.4	944.8	978.9	927.5
47.5°	414.6	418.8	433.8	454.0	483.3	529.0	597.6	693.2	798.1	871.6	864.3
50°	365.9	370.6	382.1	397.3	422.0	460.7	515.6	595.1	703.2	793.0	810.9
52.5°	327.9	331.8	339.0	353.5	373.8	403.5	447.8	519.9	617.1	712.5	754.0
55°	277.1	279.8	285.5	293.6	310.0	331.3	369.5	419.4	497.9	594.1	655.1
57.5°	235.2	236.6	240.2	247.7	259.0	274.6	302.2	344.5	400.8	487.4	554.7
60°	208.7	210.0	214.7	219.8	228.6	242.9	264.6	294.0	348.2	419.7	487.8
62.5°	187.5	188.3	190.4	195.5	203.1	214.2	231.2	255.3	298.4	361.1	425.4
65°	157.2	157.5	158.2	162.3	167.0	175.1	186.3	203.2	235.8	283.2	340.1
67.5°	128.0	128.5	130.9	132.3	137.2	141.5	148.1	161.0	184.0	215.9	260.1
70°	111.8	111.5	113.8	115.5	117.2	122.3	126.7	137.1	151.4	175.8	212.8
72.5°	96.6	95.8	96.8	97.4	99.6	103.1	107.5	113.9	124.8	141.7	169.9
75°	73.2	73.5	73.5	74.2	75.9	77.2	78.6	81.9	88.1	99.2	114.5
77.5°	51.4	50.8	52.3	52.4	53.4	54.9	56.1	57.4	59.9	64.6	72.4
80°	37.3	37.3	37.6	38.6	38.3	39.0	40.7	42.0	45.0	47.8	50.5
82.5°	28.6	28.4	28.6	28.9	28.8	29.4	30.1	30.3	31.5	32.8	34.8
85°	15.6	15.6	16.0	16.0	16.2	16.2	16.6	16.6	16.6	16.9	17.3
87.5°	9.1	8.7	8.4	8.3	8.5	8.9	8.6	8.1	7.9	7.8	7.8
90°	15.9	15.4	15.0	14.5	14.1	13.5	12.8	12.0	11.3	10.6	9.5
92.5°	14.8	14.6	14.4	14.2	14.0	13.5	12.8	12.0	11.3	10.6	9.6
95°	13.9	13.9	13.9	13.9	13.9	13.5	12.8	12.0	11.3	10.6	16.1
97.5°	13.9	13.9	13.9	13.9	13.9	16.0	20.1	24.3	28.4	32.5	43.5
100°	13.9	14.4	15.1	15.6	16.2	27.5	49.3	71.2	93.1	114.9	114.4
102.5°	83.1	93.1	103.1	113.1	123.1	130.1	134.3	138.4	142.6	146.7	146.3
105°	196.3	196.4	196.5	196.7	196.8	196.9	196.9	196.9	196.9	196.9	196.9
107.5°	247.4	247.8	248.3	248.7	249.1	249.3	249.3	249.3	249.2	249.2	249.0
110°	282.8	282.7	282.5	282.3	282.2	282.3	282.8	283.2	283.7	284.1	283.8



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	314.5	314.7	315.0	315.1	315.3	315.7	316.3	316.8	317.4	318.0	317.8
115°	362.0	362.9	363.8	364.7	365.6	366.3	366.9	367.5	368.1	368.7	368.5
117.5°	412.9	413.2	413.6	413.9	414.4	414.9	415.7	416.4	417.2	417.9	417.4
120°	444.0	444.8	445.5	446.2	446.9	447.5	447.7	448.1	448.4	448.6	448.2
122.5°	473.6	474.5	475.3	476.2	477.0	477.6	477.9	478.1	478.5	478.8	478.6
125°	518.7	519.2	519.5	520.0	520.4	520.9	521.6	522.1	522.7	523.3	523.3
127.5°	556.6	557.7	558.7	559.8	561.0	561.7	562.0	562.3	562.6	562.9	563.0
130°	584.1	584.8	585.6	586.3	587.0	587.6	588.1	588.5	588.9	589.3	589.2
132.5°	609.5	610.2	610.9	611.6	612.4	612.8	612.9	613.0	613.1	613.1	613.5
135°	644.2	645.1	646.0	646.8	647.7	648.4	648.6	648.9	649.2	649.5	649.8
137.5°	679.1	679.8	680.6	681.4	682.2	682.5	682.4	682.4	682.3	682.2	682.5
140°	699.7	700.6	701.5	702.3	703.2	703.6	703.2	702.9	702.7	702.3	702.5
142.5°	719.3	720.1	721.0	721.9	722.8	723.2	723.2	723.1	723.0	723.0	722.7
145°	748.0	748.9	749.7	750.6	751.4	751.8	751.7	751.5	751.4	751.3	751.3
147.5°	771.6	772.7	773.7	774.8	775.8	776.2	776.1	775.9	775.7	775.5	775.3
150°	786.9	788.1	789.3	790.4	791.7	792.1	791.8	791.5	791.2	790.9	790.6
152.5°	801.2	802.3	803.3	804.3	805.4	805.8	805.5	805.2	804.9	804.6	804.3
155°	819.9	821.2	822.3	823.5	824.7	825.0	824.6	824.1	823.7	823.2	823.0
157.5°	835.7	836.9	838.0	839.2	840.3	840.7	840.3	839.8	839.4	838.8	838.8
160°	845.7	846.9	848.1	849.3	850.4	850.7	850.2	849.5	849.0	848.4	848.2
162.5°	854.7	856.0	857.3	858.6	859.9	860.1	859.3	858.4	857.6	856.8	856.7
165°	866.8	868.1	869.2	870.4	871.6	871.7	870.8	870.0	869.1	868.2	868.1
167.5°	875.3	876.6	878.0	879.3	880.7	880.7	879.7	878.6	877.5	876.6	876.4
170°	880.1	881.4	882.7	884.0	885.4	885.5	884.3	883.1	881.9	880.7	880.6
172.5°	883.2	884.6	885.9	887.3	888.5	888.7	887.6	886.5	885.5	884.5	884.2
175°	887.3	888.7	890.0	891.4	892.6	892.7	891.5	890.4	889.2	888.1	887.9
177.5°	889.7	890.6	891.6	892.5	893.5	893.6	892.7	891.9	891.1	890.3	890.1
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	847.9	846.1	842.5	839.3	835.2	831.7	829.2	826.3	822.4	817.9	814.0
5°	885.5	878.0	868.2	859.7	848.9	840.4	831.6	823.1	814.7	803.8	794.3
7.5°	927.0	911.7	896.7	877.9	860.8	845.5	830.9	816.1	801.6	786.2	771.3
10°	952.5	933.9	913.2	889.5	867.8	847.2	828.2	809.6	790.0	772.7	754.0
12.5°	976.3	952.3	928.7	898.8	872.7	847.5	823.3	800.1	779.1	756.7	736.6
15°	997.9	974.2	947.8	911.2	874.9	844.5	816.0	785.9	759.8	734.7	712.4
17.5°	1006.2	981.4	950.7	915.5	875.9	837.6	800.9	767.9	737.2	707.9	682.8
20°	1003.0	978.9	947.4	913.9	871.6	831.6	791.9	755.4	721.1	690.4	663.6
22.5°	995.1	970.3	939.9	904.5	864.2	821.8	779.5	740.5	704.6	672.7	643.5
25°	983.4	949.5	918.3	883.8	845.5	803.5	759.8	716.8	678.5	646.0	614.1
27.5°	971.1	928.8	889.2	854.8	814.4	776.9	734.8	690.7	650.4	617.3	584.7
30°	960.0	912.6	868.9	829.9	791.7	756.1	716.0	673.1	631.8	597.5	564.4
32.5°	946.2	895.7	847.7	802.8	765.9	730.6	694.4	653.3	613.1	577.7	544.0
35°	928.8	864.4	812.3	764.6	723.5	689.3	656.8	623.6	583.3	546.7	513.9
37.5°	906.1	833.0	772.7	720.6	677.4	643.0	617.4	587.0	550.3	515.2	484.7
40°	892.2	810.3	744.2	692.7	647.3	611.1	587.0	561.2	527.7	494.9	464.4
42.5°	873.8	789.4	715.5	661.8	616.2	581.3	557.0	534.5	506.3	475.4	442.7
45°	837.7	748.9	671.4	613.8	567.8	533.5	510.8	490.8	469.5	441.0	412.6
47.5°	790.7	706.8	625.5	562.7	517.5	485.8	463.8	448.0	432.7	408.6	380.9
50°	753.0	672.1	592.8	531.8	483.8	453.5	432.9	420.4	406.4	384.5	361.4
52.5°	708.6	636.3	558.7	496.3	450.9	422.7	402.8	390.3	378.8	360.9	338.9
55°	638.6	575.2	504.0	447.5	405.8	377.4	358.4	346.5	339.7	324.5	307.2
57.5°	557.7	512.3	449.6	395.0	358.2	330.0	316.2	306.1	298.5	287.7	275.4
60°	501.3	469.5	413.2	361.4	327.5	300.8	288.3	279.8	272.7	263.5	254.0
62.5°	444.2	421.0	372.1	327.5	296.4	273.9	262.3	254.6	246.4	240.2	231.0
65°	367.6	346.9	313.0	278.1	249.3	231.4	222.9	216.2	211.1	204.3	197.8
67.5°	285.9	277.5	254.1	230.1	209.4	193.4	186.1	181.4	175.2	171.2	166.7
70°	235.8	231.7	215.1	199.2	179.9	169.1	162.3	160.2	152.8	148.7	145.6
72.5°	191.4	189.4	179.9	168.8	155.2	145.7	139.5	137.1	132.4	129.2	127.2
75°	131.1	131.8	130.1	123.0	117.9	111.8	106.4	105.0	101.7	98.9	97.2
77.5°	82.9	86.4	86.5	86.1	84.2	80.4	78.2	77.1	73.8	72.9	72.4
80°	56.9	60.6	64.0	63.7	63.0	62.0	60.3	59.3	57.6	56.5	55.9
82.5°	37.9	41.4	44.2	46.1	45.9	44.9	43.8	43.2	43.0	42.2	42.1
85°	17.9	18.6	19.6	22.0	23.7	24.1	23.7	23.4	22.4	22.7	23.0
87.5°	7.9	7.8	7.8	7.6	7.0	8.2	8.7	8.8	8.5	8.2	7.8
90°	8.6	7.5	6.4	5.4	4.2	3.0	1.9	0.6	1.9	3.0	4.2
92.5°	8.7	7.8	7.0	6.9	7.7	8.6	9.4	10.2	9.4	8.6	7.7
95°	21.8	27.3	32.9	35.9	36.4	36.7	37.2	37.6	37.2	36.7	36.4
97.5°	54.6	65.6	76.7	81.8	81.0	80.3	79.5	78.6	79.5	80.3	81.0
100°	113.8	113.2	112.6	112.1	111.6	111.2	110.8	110.3	110.8	111.2	111.6
102.5°	146.0	145.6	145.3	144.8	144.3	143.7	143.1	142.6	143.1	143.7	144.3
105°	196.9	196.9	196.9	196.6	196.0	195.5	194.8	194.2	194.8	195.5	196.0
107.5°	248.6	248.3	248.1	247.9	247.9	247.9	247.9	247.9	247.9	247.9	247.9
110°	283.6	283.2	282.9	282.8	282.8	282.8	282.8	282.8	282.8	282.8	282.8



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	317.6	317.4	317.3	317.0	316.6	316.3	315.9	315.6	315.9	316.3	316.6
115°	368.4	368.3	368.1	367.7	366.9	366.2	365.4	364.7	365.4	366.2	366.9
117.5°	416.9	416.3	415.7	415.4	415.5	415.5	415.5	415.6	415.5	415.5	415.5
120°	447.7	447.3	446.8	446.7	446.8	447.0	447.2	447.3	447.2	447.0	446.8
122.5°	478.3	478.1	478.0	477.6	477.0	476.4	475.9	475.3	475.9	476.4	477.0
125°	523.3	523.3	523.3	522.8	521.7	520.8	519.7	518.7	519.7	520.8	521.7
127.5°	563.1	563.2	563.3	562.9	562.2	561.5	560.8	560.0	560.8	561.5	562.2
130°	589.1	588.9	588.8	588.4	587.6	586.8	586.1	585.4	586.1	586.8	587.6
132.5°	613.8	614.1	614.5	614.2	613.3	612.5	611.6	610.7	611.6	612.5	613.3
135°	650.1	650.4	650.7	650.4	649.5	648.6	647.7	646.8	647.7	648.6	649.5
137.5°	682.8	683.1	683.3	683.1	682.3	681.5	680.8	680.0	680.8	681.5	682.3
140°	702.7	702.8	702.9	702.8	702.6	702.3	702.0	701.7	702.0	702.3	702.6
142.5°	722.6	722.4	722.1	721.9	721.8	721.6	721.4	721.2	721.4	721.6	721.8
145°	751.3	751.3	751.3	751.1	750.8	750.6	750.2	749.9	750.2	750.6	750.8
147.5°	775.2	775.1	774.9	774.8	774.9	774.9	775.0	775.1	775.0	774.9	774.9
150°	790.3	790.0	789.7	789.7	790.0	790.3	790.6	790.9	790.6	790.3	790.0
152.5°	804.1	803.8	803.4	803.6	804.3	804.9	805.6	806.2	805.6	804.9	804.3
155°	822.7	822.4	822.1	822.4	823.2	824.1	825.0	825.9	825.0	824.1	823.2
157.5°	838.8	838.7	838.7	839.0	839.5	840.1	840.6	841.1	840.6	840.1	839.5
160°	848.1	847.9	847.7	848.2	849.0	849.9	850.8	851.7	850.8	849.9	849.0
162.5°	856.6	856.4	856.2	856.6	857.5	858.4	859.3	860.1	859.3	858.4	857.5
165°	867.9	867.7	867.6	868.0	868.9	869.8	870.6	871.5	870.6	869.8	868.9
167.5°	876.2	876.1	875.9	876.3	877.3	878.2	879.0	879.9	879.0	878.2	877.3
170°	880.5	880.3	880.1	880.6	881.6	882.6	883.7	884.8	883.7	882.6	881.6
172.5°	884.0	883.7	883.4	883.8	884.8	885.8	886.9	887.9	886.9	885.8	884.8
175°	887.7	887.6	887.4	887.8	888.7	889.6	890.5	891.4	890.5	889.6	888.7
177.5°	890.0	889.9	889.7	890.1	890.8	891.5	892.2	892.9	892.2	891.5	890.8
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	811.4	807.5	804.9	799.4	795.6	794.0	791.0	790.2	793.2	791.0	790.8
5°	787.2	777.4	769.6	761.8	753.3	748.0	739.8	738.4	736.4	733.3	732.7
7.5°	758.3	745.5	735.5	722.6	711.4	702.4	692.2	687.4	684.7	680.8	675.6
10°	738.8	723.5	710.0	697.1	683.2	672.1	661.9	654.1	649.0	644.3	642.2
12.5°	719.5	704.0	686.7	671.1	655.6	643.0	631.8	626.7	621.1	615.5	610.8
15°	689.6	669.0	650.1	632.0	618.8	605.3	594.5	587.0	578.5	576.2	567.0
17.5°	658.0	637.7	615.5	596.6	581.3	566.3	554.5	546.0	539.6	530.8	526.6
20°	638.2	614.1	592.5	575.2	558.2	540.6	528.4	521.3	515.2	508.1	504.7
22.5°	617.1	593.5	571.3	551.1	533.9	516.5	507.8	500.4	493.6	487.0	482.5
25°	586.0	562.3	539.0	517.9	500.0	487.4	477.2	468.8	465.1	458.6	453.9
27.5°	555.4	530.1	505.9	484.9	470.8	458.4	450.1	443.4	436.7	431.1	427.0
30°	535.6	509.8	483.4	466.8	451.8	440.1	430.9	424.5	419.4	414.3	411.3
32.5°	515.8	489.2	465.7	447.8	433.7	423.5	414.1	407.9	402.5	396.9	393.3
35°	484.0	456.9	438.0	420.4	406.4	397.0	390.6	381.7	377.4	373.3	369.5
37.5°	454.6	429.4	408.8	393.4	381.4	371.9	363.6	358.8	353.5	349.8	346.7
40°	432.9	409.8	391.3	375.0	366.1	355.7	347.9	341.8	337.7	333.0	329.6
42.5°	413.4	392.0	373.9	359.3	348.3	339.4	331.9	325.8	320.7	317.3	314.4
45°	385.8	364.4	346.9	333.3	323.2	314.7	306.9	303.8	297.0	293.0	291.7
47.5°	357.3	338.2	321.2	308.7	298.3	290.3	282.9	276.8	273.0	269.0	266.9
50°	338.0	319.8	303.8	291.7	281.5	272.7	265.9	261.8	256.7	253.1	250.3
52.5°	318.8	301.8	286.0	274.3	265.5	256.7	249.1	245.0	240.2	237.8	235.9
55°	291.3	273.4	259.8	248.3	239.2	231.0	223.9	219.8	216.8	214.5	213.7
57.5°	260.1	245.9	233.4	222.9	213.5	205.8	199.6	195.7	193.1	192.7	190.6
60°	239.8	226.9	215.4	204.3	196.1	189.0	183.6	179.2	176.5	176.1	175.5
62.5°	219.5	207.1	196.4	186.6	179.3	172.5	167.4	162.4	160.8	159.1	157.6
65°	189.3	178.2	169.3	161.6	153.8	148.0	142.9	139.9	136.2	134.1	130.5
67.5°	159.7	151.1	142.6	136.1	129.9	124.5	120.3	115.7	113.2	111.6	108.9
70°	140.3	133.5	125.0	117.9	113.2	108.7	105.3	100.2	98.5	97.2	95.9
72.5°	121.8	115.8	108.7	103.0	98.3	94.1	90.2	87.8	86.1	84.7	83.9
75°	95.9	90.1	84.0	79.9	76.6	73.2	71.2	69.5	68.8	68.4	67.1
77.5°	70.4	67.3	62.4	59.2	57.0	55.6	53.8	52.9	52.9	51.4	50.9
80°	53.9	52.2	48.1	46.7	45.0	43.7	42.7	41.0	39.3	38.6	37.6
82.5°	40.0	38.3	36.7	34.5	33.2	32.3	31.3	30.7	30.9	30.0	29.4
85°	21.3	19.6	19.0	18.6	17.9	18.6	18.3	17.9	17.7	17.3	17.7
87.5°	7.8	8.0	8.0	8.7	8.1	8.6	8.7	8.6	8.8	8.9	8.7
90°	5.4	6.4	7.5	8.6	9.5	10.6	11.3	12.0	12.8	13.5	14.1
92.5°	6.9	7.0	7.8	8.7	9.6	10.6	11.3	12.0	12.8	13.5	14.0
95°	35.9	32.9	27.3	21.8	16.1	10.6	11.3	12.0	12.8	13.5	13.9
97.5°	81.8	76.7	65.6	54.6	43.5	32.5	28.4	24.3	20.1	16.0	13.9
100°	112.1	112.6	113.2	113.8	114.4	114.9	93.1	71.2	49.3	27.5	16.2
102.5°	144.8	145.3	145.6	146.0	146.3	146.7	142.6	138.4	134.3	130.1	123.1
105°	196.6	196.9	196.9	196.9	196.9	196.9	196.9	196.9	196.9	196.9	196.8
107.5°	247.9	248.1	248.3	248.6	249.0	249.2	249.2	249.3	249.3	249.3	249.1
110°	282.8	282.9	283.2	283.6	283.8	284.1	283.7	283.2	282.8	282.3	282.2



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	317.0	317.3	317.4	317.6	317.8	318.0	317.4	316.8	316.3	315.7	315.3
115°	367.7	368.1	368.3	368.4	368.5	368.7	368.1	367.5	366.9	366.3	365.6
117.5°	415.4	415.7	416.3	416.9	417.4	417.9	417.2	416.4	415.7	414.9	414.4
120°	446.7	446.8	447.3	447.7	448.2	448.6	448.4	448.1	447.7	447.5	446.9
122.5°	477.6	478.0	478.1	478.3	478.6	478.8	478.5	478.1	477.9	477.6	477.0
125°	522.8	523.3	523.3	523.3	523.3	523.3	522.7	522.1	521.6	520.9	520.4
127.5°	562.9	563.3	563.2	563.1	563.0	562.9	562.6	562.3	562.0	561.7	561.0
130°	588.4	588.8	588.9	589.1	589.2	589.3	588.9	588.5	588.1	587.6	587.0
132.5°	614.2	614.5	614.1	613.8	613.5	613.1	613.1	613.0	612.9	612.8	612.4
135°	650.4	650.7	650.4	650.1	649.8	649.5	649.2	648.9	648.6	648.4	647.7
137.5°	683.1	683.3	683.1	682.8	682.5	682.2	682.3	682.4	682.4	682.5	682.2
140°	702.8	702.9	702.8	702.7	702.5	702.3	702.7	702.9	703.2	703.6	703.2
142.5°	721.9	722.1	722.4	722.6	722.7	723.0	723.0	723.1	723.2	723.2	722.8
145°	751.1	751.3	751.3	751.3	751.3	751.3	751.4	751.5	751.7	751.8	751.4
147.5°	774.8	774.9	775.1	775.2	775.3	775.5	775.7	775.9	776.1	776.2	775.8
150°	789.7	789.7	790.0	790.3	790.6	790.9	791.2	791.5	791.8	792.1	791.7
152.5°	803.6	803.4	803.8	804.1	804.3	804.6	804.9	805.2	805.5	805.8	805.4
155°	822.4	822.1	822.4	822.7	823.0	823.2	823.7	824.1	824.6	825.0	824.7
157.5°	839.0	838.7	838.7	838.8	838.8	838.8	839.4	839.8	840.3	840.7	840.3
160°	848.2	847.7	847.9	848.1	848.2	848.4	849.0	849.5	850.2	850.7	850.4
162.5°	856.6	856.2	856.4	856.6	856.7	856.8	857.6	858.4	859.3	860.1	859.9
165°	868.0	867.6	867.7	867.9	868.1	868.2	869.1	870.0	870.8	871.7	871.6
167.5°	876.3	875.9	876.1	876.2	876.4	876.6	877.5	878.6	879.7	880.7	880.7
170°	880.6	880.1	880.3	880.5	880.6	880.7	881.9	883.1	884.3	885.5	885.4
172.5°	883.8	883.4	883.7	884.0	884.2	884.5	885.5	886.5	887.6	888.7	888.5
175°	887.8	887.4	887.6	887.7	887.9	888.1	889.2	890.4	891.5	892.7	892.6
177.5°	890.1	889.7	889.9	890.0	890.1	890.3	891.1	891.9	892.7	893.6	893.5
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	790.5	787.5	786.7	787.7	786.7	787.5	790.5	790.8	791.0	793.2	790.2
5°	729.3	725.9	727.6	726.9	727.6	725.9	729.3	732.7	733.3	736.4	738.4
7.5°	675.5	671.3	666.8	668.2	666.8	671.3	675.5	675.6	680.8	684.7	687.4
10°	637.8	634.5	632.4	634.1	632.4	634.5	637.8	642.2	644.3	649.0	654.1
12.5°	606.1	604.1	602.4	601.6	602.4	604.1	606.1	610.8	615.5	621.1	626.7
15°	562.9	558.9	557.2	552.9	557.2	558.9	562.9	567.0	576.2	578.5	587.0
17.5°	523.2	521.8	517.5	515.6	517.5	521.8	523.2	526.6	530.8	539.6	546.0
20°	499.6	498.3	493.9	496.6	493.9	498.3	499.6	504.7	508.1	515.2	521.3
22.5°	480.1	477.2	475.7	474.9	475.7	477.2	480.1	482.5	487.0	493.6	500.4
25°	452.5	448.2	446.5	444.4	446.5	448.2	452.5	453.9	458.6	465.1	468.8
27.5°	425.1	422.7	420.4	419.9	420.4	422.7	425.1	427.0	431.1	436.7	443.4
30°	407.2	404.7	403.1	403.1	403.1	404.7	407.2	411.3	414.3	419.4	424.5
32.5°	391.2	389.3	387.6	387.4	387.6	389.3	391.2	393.3	396.9	402.5	407.9
35°	367.8	365.2	364.4	362.5	364.4	365.2	367.8	369.5	373.3	377.4	381.7
37.5°	343.7	341.4	341.3	341.2	341.3	341.4	343.7	346.7	349.8	353.5	358.8
40°	328.2	326.5	326.2	323.9	326.2	326.5	328.2	329.6	333.0	337.7	341.8
42.5°	311.7	310.9	309.7	308.6	309.7	310.9	311.7	314.4	317.3	320.7	325.8
45°	289.3	287.0	287.0	285.3	287.0	287.0	289.3	291.7	293.0	297.0	303.8
47.5°	266.1	264.3	264.5	262.7	264.5	264.3	266.1	266.9	269.0	273.0	276.8
50°	250.7	249.7	249.3	248.6	249.3	249.7	250.7	250.3	253.1	256.7	261.8
52.5°	235.2	234.8	236.0	234.5	236.0	234.8	235.2	235.9	237.8	240.2	245.0
55°	214.5	213.4	215.4	213.4	215.4	213.4	214.5	213.7	214.5	216.8	219.8
57.5°	190.5	189.6	191.4	190.4	191.4	189.6	190.5	190.6	192.7	193.1	195.7
60°	174.8	172.7	173.8	174.2	173.8	172.7	174.8	175.5	176.1	176.5	179.2
62.5°	156.0	154.9	155.6	154.1	155.6	154.9	156.0	157.6	159.1	160.8	162.4
65°	129.7	128.8	127.3	126.7	127.3	128.8	129.7	130.5	134.1	136.2	139.9
67.5°	109.0	106.6	106.5	107.0	106.5	106.6	109.0	108.9	111.6	113.2	115.7
70°	93.8	93.8	93.5	93.5	93.5	93.8	93.8	95.9	97.2	98.5	100.2
72.5°	83.3	83.0	82.4	82.1	82.4	83.0	83.3	83.9	84.7	86.1	87.8
75°	67.1	67.4	66.7	66.4	66.7	67.4	67.1	67.1	68.4	68.8	69.5
77.5°	49.5	48.1	48.9	48.1	48.9	48.1	49.5	50.9	51.4	52.9	52.9
80°	37.6	37.3	38.3	37.3	38.3	37.3	37.6	37.6	38.6	39.3	41.0
82.5°	29.8	29.4	29.9	29.2	29.9	29.4	29.8	29.4	30.0	30.9	30.7
85°	17.9	17.7	17.3	17.7	17.3	17.7	17.9	17.7	17.3	17.7	17.9
87.5°	9.1	8.9	9.0	9.1	9.0	8.9	9.1	8.7	8.9	8.8	8.6
90°	14.5	15.0	15.4	15.9	15.4	15.0	14.5	14.1	13.5	12.8	12.0
92.5°	14.2	14.4	14.6	14.8	14.6	14.4	14.2	14.0	13.5	12.8	12.0
95°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.5	12.8	12.0
97.5°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	16.0	20.1	24.3
100°	15.6	15.1	14.4	13.9	14.4	15.1	15.6	16.2	27.5	49.3	71.2
102.5°	113.1	103.1	93.1	83.1	93.1	103.1	113.1	123.1	130.1	134.3	138.4
105°	196.7	196.5	196.4	196.3	196.4	196.5	196.7	196.8	196.9	196.9	196.9
107.5°	248.7	248.3	247.8	247.4	247.8	248.3	248.7	249.1	249.3	249.3	249.3
110°	282.3	282.5	282.7	282.8	282.7	282.5	282.3	282.2	282.3	282.8	283.2



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	315.1	315.0	314.7	314.5	314.7	315.0	315.1	315.3	315.7	316.3	316.8
115°	364.7	363.8	362.9	362.0	362.9	363.8	364.7	365.6	366.3	366.9	367.5
117.5°	413.9	413.6	413.2	412.9	413.2	413.6	413.9	414.4	414.9	415.7	416.4
120°	446.2	445.5	444.8	444.0	444.8	445.5	446.2	446.9	447.5	447.7	448.1
122.5°	476.2	475.3	474.5	473.6	474.5	475.3	476.2	477.0	477.6	477.9	478.1
125°	520.0	519.5	519.2	518.7	519.2	519.5	520.0	520.4	520.9	521.6	522.1
127.5°	559.8	558.7	557.7	556.6	557.7	558.7	559.8	561.0	561.7	562.0	562.3
130°	586.3	585.6	584.8	584.1	584.8	585.6	586.3	587.0	587.6	588.1	588.5
132.5°	611.6	610.9	610.2	609.5	610.2	610.9	611.6	612.4	612.8	612.9	613.0
135°	646.8	646.0	645.1	644.2	645.1	646.0	646.8	647.7	648.4	648.6	648.9
137.5°	681.4	680.6	679.8	679.1	679.8	680.6	681.4	682.2	682.5	682.4	682.4
140°	702.3	701.5	700.6	699.7	700.6	701.5	702.3	703.2	703.6	703.2	702.9
142.5°	721.9	721.0	720.1	719.3	720.1	721.0	721.9	722.8	723.2	723.2	723.1
145°	750.6	749.7	748.9	748.0	748.9	749.7	750.6	751.4	751.8	751.7	751.5
147.5°	774.8	773.7	772.7	771.6	772.7	773.7	774.8	775.8	776.2	776.1	775.9
150°	790.4	789.3	788.1	786.9	788.1	789.3	790.4	791.7	792.1	791.8	791.5
152.5°	804.3	803.3	802.3	801.2	802.3	803.3	804.3	805.4	805.8	805.5	805.2
155°	823.5	822.3	821.2	819.9	821.2	822.3	823.5	824.7	825.0	824.6	824.1
157.5°	839.2	838.0	836.9	835.7	836.9	838.0	839.2	840.3	840.7	840.3	839.8
160°	849.3	848.1	846.9	845.7	846.9	848.1	849.3	850.4	850.7	850.2	849.5
162.5°	858.6	857.3	856.0	854.7	856.0	857.3	858.6	859.9	860.1	859.3	858.4
165°	870.4	869.2	868.1	866.8	868.1	869.2	870.4	871.6	871.7	870.8	870.0
167.5°	879.3	878.0	876.6	875.3	876.6	878.0	879.3	880.7	880.7	879.7	878.6
170°	884.0	882.7	881.4	880.1	881.4	882.7	884.0	885.4	885.5	884.3	883.1
172.5°	887.3	885.9	884.6	883.2	884.6	885.9	887.3	888.5	888.7	887.6	886.5
175°	891.4	890.0	888.7	887.3	888.7	890.0	891.4	892.6	892.7	891.5	890.4
177.5°	892.5	891.6	890.6	889.7	890.6	891.6	892.5	893.5	893.6	892.7	891.9
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	791.0	794.0	795.6	799.4	804.9	807.5	811.4	814.0	817.9	822.4	826.3
5°	739.8	748.0	753.3	761.8	769.6	777.4	787.2	794.3	803.8	814.7	823.1
7.5°	692.2	702.4	711.4	722.6	735.5	745.5	758.3	771.3	786.2	801.6	816.1
10°	661.9	672.1	683.2	697.1	710.0	723.5	738.8	754.0	772.7	790.0	809.6
12.5°	631.8	643.0	655.6	671.1	686.7	704.0	719.5	736.6	756.7	779.1	800.1
15°	594.5	605.3	618.8	632.0	650.1	669.0	689.6	712.4	734.7	759.8	785.9
17.5°	554.5	566.3	581.3	596.6	615.5	637.7	658.0	682.8	707.9	737.2	767.9
20°	528.4	540.6	558.2	575.2	592.5	614.1	638.2	663.6	690.4	721.1	755.4
22.5°	507.8	516.5	533.9	551.1	571.3	593.5	617.1	643.5	672.7	704.6	740.5
25°	477.2	487.4	500.0	517.9	539.0	562.3	586.0	614.1	646.0	678.5	716.8
27.5°	450.1	458.4	470.8	484.9	505.9	530.1	555.4	584.7	617.3	650.4	690.7
30°	430.9	440.1	451.8	466.8	483.4	509.8	535.6	564.4	597.5	631.8	673.1
32.5°	414.1	423.5	433.7	447.8	465.7	489.2	515.8	544.0	577.7	613.1	653.3
35°	390.6	397.0	406.4	420.4	438.0	456.9	484.0	513.9	546.7	583.3	623.6
37.5°	363.6	371.9	381.4	393.4	408.8	429.4	454.6	484.7	515.2	550.3	587.0
40°	347.9	355.7	366.1	375.0	391.3	409.8	432.9	464.4	494.9	527.7	561.2
42.5°	331.9	339.4	348.3	359.3	373.9	392.0	413.4	442.7	475.4	506.3	534.5
45°	306.9	314.7	323.2	333.3	346.9	364.4	385.8	412.6	441.0	469.5	490.8
47.5°	282.9	290.3	298.3	308.7	321.2	338.2	357.3	380.9	408.6	432.7	448.0
50°	265.9	272.7	281.5	291.7	303.8	319.8	338.0	361.4	384.5	406.4	420.4
52.5°	249.1	256.7	265.5	274.3	286.0	301.8	318.8	338.9	360.9	378.8	390.3
55°	223.9	231.0	239.2	248.3	259.8	273.4	291.3	307.2	324.5	339.7	346.5
57.5°	199.6	205.8	213.5	222.9	233.4	245.9	260.1	275.4	287.7	298.5	306.1
60°	183.6	189.0	196.1	204.3	215.4	226.9	239.8	254.0	263.5	272.7	279.8
62.5°	167.4	172.5	179.3	186.6	196.4	207.1	219.5	231.0	240.2	246.4	254.6
65°	142.9	148.0	153.8	161.6	169.3	178.2	189.3	197.8	204.3	211.1	216.2
67.5°	120.3	124.5	129.9	136.1	142.6	151.1	159.7	166.7	171.2	175.2	181.4
70°	105.3	108.7	113.2	117.9	125.0	133.5	140.3	145.6	148.7	152.8	160.2
72.5°	90.2	94.1	98.3	103.0	108.7	115.8	121.8	127.2	129.2	132.4	137.1
75°	71.2	73.2	76.6	79.9	84.0	90.1	95.9	97.2	98.9	101.7	105.0
77.5°	53.8	55.6	57.0	59.2	62.4	67.3	70.4	72.4	72.9	73.8	77.1
80°	42.7	43.7	45.0	46.7	48.1	52.2	53.9	55.9	56.5	57.6	59.3
82.5°	31.3	32.3	33.2	34.5	36.7	38.3	40.0	42.1	42.2	43.0	43.2
85°	18.3	18.6	17.9	18.6	19.0	19.6	21.3	23.0	22.7	22.4	23.4
87.5°	8.7	8.6	8.1	8.7	8.0	8.0	7.8	7.8	8.2	8.5	8.8
90°	11.3	10.6	9.5	8.6	7.5	6.4	5.4	4.2	3.0	1.9	0.6
92.5°	11.3	10.6	9.6	8.7	7.8	7.0	6.9	7.7	8.6	9.4	10.2
95°	11.3	10.6	16.1	21.8	27.3	32.9	35.9	36.4	36.7	37.2	37.6
97.5°	28.4	32.5	43.5	54.6	65.6	76.7	81.8	81.0	80.3	79.5	78.6
100°	93.1	114.9	114.4	113.8	113.2	112.6	112.1	111.6	111.2	110.8	110.3
102.5°	142.6	146.7	146.3	146.0	145.6	145.3	144.8	144.3	143.7	143.1	142.6
105°	196.9	196.9	196.9	196.9	196.9	196.9	196.6	196.0	195.5	194.8	194.2
107.5°	249.2	249.2	249.0	248.6	248.3	248.1	247.9	247.9	247.9	247.9	247.9
110°	283.7	284.1	283.8	283.6	283.2	282.9	282.8	282.8	282.8	282.8	282.8



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	317.4	318.0	317.8	317.6	317.4	317.3	317.0	316.6	316.3	315.9	315.6
115°	368.1	368.7	368.5	368.4	368.3	368.1	367.7	366.9	366.2	365.4	364.7
117.5°	417.2	417.9	417.4	416.9	416.3	415.7	415.4	415.5	415.5	415.5	415.6
120°	448.4	448.6	448.2	447.7	447.3	446.8	446.7	446.8	447.0	447.2	447.3
122.5°	478.5	478.8	478.6	478.3	478.1	478.0	477.6	477.0	476.4	475.9	475.3
125°	522.7	523.3	523.3	523.3	523.3	523.3	522.8	521.7	520.8	519.7	518.7
127.5°	562.6	562.9	563.0	563.1	563.2	563.3	562.9	562.2	561.5	560.8	560.0
130°	588.9	589.3	589.2	589.1	588.9	588.8	588.4	587.6	586.8	586.1	585.4
132.5°	613.1	613.1	613.5	613.8	614.1	614.5	614.2	613.3	612.5	611.6	610.7
135°	649.2	649.5	649.8	650.1	650.4	650.7	650.4	649.5	648.6	647.7	646.8
137.5°	682.3	682.2	682.5	682.8	683.1	683.3	683.1	682.3	681.5	680.8	680.0
140°	702.7	702.3	702.5	702.7	702.8	702.9	702.8	702.6	702.3	702.0	701.7
142.5°	723.0	723.0	722.7	722.6	722.4	722.1	721.9	721.8	721.6	721.4	721.2
145°	751.4	751.3	751.3	751.3	751.3	751.3	751.1	750.8	750.6	750.2	749.9
147.5°	775.7	775.5	775.3	775.2	775.1	774.9	774.8	774.9	774.9	775.0	775.1
150°	791.2	790.9	790.6	790.3	790.0	789.7	789.7	790.0	790.3	790.6	790.9
152.5°	804.9	804.6	804.3	804.1	803.8	803.4	803.6	804.3	804.9	805.6	806.2
155°	823.7	823.2	823.0	822.7	822.4	822.1	822.4	823.2	824.1	825.0	825.9
157.5°	839.4	838.8	838.8	838.8	838.7	838.7	839.0	839.5	840.1	840.6	841.1
160°	849.0	848.4	848.2	848.1	847.9	847.7	848.2	849.0	849.9	850.8	851.7
162.5°	857.6	856.8	856.7	856.6	856.4	856.2	856.6	857.5	858.4	859.3	860.1
165°	869.1	868.2	868.1	867.9	867.7	867.6	868.0	868.9	869.8	870.6	871.5
167.5°	877.5	876.6	876.4	876.2	876.1	875.9	876.3	877.3	878.2	879.0	879.9
170°	881.9	880.7	880.6	880.5	880.3	880.1	880.6	881.6	882.6	883.7	884.8
172.5°	885.5	884.5	884.2	884.0	883.7	883.4	883.8	884.8	885.8	886.9	887.9
175°	889.2	888.1	887.9	887.7	887.6	887.4	887.8	888.7	889.6	890.5	891.4
177.5°	891.1	890.3	890.1	890.0	889.9	889.7	890.1	890.8	891.5	892.2	892.9
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	829.2	831.7	835.2	839.3	842.5	846.1	847.9	847.9	849.5	853.1	857.6
5°	831.6	840.4	848.9	859.7	868.2	878.0	885.5	892.6	899.0	907.1	915.6
7.5°	830.9	845.5	860.8	877.9	896.7	911.7	927.0	939.1	951.0	966.6	978.9
10°	828.2	847.2	867.8	889.5	913.2	933.9	952.5	969.5	985.7	1002.6	1017.9
12.5°	823.3	847.5	872.7	898.8	928.7	952.3	976.3	994.4	1013.3	1031.9	1050.7
15°	816.0	844.5	874.9	911.2	947.8	974.2	997.9	1021.3	1038.9	1059.9	1077.9
17.5°	800.9	837.6	875.9	915.5	950.7	981.4	1006.2	1028.5	1047.2	1070.3	1094.8
20°	791.9	831.6	871.6	913.9	947.4	978.9	1003.0	1026.0	1049.4	1079.6	1109.4
22.5°	779.5	821.8	864.2	904.5	939.9	970.3	995.1	1023.3	1054.0	1088.2	1124.3
25°	759.8	803.5	845.5	883.8	918.3	949.5	983.4	1021.3	1058.5	1103.6	1155.4
27.5°	734.8	776.9	814.4	854.8	889.2	928.8	971.1	1012.2	1066.0	1127.9	1192.7
30°	716.0	756.1	791.7	829.9	868.9	912.6	960.0	1008.4	1072.5	1145.2	1222.2
32.5°	694.4	730.6	765.9	802.8	847.7	895.7	946.2	1005.4	1081.9	1164.8	1244.4
35°	656.8	689.3	723.5	764.6	812.3	864.4	928.8	1000.9	1093.4	1182.5	1254.0
37.5°	617.4	643.0	677.4	720.6	772.7	833.0	906.1	993.7	1088.7	1168.7	1199.1
40°	587.0	611.1	647.3	692.7	744.2	810.3	892.2	982.3	1077.9	1133.4	1131.0
42.5°	557.0	581.3	616.2	661.8	715.5	789.4	873.8	967.4	1048.0	1069.2	1025.1
45°	510.8	533.5	567.8	613.8	671.4	748.9	837.7	927.5	978.9	944.8	857.4
47.5°	463.8	485.8	517.5	562.7	625.5	706.8	790.7	864.3	871.6	798.1	693.2
50°	432.9	453.5	483.8	531.8	592.8	672.1	753.0	810.9	793.0	703.2	595.1
52.5°	402.8	422.7	450.9	496.3	558.7	636.3	708.6	754.0	712.5	617.1	519.9
55°	358.4	377.4	405.8	447.5	504.0	575.2	638.6	655.1	594.1	497.9	419.4
57.5°	316.2	330.0	358.2	395.0	449.6	512.3	557.7	554.7	487.4	400.8	344.5
60°	288.3	300.8	327.5	361.4	413.2	469.5	501.3	487.8	419.7	348.2	294.0
62.5°	262.3	273.9	296.4	327.5	372.1	421.0	444.2	425.4	361.1	298.4	255.3
65°	222.9	231.4	249.3	278.1	313.0	346.9	367.6	340.1	283.2	235.8	203.2
67.5°	186.1	193.4	209.4	230.1	254.1	277.5	285.9	260.1	215.9	184.0	161.0
70°	162.3	169.1	179.9	199.2	215.1	231.7	235.8	212.8	175.8	151.4	137.1
72.5°	139.5	145.7	155.2	168.8	179.9	189.4	191.4	169.9	141.7	124.8	113.9
75°	106.4	111.8	117.9	123.0	130.1	131.8	131.1	114.5	99.2	88.1	81.9
77.5°	78.2	80.4	84.2	86.1	86.5	86.4	82.9	72.4	64.6	59.9	57.4
80°	60.3	62.0	63.0	63.7	64.0	60.6	56.9	50.5	47.8	45.0	42.0
82.5°	43.8	44.9	45.9	46.1	44.2	41.4	37.9	34.8	32.8	31.5	30.3
85°	23.7	24.1	23.7	22.0	19.6	18.6	17.9	17.3	16.9	16.6	16.6
87.5°	8.7	8.2	7.0	7.6	7.8	7.8	7.9	7.8	7.8	7.9	8.1
90°	1.9	3.0	4.2	5.4	6.4	7.5	8.6	9.5	10.6	11.3	12.0
92.5°	9.4	8.6	7.7	6.9	7.0	7.8	8.7	9.6	10.6	11.3	12.0
95°	37.2	36.7	36.4	35.9	32.9	27.3	21.8	16.1	10.6	11.3	12.0
97.5°	79.5	80.3	81.0	81.8	76.7	65.6	54.6	43.5	32.5	28.4	24.3
100°	110.8	111.2	111.6	112.1	112.6	113.2	113.8	114.4	114.9	93.1	71.2
102.5°	143.1	143.7	144.3	144.8	145.3	145.6	146.0	146.3	146.7	142.6	138.4
105°	194.8	195.5	196.0	196.6	196.9	196.9	196.9	196.9	196.9	196.9	196.9
107.5°	247.9	247.9	247.9	247.9	248.1	248.3	248.6	249.0	249.2	249.2	249.3
110°	282.8	282.8	282.8	282.8	282.9	283.2	283.6	283.8	284.1	283.7	283.2



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	315.9	316.3	316.6	317.0	317.3	317.4	317.6	317.8	318.0	317.4	316.8
115°	365.4	366.2	366.9	367.7	368.1	368.3	368.4	368.5	368.7	368.1	367.5
117.5°	415.5	415.5	415.5	415.4	415.7	416.3	416.9	417.4	417.9	417.2	416.4
120°	447.2	447.0	446.8	446.7	446.8	447.3	447.7	448.2	448.6	448.4	448.1
122.5°	475.9	476.4	477.0	477.6	478.0	478.1	478.3	478.6	478.8	478.5	478.1
125°	519.7	520.8	521.7	522.8	523.3	523.3	523.3	523.3	523.3	522.7	522.1
127.5°	560.8	561.5	562.2	562.9	563.3	563.2	563.1	563.0	562.9	562.6	562.3
130°	586.1	586.8	587.6	588.4	588.8	588.9	589.1	589.2	589.3	588.9	588.5
132.5°	611.6	612.5	613.3	614.2	614.5	614.1	613.8	613.5	613.1	613.1	613.0
135°	647.7	648.6	649.5	650.4	650.7	650.4	650.1	649.8	649.5	649.2	648.9
137.5°	680.8	681.5	682.3	683.1	683.3	683.1	682.8	682.5	682.2	682.3	682.4
140°	702.0	702.3	702.6	702.8	702.9	702.8	702.7	702.5	702.3	702.7	702.9
142.5°	721.4	721.6	721.8	721.9	722.1	722.4	722.6	722.7	723.0	723.0	723.1
145°	750.2	750.6	750.8	751.1	751.3	751.3	751.3	751.3	751.3	751.4	751.5
147.5°	775.0	774.9	774.9	774.8	774.9	775.1	775.2	775.3	775.5	775.7	775.9
150°	790.6	790.3	790.0	789.7	789.7	790.0	790.3	790.6	790.9	791.2	791.5
152.5°	805.6	804.9	804.3	803.6	803.4	803.8	804.1	804.3	804.6	804.9	805.2
155°	825.0	824.1	823.2	822.4	822.1	822.4	822.7	823.0	823.2	823.7	824.1
157.5°	840.6	840.1	839.5	839.0	838.7	838.7	838.8	838.8	838.8	839.4	839.8
160°	850.8	849.9	849.0	848.2	847.7	847.9	848.1	848.2	848.4	849.0	849.5
162.5°	859.3	858.4	857.5	856.6	856.2	856.4	856.6	856.7	856.8	857.6	858.4
165°	870.6	869.8	868.9	868.0	867.6	867.7	867.9	868.1	868.2	869.1	870.0
167.5°	879.0	878.2	877.3	876.3	875.9	876.1	876.2	876.4	876.6	877.5	878.6
170°	883.7	882.6	881.6	880.6	880.1	880.3	880.5	880.6	880.7	881.9	883.1
172.5°	886.9	885.8	884.8	883.8	883.4	883.7	884.0	884.2	884.5	885.5	886.5
175°	890.5	889.6	888.7	887.8	887.4	887.6	887.7	887.9	888.1	889.2	890.4
177.5°	892.2	891.5	890.8	890.1	889.7	889.9	890.0	890.1	890.3	891.1	891.9
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	861.2	861.2	865.9	865.5	868.5	867.5	868.0
5°	925.8	931.5	936.6	940.0	945.0	946.5	945.7
7.5°	992.7	1005.5	1011.7	1020.3	1021.8	1026.3	1025.8
10°	1034.1	1046.7	1056.1	1063.6	1067.4	1072.1	1072.5
12.5°	1066.7	1077.3	1085.7	1092.6	1097.2	1098.7	1099.6
15°	1092.1	1103.9	1113.7	1123.6	1129.4	1133.7	1136.1
17.5°	1117.7	1136.0	1153.3	1166.7	1174.7	1181.4	1181.3
20°	1137.5	1158.5	1180.2	1195.4	1210.9	1217.7	1218.8
22.5°	1158.6	1190.7	1218.6	1242.2	1262.8	1269.8	1272.4
25°	1202.5	1244.5	1287.5	1320.7	1344.4	1358.3	1360.4
27.5°	1255.5	1312.4	1357.6	1388.3	1408.0	1418.3	1420.5
30°	1293.0	1345.4	1386.1	1409.2	1418.3	1419.6	1414.5
32.5°	1309.7	1349.0	1365.2	1363.9	1345.9	1334.0	1329.5
35°	1289.2	1281.1	1241.4	1194.0	1157.8	1134.8	1128.6
37.5°	1173.2	1103.1	1030.2	958.6	920.4	901.1	867.7
40°	1058.9	958.9	883.1	822.8	779.8	745.2	737.1
42.5°	929.9	826.7	750.8	699.2	664.9	641.1	630.9
45°	747.3	658.5	595.8	556.2	529.8	512.5	504.7
47.5°	597.6	529.0	483.3	454.0	433.8	418.8	414.6
50°	515.6	460.7	422.0	397.3	382.1	370.6	365.9
52.5°	447.8	403.5	373.8	353.5	339.0	331.8	327.9
55°	369.5	331.3	310.0	293.6	285.5	279.8	277.1
57.5°	302.2	274.6	259.0	247.7	240.2	236.6	235.2
60°	264.6	242.9	228.6	219.8	214.7	210.0	208.7
62.5°	231.2	214.2	203.1	195.5	190.4	188.3	187.5
65°	186.3	175.1	167.0	162.3	158.2	157.5	157.2
67.5°	148.1	141.5	137.2	132.3	130.9	128.5	128.0
70°	126.7	122.3	117.2	115.5	113.8	111.5	111.8
72.5°	107.5	103.1	99.6	97.4	96.8	95.8	96.6
75°	78.6	77.2	75.9	74.2	73.5	73.5	73.2
77.5°	56.1	54.9	53.4	52.4	52.3	50.8	51.4
80°	40.7	39.0	38.3	38.6	37.6	37.3	37.3
82.5°	30.1	29.4	28.8	28.9	28.6	28.4	28.6
85°	16.6	16.2	16.2	16.0	16.0	15.6	15.6
87.5°	8.6	8.9	8.5	8.3	8.4	8.7	9.1
90°	12.8	13.5	14.1	14.5	15.0	15.4	15.9
92.5°	12.8	13.5	14.0	14.2	14.4	14.6	14.8
95°	12.8	13.5	13.9	13.9	13.9	13.9	13.9
97.5°	20.1	16.0	13.9	13.9	13.9	13.9	13.9
100°	49.3	27.5	16.2	15.6	15.1	14.4	13.9
102.5°	134.3	130.1	123.1	113.1	103.1	93.1	83.1
105°	196.9	196.9	196.8	196.7	196.5	196.4	196.3
107.5°	249.3	249.3	249.1	248.7	248.3	247.8	247.4
110°	282.8	282.3	282.2	282.3	282.5	282.7	282.8



TEST NUMBER: P333664-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	316.3	315.7	315.3	315.1	315.0	314.7	314.5
115°	366.9	366.3	365.6	364.7	363.8	362.9	362.0
117.5°	415.7	414.9	414.4	413.9	413.6	413.2	412.9
120°	447.7	447.5	446.9	446.2	445.5	444.8	444.0
122.5°	477.9	477.6	477.0	476.2	475.3	474.5	473.6
125°	521.6	520.9	520.4	520.0	519.5	519.2	518.7
127.5°	562.0	561.7	561.0	559.8	558.7	557.7	556.6
130°	588.1	587.6	587.0	586.3	585.6	584.8	584.1
132.5°	612.9	612.8	612.4	611.6	610.9	610.2	609.5
135°	648.6	648.4	647.7	646.8	646.0	645.1	644.2
137.5°	682.4	682.5	682.2	681.4	680.6	679.8	679.1
140°	703.2	703.6	703.2	702.3	701.5	700.6	699.7
142.5°	723.2	723.2	722.8	721.9	721.0	720.1	719.3
145°	751.7	751.8	751.4	750.6	749.7	748.9	748.0
147.5°	776.1	776.2	775.8	774.8	773.7	772.7	771.6
150°	791.8	792.1	791.7	790.4	789.3	788.1	786.9
152.5°	805.5	805.8	805.4	804.3	803.3	802.3	801.2
155°	824.6	825.0	824.7	823.5	822.3	821.2	819.9
157.5°	840.3	840.7	840.3	839.2	838.0	836.9	835.7
160°	850.2	850.7	850.4	849.3	848.1	846.9	845.7
162.5°	859.3	860.1	859.9	858.6	857.3	856.0	854.7
165°	870.8	871.7	871.6	870.4	869.2	868.1	866.8
167.5°	879.7	880.7	880.7	879.3	878.0	876.6	875.3
170°	884.3	885.5	885.4	884.0	882.7	881.4	880.1
172.5°	887.6	888.7	888.5	887.3	885.9	884.6	883.2
175°	891.5	892.7	892.6	891.4	890.0	888.7	887.3
177.5°	892.7	893.6	893.5	892.5	891.6	890.6	889.7
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4

(END OF REPORT)