

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333665-940

Luminaire Tested: **S125RDIW-S610D770U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333665-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S610D770U940-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4513.3 lumens  
Efficiency: N/A  
Efficacy: 120.0 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47								
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41								
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35								
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30								
4	75	64	57	51	69	59	53	48	50	45	41	42	38	35	34	32	30	26								
5	69	57	49	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23								
6	63	51	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20								
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18								
8	54	42	35	29	50	39	33	28	34	28	25	29	24	21	24	21	18	16								
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14								
10	47	35	28	24	44	33	27	22	29	23	20	24	20	17	20	17	15	13								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5329	5329	5329	5329
5°	6131	5336	4713	5336
10°	7033	5309	4158	5309
15°	7596	5255	3697	5255
20°	8377	5192	3413	5192
25°	9694	5108	3167	5108
30°	10549	5020	3006	5020
35°	8898	4917	2858	4917
40°	6214	4731	2731	4731
45°	4610	4483	2606	4483
50°	3676	4224	2498	4224
55°	3120	3902	2403	3902
60°	2696	3614	2250	3614
65°	2402	3304	1936	3304
70°	2111	3025	1766	3025
75°	1827	2620	1657	2620
80°	1387	2205	1387	2205
85°	1156	1734	1312	1734



TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.1	1.8
10°-20°	231.9	5.1
20°-30°	367.7	8.1
30°-40°	443.4	9.8
40°-50°	396.0	8.8
50°-60°	303.6	6.7
60°-70°	197.3	4.4
70°-80°	95.9	2.1
80°-90°	24.8	0.5
90°-100°	57.0	1.3
100°-110°	168.2	3.7
110°-120°	285.0	6.3
120°-130°	375.0	8.3
130°-140°	420.2	9.3
140°-150°	411.8	9.1
150°-160°	345.9	7.7
160°-170°	229.9	5.1
170°-180°	80.5	1.8
0°-30°	678.7	15.0
0°-40°	1122.1	24.9
0°-60°	1821.7	40.4
0°-90°	2139.7	47.4
90°-120°	510.2	11.3
90°-150°	1717.2	38.0
90°-180°	2374.0	52.6
0°-180°	4513.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	825	825	825	825	825	
5°	946	823	727	823	946	94
15°	1136	786	553	786	1136	326
25°	1360	717	444	717	1360	625
35°	1129	624	362	624	1129	682
45°	505	491	285	491	505	403
55°	277	346	213	346	277	251
65°	157	216	127	216	157	156
75°	73	105	66	105	73	78
85°	16	23	18	23	16	18
90°	16	1	16	1	16	10
95°	57	43	57	43	57	58
105°	164	151	164	151	164	174
115°	288	285	288	285	288	285
125°	419	416	419	416	419	374
135°	544	541	544	541	544	419
145°	659	656	659	656	659	411
155°	751	751	751	751	751	345
165°	814	816	814	816	814	230
175°	845	849	845	849	845	80
180°	851	851	851	851	851	



TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	868.0	867.5	868.5	865.5	865.9	861.2	861.2	857.6	853.1	849.5	847.9
5°	945.7	946.5	945.0	940.0	936.6	931.5	925.8	915.6	907.1	899.0	892.6
7.5°	1025.8	1026.3	1021.8	1020.3	1011.7	1005.5	992.7	978.9	966.6	951.0	939.1
10°	1072.5	1072.1	1067.4	1063.6	1056.1	1046.7	1034.1	1017.9	1002.6	985.7	969.5
12.5°	1099.6	1098.7	1097.2	1092.6	1085.7	1077.3	1066.7	1050.7	1031.9	1013.3	994.4
15°	1136.1	1133.7	1129.4	1123.6	1113.7	1103.9	1092.1	1077.9	1059.9	1038.9	1021.3
17.5°	1181.3	1181.4	1174.7	1166.7	1153.3	1136.0	1117.7	1094.8	1070.3	1047.2	1028.5
20°	1218.8	1217.7	1210.9	1195.4	1180.2	1158.5	1137.5	1109.4	1079.6	1049.4	1026.0
22.5°	1272.4	1269.8	1262.8	1242.2	1218.6	1190.7	1158.6	1124.3	1088.2	1054.0	1023.3
25°	1360.4	1358.3	1344.4	1320.7	1287.5	1244.5	1202.5	1155.4	1103.6	1058.5	1021.3
27.5°	1420.5	1418.3	1408.0	1388.3	1357.6	1312.4	1255.5	1192.7	1127.9	1066.0	1012.2
30°	1414.5	1419.6	1418.3	1409.2	1386.1	1345.4	1293.0	1222.2	1145.2	1072.5	1008.4
32.5°	1329.5	1334.0	1345.9	1363.9	1365.2	1349.0	1309.7	1244.4	1164.8	1081.9	1005.4
35°	1128.6	1134.8	1157.8	1194.0	1241.4	1281.1	1289.2	1254.0	1182.5	1093.4	1000.9
37.5°	867.7	901.1	920.4	958.6	1030.2	1103.1	1173.2	1199.1	1168.7	1088.7	993.7
40°	737.1	745.2	779.8	822.8	883.1	958.9	1058.9	1131.0	1133.4	1077.9	982.3
42.5°	630.9	641.1	664.9	699.2	750.8	826.7	929.9	1025.1	1069.2	1048.0	967.4
45°	504.7	512.5	529.8	556.2	595.8	658.5	747.3	857.4	944.8	978.9	927.5
47.5°	414.6	418.8	433.8	454.0	483.3	529.0	597.6	693.2	798.1	871.6	864.3
50°	365.9	370.6	382.1	397.3	422.0	460.7	515.6	595.1	703.2	793.0	810.9
52.5°	327.9	331.8	339.0	353.5	373.8	403.5	447.8	519.9	617.1	712.5	754.0
55°	277.1	279.8	285.5	293.6	310.0	331.3	369.5	419.4	497.9	594.1	655.1
57.5°	235.2	236.6	240.2	247.7	259.0	274.6	302.2	344.5	400.8	487.4	554.7
60°	208.7	210.0	214.7	219.8	228.6	242.9	264.6	294.0	348.2	419.7	487.8
62.5°	187.5	188.3	190.4	195.5	203.1	214.2	231.2	255.3	298.4	361.1	425.4
65°	157.2	157.5	158.2	162.3	167.0	175.1	186.3	203.2	235.8	283.2	340.1
67.5°	128.0	128.5	130.9	132.3	137.2	141.5	148.1	161.0	184.0	215.9	260.1
70°	111.8	111.5	113.8	115.5	117.2	122.3	126.7	137.1	151.4	175.8	212.8
72.5°	96.6	95.8	96.8	97.4	99.6	103.1	107.5	113.9	124.8	141.7	169.9
75°	73.2	73.5	73.5	74.2	75.9	77.2	78.6	81.9	88.1	99.2	114.5
77.5°	51.4	50.8	52.3	52.4	53.4	54.9	56.1	57.4	59.9	64.6	72.4
80°	37.3	37.3	37.6	38.6	38.3	39.0	40.7	42.0	45.0	47.8	50.5
82.5°	28.6	28.4	28.6	28.9	28.8	29.4	30.1	30.3	31.5	32.8	34.8
85°	15.6	15.6	16.0	16.0	16.2	16.2	16.6	16.6	16.6	16.9	17.3
87.5°	9.1	8.7	8.4	8.3	8.5	8.9	8.6	8.1	7.9	7.8	7.8
90°	15.9	15.4	15.0	14.5	14.1	13.6	12.8	12.0	11.3	10.6	9.5
92.5°	31.2	30.9	30.6	30.3	30.0	29.3	28.4	27.4	26.4	25.4	24.2
95°	56.9	56.6	56.4	56.1	55.7	55.1	54.0	53.1	52.0	51.0	49.5
97.5°	86.3	86.1	86.0	85.8	85.6	85.1	84.1	83.1	82.1	81.1	79.1
100°	108.5	108.3	108.0	107.7	107.4	106.6	105.2	103.9	102.6	101.3	99.3
102.5°	130.8	130.4	130.0	129.6	129.1	128.2	126.8	125.4	123.9	122.4	121.5
105°	164.2	163.7	163.3	162.8	162.4	161.8	160.9	160.0	159.1	158.2	157.3
107.5°	198.3	198.3	198.4	198.4	198.4	198.2	197.8	197.3	196.9	196.4	195.8
110°	223.7	223.9	224.0	224.2	224.4	224.2	223.7	223.3	222.8	222.4	221.9



TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	248.6	248.9	249.1	249.4	249.7	249.7	249.5	249.3	249.1	248.9	248.3
115°	287.9	288.1	288.3	288.4	288.6	288.6	288.8	289.0	289.1	289.3	289.0
117.5°	326.4	326.9	327.5	328.1	328.7	329.0	328.8	328.7	328.6	328.5	328.2
120°	352.8	353.4	354.0	354.6	355.2	355.4	355.4	355.4	355.4	355.4	355.3
122.5°	379.3	379.8	380.2	380.7	381.2	381.5	381.6	381.7	381.8	381.9	381.6
125°	419.0	419.2	419.3	419.5	419.6	419.8	420.1	420.4	420.7	421.0	420.9
127.5°	457.2	457.4	457.7	458.1	458.3	458.5	458.7	458.9	459.0	459.1	459.0
130°	482.6	482.9	483.1	483.5	483.8	483.9	484.1	484.3	484.4	484.6	484.3
132.5°	506.4	506.8	507.2	507.7	508.0	508.4	508.5	508.6	508.8	508.9	509.0
135°	543.5	544.0	544.7	545.2	545.8	546.1	546.1	546.1	546.1	546.1	546.0
137.5°	579.7	580.5	581.2	581.9	582.6	583.0	582.8	582.6	582.5	582.3	581.9
140°	603.1	603.8	604.5	605.3	606.0	606.2	605.9	605.6	605.3	605.0	604.6
142.5°	625.3	626.0	626.8	627.5	628.2	628.5	628.3	628.1	627.9	627.8	627.2
145°	658.6	659.1	659.5	660.0	660.4	660.7	660.7	660.7	660.7	660.7	660.2
147.5°	687.2	688.1	689.1	690.1	691.1	691.4	691.1	690.7	690.4	690.0	689.6
150°	708.3	708.6	708.9	709.2	709.4	709.6	709.6	709.6	709.6	709.6	709.0
152.5°	725.8	726.3	726.8	727.4	727.9	728.0	727.6	727.3	726.9	726.6	726.3
155°	750.6	751.4	752.2	752.9	753.6	753.7	753.0	752.5	751.9	751.4	751.2
157.5°	771.4	772.4	773.4	774.4	775.3	775.5	774.9	774.4	773.7	773.2	773.0
160°	785.8	786.5	787.2	787.9	788.7	788.7	788.2	787.6	787.0	786.4	786.2
162.5°	797.9	798.8	799.6	800.5	801.4	801.4	800.7	800.0	799.3	798.6	798.5
165°	814.2	815.1	816.0	816.9	817.7	817.9	817.3	816.7	816.1	815.6	815.4
167.5°	827.2	828.1	829.0	829.9	830.8	830.8	830.0	829.1	828.2	827.3	827.3
170°	834.1	835.1	836.2	837.1	838.2	838.3	837.4	836.5	835.6	834.7	834.7
172.5°	839.9	840.8	841.7	842.7	843.6	843.6	842.7	841.8	840.9	840.0	840.0
175°	845.3	846.3	847.4	848.4	849.4	849.5	848.6	847.7	846.9	846.0	846.0
177.5°	848.5	849.4	850.2	851.0	851.8	851.9	851.1	850.4	849.7	849.0	849.2
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	847.9	846.1	842.5	839.3	835.2	831.7	829.2	826.3	822.4	817.9	814.0
5°	885.5	878.0	868.2	859.7	848.9	840.4	831.6	823.1	814.7	803.8	794.3
7.5°	927.0	911.7	896.7	877.9	860.8	845.5	830.9	816.1	801.6	786.2	771.3
10°	952.5	933.9	913.2	889.5	867.8	847.2	828.2	809.6	790.0	772.7	754.0
12.5°	976.3	952.3	928.7	898.8	872.7	847.5	823.3	800.1	779.1	756.7	736.6
15°	997.9	974.2	947.8	911.2	874.9	844.5	816.0	785.9	759.8	734.7	712.4
17.5°	1006.2	981.4	950.7	915.5	875.9	837.6	800.9	767.9	737.2	707.9	682.8
20°	1003.0	978.9	947.4	913.9	871.6	831.6	791.9	755.4	721.1	690.4	663.6
22.5°	995.1	970.3	939.9	904.5	864.2	821.8	779.5	740.5	704.6	672.7	643.5
25°	983.4	949.5	918.3	883.8	845.5	803.5	759.8	716.8	678.5	646.0	614.1
27.5°	971.1	928.8	889.2	854.8	814.4	776.9	734.8	690.7	650.4	617.3	584.7
30°	960.0	912.6	868.9	829.9	791.7	756.1	716.0	673.1	631.8	597.5	564.4
32.5°	946.2	895.7	847.7	802.8	765.9	730.6	694.4	653.3	613.1	577.7	544.0
35°	928.8	864.4	812.3	764.6	723.5	689.3	656.8	623.6	583.3	546.7	513.9
37.5°	906.1	833.0	772.7	720.6	677.4	643.0	617.4	587.0	550.3	515.2	484.7
40°	892.2	810.3	744.2	692.7	647.3	611.1	587.0	561.2	527.7	494.9	464.4
42.5°	873.8	789.4	715.5	661.8	616.2	581.3	557.0	534.5	506.3	475.4	442.7
45°	837.7	748.9	671.4	613.8	567.8	533.5	510.8	490.8	469.5	441.0	412.6
47.5°	790.7	706.8	625.5	562.7	517.5	485.8	463.8	448.0	432.7	408.6	380.9
50°	753.0	672.1	592.8	531.8	483.8	453.5	432.9	420.4	406.4	384.5	361.4
52.5°	708.6	636.3	558.7	496.3	450.9	422.7	402.8	390.3	378.8	360.9	338.9
55°	638.6	575.2	504.0	447.5	405.8	377.4	358.4	346.5	339.7	324.5	307.2
57.5°	557.7	512.3	449.6	395.0	358.2	330.0	316.2	306.1	298.5	287.7	275.4
60°	501.3	469.5	413.2	361.4	327.5	300.8	288.3	279.8	272.7	263.5	254.0
62.5°	444.2	421.0	372.1	327.5	296.4	273.9	262.3	254.6	246.4	240.2	231.0
65°	367.6	346.9	313.0	278.1	249.3	231.4	222.9	216.2	211.1	204.3	197.8
67.5°	285.9	277.5	254.1	230.1	209.4	193.4	186.1	181.4	175.2	171.2	166.7
70°	235.8	231.7	215.1	199.2	179.9	169.1	162.3	160.2	152.8	148.7	145.6
72.5°	191.4	189.4	179.9	168.8	155.2	145.7	139.5	137.1	132.4	129.2	127.2
75°	131.1	131.8	130.1	123.0	117.9	111.8	106.4	105.0	101.7	98.9	97.2
77.5°	82.9	86.4	86.5	86.1	84.2	80.4	78.2	77.1	73.8	72.9	72.4
80°	56.9	60.6	64.0	63.7	63.0	62.0	60.3	59.3	57.6	56.5	55.9
82.5°	37.9	41.4	44.2	46.1	45.9	44.9	43.8	43.2	43.0	42.2	42.1
85°	17.9	18.6	19.6	22.0	23.7	24.1	23.7	23.4	22.4	22.7	23.0
87.5°	7.9	7.8	7.8	7.6	7.0	8.2	8.7	8.8	8.5	8.2	7.8
90°	8.6	7.5	6.5	5.4	4.2	3.0	1.9	0.6	1.9	3.0	4.2
92.5°	22.9	21.7	20.3	19.4	18.5	17.7	16.9	16.1	16.9	17.7	18.5
95°	48.1	46.5	45.1	44.2	43.9	43.6	43.3	43.1	43.3	43.6	43.9
97.5°	77.1	75.1	73.0	72.0	71.9	71.7	71.6	71.5	71.6	71.7	71.9
100°	97.5	95.5	93.6	92.6	92.6	92.6	92.6	92.6	92.6	92.6	92.6
102.5°	120.6	119.6	118.6	117.8	117.2	116.6	116.0	115.5	116.0	116.6	117.2
105°	156.4	155.6	154.7	153.9	153.1	152.4	151.7	151.0	151.7	152.4	153.1
107.5°	195.1	194.5	193.8	193.1	192.3	191.6	190.8	190.1	190.8	191.6	192.3
110°	221.5	221.1	220.6	220.1	219.4	218.6	217.8	217.1	217.8	218.6	219.4





TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	247.8	247.2	246.6	246.2	245.8	245.4	245.0	244.7	245.0	245.4	245.8
115°	288.6	288.4	288.1	287.7	287.0	286.5	285.9	285.3	285.9	286.5	287.0
117.5°	328.0	327.7	327.4	327.2	326.9	326.6	326.4	326.1	326.4	326.6	326.9
120°	355.2	355.0	354.9	354.5	353.7	352.9	352.2	351.5	352.2	352.9	353.7
122.5°	381.2	380.8	380.4	380.1	379.9	379.6	379.3	379.1	379.3	379.6	379.9
125°	420.7	420.5	420.4	419.9	419.0	418.1	417.2	416.3	417.2	418.1	419.0
127.5°	458.8	458.6	458.4	458.1	457.6	457.1	456.6	456.1	456.6	457.1	457.6
130°	483.9	483.7	483.4	482.9	482.1	481.4	480.6	479.9	480.6	481.4	482.1
132.5°	509.0	509.1	509.2	508.5	507.4	506.1	505.0	503.7	505.0	506.1	507.4
135°	545.8	545.6	545.5	545.0	544.1	543.2	542.3	541.4	542.3	543.2	544.1
137.5°	581.6	581.3	580.9	580.4	579.5	578.6	577.8	576.9	577.8	578.6	579.5
140°	604.1	603.7	603.2	602.7	601.9	601.2	600.5	599.8	600.5	601.2	601.9
142.5°	626.7	626.2	625.5	625.0	624.4	623.8	623.1	622.5	623.1	623.8	624.4
145°	659.8	659.3	658.9	658.4	657.7	657.2	656.6	656.0	656.6	657.2	657.7
147.5°	689.3	688.9	688.6	688.3	688.0	687.6	687.3	687.0	687.3	687.6	688.0
150°	708.5	707.8	707.3	707.0	707.2	707.3	707.5	707.7	707.5	707.3	707.2
152.5°	726.1	725.9	725.6	725.4	725.2	725.0	724.8	724.6	724.8	725.0	725.2
155°	751.0	750.9	750.7	750.6	750.6	750.6	750.6	750.6	750.6	750.6	750.6
157.5°	772.8	772.8	772.6	772.7	773.0	773.3	773.6	774.0	773.6	773.3	773.0
160°	786.1	786.0	785.8	786.0	786.4	786.8	787.3	787.7	787.3	786.8	786.4
162.5°	798.5	798.5	798.4	798.6	799.0	799.2	799.6	800.0	799.6	799.2	799.0
165°	815.2	815.1	814.9	815.0	815.3	815.6	815.9	816.2	815.9	815.6	815.3
167.5°	827.3	827.3	827.3	827.6	828.2	828.8	829.4	830.0	829.4	828.8	828.2
170°	834.7	834.7	834.7	835.0	835.6	836.2	836.8	837.4	836.8	836.2	835.6
172.5°	840.0	840.0	840.0	840.3	840.9	841.5	842.0	842.7	842.0	841.5	840.9
175°	846.0	846.0	846.0	846.2	846.9	847.5	848.0	848.6	848.0	847.5	846.9
177.5°	849.3	849.4	849.5	849.8	850.2	850.7	851.2	851.7	851.2	850.7	850.2
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	811.4	807.5	804.9	799.4	795.6	794.0	791.0	790.2	793.2	791.0	790.8
5°	787.2	777.4	769.6	761.8	753.3	748.0	739.8	738.4	736.4	733.3	732.7
7.5°	758.3	745.5	735.5	722.6	711.4	702.4	692.2	687.4	684.7	680.8	675.6
10°	738.8	723.5	710.0	697.1	683.2	672.1	661.9	654.1	649.0	644.3	642.2
12.5°	719.5	704.0	686.7	671.1	655.6	643.0	631.8	626.7	621.1	615.5	610.8
15°	689.6	669.0	650.1	632.0	618.8	605.3	594.5	587.0	578.5	576.2	567.0
17.5°	658.0	637.7	615.5	596.6	581.3	566.3	554.5	546.0	539.6	530.8	526.6
20°	638.2	614.1	592.5	575.2	558.2	540.6	528.4	521.3	515.2	508.1	504.7
22.5°	617.1	593.5	571.3	551.1	533.9	516.5	507.8	500.4	493.6	487.0	482.5
25°	586.0	562.3	539.0	517.9	500.0	487.4	477.2	468.8	465.1	458.6	453.9
27.5°	555.4	530.1	505.9	484.9	470.8	458.4	450.1	443.4	436.7	431.1	427.0
30°	535.6	509.8	483.4	466.8	451.8	440.1	430.9	424.5	419.4	414.3	411.3
32.5°	515.8	489.2	465.7	447.8	433.7	423.5	414.1	407.9	402.5	396.9	393.3
35°	484.0	456.9	438.0	420.4	406.4	397.0	390.6	381.7	377.4	373.3	369.5
37.5°	454.6	429.4	408.8	393.4	381.4	371.9	363.6	358.8	353.5	349.8	346.7
40°	432.9	409.8	391.3	375.0	366.1	355.7	347.9	341.8	337.7	333.0	329.6
42.5°	413.4	392.0	373.9	359.3	348.3	339.4	331.9	325.8	320.7	317.3	314.4
45°	385.8	364.4	346.9	333.3	323.2	314.7	306.9	303.8	297.0	293.0	291.7
47.5°	357.3	338.2	321.2	308.7	298.3	290.3	282.9	276.8	273.0	269.0	266.9
50°	338.0	319.8	303.8	291.7	281.5	272.7	265.9	261.8	256.7	253.1	250.3
52.5°	318.8	301.8	286.0	274.3	265.5	256.7	249.1	245.0	240.2	237.8	235.9
55°	291.3	273.4	259.8	248.3	239.2	231.0	223.9	219.8	216.8	214.5	213.7
57.5°	260.1	245.9	233.4	222.9	213.5	205.8	199.6	195.7	193.1	192.7	190.6
60°	239.8	226.9	215.4	204.3	196.1	189.0	183.6	179.2	176.5	176.1	175.5
62.5°	219.5	207.1	196.4	186.6	179.3	172.5	167.4	162.4	160.8	159.1	157.6
65°	189.3	178.2	169.3	161.6	153.8	148.0	142.9	139.9	136.2	134.1	130.5
67.5°	159.7	151.1	142.6	136.1	129.9	124.5	120.3	115.7	113.2	111.6	108.9
70°	140.3	133.5	125.0	117.9	113.2	108.7	105.3	100.2	98.5	97.2	95.9
72.5°	121.8	115.8	108.7	103.0	98.3	94.1	90.2	87.8	86.1	84.7	83.9
75°	95.9	90.1	84.0	79.9	76.6	73.2	71.2	69.5	68.8	68.4	67.1
77.5°	70.4	67.3	62.4	59.2	57.0	55.6	53.8	52.9	52.9	51.4	50.9
80°	53.9	52.2	48.1	46.7	45.0	43.7	42.7	41.0	39.3	38.6	37.6
82.5°	40.0	38.3	36.7	34.5	33.2	32.3	31.3	30.7	30.9	30.0	29.4
85°	21.3	19.6	19.0	18.6	17.9	18.6	18.3	17.9	17.7	17.3	17.7
87.5°	7.8	8.0	8.0	8.7	8.1	8.6	8.7	8.6	8.8	8.9	8.8
90°	5.4	6.5	7.5	8.6	9.5	10.6	11.3	12.0	12.8	13.6	14.1
92.5°	19.4	20.3	21.7	22.9	24.2	25.4	26.4	27.4	28.4	29.3	30.0
95°	44.2	45.1	46.5	48.1	49.5	51.0	52.0	53.1	54.0	55.1	55.7
97.5°	72.0	73.0	75.1	77.1	79.1	81.1	82.1	83.1	84.1	85.1	85.6
100°	92.6	93.6	95.5	97.5	99.3	101.3	102.6	103.9	105.2	106.6	107.4
102.5°	117.8	118.6	119.6	120.6	121.5	122.4	123.9	125.4	126.8	128.2	129.1
105°	153.9	154.7	155.6	156.4	157.3	158.2	159.1	160.0	160.9	161.8	162.4
107.5°	193.1	193.8	194.5	195.1	195.8	196.4	196.9	197.3	197.8	198.2	198.4
110°	220.1	220.6	221.1	221.5	221.9	222.4	222.8	223.3	223.7	224.2	224.4



TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	246.2	246.6	247.2	247.8	248.3	248.9	249.1	249.3	249.5	249.7	249.7
115°	287.7	288.1	288.4	288.6	289.0	289.3	289.1	289.0	288.8	288.6	288.6
117.5°	327.2	327.4	327.7	328.0	328.2	328.5	328.6	328.7	328.8	329.0	328.7
120°	354.5	354.9	355.0	355.2	355.3	355.4	355.4	355.4	355.4	355.4	355.2
122.5°	380.1	380.4	380.8	381.2	381.6	381.9	381.8	381.7	381.6	381.5	381.2
125°	419.9	420.4	420.5	420.7	420.9	421.0	420.7	420.4	420.1	419.8	419.6
127.5°	458.1	458.4	458.6	458.8	459.0	459.1	459.0	458.9	458.7	458.5	458.3
130°	482.9	483.4	483.7	483.9	484.3	484.6	484.4	484.3	484.1	483.9	483.8
132.5°	508.5	509.2	509.1	509.0	509.0	508.9	508.8	508.6	508.5	508.4	508.0
135°	545.0	545.5	545.6	545.8	546.0	546.1	546.1	546.1	546.1	546.1	545.8
137.5°	580.4	580.9	581.3	581.6	581.9	582.3	582.5	582.6	582.8	583.0	582.6
140°	602.7	603.2	603.7	604.1	604.6	605.0	605.3	605.6	605.9	606.2	606.0
142.5°	625.0	625.5	626.2	626.7	627.2	627.8	627.9	628.1	628.3	628.5	628.2
145°	658.4	658.9	659.3	659.8	660.2	660.7	660.7	660.7	660.7	660.7	660.4
147.5°	688.3	688.6	688.9	689.3	689.6	690.0	690.4	690.7	691.1	691.4	691.1
150°	707.0	707.3	707.8	708.5	709.0	709.6	709.6	709.6	709.6	709.6	709.4
152.5°	725.4	725.6	725.9	726.1	726.3	726.6	726.9	727.3	727.6	728.0	727.9
155°	750.6	750.7	750.9	751.0	751.2	751.4	751.9	752.5	753.0	753.7	753.6
157.5°	772.7	772.6	772.8	772.8	773.0	773.2	773.7	774.4	774.9	775.5	775.3
160°	786.0	785.8	786.0	786.1	786.2	786.4	787.0	787.6	788.2	788.7	788.7
162.5°	798.6	798.4	798.5	798.5	798.5	798.6	799.3	800.0	800.7	801.4	801.4
165°	815.0	814.9	815.1	815.2	815.4	815.6	816.1	816.7	817.3	817.9	817.7
167.5°	827.6	827.3	827.3	827.3	827.3	827.3	828.2	829.1	830.0	830.8	830.8
170°	835.0	834.7	834.7	834.7	834.7	834.7	835.6	836.5	837.4	838.3	838.2
172.5°	840.3	840.0	840.0	840.0	840.0	840.0	840.9	841.8	842.7	843.6	843.6
175°	846.2	846.0	846.0	846.0	846.0	846.0	846.9	847.7	848.6	849.5	849.4
177.5°	849.8	849.5	849.4	849.3	849.2	849.0	849.7	850.4	851.1	851.9	851.8
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	790.5	787.5	786.7	787.7	786.7	787.5	790.5	790.8	791.0	793.2	790.2
5°	729.3	725.9	727.6	726.9	727.6	725.9	729.3	732.7	733.3	736.4	738.4
7.5°	675.5	671.3	666.8	668.2	666.8	671.3	675.5	675.6	680.8	684.7	687.4
10°	637.8	634.5	632.4	634.1	632.4	634.5	637.8	642.2	644.3	649.0	654.1
12.5°	606.1	604.1	602.4	601.6	602.4	604.1	606.1	610.8	615.5	621.1	626.7
15°	562.9	558.9	557.2	552.9	557.2	558.9	562.9	567.0	576.2	578.5	587.0
17.5°	523.2	521.8	517.5	515.6	517.5	521.8	523.2	526.6	530.8	539.6	546.0
20°	499.6	498.3	493.9	496.6	493.9	498.3	499.6	504.7	508.1	515.2	521.3
22.5°	480.1	477.2	475.7	474.9	475.7	477.2	480.1	482.5	487.0	493.6	500.4
25°	452.5	448.2	446.5	444.4	446.5	448.2	452.5	453.9	458.6	465.1	468.8
27.5°	425.1	422.7	420.4	419.9	420.4	422.7	425.1	427.0	431.1	436.7	443.4
30°	407.2	404.7	403.1	403.1	403.1	404.7	407.2	411.3	414.3	419.4	424.5
32.5°	391.2	389.3	387.6	387.4	387.6	389.3	391.2	393.3	396.9	402.5	407.9
35°	367.8	365.2	364.4	362.5	364.4	365.2	367.8	369.5	373.3	377.4	381.7
37.5°	343.7	341.4	341.3	341.2	341.3	341.4	343.7	346.7	349.8	353.5	358.8
40°	328.2	326.5	326.2	323.9	326.2	326.5	328.2	329.6	333.0	337.7	341.8
42.5°	311.7	310.9	309.7	308.6	309.7	310.9	311.7	314.4	317.3	320.7	325.8
45°	289.3	287.0	287.0	285.3	287.0	287.0	289.3	291.7	293.0	297.0	303.8
47.5°	266.1	264.3	264.5	262.7	264.5	264.3	266.1	266.9	269.0	273.0	276.8
50°	250.7	249.7	249.3	248.6	249.3	249.7	250.7	250.3	253.1	256.7	261.8
52.5°	235.2	234.8	236.0	234.5	236.0	234.8	235.2	235.9	237.8	240.2	245.0
55°	214.5	213.4	215.4	213.4	215.4	213.4	214.5	213.7	214.5	216.8	219.8
57.5°	190.5	189.6	191.4	190.4	191.4	189.6	190.5	190.6	192.7	193.1	195.7
60°	174.8	172.7	173.8	174.2	173.8	172.7	174.8	175.5	176.1	176.5	179.2
62.5°	156.0	154.9	155.6	154.1	155.6	154.9	156.0	157.6	159.1	160.8	162.4
65°	129.7	128.8	127.3	126.7	127.3	128.8	129.7	130.5	134.1	136.2	139.9
67.5°	109.0	106.6	106.5	107.0	106.5	106.6	109.0	108.9	111.6	113.2	115.7
70°	93.8	93.8	93.5	93.5	93.5	93.8	93.8	95.9	97.2	98.5	100.2
72.5°	83.3	83.0	82.4	82.1	82.4	83.0	83.3	83.9	84.7	86.1	87.8
75°	67.1	67.4	66.7	66.4	66.7	67.4	67.1	67.1	68.4	68.8	69.5
77.5°	49.5	48.1	48.9	48.1	48.9	48.1	49.5	50.9	51.4	52.9	52.9
80°	37.6	37.3	38.3	37.3	38.3	37.3	37.6	37.6	38.6	39.3	41.0
82.5°	29.8	29.4	29.9	29.2	29.9	29.4	29.8	29.4	30.0	30.9	30.7
85°	17.9	17.7	17.3	17.7	17.3	17.7	17.9	17.7	17.3	17.7	17.9
87.5°	9.2	9.0	9.1	9.1	9.1	9.0	9.2	8.8	8.9	8.8	8.6
90°	14.5	15.0	15.4	15.9	15.4	15.0	14.5	14.1	13.6	12.8	12.0
92.5°	30.3	30.6	30.9	31.2	30.9	30.6	30.3	30.0	29.3	28.4	27.4
95°	56.1	56.4	56.6	56.9	56.6	56.4	56.1	55.7	55.1	54.0	53.1
97.5°	85.8	86.0	86.1	86.3	86.1	86.0	85.8	85.6	85.1	84.1	83.1
100°	107.7	108.0	108.3	108.5	108.3	108.0	107.7	107.4	106.6	105.2	103.9
102.5°	129.6	130.0	130.4	130.8	130.4	130.0	129.6	129.1	128.2	126.8	125.4
105°	162.8	163.3	163.7	164.2	163.7	163.3	162.8	162.4	161.8	160.9	160.0
107.5°	198.4	198.4	198.3	198.3	198.3	198.4	198.4	198.4	198.2	197.8	197.3
110°	224.2	224.0	223.9	223.7	223.9	224.0	224.2	224.4	224.2	223.7	223.3



TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	249.4	249.1	248.9	248.6	248.9	249.1	249.4	249.7	249.7	249.5	249.3
115°	288.4	288.3	288.1	287.9	288.1	288.3	288.4	288.6	288.6	288.8	289.0
117.5°	328.1	327.5	326.9	326.4	326.9	327.5	328.1	328.7	329.0	328.8	328.7
120°	354.6	354.0	353.4	352.8	353.4	354.0	354.6	355.2	355.4	355.4	355.4
122.5°	380.7	380.2	379.8	379.3	379.8	380.2	380.7	381.2	381.5	381.6	381.7
125°	419.5	419.3	419.2	419.0	419.2	419.3	419.5	419.6	419.8	420.1	420.4
127.5°	458.1	457.7	457.4	457.2	457.4	457.7	458.1	458.3	458.5	458.7	458.9
130°	483.5	483.1	482.9	482.6	482.9	483.1	483.5	483.8	483.9	484.1	484.3
132.5°	507.7	507.2	506.8	506.4	506.8	507.2	507.7	508.0	508.4	508.5	508.6
135°	545.2	544.7	544.0	543.5	544.0	544.7	545.2	545.8	546.1	546.1	546.1
137.5°	581.9	581.2	580.5	579.7	580.5	581.2	581.9	582.6	583.0	582.8	582.6
140°	605.3	604.5	603.8	603.1	603.8	604.5	605.3	606.0	606.2	605.9	605.6
142.5°	627.5	626.8	626.0	625.3	626.0	626.8	627.5	628.2	628.5	628.3	628.1
145°	660.0	659.5	659.1	658.6	659.1	659.5	660.0	660.4	660.7	660.7	660.7
147.5°	690.1	689.1	688.1	687.2	688.1	689.1	690.1	691.1	691.4	691.1	690.7
150°	709.2	708.9	708.6	708.3	708.6	708.9	709.2	709.4	709.6	709.6	709.6
152.5°	727.4	726.8	726.3	725.8	726.3	726.8	727.4	727.9	728.0	727.6	727.3
155°	752.9	752.2	751.4	750.6	751.4	752.2	752.9	753.6	753.7	753.0	752.5
157.5°	774.4	773.4	772.4	771.4	772.4	773.4	774.4	775.3	775.5	774.9	774.4
160°	787.9	787.2	786.5	785.8	786.5	787.2	787.9	788.7	788.7	788.2	787.6
162.5°	800.5	799.6	798.8	797.9	798.8	799.6	800.5	801.4	801.4	800.7	800.0
165°	816.9	816.0	815.1	814.2	815.1	816.0	816.9	817.7	817.9	817.3	816.7
167.5°	829.9	829.0	828.1	827.2	828.1	829.0	829.9	830.8	830.8	830.0	829.1
170°	837.1	836.2	835.1	834.1	835.1	836.2	837.1	838.2	838.3	837.4	836.5
172.5°	842.7	841.7	840.8	839.9	840.8	841.7	842.7	843.6	843.6	842.7	841.8
175°	848.4	847.4	846.3	845.3	846.3	847.4	848.4	849.4	849.5	848.6	847.7
177.5°	851.0	850.2	849.4	848.5	849.4	850.2	851.0	851.8	851.9	851.1	850.4
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	791.0	794.0	795.6	799.4	804.9	807.5	811.4	814.0	817.9	822.4	826.3
5°	739.8	748.0	753.3	761.8	769.6	777.4	787.2	794.3	803.8	814.7	823.1
7.5°	692.2	702.4	711.4	722.6	735.5	745.5	758.3	771.3	786.2	801.6	816.1
10°	661.9	672.1	683.2	697.1	710.0	723.5	738.8	754.0	772.7	790.0	809.6
12.5°	631.8	643.0	655.6	671.1	686.7	704.0	719.5	736.6	756.7	779.1	800.1
15°	594.5	605.3	618.8	632.0	650.1	669.0	689.6	712.4	734.7	759.8	785.9
17.5°	554.5	566.3	581.3	596.6	615.5	637.7	658.0	682.8	707.9	737.2	767.9
20°	528.4	540.6	558.2	575.2	592.5	614.1	638.2	663.6	690.4	721.1	755.4
22.5°	507.8	516.5	533.9	551.1	571.3	593.5	617.1	643.5	672.7	704.6	740.5
25°	477.2	487.4	500.0	517.9	539.0	562.3	586.0	614.1	646.0	678.5	716.8
27.5°	450.1	458.4	470.8	484.9	505.9	530.1	555.4	584.7	617.3	650.4	690.7
30°	430.9	440.1	451.8	466.8	483.4	509.8	535.6	564.4	597.5	631.8	673.1
32.5°	414.1	423.5	433.7	447.8	465.7	489.2	515.8	544.0	577.7	613.1	653.3
35°	390.6	397.0	406.4	420.4	438.0	456.9	484.0	513.9	546.7	583.3	623.6
37.5°	363.6	371.9	381.4	393.4	408.8	429.4	454.6	484.7	515.2	550.3	587.0
40°	347.9	355.7	366.1	375.0	391.3	409.8	432.9	464.4	494.9	527.7	561.2
42.5°	331.9	339.4	348.3	359.3	373.9	392.0	413.4	442.7	475.4	506.3	534.5
45°	306.9	314.7	323.2	333.3	346.9	364.4	385.8	412.6	441.0	469.5	490.8
47.5°	282.9	290.3	298.3	308.7	321.2	338.2	357.3	380.9	408.6	432.7	448.0
50°	265.9	272.7	281.5	291.7	303.8	319.8	338.0	361.4	384.5	406.4	420.4
52.5°	249.1	256.7	265.5	274.3	286.0	301.8	318.8	338.9	360.9	378.8	390.3
55°	223.9	231.0	239.2	248.3	259.8	273.4	291.3	307.2	324.5	339.7	346.5
57.5°	199.6	205.8	213.5	222.9	233.4	245.9	260.1	275.4	287.7	298.5	306.1
60°	183.6	189.0	196.1	204.3	215.4	226.9	239.8	254.0	263.5	272.7	279.8
62.5°	167.4	172.5	179.3	186.6	196.4	207.1	219.5	231.0	240.2	246.4	254.6
65°	142.9	148.0	153.8	161.6	169.3	178.2	189.3	197.8	204.3	211.1	216.2
67.5°	120.3	124.5	129.9	136.1	142.6	151.1	159.7	166.7	171.2	175.2	181.4
70°	105.3	108.7	113.2	117.9	125.0	133.5	140.3	145.6	148.7	152.8	160.2
72.5°	90.2	94.1	98.3	103.0	108.7	115.8	121.8	127.2	129.2	132.4	137.1
75°	71.2	73.2	76.6	79.9	84.0	90.1	95.9	97.2	98.9	101.7	105.0
77.5°	53.8	55.6	57.0	59.2	62.4	67.3	70.4	72.4	72.9	73.8	77.1
80°	42.7	43.7	45.0	46.7	48.1	52.2	53.9	55.9	56.5	57.6	59.3
82.5°	31.3	32.3	33.2	34.5	36.7	38.3	40.0	42.1	42.2	43.0	43.2
85°	18.3	18.6	17.9	18.6	19.0	19.6	21.3	23.0	22.7	22.4	23.4
87.5°	8.7	8.6	8.1	8.7	8.0	8.0	7.8	7.8	8.2	8.5	8.8
90°	11.3	10.6	9.5	8.6	7.5	6.5	5.4	4.2	3.0	1.9	0.6
92.5°	26.4	25.4	24.2	22.9	21.7	20.3	19.4	18.5	17.7	16.9	16.1
95°	52.0	51.0	49.5	48.1	46.5	45.1	44.2	43.9	43.6	43.3	43.1
97.5°	82.1	81.1	79.1	77.1	75.1	73.0	72.0	71.9	71.7	71.6	71.5
100°	102.6	101.3	99.3	97.5	95.5	93.6	92.6	92.6	92.6	92.6	92.6
102.5°	123.9	122.4	121.5	120.6	119.6	118.6	117.8	117.2	116.6	116.0	115.5
105°	159.1	158.2	157.3	156.4	155.6	154.7	153.9	153.1	152.4	151.7	151.0
107.5°	196.9	196.4	195.8	195.1	194.5	193.8	193.1	192.3	191.6	190.8	190.1
110°	222.8	222.4	221.9	221.5	221.1	220.6	220.1	219.4	218.6	217.8	217.1



TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	249.1	248.9	248.3	247.8	247.2	246.6	246.2	245.8	245.4	245.0	244.7
115°	289.1	289.3	289.0	288.6	288.4	288.1	287.7	287.0	286.5	285.9	285.3
117.5°	328.6	328.5	328.2	328.0	327.7	327.4	327.2	326.9	326.6	326.4	326.1
120°	355.4	355.4	355.3	355.2	355.0	354.9	354.5	353.7	352.9	352.2	351.5
122.5°	381.8	381.9	381.6	381.2	380.8	380.4	380.1	379.9	379.6	379.3	379.1
125°	420.7	421.0	420.9	420.7	420.5	420.4	419.9	419.0	418.1	417.2	416.3
127.5°	459.0	459.1	459.0	458.8	458.6	458.4	458.1	457.6	457.1	456.6	456.1
130°	484.4	484.6	484.3	483.9	483.7	483.4	482.9	482.1	481.4	480.6	479.9
132.5°	508.8	508.9	509.0	509.0	509.1	509.2	508.5	507.4	506.1	505.0	503.7
135°	546.1	546.1	546.0	545.8	545.6	545.5	545.0	544.1	543.2	542.3	541.4
137.5°	582.5	582.3	581.9	581.6	581.3	580.9	580.4	579.5	578.6	577.8	576.9
140°	605.3	605.0	604.6	604.1	603.7	603.2	602.7	601.9	601.2	600.5	599.8
142.5°	627.9	627.8	627.2	626.7	626.2	625.5	625.0	624.4	623.8	623.1	622.5
145°	660.7	660.7	660.2	659.8	659.3	658.9	658.4	657.7	657.2	656.6	656.0
147.5°	690.4	690.0	689.6	689.3	688.9	688.6	688.3	688.0	687.6	687.3	687.0
150°	709.6	709.6	709.0	708.5	707.8	707.3	707.0	707.2	707.3	707.5	707.7
152.5°	726.9	726.6	726.3	726.1	725.9	725.6	725.4	725.2	725.0	724.8	724.6
155°	751.9	751.4	751.2	751.0	750.9	750.7	750.6	750.6	750.6	750.6	750.6
157.5°	773.7	773.2	773.0	772.8	772.8	772.6	772.7	773.0	773.3	773.6	774.0
160°	787.0	786.4	786.2	786.1	786.0	785.8	786.0	786.4	786.8	787.3	787.7
162.5°	799.3	798.6	798.5	798.5	798.5	798.4	798.6	799.0	799.2	799.6	800.0
165°	816.1	815.6	815.4	815.2	815.1	814.9	815.0	815.3	815.6	815.9	816.2
167.5°	828.2	827.3	827.3	827.3	827.3	827.3	827.6	828.2	828.8	829.4	830.0
170°	835.6	834.7	834.7	834.7	834.7	834.7	835.0	835.6	836.2	836.8	837.4
172.5°	840.9	840.0	840.0	840.0	840.0	840.0	840.3	840.9	841.5	842.0	842.7
175°	846.9	846.0	846.0	846.0	846.0	846.0	846.2	846.9	847.5	848.0	848.6
177.5°	849.7	849.0	849.2	849.3	849.4	849.5	849.8	850.2	850.7	851.2	851.7
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	829.2	831.7	835.2	839.3	842.5	846.1	847.9	847.9	849.5	853.1	857.6
5°	831.6	840.4	848.9	859.7	868.2	878.0	885.5	892.6	899.0	907.1	915.6
7.5°	830.9	845.5	860.8	877.9	896.7	911.7	927.0	939.1	951.0	966.6	978.9
10°	828.2	847.2	867.8	889.5	913.2	933.9	952.5	969.5	985.7	1002.6	1017.9
12.5°	823.3	847.5	872.7	898.8	928.7	952.3	976.3	994.4	1013.3	1031.9	1050.7
15°	816.0	844.5	874.9	911.2	947.8	974.2	997.9	1021.3	1038.9	1059.9	1077.9
17.5°	800.9	837.6	875.9	915.5	950.7	981.4	1006.2	1028.5	1047.2	1070.3	1094.8
20°	791.9	831.6	871.6	913.9	947.4	978.9	1003.0	1026.0	1049.4	1079.6	1109.4
22.5°	779.5	821.8	864.2	904.5	939.9	970.3	995.1	1023.3	1054.0	1088.2	1124.3
25°	759.8	803.5	845.5	883.8	918.3	949.5	983.4	1021.3	1058.5	1103.6	1155.4
27.5°	734.8	776.9	814.4	854.8	889.2	928.8	971.1	1012.2	1066.0	1127.9	1192.7
30°	716.0	756.1	791.7	829.9	868.9	912.6	960.0	1008.4	1072.5	1145.2	1222.2
32.5°	694.4	730.6	765.9	802.8	847.7	895.7	946.2	1005.4	1081.9	1164.8	1244.4
35°	656.8	689.3	723.5	764.6	812.3	864.4	928.8	1000.9	1093.4	1182.5	1254.0
37.5°	617.4	643.0	677.4	720.6	772.7	833.0	906.1	993.7	1088.7	1168.7	1199.1
40°	587.0	611.1	647.3	692.7	744.2	810.3	892.2	982.3	1077.9	1133.4	1131.0
42.5°	557.0	581.3	616.2	661.8	715.5	789.4	873.8	967.4	1048.0	1069.2	1025.1
45°	510.8	533.5	567.8	613.8	671.4	748.9	837.7	927.5	978.9	944.8	857.4
47.5°	463.8	485.8	517.5	562.7	625.5	706.8	790.7	864.3	871.6	798.1	693.2
50°	432.9	453.5	483.8	531.8	592.8	672.1	753.0	810.9	793.0	703.2	595.1
52.5°	402.8	422.7	450.9	496.3	558.7	636.3	708.6	754.0	712.5	617.1	519.9
55°	358.4	377.4	405.8	447.5	504.0	575.2	638.6	655.1	594.1	497.9	419.4
57.5°	316.2	330.0	358.2	395.0	449.6	512.3	557.7	554.7	487.4	400.8	344.5
60°	288.3	300.8	327.5	361.4	413.2	469.5	501.3	487.8	419.7	348.2	294.0
62.5°	262.3	273.9	296.4	327.5	372.1	421.0	444.2	425.4	361.1	298.4	255.3
65°	222.9	231.4	249.3	278.1	313.0	346.9	367.6	340.1	283.2	235.8	203.2
67.5°	186.1	193.4	209.4	230.1	254.1	277.5	285.9	260.1	215.9	184.0	161.0
70°	162.3	169.1	179.9	199.2	215.1	231.7	235.8	212.8	175.8	151.4	137.1
72.5°	139.5	145.7	155.2	168.8	179.9	189.4	191.4	169.9	141.7	124.8	113.9
75°	106.4	111.8	117.9	123.0	130.1	131.8	131.1	114.5	99.2	88.1	81.9
77.5°	78.2	80.4	84.2	86.1	86.5	86.4	82.9	72.4	64.6	59.9	57.4
80°	60.3	62.0	63.0	63.7	64.0	60.6	56.9	50.5	47.8	45.0	42.0
82.5°	43.8	44.9	45.9	46.1	44.2	41.4	37.9	34.8	32.8	31.5	30.3
85°	23.7	24.1	23.7	22.0	19.6	18.6	17.9	17.3	16.9	16.6	16.6
87.5°	8.7	8.2	7.0	7.6	7.8	7.8	7.9	7.8	7.8	7.9	8.1
90°	1.9	3.0	4.2	5.4	6.5	7.5	8.6	9.5	10.6	11.3	12.0
92.5°	16.9	17.7	18.5	19.4	20.3	21.7	22.9	24.2	25.4	26.4	27.4
95°	43.3	43.6	43.9	44.2	45.1	46.5	48.1	49.5	51.0	52.0	53.1
97.5°	71.6	71.7	71.9	72.0	73.0	75.1	77.1	79.1	81.1	82.1	83.1
100°	92.6	92.6	92.6	92.6	93.6	95.5	97.5	99.3	101.3	102.6	103.9
102.5°	116.0	116.6	117.2	117.8	118.6	119.6	120.6	121.5	122.4	123.9	125.4
105°	151.7	152.4	153.1	153.9	154.7	155.6	156.4	157.3	158.2	159.1	160.0
107.5°	190.8	191.6	192.3	193.1	193.8	194.5	195.1	195.8	196.4	196.9	197.3
110°	217.8	218.6	219.4	220.1	220.6	221.1	221.5	221.9	222.4	222.8	223.3





TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	245.0	245.4	245.8	246.2	246.6	247.2	247.8	248.3	248.9	249.1	249.3
115°	285.9	286.5	287.0	287.7	288.1	288.4	288.6	289.0	289.3	289.1	289.0
117.5°	326.4	326.6	326.9	327.2	327.4	327.7	328.0	328.2	328.5	328.6	328.7
120°	352.2	352.9	353.7	354.5	354.9	355.0	355.2	355.3	355.4	355.4	355.4
122.5°	379.3	379.6	379.9	380.1	380.4	380.8	381.2	381.6	381.9	381.8	381.7
125°	417.2	418.1	419.0	419.9	420.4	420.5	420.7	420.9	421.0	420.7	420.4
127.5°	456.6	457.1	457.6	458.1	458.4	458.6	458.8	459.0	459.1	459.0	458.9
130°	480.6	481.4	482.1	482.9	483.4	483.7	483.9	484.3	484.6	484.4	484.3
132.5°	505.0	506.1	507.4	508.5	509.2	509.1	509.0	509.0	508.9	508.8	508.6
135°	542.3	543.2	544.1	545.0	545.5	545.6	545.8	546.0	546.1	546.1	546.1
137.5°	577.8	578.6	579.5	580.4	580.9	581.3	581.6	581.9	582.3	582.5	582.6
140°	600.5	601.2	601.9	602.7	603.2	603.7	604.1	604.6	605.0	605.3	605.6
142.5°	623.1	623.8	624.4	625.0	625.5	626.2	626.7	627.2	627.8	627.9	628.1
145°	656.6	657.2	657.7	658.4	658.9	659.3	659.8	660.2	660.7	660.7	660.7
147.5°	687.3	687.6	688.0	688.3	688.6	688.9	689.3	689.6	690.0	690.4	690.7
150°	707.5	707.3	707.2	707.0	707.3	707.8	708.5	709.0	709.6	709.6	709.6
152.5°	724.8	725.0	725.2	725.4	725.6	725.9	726.1	726.3	726.6	726.9	727.3
155°	750.6	750.6	750.6	750.6	750.7	750.9	751.0	751.2	751.4	751.9	752.5
157.5°	773.6	773.3	773.0	772.7	772.6	772.8	772.8	773.0	773.2	773.7	774.4
160°	787.3	786.8	786.4	786.0	785.8	786.0	786.1	786.2	786.4	787.0	787.6
162.5°	799.6	799.2	799.0	798.6	798.4	798.5	798.5	798.5	798.6	799.3	800.0
165°	815.9	815.6	815.3	815.0	814.9	815.1	815.2	815.4	815.6	816.1	816.7
167.5°	829.4	828.8	828.2	827.6	827.3	827.3	827.3	827.3	827.3	828.2	829.1
170°	836.8	836.2	835.6	835.0	834.7	834.7	834.7	834.7	834.7	835.6	836.5
172.5°	842.0	841.5	840.9	840.3	840.0	840.0	840.0	840.0	840.0	840.9	841.8
175°	848.0	847.5	846.9	846.2	846.0	846.0	846.0	846.0	846.0	846.9	847.7
177.5°	851.2	850.7	850.2	849.8	849.5	849.4	849.3	849.2	849.0	849.7	850.4
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	861.2	861.2	865.9	865.5	868.5	867.5	868.0
5°	925.8	931.5	936.6	940.0	945.0	946.5	945.7
7.5°	992.7	1005.5	1011.7	1020.3	1021.8	1026.3	1025.8
10°	1034.1	1046.7	1056.1	1063.6	1067.4	1072.1	1072.5
12.5°	1066.7	1077.3	1085.7	1092.6	1097.2	1098.7	1099.6
15°	1092.1	1103.9	1113.7	1123.6	1129.4	1133.7	1136.1
17.5°	1117.7	1136.0	1153.3	1166.7	1174.7	1181.4	1181.3
20°	1137.5	1158.5	1180.2	1195.4	1210.9	1217.7	1218.8
22.5°	1158.6	1190.7	1218.6	1242.2	1262.8	1269.8	1272.4
25°	1202.5	1244.5	1287.5	1320.7	1344.4	1358.3	1360.4
27.5°	1255.5	1312.4	1357.6	1388.3	1408.0	1418.3	1420.5
30°	1293.0	1345.4	1386.1	1409.2	1418.3	1419.6	1414.5
32.5°	1309.7	1349.0	1365.2	1363.9	1345.9	1334.0	1329.5
35°	1289.2	1281.1	1241.4	1194.0	1157.8	1134.8	1128.6
37.5°	1173.2	1103.1	1030.2	958.6	920.4	901.1	867.7
40°	1058.9	958.9	883.1	822.8	779.8	745.2	737.1
42.5°	929.9	826.7	750.8	699.2	664.9	641.1	630.9
45°	747.3	658.5	595.8	556.2	529.8	512.5	504.7
47.5°	597.6	529.0	483.3	454.0	433.8	418.8	414.6
50°	515.6	460.7	422.0	397.3	382.1	370.6	365.9
52.5°	447.8	403.5	373.8	353.5	339.0	331.8	327.9
55°	369.5	331.3	310.0	293.6	285.5	279.8	277.1
57.5°	302.2	274.6	259.0	247.7	240.2	236.6	235.2
60°	264.6	242.9	228.6	219.8	214.7	210.0	208.7
62.5°	231.2	214.2	203.1	195.5	190.4	188.3	187.5
65°	186.3	175.1	167.0	162.3	158.2	157.5	157.2
67.5°	148.1	141.5	137.2	132.3	130.9	128.5	128.0
70°	126.7	122.3	117.2	115.5	113.8	111.5	111.8
72.5°	107.5	103.1	99.6	97.4	96.8	95.8	96.6
75°	78.6	77.2	75.9	74.2	73.5	73.5	73.2
77.5°	56.1	54.9	53.4	52.4	52.3	50.8	51.4
80°	40.7	39.0	38.3	38.6	37.6	37.3	37.3
82.5°	30.1	29.4	28.8	28.9	28.6	28.4	28.6
85°	16.6	16.2	16.2	16.0	16.0	15.6	15.6
87.5°	8.6	8.9	8.5	8.3	8.4	8.7	9.1
90°	12.8	13.6	14.1	14.5	15.0	15.4	15.9
92.5°	28.4	29.3	30.0	30.3	30.6	30.9	31.2
95°	54.0	55.1	55.7	56.1	56.4	56.6	56.9
97.5°	84.1	85.1	85.6	85.8	86.0	86.1	86.3
100°	105.2	106.6	107.4	107.7	108.0	108.3	108.5
102.5°	126.8	128.2	129.1	129.6	130.0	130.4	130.8
105°	160.9	161.8	162.4	162.8	163.3	163.7	164.2
107.5°	197.8	198.2	198.4	198.4	198.4	198.3	198.3
110°	223.7	224.2	224.4	224.2	224.0	223.9	223.7



TEST NUMBER: P333665-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	249.5	249.7	249.7	249.4	249.1	248.9	248.6
115°	288.8	288.6	288.6	288.4	288.3	288.1	287.9
117.5°	328.8	329.0	328.7	328.1	327.5	326.9	326.4
120°	355.4	355.4	355.2	354.6	354.0	353.4	352.8
122.5°	381.6	381.5	381.2	380.7	380.2	379.8	379.3
125°	420.1	419.8	419.6	419.5	419.3	419.2	419.0
127.5°	458.7	458.5	458.3	458.1	457.7	457.4	457.2
130°	484.1	483.9	483.8	483.5	483.1	482.9	482.6
132.5°	508.5	508.4	508.0	507.7	507.2	506.8	506.4
135°	546.1	546.1	545.8	545.2	544.7	544.0	543.5
137.5°	582.8	583.0	582.6	581.9	581.2	580.5	579.7
140°	605.9	606.2	606.0	605.3	604.5	603.8	603.1
142.5°	628.3	628.5	628.2	627.5	626.8	626.0	625.3
145°	660.7	660.7	660.4	660.0	659.5	659.1	658.6
147.5°	691.1	691.4	691.1	690.1	689.1	688.1	687.2
150°	709.6	709.6	709.4	709.2	708.9	708.6	708.3
152.5°	727.6	728.0	727.9	727.4	726.8	726.3	725.8
155°	753.0	753.7	753.6	752.9	752.2	751.4	750.6
157.5°	774.9	775.5	775.3	774.4	773.4	772.4	771.4
160°	788.2	788.7	788.7	787.9	787.2	786.5	785.8
162.5°	800.7	801.4	801.4	800.5	799.6	798.8	797.9
165°	817.3	817.9	817.7	816.9	816.0	815.1	814.2
167.5°	830.0	830.8	830.8	829.9	829.0	828.1	827.2
170°	837.4	838.3	838.2	837.1	836.2	835.1	834.1
172.5°	842.7	843.6	843.6	842.7	841.7	840.8	839.9
175°	848.6	849.5	849.4	848.4	847.4	846.3	845.3
177.5°	851.1	851.9	851.8	851.0	850.2	849.4	848.5
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6

(END OF REPORT)