

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742623

Luminaire Tested: LD4D10D010-EU4DR600210IC9040-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P742623
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D10D010-EU4DR600210IC9040-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 984.7 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P742623

CATALOG NUMBER: LD4D10D010-EU4DR600210IC9040-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P742623

CATALOG NUMBER: LD4D10D010-EU4DR600210IC9040-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127759
5°	130912
10°	132481
15°	126214
20°	111285
25°	90007
30°	60874
35°	30505
40°	4949
45°	4836
50°	4929
55°	5029
60°	5157
65°	5274
70°	5399
75°	5446
80°	5285
85°	4388

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 5446 cd/sqm



TEST NUMBER: P742623

CATALOG NUMBER: LD4D10D010-EU4DR600210IC9040-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.1	11.6
10°-20°	308.6	31.3
20°-30°	332.1	33.7
30°-40°	144.4	14.7
40°-50°	24.2	2.5
50°-60°	23.6	2.4
60°-70°	20.2	2.0
70°-80°	13.5	1.4
80°-90°	4.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	754.8	76.7
0°-40°	899.1	91.3
0°-60°	947.0	96.2
0°-90°	984.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	984.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1169	
5°	1194	114
15°	1116	309
25°	747	332
35°	229	144
45°	31	24
55°	26	24
65°	20	20
75°	13	13
85°	4	4
90°	0	



TEST NUMBER: P742623

CATALOG NUMBER: LD4D10D010-EU4DR600210IC9040-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1169.3
2.5°	1202.2
5°	1193.6
7.5°	1196.3
10°	1194.1
12.5°	1169.5
15°	1115.8
17.5°	1043.7
20°	957.1
22.5°	864.4
25°	746.6
27.5°	597.2
30°	482.5
32.5°	372.0
35°	228.7
37.5°	97.9
40°	34.7
42.5°	32.0
45°	31.3
47.5°	30.3
50°	29.0
52.5°	27.7
55°	26.4
57.5°	25.0
60°	23.6
62.5°	22.1
65°	20.4
67.5°	18.7
70°	16.9
72.5°	14.9
75°	12.9
77.5°	10.7
80°	8.4
82.5°	6.0
85°	3.5
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)