

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743591

Luminaire Tested: LD4D15D010-EU4DR600215IC9030-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P743591
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR600215IC9030-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1219.5 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743591
CATALOG NUMBER: LD4D15D010-EU4DR600215IC9030-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P743591

CATALOG NUMBER: LD4D15D010-EU4DR600215IC9030-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158253
5°	162137
10°	164101
15°	156325
20°	137830
25°	111478
30°	75408
35°	37787
40°	6133
45°	5995
50°	6119
55°	6210
60°	6381
65°	6541
70°	6677
75°	6754
80°	6544
85°	5516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 6754 cd/sqm



TEST NUMBER: P743591

CATALOG NUMBER: LD4D15D010-EU4DR600215IC9030-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.3	11.6
10°-20°	382.3	31.3
20°-30°	411.3	33.7
30°-40°	178.8	14.7
40°-50°	30.0	2.5
50°-60°	29.2	2.4
60°-70°	25.0	2.0
70°-80°	16.7	1.4
80°-90°	5.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	934.9	76.7
0°-40°	1113.6	91.3
0°-60°	1172.9	96.2
0°-90°	1219.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1219.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1448	
5°	1478	141
15°	1382	382
25°	925	411
35°	283	179
45°	39	30
55°	33	29
65°	25	25
75°	16	17
85°	4	5
90°	0	



TEST NUMBER: P743591

CATALOG NUMBER: LD4D15D010-EU4DR600215IC9030-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1448.4
2.5°	1489.1
5°	1478.3
7.5°	1481.8
10°	1479.1
12.5°	1448.6
15°	1382.0
17.5°	1292.7
20°	1185.4
22.5°	1070.6
25°	924.7
27.5°	739.6
30°	597.7
32.5°	460.7
35°	283.3
37.5°	121.2
40°	43.0
42.5°	39.6
45°	38.8
47.5°	37.5
50°	36.0
52.5°	34.3
55°	32.6
57.5°	30.9
60°	29.2
62.5°	27.3
65°	25.3
67.5°	23.2
70°	20.9
72.5°	18.4
75°	16.0
77.5°	13.2
80°	10.4
82.5°	7.3
85°	4.4
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)