

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742935

Luminaire Tested: LD4D15D010-EU4DR1515309040-4LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P742935  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D15D010-EU4DR1515309040-4LBS1MW  
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 15° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1471.2 lumens  
Efficiency: N/A  
Efficacy: 93.1 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23  
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P742935  
CATALOG NUMBER: LD4D15D010-EU4DR1515309040-4LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P742935

CATALOG NUMBER: LD4D15D010-EU4DR1515309040-4LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	99	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2255609	2255609	2255609
5°	1325505	1308340	1318696
10°	395606	398377	404470
15°	98400	100320	97219
20°	29440	34096	30070
25°	10376	13220	10509
30°	3811	5017	3879
35°	1910	2157	1852
40°	1207	1328	1207
45°	889	952	889
50°	709	709	709
55°	592	592	592
60°	477	477	477
65°	364	364	364
70°	307	307	307
75°	189	189	257
80°	134	134	134
85°	66	66	66

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 952 cd/sqm



TEST NUMBER: P742935

CATALOG NUMBER: LD4D15D010-EU4DR1515309040-4LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	954.2	64.9
10°-20°	392.5	26.7
20°-30°	78.0	5.3
30°-40°	19.5	1.3
40°-50°	10.2	0.7
50°-60°	7.6	0.5
60°-70°	5.3	0.4
70°-80°	3.0	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1424.7	96.8
0°-40°	1444.2	98.2
0°-60°	1462.0	99.4
0°-90°	1471.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1471.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	20046	20046	20046	20046	20046	
5°	13043	12908	12874	12963	12976	952
15°	1133	1154	1155	1135	1119	388
25°	133	151	170	150	135	70
35°	26	28	30	28	26	18
45°	13	13	14	13	13	10
55°	8	8	8	8	8	8
65°	5	5	5	5	5	5
75°	2	2	2	2	3	3
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P742935

CATALOG NUMBER: LD4D15D010-EU4DR1515309040-4LBS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	20046.3	20046.3	20046.3	20046.3	20046.3
2.5°	18082.6	18097.9	18103.8	18121.6	18187.8
5°	13042.6	12908.5	12873.7	12962.8	12975.6
7.5°	7725.9	7753.1	7852.4	7874.4	7794.7
10°	4239.8	4274.5	4269.5	4300.0	4334.8
12.5°	2168.2	2141.1	2132.6	2167.4	2119.0
15°	1132.9	1154.1	1155.0	1134.6	1119.3
17.5°	609.3	633.9	674.7	641.6	590.6
20°	359.8	381.9	416.7	389.5	367.5
22.5°	222.3	240.2	264.8	243.6	225.7
25°	133.2	151.1	169.7	150.2	134.9
27.5°	78.9	94.2	106.1	93.3	78.1
30°	50.9	59.4	67.0	58.6	51.8
32.5°	35.6	39.0	42.4	39.0	35.6
35°	26.3	28.0	29.7	28.0	25.5
37.5°	20.4	22.1	22.9	21.2	19.5
40°	17.0	17.8	18.7	17.8	17.0
42.5°	14.4	15.3	15.3	15.3	14.4
45°	12.7	12.7	13.6	12.7	12.7
47.5°	11.0	11.0	11.9	11.0	11.0
50°	10.2	10.2	10.2	10.2	10.2
52.5°	9.3	9.3	9.3	9.3	9.3
55°	8.5	8.5	8.5	8.5	8.5
57.5°	7.6	7.6	7.6	7.6	7.6
60°	6.8	6.8	6.8	6.8	6.8
62.5°	5.9	5.9	5.9	5.9	5.9
65°	5.1	5.1	5.1	5.1	5.1
67.5°	5.1	5.1	5.1	5.1	5.1
70°	4.2	4.2	4.2	4.2	4.2
72.5°	3.4	3.4	3.4	3.4	3.4
75°	2.5	2.5	2.5	2.5	3.4
77.5°	2.5	2.5	2.5	2.5	2.5
80°	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7
85°	0.8	0.8	0.8	0.8	0.8
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)