

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739539

Luminaire Tested: LD4D02D010-EU4DR600210IC9027-4LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P739539  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D02D010-EU4DR600210IC9027-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 266.5 lumens  
Efficiency: N/A  
Efficacy: 52.3 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P739539

CATALOG NUMBER: LD4D02D010-EU4DR600210IC9027-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P739539

CATALOG NUMBER: LD4D02D010-EU4DR600210IC9027-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80		
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62		
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	34592
5°	35437
10°	35869
15°	34172
20°	30126
25°	24364
30°	16477
35°	8256
40°	1341
45°	1313
50°	1326
55°	1352
60°	1399
65°	1422
70°	1470
75°	1478
80°	1447
85°	1254

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 1478 cd/sqm



TEST NUMBER: P739539

CATALOG NUMBER: LD4D02D010-EU4DR600210IC9027-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	30.9	11.6
10°-20°	83.6	31.3
20°-30°	89.9	33.7
30°-40°	39.1	14.7
40°-50°	6.6	2.5
50°-60°	6.4	2.4
60°-70°	5.4	2.0
70°-80°	3.7	1.4
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	204.3	76.7
0°-40°	243.4	91.3
0°-60°	256.3	96.2
0°-90°	266.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	266.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	317	
5°	323	31
15°	302	84
25°	202	90
35°	62	39
45°	8	7
55°	7	6
65°	6	5
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P739539

CATALOG NUMBER: LD4D02D010-EU4DR600210IC9027-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	316.6
2.5°	325.4
5°	323.1
7.5°	323.8
10°	323.3
12.5°	316.6
15°	302.1
17.5°	282.5
20°	259.1
22.5°	234.0
25°	202.1
27.5°	161.6
30°	130.6
32.5°	100.7
35°	61.9
37.5°	26.5
40°	9.4
42.5°	8.7
45°	8.5
47.5°	8.2
50°	7.8
52.5°	7.5
55°	7.1
57.5°	6.8
60°	6.4
62.5°	6.0
65°	5.5
67.5°	5.0
70°	4.6
72.5°	4.0
75°	3.5
77.5°	2.9
80°	2.3
82.5°	1.6
85°	1.0
87.5°	0.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)