

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745503

Luminaire Tested: LD4D25D010-EU4DR6020359024-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P745503
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR6020359024-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1887.9 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745503

CATALOG NUMBER: LD4D25D010-EU4DR6020359024-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P745503

CATALOG NUMBER: LD4D25D010-EU4DR6020359024-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	244984
5°	251009
10°	254034
15°	242010
20°	213372
25°	172588
30°	116739
35°	58502
40°	9485
45°	9287
50°	9468
55°	9620
60°	9877
65°	10109
70°	10350
75°	10469
80°	10067
85°	8399

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 10469 cd/sqm



TEST NUMBER: P745503

CATALOG NUMBER: LD4D25D010-EU4DR6020359024-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.7	11.6
10°-20°	591.8	31.3
20°-30°	636.7	33.7
30°-40°	276.8	14.7
40°-50°	46.5	2.5
50°-60°	45.2	2.4
60°-70°	38.7	2.0
70°-80°	25.9	1.4
80°-90°	7.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1447.2	76.7
0°-40°	1724.0	91.3
0°-60°	1815.7	96.2
0°-90°	1887.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1887.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2242	
5°	2289	219
15°	2140	592
25°	1432	637
35°	439	277
45°	60	46
55°	50	45
65°	39	39
75°	25	26
85°	7	8
90°	0	



TEST NUMBER: P745503

CATALOG NUMBER: LD4D25D010-EU4DR6020359024-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2242.2
2.5°	2305.2
5°	2288.6
7.5°	2293.8
10°	2289.7
12.5°	2242.5
15°	2139.5
17.5°	2001.1
20°	1835.1
22.5°	1657.4
25°	1431.6
27.5°	1145.0
30°	925.3
32.5°	713.2
35°	438.6
37.5°	187.6
40°	66.5
42.5°	61.3
45°	60.1
47.5°	58.0
50°	55.7
52.5°	53.1
55°	50.5
57.5°	47.8
60°	45.2
62.5°	42.3
65°	39.1
67.5°	35.9
70°	32.4
72.5°	28.6
75°	24.8
77.5°	20.5
80°	16.0
82.5°	11.4
85°	6.7
87.5°	2.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)