

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748913

Luminaire Tested: LD4D45BD010-EU4DR6540509040-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P748913
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR6540509040-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3820.3 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P748913

CATALOG NUMBER: LD4D45BD010-EU4DR6540509040-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P748913

CATALOG NUMBER: LD4D45BD010-EU4DR6540509040-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	202591
5°	202081
10°	201909
15°	195680
20°	178147
25°	155240
30°	129119
35°	102305
40°	73839
45°	46650
50°	24314
55°	12921
60°	6787
65°	3731
70°	1571
75°	1715
80°	1211
85°	1005

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 46650 cd/sqm



TEST NUMBER: P748913

CATALOG NUMBER: LD4D45BD010-EU4DR6540509040-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.0	8.6
10°-20°	898.3	23.5
20°-30°	1098.0	28.7
30°-40°	890.9	23.3
40°-50°	443.9	11.6
50°-60°	123.8	3.2
60°-70°	28.2	0.7
70°-80°	7.3	0.2
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2324.3	60.8
0°-40°	3215.2	84.2
0°-60°	3783.0	99.0
0°-90°	3820.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3820.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3469	
5°	3447	328
15°	3236	898
25°	2409	1098
35°	1435	891
45°	565	444
55°	127	124
65°	27	28
75°	8	7
85°	2	2
90°	0	



TEST NUMBER: P748913

CATALOG NUMBER: LD4D45BD010-EU4DR6540509040-4LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3468.8
2.5°	3466.2
5°	3446.9
7.5°	3435.6
10°	3404.6
12.5°	3341.3
15°	3236.3
17.5°	3072.2
20°	2866.3
22.5°	2644.0
25°	2409.0
27.5°	2157.7
30°	1914.6
32.5°	1674.5
35°	1434.9
37.5°	1195.8
40°	968.5
42.5°	755.4
45°	564.8
47.5°	393.5
50°	267.6
52.5°	184.5
55°	126.9
57.5°	85.6
60°	58.1
62.5°	40.3
65°	27.0
67.5°	13.8
70°	9.2
72.5°	8.7
75°	7.6
77.5°	5.1
80°	3.6
82.5°	2.5
85°	1.5
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)