

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753235

Luminaire Tested: LD4D75BD010-EU4DR4570959027-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753235
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR4570959027-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6282.8 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753235

CATALOG NUMBER: LD4D75BD010-EU4DR4570959027-4LBDP1B

Luminous Intensity Polar Plot



TEST NUMBER: P753235

CATALOG NUMBER: LD4D75BD010-EU4DR4570959027-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95		
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90		
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85		
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81		
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77		
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73		
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69		
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66		
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63		
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1213330
5°	1178776
10°	1127769
15°	1032152
20°	818852
25°	511217
30°	281773
35°	126527
40°	49835
45°	23487
50°	11134
55°	5829
60°	2863
65°	672
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23487 cd/sqm

TEST NUMBER: P753235

CATALOG NUMBER: LD4D75BD010-EU4DR4570959027-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1009.8	16.1
10°-20°	2485.3	39.6
20°-30°	1968.1	31.3
30°-40°	655.4	10.4
40°-50°	130.1	2.1
50°-60°	29.6	0.5
60°-70°	4.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5463.3	87.0
0°-40°	6118.8	97.4
0°-60°	6278.4	99.9
0°-90°	6282.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6282.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11105	
5°	10748	###
15°	9125	2485
25°	4240	1968
35°	949	655
45°	152	130
55°	31	30
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753235

CATALOG NUMBER: LD4D75BD010-EU4DR4570959027-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	11104.9
2.5°	11032.4
5°	10747.6
7.5°	10512.7
10°	10165.0
12.5°	9702.1
15°	9124.8
17.5°	8256.6
20°	7042.5
22.5°	5596.1
25°	4240.5
27.5°	3105.1
30°	2233.4
32.5°	1518.9
35°	948.6
37.5°	562.5
40°	349.4
42.5°	229.7
45°	152.0
47.5°	97.8
50°	65.5
52.5°	43.7
55°	30.6
57.5°	20.1
60°	13.1
62.5°	7.0
65°	2.6
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)