

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748708

Luminaire Tested: LD4D45BD010-EU4DR5540509027-4LBCSSQMB

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P748708
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR5540509027-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4020.1 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748708

CATALOG NUMBER: LD4D45BD010-EU4DR5540509027-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P748708
 CATALOG NUMBER: LD4D45BD010-EU4DR5540509027-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			94	
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87			87	
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			81	
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75			75	
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			70	
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65			65	
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61			61	
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			57	
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54			54	
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50			50	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	492526
5°	472965
10°	471189
15°	457652
20°	410350
25°	339136
30°	256175
35°	185749
40°	118868
45°	54298
50°	17763
55°	7658
60°	3300
65°	440
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 54298 cd/sqm



TEST NUMBER: P748708

CATALOG NUMBER: LD4D45BD010-EU4DR5540509027-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	410.3	10.2
10°-20°	1119.9	27.9
20°-30°	1276.2	31.7
30°-40°	868.8	21.6
40°-50°	299.4	7.4
50°-60°	41.4	1.0
60°-70°	4.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2806.5	69.8
0°-40°	3675.3	91.4
0°-60°	4016.1	99.9
0°-90°	4020.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4020.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4508	
5°	4312	410
15°	4046	1120
25°	2813	1276
35°	1393	869
45°	351	299
55°	40	41
65°	2	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P748708

CATALOG NUMBER: LD4D45BD010-EU4DR5540509027-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	4507.8
2.5°	4404.5
5°	4312.3
7.5°	4267.1
10°	4247.0
12.5°	4179.9
15°	4045.9
17.5°	3833.1
20°	3529.2
22.5°	3178.4
25°	2813.1
27.5°	2432.7
30°	2030.5
32.5°	1689.7
35°	1392.6
37.5°	1109.9
40°	833.4
42.5°	577.6
45°	351.4
47.5°	189.4
50°	104.5
52.5°	62.0
55°	40.2
57.5°	25.7
60°	15.1
62.5°	6.7
65°	1.7
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)