

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751125

Luminaire Tested: LD4D60D010-EU4DR6055659024-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P751125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6055659024-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4647.5 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P751125

CATALOG NUMBER: LD4D60D010-EU4DR6055659024-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P751125

CATALOG NUMBER: LD4D60D010-EU4DR6055659024-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80		
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62		
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	603065
5°	617894
10°	625360
15°	595743
20°	525263
25°	424839
30°	287375
35°	144000
40°	23363
45°	22869
50°	23321
55°	23678
60°	24321
65°	24897
70°	25461
75°	25793
80°	24854
85°	20685

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 25793 cd/sqm



TEST NUMBER: P751125

CATALOG NUMBER: LD4D60D010-EU4DR6055659024-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	538.4	11.6
10°-20°	1456.8	31.3
20°-30°	1567.4	33.7
30°-40°	681.3	14.7
40°-50°	114.4	2.5
50°-60°	111.3	2.4
60°-70°	95.2	2.0
70°-80°	63.7	1.4
80°-90°	19.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3562.6	76.7
0°-40°	4243.9	91.3
0°-60°	4469.6	96.2
0°-90°	4647.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4647.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5520	
5°	5634	538
15°	5267	1457
25°	3524	1567
35°	1080	681
45°	148	114
55°	124	111
65°	96	95
75°	61	64
85°	16	19
90°	0	



TEST NUMBER: P751125

CATALOG NUMBER: LD4D60D010-EU4DR6055659024-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5519.5
2.5°	5674.7
5°	5633.7
7.5°	5646.6
10°	5636.6
12.5°	5520.2
15°	5266.7
17.5°	4926.2
20°	4517.5
22.5°	4080.0
25°	3524.0
27.5°	2818.7
30°	2277.8
32.5°	1755.6
35°	1079.6
37.5°	461.9
40°	163.8
42.5°	150.8
45°	148.0
47.5°	142.9
50°	137.2
52.5°	130.7
55°	124.3
57.5°	117.8
60°	111.3
62.5°	104.2
65°	96.3
67.5°	88.4
70°	79.7
72.5°	70.4
75°	61.1
77.5°	50.3
80°	39.5
82.5°	28.0
85°	16.5
87.5°	5.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)