

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751256

Luminaire Tested: LD4D60D010-EU4DR6555659050-4LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P751256
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6555659050-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5640.4 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P751256
CATALOG NUMBER: LD4D60D010-EU4DR6555659050-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P751256
 CATALOG NUMBER: LD4D60D010-EU4DR6555659050-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	299104
5°	298353
10°	298096
15°	288904
20°	263015
25°	229199
30°	190630
35°	151045
40°	109017
45°	68876
50°	35899
55°	19082
60°	10022
65°	5514
70°	2305
75°	2550
80°	1783
85°	1541

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 68876 cd/sqm



TEST NUMBER: P751256

CATALOG NUMBER: LD4D60D010-EU4DR6555659050-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	484.3	8.6
10°-20°	1326.2	23.5
20°-30°	1621.1	28.7
30°-40°	1315.3	23.3
40°-50°	655.5	11.6
50°-60°	182.8	3.2
60°-70°	41.6	0.7
70°-80°	10.8	0.2
80°-90°	2.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3431.7	60.8
0°-40°	4747.0	84.2
0°-60°	5585.3	99.0
0°-90°	5640.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5640.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5121	
5°	5089	484
15°	4778	1326
25°	3557	1621
35°	2118	1315
45°	834	655
55°	187	183
65°	40	42
75°	11	11
85°	2	3
90°	0	



TEST NUMBER: P751256

CATALOG NUMBER: LD4D60D010-EU4DR6555659050-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

0°	
0°	5121.3
2.5°	5117.6
5°	5089.0
7.5°	5072.4
10°	5026.5
12.5°	4933.2
15°	4778.1
17.5°	4535.8
20°	4231.8
22.5°	3903.6
25°	3556.7
27.5°	3185.7
30°	2826.7
32.5°	2472.2
35°	2118.5
37.5°	1765.6
40°	1429.9
42.5°	1115.3
45°	833.9
47.5°	581.0
50°	395.1
52.5°	272.4
55°	187.4
57.5°	126.4
60°	85.8
62.5°	59.5
65°	39.9
67.5°	20.3
70°	13.5
72.5°	12.8
75°	11.3
77.5°	7.5
80°	5.3
82.5°	3.8
85°	2.3
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)