

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752113

Luminaire Tested: LD4D65D010-EU4DR7055659040-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P752113
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR7055659040-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5845.2 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P752113

CATALOG NUMBER: LD4D65D010-EU4DR7055659040-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P752113

CATALOG NUMBER: LD4D65D010-EU4DR7055659040-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	718018
5°	696686
10°	677272
15°	668386
20°	624129
25°	468878
30°	331457
35°	117403
40°	61730
45°	65763
50°	68094
55°	69377
60°	69796
65°	68330
70°	64498
75°	59734
80°	53042
85°	42999

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 69831 cd/sqm



TEST NUMBER: P752113

CATALOG NUMBER: LD4D65D010-EU4DR7055659040-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	599.1	10.3
10°-20°	1643.4	28.1
20°-30°	1810.0	31.0
30°-40°	691.5	11.8
40°-50°	326.5	5.6
50°-60°	324.6	5.6
60°-70°	259.9	4.4
70°-80°	149.4	2.6
80°-90°	40.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4052.6	69.3
0°-40°	4744.1	81.2
0°-60°	5395.3	92.3
0°-90°	5845.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5845.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6572	
5°	6352	599
15°	5909	1643
25°	3889	1810
35°	880	692
45°	426	327
55°	364	325
65°	264	260
75°	142	149
85°	34	41
90°	0	



TEST NUMBER: P752113

CATALOG NUMBER: LD4D65D010-EU4DR7055659040-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6571.6
2.5°	6503.0
5°	6352.1
7.5°	6226.2
10°	6104.5
12.5°	6001.5
15°	5908.9
17.5°	5685.2
20°	5367.8
22.5°	4683.2
25°	3889.3
27.5°	3385.7
30°	2627.2
32.5°	1697.0
35°	880.2
37.5°	475.5
40°	432.8
42.5°	429.7
45°	425.6
47.5°	416.2
50°	400.6
52.5°	382.9
55°	364.2
57.5°	343.4
60°	319.4
62.5°	292.4
65°	264.3
67.5°	233.1
70°	201.9
72.5°	170.6
75°	141.5
77.5°	111.3
80°	84.3
82.5°	59.3
85°	34.3
87.5°	13.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)