

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753621

Luminaire Tested: LD4D75BD010-EU4DR7070959024-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P753621
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR7070959024-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5101.4 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P753621
CATALOG NUMBER: LD4D75BD010-EU4DR7070959024-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P753621

CATALOG NUMBER: LD4D75BD010-EU4DR7070959024-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65		
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61		
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57		
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53		
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50		
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	626654
5°	608034
10°	591088
15°	583323
20°	544703
25°	409215
30°	289280
35°	102465
40°	53886
45°	57388
50°	59425
55°	60538
60°	60924
65°	59644
70°	56288
75°	52136
80°	46310
85°	37609

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 60944 cd/sqm



TEST NUMBER: P753621

CATALOG NUMBER: LD4D75BD010-EU4DR7070959024-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	522.9	10.3
10°-20°	1434.3	28.1
20°-30°	1579.7	31.0
30°-40°	603.6	11.8
40°-50°	285.0	5.6
50°-60°	283.3	5.6
60°-70°	226.9	4.4
70°-80°	130.4	2.6
80°-90°	35.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3536.9	69.3
0°-40°	4140.4	81.2
0°-60°	4708.7	92.3
0°-90°	5101.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5101.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5735	
5°	5544	523
15°	5157	1434
25°	3394	1580
35°	768	604
45°	371	285
55°	318	283
65°	231	227
75°	124	130
85°	30	35
90°	0	



TEST NUMBER: P753621

CATALOG NUMBER: LD4D75BD010-EU4DR7070959024-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5735.4
2.5°	5675.5
5°	5543.8
7.5°	5433.9
10°	5327.7
12.5°	5237.8
15°	5156.9
17.5°	4961.7
20°	4684.7
22.5°	4087.2
25°	3394.4
27.5°	2954.9
30°	2292.9
32.5°	1481.1
35°	768.2
37.5°	415.0
40°	377.8
42.5°	375.0
45°	371.4
47.5°	363.2
50°	349.6
52.5°	334.2
55°	317.8
57.5°	299.7
60°	278.8
62.5°	255.2
65°	230.7
67.5°	203.4
70°	176.2
72.5°	148.9
75°	123.5
77.5°	97.2
80°	73.6
82.5°	51.8
85°	30.0
87.5°	11.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)