

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839282

Luminaire Tested: **LD4C40D010 EU4409027 4LBSH**

Issue Date: 2/14/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P839282  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C40D010 EU4409027 4LBSH  
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 4LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3802.0 lumens  
Efficiency: N/A  
Efficacy: 80.9 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 47  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839282

CATALOG NUMBER: LD4C40D010 EU4409027 4LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P839282

CATALOG NUMBER: LD4C40D010 EU4409027 4LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			77
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			67
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			58
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			51
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			41
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			34
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			31

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	244282
5°	243155
10°	238133
15°	229484
20°	218921
25°	207113
30°	195368
35°	183946
40°	173204
45°	161458
50°	147224
55°	130012
60°	110052
65°	86395
70°	61675
75°	33796
80°	5943
85°	0



TEST NUMBER: P839282

CATALOG NUMBER: LD4C40D010 EU4409027 4LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	186.3	4.9
10°-20°	506.2	13.3
20°-30°	703.0	18.5
30°-40°	767.2	20.2
40°-50°	715.7	18.8
50°-60°	543.2	14.3
60°-70°	297.4	7.8
70°-80°	81.9	2.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1395.5	36.7
0°-40°	2162.7	56.9
0°-60°	3421.6	90.0
0°-90°	3802.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3802.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1988	
5°	1972	186
15°	1804	506
25°	1528	703
35°	1226	767
45°	929	716
55°	607	543
65°	297	297
75°	71	82
85°	0	1
90°	0	



TEST NUMBER: P839282

CATALOG NUMBER: LD4C40D010 EU4409027 4LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1988.4
2.5°	1988.4
5°	1971.7
7.5°	1946.6
10°	1908.9
12.5°	1858.7
15°	1804.3
17.5°	1737.3
20°	1674.5
22.5°	1599.1
25°	1527.9
27.5°	1456.8
30°	1377.2
32.5°	1301.9
35°	1226.5
37.5°	1151.2
40°	1080.0
42.5°	1004.7
45°	929.3
47.5°	854.0
50°	770.3
52.5°	690.7
55°	607.0
57.5°	527.4
60°	447.9
62.5°	368.4
65°	297.2
67.5°	230.2
70°	171.7
72.5°	117.2
75°	71.2
77.5°	33.5
80°	8.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)