

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839358

Luminaire Tested: **LD4C65D010 EU4659027 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P839358
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C65D010 EU4659027 4LBSLI
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6573.0 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839358

CATALOG NUMBER: LD4C65D010 EU4659027 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839358

CATALOG NUMBER: LD4C65D010 EU4659027 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			71
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			57
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	576588
5°	563536
10°	529196
15°	492342
20°	456628
25°	416245
30°	370578
35°	328478
40°	295232
45°	264225
50°	226676
55°	182360
60°	135876
65°	86744
70°	41811
75°	6930
80°	5094
85°	0



TEST NUMBER: P839358

CATALOG NUMBER: LD4C65D010 EU4659027 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	425.6	6.5
10°-20°	1085.3	16.5
20°-30°	1406.4	21.4
30°-40°	1378.0	21.0
40°-50°	1168.0	17.8
50°-60°	765.7	11.6
60°-70°	307.8	4.7
70°-80°	35.2	0.5
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2917.3	44.4
0°-40°	4295.3	65.3
0°-60°	6229.1	94.8
0°-90°	6573.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6573.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4693	
5°	4570	426
15°	3871	1085
25°	3071	1406
35°	2190	1378
45°	1521	1168
55°	851	766
65°	298	308
75°	15	35
85°	0	1
90°	0	



TEST NUMBER: P839358

CATALOG NUMBER: LD4C65D010 EU4659027 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4693.3
2.5°	4656.9
5°	4569.6
7.5°	4424.0
10°	4242.1
12.5°	4045.7
15°	3871.0
17.5°	3682.0
20°	3492.7
22.5°	3289.0
25°	3070.7
27.5°	2845.1
30°	2612.3
32.5°	2394.0
35°	2190.2
37.5°	2022.9
40°	1840.9
42.5°	1680.9
45°	1520.8
47.5°	1353.4
50°	1186.0
52.5°	1018.8
55°	851.4
57.5°	698.5
60°	553.0
62.5°	422.0
65°	298.4
67.5°	196.5
70°	116.4
72.5°	50.9
75°	14.6
77.5°	7.2
80°	7.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)