

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839367

Luminaire Tested: **LD4C65D010 EU4659040 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P839367
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C65D010 EU4659040 4LBSLI
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6940.0 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839367

CATALOG NUMBER: LD4C65D010 EU4659040 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839367

CATALOG NUMBER: LD4C65D010 EU4659040 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	608788
5°	594995
10°	558749
15°	519840
20°	482122
25°	439493
30°	391275
35°	346820
40°	311719
45°	278993
50°	239328
55°	192534
60°	143444
65°	91598
70°	44146
75°	7310
80°	5377
85°	0



TEST NUMBER: P839367

CATALOG NUMBER: LD4C65D010 EU4659040 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	449.3	6.5
10°-20°	1145.9	16.5
20°-30°	1484.9	21.4
30°-40°	1455.0	21.0
40°-50°	1233.3	17.8
50°-60°	808.4	11.6
60°-70°	324.9	4.7
70°-80°	37.1	0.5
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3080.2	44.4
0°-40°	4535.2	65.3
0°-60°	6576.9	94.8
0°-90°	6940.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6940.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4955	
5°	4825	449
15°	4087	1146
25°	3242	1485
35°	2312	1455
45°	1606	1233
55°	899	808
65°	315	325
75°	15	37
85°	0	1
90°	0	



TEST NUMBER: P839367

CATALOG NUMBER: LD4C65D010 EU4659040 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4955.4
2.5°	4916.9
5°	4824.7
7.5°	4671.0
10°	4479.0
12.5°	4271.6
15°	4087.2
17.5°	3887.5
20°	3687.7
22.5°	3472.7
25°	3242.2
27.5°	3003.9
30°	2758.2
32.5°	2527.7
35°	2312.5
37.5°	2135.9
40°	1943.7
42.5°	1774.7
45°	1605.8
47.5°	1429.0
50°	1252.2
52.5°	1075.6
55°	898.9
57.5°	737.5
60°	583.8
62.5°	445.5
65°	315.1
67.5°	207.4
70°	122.9
72.5°	53.7
75°	15.4
77.5°	7.6
80°	7.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)