

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839391

Luminaire Tested: **LD4C75D010 EU4759030 4LBSLI**

Issue Date: 2/9/2022

Test Information

Test Method: LM-79-08
Report Number: P839391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C75D010 EU4759030 4LBSLI
Description: 4 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8439.0 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839391

CATALOG NUMBER: LD4C75D010 EU4759030 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839391

CATALOG NUMBER: LD4C75D010 EU4759030 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80																			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71																			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63																			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57																			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51																			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39																			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	740278
5°	723510
10°	679431
15°	632121
20°	586268
25°	534421
30°	475781
35°	421719
40°	379044
45°	339247
50°	291028
55°	234108
60°	174427
65°	111366
70°	53664
75°	8924
80°	6580
85°	0



TEST NUMBER: P839391

CATALOG NUMBER: LD4C75D010 EU4759030 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	546.4	6.5
10°-20°	1393.5	16.5
20°-30°	1805.7	21.4
30°-40°	1769.2	21.0
40°-50°	1499.6	17.8
50°-60°	983.1	11.6
60°-70°	395.1	4.7
70°-80°	45.2	0.5
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3745.5	44.4
0°-40°	5514.8	65.3
0°-60°	7997.5	94.8
0°-90°	8439.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8439.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6026	
5°	5867	546
15°	4970	1393
25°	3942	1806
35°	2812	1769
45°	1953	1500
55°	1093	983
65°	383	395
75°	19	45
85°	0	1
90°	0	



TEST NUMBER: P839391

CATALOG NUMBER: LD4C75D010 EU4759030 4LBSLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6025.7
2.5°	5979.0
5°	5866.8
7.5°	5679.9
10°	5446.4
12.5°	5194.2
15°	4970.0
17.5°	4727.2
20°	4484.3
22.5°	4222.8
25°	3942.5
27.5°	3652.7
30°	3353.9
32.5°	3073.7
35°	2811.9
37.5°	2597.2
40°	2363.5
42.5°	2158.1
45°	1952.6
47.5°	1737.7
50°	1522.7
52.5°	1308.0
55°	1093.0
57.5°	896.9
60°	709.9
62.5°	541.8
65°	383.1
67.5°	252.2
70°	149.4
72.5°	65.3
75°	18.8
77.5°	9.3
80°	9.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)