

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839427

Luminaire Tested: **LD4C90D010 EU4909040 4LBSLI**

Issue Date: 2/9/2022

Test Information

Test Method: LM-79-08
Report Number: P839427
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C90D010 EU4909040 4LBSLI
Description: 4 INCH 9000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9859.9 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839427

CATALOG NUMBER: LD4C90D010 EU4909040 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839427

CATALOG NUMBER: LD4C90D010 EU4909040 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			71
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			57
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	864938
5°	845340
10°	793838
15°	738564
20°	684988
25°	624402
30°	555903
35°	492732
40°	442872
45°	396373
50°	340032
55°	273540
60°	203814
65°	130116
70°	62716
75°	10395
80°	7641
85°	0



TEST NUMBER: P839427

CATALOG NUMBER: LD4C90D010 EU4909040 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	638.4	6.5
10°-20°	1628.1	16.5
20°-30°	2109.7	21.4
30°-40°	2067.1	21.0
40°-50°	1752.1	17.8
50°-60°	1148.6	11.6
60°-70°	461.7	4.7
70°-80°	52.7	0.5
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4376.2	44.4
0°-40°	6443.3	65.3
0°-60°	9344.1	94.8
0°-90°	9859.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9859.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7040	
5°	6855	638
15°	5807	1628
25°	4606	2110
35°	3285	2067
45°	2281	1752
55°	1277	1149
65°	448	462
75°	22	53
85°	0	1
90°	0	



TEST NUMBER: P839427

CATALOG NUMBER: LD4C90D010 EU4909040 4LBSLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	7040.4
2.5°	6985.7
5°	6854.7
7.5°	6636.3
10°	6363.5
12.5°	6068.8
15°	5806.9
17.5°	5523.2
20°	5239.4
22.5°	4933.8
25°	4606.3
27.5°	4267.8
30°	3918.7
32.5°	3591.2
35°	3285.4
37.5°	3034.5
40°	2761.5
42.5°	2521.4
45°	2281.4
47.5°	2030.2
50°	1779.1
52.5°	1528.2
55°	1277.1
57.5°	1047.9
60°	829.5
62.5°	633.0
65°	447.6
67.5°	294.7
70°	174.6
72.5°	76.3
75°	21.9
77.5°	10.8
80°	10.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)