

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840005

Luminaire Tested: **LDS4C40D010 EU4409027 4LBSWMH**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P840005  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C40D010 EU4409027 4LBSWMH  
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 4LBS TRIM WITH WMH FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3376.0 lumens  
Efficiency: N/A  
Efficacy: 71.8 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 47  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P840005

CATALOG NUMBER: LDS4C40D010 EU4409027 4LBSWMH

### Luminous Intensity Polar Plot





TEST NUMBER: P840005

CATALOG NUMBER: LDS4C40D010 EU4409027 4LBSWMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	216910
5°	215913
10°	211449
15°	203767
20°	194381
25°	183906
30°	173479
35°	163339
40°	153798
45°	143371
50°	130730
55°	115448
60°	97718
65°	76715
70°	54742
75°	29999
80°	5306
85°	0



TEST NUMBER: P840005

CATALOG NUMBER: LDS4C40D010 EU4409027 4LBSWMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	165.4	4.9
10°-20°	449.5	13.3
20°-30°	624.3	18.5
30°-40°	681.2	20.2
40°-50°	635.5	18.8
50°-60°	482.3	14.3
60°-70°	264.1	7.8
70°-80°	72.7	2.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1239.2	36.7
0°-40°	1920.4	56.9
0°-60°	3038.2	90.0
0°-90°	3376.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3376.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1766	
5°	1751	165
15°	1602	450
25°	1357	624
35°	1089	681
45°	825	635
55°	539	482
65°	264	264
75°	63	73
85°	0	1
90°	0	



TEST NUMBER: P840005

CATALOG NUMBER: LDS4C40D010 EU4409027 4LBSWMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1765.6
2.5°	1765.6
5°	1750.8
7.5°	1728.5
10°	1695.0
12.5°	1650.5
15°	1602.1
17.5°	1542.7
20°	1486.8
22.5°	1419.9
25°	1356.7
27.5°	1293.6
30°	1222.9
32.5°	1156.0
35°	1089.1
37.5°	1022.2
40°	959.0
42.5°	892.1
45°	825.2
47.5°	758.3
50°	684.0
52.5°	613.3
55°	539.0
57.5°	468.3
60°	397.7
62.5°	327.1
65°	263.9
67.5°	204.4
70°	152.4
72.5°	104.1
75°	63.2
77.5°	29.7
80°	7.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)