

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840015

Luminaire Tested: **LDS4C40D010 EU4409030 4LBSWMH**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P840015  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C40D010 EU4409030 4LBSWMH  
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 4LBS TRIM WITH WMH FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3510.0 lumens  
Efficiency: N/A  
Efficacy: 74.7 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 47  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P840015

CATALOG NUMBER: LDS4C40D010 EU4409030 4LBSWMH

### Luminous Intensity Polar Plot





TEST NUMBER: P840015

CATALOG NUMBER: LDS4C40D010 EU4409030 4LBSWMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	225522
5°	224484
10°	219845
15°	211856
20°	202108
25°	191212
30°	180374
35°	169818
40°	159909
45°	149052
50°	135910
55°	120031
60°	101600
65°	79767
70°	56933
75°	31186
80°	5518
85°	0



TEST NUMBER: P840015

CATALOG NUMBER: LDS4C40D010 EU4409030 4LBSWMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.9	4.9
10°-20°	467.4	13.3
20°-30°	649.0	18.5
30°-40°	708.3	20.2
40°-50°	660.7	18.8
50°-60°	501.5	14.3
60°-70°	274.6	7.8
70°-80°	75.6	2.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1288.4	36.7
0°-40°	1996.6	56.9
0°-60°	3158.8	90.0
0°-90°	3510.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3510.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1836	
5°	1820	172
15°	1666	467
25°	1411	649
35°	1132	708
45°	858	661
55°	560	501
65°	274	275
75°	66	76
85°	0	1
90°	0	



TEST NUMBER: P840015

CATALOG NUMBER: LDS4C40D010 EU4409030 4LBSWMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1835.7
2.5°	1835.7
5°	1820.3
7.5°	1797.1
10°	1762.3
12.5°	1716.0
15°	1665.7
17.5°	1603.9
20°	1545.9
22.5°	1476.3
25°	1410.6
27.5°	1344.9
30°	1271.5
32.5°	1201.9
35°	1132.3
37.5°	1062.8
40°	997.1
42.5°	927.5
45°	857.9
47.5°	788.4
50°	711.1
52.5°	637.6
55°	560.4
57.5°	486.9
60°	413.5
62.5°	340.1
65°	274.4
67.5°	212.5
70°	158.5
72.5°	108.2
75°	65.7
77.5°	30.9
80°	7.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)