

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858133

Luminaire Tested: **LX4C45D010 EX4C459030 4LBSH**

Issue Date: 2/14/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P858133  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C45D010 EX4C459030 4LBSH  
Description: 4 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 4LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4576.0 lumens  
Efficiency: N/A  
Efficacy: 92.3 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 49.6  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858133

CATALOG NUMBER: LX4C45D010 EX4C459030 4LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P858133

CATALOG NUMBER: LX4C45D010 EX4C459030 4LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	294013
5°	292657
10°	286610
15°	276200
20°	263476
25°	249283
30°	235145
35°	221395
40°	208470
45°	194329
50°	177193
55°	156486
60°	132461
65°	103982
70°	74211
75°	40679
80°	7146
85°	0



TEST NUMBER: P858133

CATALOG NUMBER: LX4C45D010 EX4C459030 4LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	224.2	4.9
10°-20°	609.3	13.3
20°-30°	846.2	18.5
30°-40°	923.3	20.2
40°-50°	861.4	18.8
50°-60°	653.8	14.3
60°-70°	358.0	7.8
70°-80°	98.5	2.2
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1679.6	36.7
0°-40°	2603.0	56.9
0°-60°	4118.1	90.0
0°-90°	4576.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4576.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2393	
5°	2373	224
15°	2172	609
25°	1839	846
35°	1476	923
45°	1118	861
55°	731	654
65°	358	358
75°	86	99
85°	0	1
90°	0	



TEST NUMBER: P858133

CATALOG NUMBER: LX4C45D010 EX4C459030 4LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2393.2
2.5°	2393.2
5°	2373.1
7.5°	2342.9
10°	2297.5
12.5°	2237.1
15°	2171.6
17.5°	2091.0
20°	2015.3
22.5°	1924.7
25°	1839.0
27.5°	1753.4
30°	1657.6
32.5°	1566.9
35°	1476.2
37.5°	1385.5
40°	1299.9
42.5°	1209.2
45°	1118.5
47.5°	1027.8
50°	927.1
52.5°	831.3
55°	730.6
57.5°	634.8
60°	539.1
62.5°	443.4
65°	357.7
67.5°	277.1
70°	206.6
72.5°	141.1
75°	85.7
77.5°	40.3
80°	10.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)