

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859245

Luminaire Tested: **LX4C60D010 EX4C609040 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P859245
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C60D010 EX4C609040 4LBSH
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6362.1 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859245

CATALOG NUMBER: LX4C60D010 EX4C609040 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P859245

CATALOG NUMBER: LX4C60D010 EX4C609040 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	408770
5°	406879
10°	398472
15°	383991
20°	366315
25°	346570
30°	326928
35°	307812
40°	289828
45°	270167
50°	246362
55°	217573
60°	184157
65°	144592
70°	103198
75°	56533
80°	9976
85°	0



TEST NUMBER: P859245

CATALOG NUMBER: LX4C60D010 EX4C609040 4LSBH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.7	4.9
10°-20°	847.1	13.3
20°-30°	1176.4	18.5
30°-40°	1283.7	20.2
40°-50°	1197.5	18.8
50°-60°	909.0	14.3
60°-70°	497.7	7.8
70°-80°	137.0	2.2
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2335.2	36.7
0°-40°	3618.9	56.9
0°-60°	5725.4	90.0
0°-90°	6362.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6362.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3327	
5°	3299	312
15°	3019	847
25°	2557	1176
35°	2052	1284
45°	1555	1198
55°	1016	909
65°	497	498
75°	119	137
85°	0	2
90°	0	



TEST NUMBER: P859245

CATALOG NUMBER: LX4C60D010 EX4C609040 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3327.3
2.5°	3327.3
5°	3299.3
7.5°	3257.4
10°	3194.2
12.5°	3110.2
15°	3019.1
17.5°	2907.1
20°	2801.9
22.5°	2675.8
25°	2556.7
27.5°	2437.8
30°	2304.6
32.5°	2178.5
35°	2052.4
37.5°	1926.3
40°	1807.2
42.5°	1681.1
45°	1555.0
47.5°	1429.0
50°	1289.0
52.5°	1155.8
55°	1015.8
57.5°	882.6
60°	749.5
62.5°	616.5
65°	497.4
67.5°	385.2
70°	287.3
72.5°	196.2
75°	119.1
77.5°	56.0
80°	14.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)