

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859269

Luminaire Tested: **LX4C60D010 EX4C609050 4LBWH**

Issue Date: 2/8/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P859269  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C60D010 EX4C609050 4LBWH  
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 4LBW TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver:


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5525.0 lumens  
Efficiency: N/A  
Efficacy: 76.7 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 72  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859269

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P859269

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	437506
5°	439177
10°	440513
15°	440526
20°	438116
25°	427848
30°	399886
35°	346296
40°	270519
45°	194086
50°	126086
55°	75480
60°	44178
65°	28372
70°	18858
75°	14240
80°	10612
85°	0



TEST NUMBER: P859269

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	339.1	6.1
10°-20°	977.2	17.7
20°-30°	1442.0	26.1
30°-40°	1423.0	25.8
40°-50°	870.8	15.8
50°-60°	333.8	6.0
60°-70°	104.4	1.9
70°-80°	30.6	0.6
80°-90°	4.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2758.3	49.9
0°-40°	4181.3	75.7
0°-60°	5385.9	97.5
0°-90°	5525.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5525.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3561	
5°	3561	339
15°	3464	977
25°	3156	1442
35°	2309	1423
45°	1117	871
55°	352	334
65°	98	104
75°	30	31
85°	0	4
90°	0	



TEST NUMBER: P859269

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3561.2
2.5°	3568.7
5°	3561.2
7.5°	3553.7
10°	3531.2
12.5°	3501.2
15°	3463.6
17.5°	3418.6
20°	3351.1
22.5°	3276.4
25°	3156.3
27.5°	3006.2
30°	2818.9
32.5°	2586.6
35°	2309.0
37.5°	2001.6
40°	1686.8
42.5°	1394.5
45°	1117.1
47.5°	869.5
50°	659.7
52.5°	487.4
55°	352.4
57.5°	247.3
60°	179.8
62.5°	135.1
65°	97.6
67.5°	75.0
70°	52.5
72.5°	37.5
75°	30.0
77.5°	15.0
80°	15.0
82.5°	7.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)