

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859273

Luminaire Tested: **LX4C60D010 EX4C609727 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859273
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C60D010 EX4C609727 4LBWH
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 97CRI LEDS
AND 4LBW TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5128.0 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859273

CATALOG NUMBER: LX4C60D010 EX4C609727 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P859273

CATALOG NUMBER: LX4C60D010 EX4C609727 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	406068
5°	407619
10°	408851
15°	408882
20°	406634
25°	397105
30°	371160
35°	321414
40°	251081
45°	180152
50°	117026
55°	70040
60°	40984
65°	26308
70°	17529
75°	13243
80°	9834
85°	0



TEST NUMBER: P859273

CATALOG NUMBER: LX4C60D010 EX4C609727 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	314.8	6.1
10°-20°	907.0	17.7
20°-30°	1338.4	26.1
30°-40°	1320.8	25.8
40°-50°	808.3	15.8
50°-60°	309.8	6.0
60°-70°	96.9	1.9
70°-80°	28.4	0.6
80°-90°	3.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2560.1	49.9
0°-40°	3880.8	75.7
0°-60°	4998.9	97.5
0°-90°	5128.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5128.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3305	
5°	3305	315
15°	3215	907
25°	2930	1338
35°	2143	1321
45°	1037	808
55°	327	310
65°	90	97
75°	28	28
85°	0	4
90°	0	



TEST NUMBER: P859273

CATALOG NUMBER: LX4C60D010 EX4C609727 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3305.3
2.5°	3312.3
5°	3305.3
7.5°	3298.3
10°	3277.4
12.5°	3249.6
15°	3214.8
17.5°	3173.0
20°	3110.3
22.5°	3040.9
25°	2929.5
27.5°	2790.2
30°	2616.4
32.5°	2400.8
35°	2143.1
37.5°	1857.8
40°	1565.6
42.5°	1294.3
45°	1036.9
47.5°	807.0
50°	612.3
52.5°	452.4
55°	327.0
57.5°	229.5
60°	166.8
62.5°	125.4
65°	90.5
67.5°	69.7
70°	48.8
72.5°	34.8
75°	27.9
77.5°	13.9
80°	13.9
82.5°	7.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)