

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859376

Luminaire Tested: **LX4C65D010 EX4C659035 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P859376
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C65D010 EX4C659035 4LBSLI
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6930.0 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859376

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P859376

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 102 | 100 | 98 | 98 | 96 | 95 | 95 | 93 | 92 | 90 |
| 2 | 104 | 98 | 93 | 88 | 102 | 96 | 91 | 87 | 93 | 89 | 85 | 90 | 86 | 84 | 87 | 84 | 82 | 80 |
| 3 | 97 | 89 | 82 | 77 | 95 | 87 | 81 | 77 | 84 | 79 | 75 | 82 | 78 | 74 | 79 | 76 | 73 | 71 |
| 4 | 90 | 81 | 73 | 68 | 88 | 79 | 73 | 68 | 77 | 71 | 67 | 75 | 70 | 66 | 73 | 69 | 65 | 63 |
| 5 | 84 | 73 | 66 | 61 | 82 | 72 | 65 | 60 | 70 | 64 | 60 | 69 | 63 | 59 | 67 | 62 | 59 | 57 |
| 6 | 79 | 67 | 60 | 54 | 77 | 66 | 59 | 54 | 65 | 58 | 54 | 63 | 58 | 53 | 62 | 57 | 53 | 51 |
| 7 | 74 | 62 | 54 | 49 | 72 | 61 | 54 | 49 | 60 | 53 | 49 | 58 | 53 | 48 | 57 | 52 | 48 | 46 |
| 8 | 69 | 57 | 50 | 45 | 68 | 57 | 50 | 45 | 55 | 49 | 45 | 54 | 49 | 44 | 53 | 48 | 44 | 42 |
| 9 | 65 | 53 | 46 | 41 | 64 | 53 | 46 | 41 | 52 | 45 | 41 | 51 | 45 | 41 | 50 | 44 | 41 | 39 |
| 10 | 61 | 50 | 43 | 38 | 60 | 49 | 42 | 38 | 48 | 42 | 38 | 47 | 42 | 38 | 46 | 41 | 37 | 36 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 607916 |
| 5° | 594144 |
| 10° | 557951 |
| 15° | 519089 |
| 20° | 481429 |
| 25° | 438855 |
| 30° | 390708 |
| 35° | 346311 |
| 40° | 311270 |
| 45° | 278576 |
| 50° | 238984 |
| 55° | 192256 |
| 60° | 143247 |
| 65° | 91453 |
| 70° | 44074 |
| 75° | 7310 |
| 80° | 5377 |
| 85° | 0 |



TEST NUMBER: P859376

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBSLI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 448.7 | 6.5 |
| 10°-20° | 1144.3 | 16.5 |
| 20°-30° | 1482.8 | 21.4 |
| 30°-40° | 1452.9 | 21.0 |
| 40°-50° | 1231.5 | 17.8 |
| 50°-60° | 807.3 | 11.6 |
| 60°-70° | 324.5 | 4.7 |
| 70°-80° | 37.1 | 0.5 |
| 80°-90° | 1.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 3075.8 | 44.4 |
| 0°-40° | 4528.7 | 65.3 |
| 0°-60° | 6567.4 | 94.8 |
| 0°-90° | 6930.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 6930.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4948 | |
| 5° | 4818 | 449 |
| 15° | 4081 | 1144 |
| 25° | 3238 | 1483 |
| 35° | 2309 | 1453 |
| 45° | 1603 | 1231 |
| 55° | 898 | 807 |
| 65° | 315 | 324 |
| 75° | 15 | 37 |
| 85° | 0 | 1 |
| 90° | 0 | |



TEST NUMBER: P859376

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBSLI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 4948.3 |
| 2.5° | 4909.8 |
| 5° | 4817.8 |
| 7.5° | 4664.3 |
| 10° | 4472.6 |
| 12.5° | 4265.4 |
| 15° | 4081.3 |
| 17.5° | 3881.9 |
| 20° | 3682.4 |
| 22.5° | 3467.7 |
| 25° | 3237.5 |
| 27.5° | 2999.6 |
| 30° | 2754.2 |
| 32.5° | 2524.1 |
| 35° | 2309.1 |
| 37.5° | 2132.8 |
| 40° | 1940.9 |
| 42.5° | 1772.2 |
| 45° | 1603.4 |
| 47.5° | 1426.9 |
| 50° | 1250.4 |
| 52.5° | 1074.1 |
| 55° | 897.6 |
| 57.5° | 736.5 |
| 60° | 583.0 |
| 62.5° | 444.9 |
| 65° | 314.6 |
| 67.5° | 207.1 |
| 70° | 122.7 |
| 72.5° | 53.6 |
| 75° | 15.4 |
| 77.5° | 7.6 |
| 80° | 7.6 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)