

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859378

Luminaire Tested: **LX4C65D010 EX4C659035 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C65D010 EX4C659035 4LBWH
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBW TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5654.0 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859378

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P859378

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	447715
5°	449425
10°	450792
15°	450815
20°	448340
25°	437839
30°	409235
35°	354379
40°	276837
45°	198621
50°	129029
55°	77236
60°	45210
65°	29011
70°	19325
75°	14572
80°	10895
85°	0



TEST NUMBER: P859378

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.0	6.1
10°-20°	1000.0	17.7
20°-30°	1475.6	26.1
30°-40°	1456.2	25.8
40°-50°	891.1	15.8
50°-60°	341.6	6.0
60°-70°	106.8	1.9
70°-80°	31.3	0.6
80°-90°	4.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2822.7	49.9
0°-40°	4278.9	75.7
0°-60°	5511.7	97.5
0°-90°	5654.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5654.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3644	
5°	3644	347
15°	3544	1000
25°	3230	1476
35°	2363	1456
45°	1143	891
55°	361	342
65°	100	107
75°	31	31
85°	0	4
90°	0	



TEST NUMBER: P859378

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3644.3
2.5°	3652.0
5°	3644.3
7.5°	3636.7
10°	3613.6
12.5°	3582.9
15°	3544.5
17.5°	3498.4
20°	3429.3
22.5°	3352.9
25°	3230.0
27.5°	3076.4
30°	2884.8
32.5°	2647.0
35°	2362.9
37.5°	2048.4
40°	1726.2
42.5°	1427.0
45°	1143.2
47.5°	889.8
50°	675.1
52.5°	498.8
55°	360.6
57.5°	253.1
60°	184.0
62.5°	138.2
65°	99.8
67.5°	76.8
70°	53.8
72.5°	38.4
75°	30.7
77.5°	15.4
80°	15.4
82.5°	7.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)