

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859392

Luminaire Tested: **LX4C65D010 EX4C659040 4LBMH**

Issue Date: 2/8/2022

Test Information

Test Method: LM-79-08
Report Number: P859392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C65D010 EX4C659040 4LBMH
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBM TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5094.0 lumens
Efficiency: N/A
Efficacy: 70.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859392

CATALOG NUMBER: LX4C65D010 EX4C659040 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P859392

CATALOG NUMBER: LX4C65D010 EX4C659040 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	403377
5°	404918
10°	406144
15°	406160
20°	403941
25°	394475
30°	368691
35°	319285
40°	249413
45°	178953
50°	116243
55°	69590
60°	40714
65°	26134
70°	17385
75°	13148
80°	9763
85°	0



TEST NUMBER: P859392

CATALOG NUMBER: LX4C65D010 EX4C659040 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	312.7	6.1
10°-20°	901.0	17.7
20°-30°	1329.5	26.1
30°-40°	1312.0	25.8
40°-50°	802.9	15.8
50°-60°	307.8	6.0
60°-70°	96.2	1.9
70°-80°	28.2	0.6
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2543.1	49.9
0°-40°	3855.1	75.7
0°-60°	4965.8	97.5
0°-90°	5094.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5094.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3283	
5°	3283	313
15°	3193	901
25°	2910	1329
35°	2129	1312
45°	1030	803
55°	325	308
65°	90	96
75°	28	28
85°	0	4
90°	0	



TEST NUMBER: P859392

CATALOG NUMBER: LX4C65D010 EX4C659040 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3283.4
2.5°	3290.3
5°	3283.4
7.5°	3276.5
10°	3255.7
12.5°	3228.0
15°	3193.4
17.5°	3151.9
20°	3089.7
22.5°	3020.8
25°	2910.1
27.5°	2771.7
30°	2599.0
32.5°	2384.9
35°	2128.9
37.5°	1845.5
40°	1555.2
42.5°	1285.7
45°	1030.0
47.5°	801.7
50°	608.2
52.5°	449.4
55°	324.9
57.5°	228.0
60°	165.7
62.5°	124.5
65°	89.9
67.5°	69.2
70°	48.4
72.5°	34.6
75°	27.7
77.5°	13.8
80°	13.8
82.5°	6.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)