

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757935

Luminaire Tested: LD6D05D010-EU6DR150210IC9030-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P757935  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D05D010-EU6DR150210IC9030-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 15° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 667.4 lumens  
Efficiency: N/A  
Efficacy: 89.0 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23  
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P757935  
CATALOG NUMBER: LD6D05D010-EU6DR150210IC9030-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P757935

CATALOG NUMBER: LD6D05D010-EU6DR150210IC9030-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1023155	1023155	1023155
5°	601257	593462	598157
10°	179449	180699	183471
15°	44636	45504	44097
20°	13353	15465	13640
25°	4705	5998	4768
30°	1730	2276	1760
35°	864	980	835
40°	547	604	547
45°	406	434	406
50°	320	320	320
55°	264	264	264
60°	218	218	218
65°	164	164	164
70°	139	139	139
75°	91	91	113
80°	63	63	63
85°	33	33	33

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 434 cd/sqm



TEST NUMBER: P757935

CATALOG NUMBER: LD6D05D010-EU6DR150210IC9030-6LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	432.8	64.9
10°-20°	178.0	26.7
20°-30°	35.4	5.3
30°-40°	8.8	1.3
40°-50°	4.6	0.7
50°-60°	3.4	0.5
60°-70°	2.4	0.4
70°-80°	1.4	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	646.2	96.8
0°-40°	655.1	98.2
0°-60°	663.1	99.4
0°-90°	667.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	667.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	9093	9093	9093	9093	9093	
5°	5916	5855	5840	5880	5886	432
15°	514	524	524	515	508	176
25°	60	68	77	68	61	32
35°	12	13	14	13	12	8
45°	6	6	6	6	6	5
55°	4	4	4	4	4	3
65°	2	2	2	2	2	2
75°	1	1	1	1	2	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P757935

CATALOG NUMBER: LD6D05D010-EU6DR150210IC9030-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	9093.1	9093.1	9093.1	9093.1	9093.1
2.5°	8202.3	8209.2	8211.9	8220.0	8250.0
5°	5916.2	5855.3	5839.5	5880.0	5885.7
7.5°	3504.5	3516.8	3561.9	3571.9	3535.7
10°	1923.2	1938.9	1936.6	1950.5	1966.3
12.5°	983.5	971.2	967.4	983.1	961.2
15°	513.9	523.5	523.9	514.7	507.7
17.5°	276.4	287.6	306.0	291.0	267.9
20°	163.2	173.2	189.0	176.7	166.7
22.5°	100.9	108.9	120.1	110.5	102.4
25°	60.4	68.5	77.0	68.1	61.2
27.5°	35.8	42.7	48.1	42.3	35.4
30°	23.1	26.9	30.4	26.6	23.5
32.5°	16.2	17.7	19.2	17.7	16.2
35°	11.9	12.7	13.5	12.7	11.5
37.5°	9.2	10.0	10.4	9.6	8.9
40°	7.7	8.1	8.5	8.1	7.7
42.5°	6.5	6.9	6.9	6.9	6.5
45°	5.8	5.8	6.2	5.8	5.8
47.5°	5.0	5.0	5.4	5.0	5.0
50°	4.6	4.6	4.6	4.6	4.6
52.5°	4.2	4.2	4.2	4.2	4.2
55°	3.8	3.8	3.8	3.8	3.8
57.5°	3.5	3.5	3.5	3.5	3.5
60°	3.1	3.1	3.1	3.1	3.1
62.5°	2.7	2.7	2.7	2.7	2.7
65°	2.3	2.3	2.3	2.3	2.3
67.5°	2.3	2.3	2.3	2.3	2.3
70°	1.9	1.9	1.9	1.9	1.9
72.5°	1.5	1.5	1.5	1.5	1.5
75°	1.2	1.2	1.2	1.2	1.5
77.5°	1.2	1.2	1.2	1.2	1.2
80°	0.8	0.8	0.8	0.8	0.8
82.5°	0.8	0.8	0.8	0.8	0.8
85°	0.4	0.4	0.4	0.4	0.4
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)