

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P758714

Luminaire Tested: LD6D05D010-EU6DR650210IC9030-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P758714  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D05D010-EU6DR650210IC9030-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 640.0 lumens  
Efficiency: N/A  
Efficacy: 85.3 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P758714  
CATALOG NUMBER: LD6D05D010-EU6DR650210IC9030-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P758714

CATALOG NUMBER: LD6D05D010-EU6DR650210IC9030-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	33938
5°	33851
10°	33822
15°	32784
20°	29845
25°	26009
30°	21628
35°	17140
40°	12374
45°	7814
50°	4071
55°	2169
60°	1133
65°	622
70°	256
75°	293
80°	202
85°	134

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7814 cd/sqm



TEST NUMBER: P758714

CATALOG NUMBER: LD6D05D010-EU6DR650210IC9030-6LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.0	8.6
10°-20°	150.5	23.5
20°-30°	183.9	28.7
30°-40°	149.2	23.3
40°-50°	74.4	11.6
50°-60°	20.7	3.2
60°-70°	4.7	0.7
70°-80°	1.2	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	389.4	60.8
0°-40°	538.6	84.2
0°-60°	633.7	99.0
0°-90°	640.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	640.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	581	
5°	577	55
15°	542	150
25°	404	184
35°	240	149
45°	95	74
55°	21	21
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P758714

CATALOG NUMBER: LD6D05D010-EU6DR650210IC9030-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	581.1
2.5°	580.7
5°	577.4
7.5°	575.5
10°	570.3
12.5°	559.8
15°	542.2
17.5°	514.7
20°	480.2
22.5°	442.9
25°	403.6
27.5°	361.5
30°	320.7
32.5°	280.5
35°	240.4
37.5°	200.3
40°	162.3
42.5°	126.6
45°	94.6
47.5°	65.9
50°	44.8
52.5°	30.9
55°	21.3
57.5°	14.3
60°	9.7
62.5°	6.8
65°	4.5
67.5°	2.3
70°	1.5
72.5°	1.4
75°	1.3
77.5°	0.9
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)