

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769339

Luminaire Tested: LD6D60D010-EU6DR7055659024-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P769339
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR7055659024-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4837.3 lumens
Efficiency: N/A
Efficacy: 75.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P769339
CATALOG NUMBER: LD6D60D010-EU6DR7055659024-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P769339

CATALOG NUMBER: LD6D60D010-EU6DR7055659024-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65		
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61		
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57		
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53		
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50		
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	594215
5°	576556
10°	560489
15°	553133
20°	516507
25°	388033
30°	274305
35°	97169
40°	51090
45°	54421
50°	56348
55°	57414
60°	57755
65°	56541
70°	53349
75°	49434
80°	43856
85°	35603

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 57793 cd/sqm



TEST NUMBER: P769339

CATALOG NUMBER: LD6D60D010-EU6DR7055659024-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	495.8	10.3
10°-20°	1360.0	28.1
20°-30°	1497.9	31.0
30°-40°	572.3	11.8
40°-50°	270.2	5.6
50°-60°	268.7	5.6
60°-70°	215.1	4.4
70°-80°	123.6	2.6
80°-90°	33.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3353.8	69.3
0°-40°	3926.1	81.2
0°-60°	4465.0	92.3
0°-90°	4837.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4837.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5438	
5°	5257	496
15°	4890	1360
25°	3219	1498
35°	728	572
45°	352	270
55°	301	269
65°	219	215
75°	117	124
85°	28	34
90°	0	



TEST NUMBER: P769339

CATALOG NUMBER: LD6D60D010-EU6DR7055659024-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5438.5
2.5°	5381.7
5°	5256.8
7.5°	5152.6
10°	5051.9
12.5°	4966.6
15°	4890.0
17.5°	4704.9
20°	4442.2
22.5°	3875.7
25°	3218.7
27.5°	2801.9
30°	2174.2
32.5°	1404.4
35°	728.5
37.5°	393.5
40°	358.2
42.5°	355.6
45°	352.2
47.5°	344.4
50°	331.5
52.5°	316.9
55°	301.4
57.5°	284.2
60°	264.3
62.5°	242.0
65°	218.7
67.5°	192.9
70°	167.0
72.5°	141.2
75°	117.1
77.5°	92.1
80°	69.7
82.5°	49.1
85°	28.4
87.5°	11.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)