

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769315

Luminaire Tested: LD6D60D010-EU6DR6555659040-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P769315
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR6555659040-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6985.6 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P769315
CATALOG NUMBER: LD6D60D010-EU6DR6555659040-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P769315
 CATALOG NUMBER: LD6D60D010-EU6DR6555659040-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	370438
5°	369508
10°	369190
15°	357809
20°	325739
25°	283865
30°	236097
35°	187072
40°	135015
45°	85296
50°	44458
55°	23633
60°	12417
65°	6827
70°	2869
75°	3159
80°	2186
85°	1876

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 85296 cd/sqm



TEST NUMBER: P769315

CATALOG NUMBER: LD6D60D010-EU6DR6555659040-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	599.8	8.6
10°-20°	1642.5	23.5
20°-30°	2007.7	28.7
30°-40°	1629.0	23.3
40°-50°	811.8	11.6
50°-60°	226.4	3.2
60°-70°	51.5	0.7
70°-80°	13.4	0.2
80°-90°	3.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4250.1	60.8
0°-40°	5879.1	84.2
0°-60°	6917.3	99.0
0°-90°	6985.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6985.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6343	
5°	6303	600
15°	5918	1643
25°	4405	2008
35°	2624	1629
45°	1033	812
55°	232	226
65°	49	51
75°	14	13
85°	3	3
90°	0	



TEST NUMBER: P769315
CATALOG NUMBER: LD6D60D010-EU6DR6555659040-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	6342.7
2.5°	6338.1
5°	6302.7
7.5°	6282.1
10°	6225.3
12.5°	6109.7
15°	5917.7
17.5°	5617.6
20°	5241.0
22.5°	4834.6
25°	4405.0
27.5°	3945.4
30°	3500.9
32.5°	3061.8
35°	2623.8
37.5°	2186.6
40°	1770.9
42.5°	1381.3
45°	1032.7
47.5°	719.6
50°	489.3
52.5°	337.4
55°	232.1
57.5°	156.6
60°	106.3
62.5°	73.6
65°	49.4
67.5°	25.2
70°	16.8
72.5°	15.8
75°	14.0
77.5°	9.3
80°	6.5
82.5°	4.7
85°	2.8
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)