

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770069

Luminaire Tested: LD6D65D010-EU6DR6555659030-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P770069  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D65D010-EU6DR6555659030-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7303.9 lumens  
Efficiency: N/A  
Efficacy: 100.3 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P770069  
CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P770069  
 CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	387323
5°	386346
10°	386015
15°	374116
20°	340587
25°	296798
30°	246854
35°	195592
40°	141168
45°	89187
50°	46484
55°	24713
60°	12977
65°	7145
70°	2988
75°	3295
80°	2287
85°	1943

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 89187 cd/sqm



TEST NUMBER: P770069

CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	627.2	8.6
10°-20°	1717.4	23.5
20°-30°	2099.3	28.7
30°-40°	1703.3	23.3
40°-50°	848.8	11.6
50°-60°	236.7	3.2
60°-70°	53.8	0.7
70°-80°	14.0	0.2
80°-90°	3.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4443.8	60.8
0°-40°	6147.1	84.2
0°-60°	7232.6	99.0
0°-90°	7303.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7303.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6632	
5°	6590	627
15°	6187	1717
25°	4606	2099
35°	2743	1703
45°	1080	849
55°	243	237
65°	52	54
75°	15	14
85°	3	4
90°	0	



TEST NUMBER: P770069

CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6631.8
2.5°	6626.9
5°	6589.9
7.5°	6568.4
10°	6509.0
12.5°	6388.1
15°	6187.4
17.5°	5873.6
20°	5479.9
22.5°	5055.0
25°	4605.7
27.5°	4125.3
30°	3660.4
32.5°	3201.4
35°	2743.3
37.5°	2286.3
40°	1851.6
42.5°	1444.3
45°	1079.8
47.5°	752.3
50°	511.6
52.5°	352.8
55°	242.7
57.5°	163.7
60°	111.1
62.5°	77.0
65°	51.7
67.5°	26.3
70°	17.5
72.5°	16.6
75°	14.6
77.5°	9.7
80°	6.8
82.5°	4.9
85°	2.9
87.5°	1.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)