

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760122

Luminaire Tested: LD6D10D010-EU6DR250210IC9035-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P760122
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR250210IC9035-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 901.7 lumens
Efficiency: N/A
Efficacy: 77.1 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760122
CATALOG NUMBER: LD6D10D010-EU6DR250210IC9035-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P760122

CATALOG NUMBER: LD6D10D010-EU6DR250210IC9035-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96	96	96	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92	92	92	92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89	89	89	89
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85	85	85	85
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82	82	82	82
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79	79	79	79
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77	77	77	77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74	74	74	74
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72	72	72	72
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69	69	69	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	373683
5°	348042
10°	248264
15°	146213
20°	90984
25°	49934
30°	22836
35°	8657
40°	3908
45°	2349
50°	969
55°	629
60°	437
65°	284
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2349 cd/sqm



TEST NUMBER: P760122

CATALOG NUMBER: LD6D10D010-EU6DR250210IC9035-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	272.7	30.2
10°-20°	369.4	41.0
20°-30°	195.5	21.7
30°-40°	48.2	5.4
40°-50°	11.8	1.3
50°-60°	3.1	0.3
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	837.6	92.9
0°-40°	885.8	98.2
0°-60°	900.7	99.9
0°-90°	901.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	901.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3420	
5°	3173	273
15°	1293	369
25°	414	195
35°	65	48
45°	15	12
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P760122

CATALOG NUMBER: LD6D10D010-EU6DR250210IC9035-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

0°	
0°	3420.1
2.5°	3363.9
5°	3173.3
7.5°	2790.3
10°	2237.7
12.5°	1691.6
15°	1292.6
17.5°	1007.4
20°	782.5
22.5°	586.8
25°	414.2
27.5°	277.7
30°	181.0
32.5°	110.1
35°	64.9
37.5°	39.6
40°	27.4
42.5°	21.0
45°	15.2
47.5°	9.2
50°	5.7
52.5°	4.2
55°	3.3
57.5°	2.6
60°	2.0
62.5°	1.6
65°	1.1
67.5°	0.5
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)