

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761634

Luminaire Tested: LD6D15D010-EU6DR600215IC9024-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P761634
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR600215IC9024-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 975.0 lumens
Efficiency: N/A
Efficacy: 61.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761634
CATALOG NUMBER: LD6D15D010-EU6DR600215IC9024-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P761634

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9024-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	126513
5°	129629
10°	131194
15°	124981
20°	110192
25°	89127
30°	60281
35°	30211
40°	4906
45°	4806
50°	4895
55°	4972
60°	5113
65°	5222
70°	5335
75°	5404
80°	5222
85°	4262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 5404 cd/sqm



TEST NUMBER: P761634

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9024-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.0	11.6
10°-20°	305.6	31.3
20°-30°	328.8	33.7
30°-40°	142.9	14.7
40°-50°	24.0	2.5
50°-60°	23.3	2.4
60°-70°	20.0	2.0
70°-80°	13.3	1.4
80°-90°	4.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	747.4	76.7
0°-40°	890.3	91.3
0°-60°	937.7	96.2
0°-90°	975.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	975.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1158	
5°	1182	113
15°	1105	306
25°	739	329
35°	226	143
45°	31	24
55°	26	23
65°	20	20
75°	13	13
85°	3	4
90°	0	



TEST NUMBER: P761634

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9024-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1157.9
2.5°	1190.5
5°	1181.9
7.5°	1184.6
10°	1182.5
12.5°	1158.1
15°	1104.9
17.5°	1033.5
20°	947.7
22.5°	856.0
25°	739.3
27.5°	591.3
30°	477.8
32.5°	368.3
35°	226.5
37.5°	96.9
40°	34.4
42.5°	31.6
45°	31.1
47.5°	30.0
50°	28.8
52.5°	27.4
55°	26.1
57.5°	24.7
60°	23.4
62.5°	21.8
65°	20.2
67.5°	18.6
70°	16.7
72.5°	14.8
75°	12.8
77.5°	10.5
80°	8.3
82.5°	5.9
85°	3.4
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)