

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761830

Luminaire Tested: LD6D15D010-EU6DR700215IC9040-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P761830
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR700215IC9040-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 944.7 lumens
Efficiency: N/A
Efficacy: 59.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761830
CATALOG NUMBER: LD6D15D010-EU6DR700215IC9040-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P761830

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9040-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116046
5°	112596
10°	109460
15°	108025
20°	100878
25°	75781
30°	53569
35°	18980
40°	9984
45°	10631
50°	10998
55°	11201
60°	11276
65°	11039
70°	10414
75°	9667
80°	8557
85°	7020

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 11286 cd/sqm



TEST NUMBER: P761830

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9040-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.8	10.3
10°-20°	265.6	28.1
20°-30°	292.5	31.0
30°-40°	111.8	11.8
40°-50°	52.8	5.6
50°-60°	52.5	5.6
60°-70°	42.0	4.4
70°-80°	24.2	2.6
80°-90°	6.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	655.0	69.3
0°-40°	766.7	81.2
0°-60°	872.0	92.3
0°-90°	944.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	944.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1062	
5°	1027	97
15°	955	266
25°	629	293
35°	142	112
45°	69	53
55°	59	52
65°	43	42
75°	23	24
85°	6	7
90°	0	



TEST NUMBER: P761830

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9040-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1062.1
2.5°	1051.0
5°	1026.6
7.5°	1006.3
10°	986.6
12.5°	969.9
15°	955.0
17.5°	918.8
20°	867.6
22.5°	756.9
25°	628.6
27.5°	547.2
30°	424.6
32.5°	274.3
35°	142.3
37.5°	76.8
40°	70.0
42.5°	69.4
45°	68.8
47.5°	67.3
50°	64.7
52.5°	61.9
55°	58.8
57.5°	55.5
60°	51.6
62.5°	47.3
65°	42.7
67.5°	37.6
70°	32.6
72.5°	27.6
75°	22.9
77.5°	18.0
80°	13.6
82.5°	9.6
85°	5.6
87.5°	2.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)