

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763121

Luminaire Tested: LD6D25D010-EU6DR3020359030-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P763121
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D25D010-EU6DR3020359030-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2529.0 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763121

CATALOG NUMBER: LD6D25D010-EU6DR3020359030-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P763121

CATALOG NUMBER: LD6D25D010-EU6DR3020359030-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	622443	622443	622443
5°	604575	603875	604605
10°	523659	519967	523535
15°	341659	339828	338116
20°	169892	176262	169664
25°	85580	96500	83823
30°	34267	37334	29856
35°	15895	15222	12755
40°	6865	7624	6465
45°	4839	6008	4882
50°	1667	4370	1762
55°	961	1815	1014
60°	674	796	674
65°	435	435	435
70°	269	179	269
75°	0	118	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 6008 cd/sqm



TEST NUMBER: P763121

CATALOG NUMBER: LD6D25D010-EU6DR3020359030-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	715.1	28.3
10°-20°	1151.7	45.5
20°-30°	497.7	19.7
30°-40°	113.4	4.5
40°-50°	38.9	1.5
50°-60°	9.5	0.4
60°-70°	2.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2364.4	93.5
0°-40°	2477.8	98.0
0°-60°	2526.3	99.9
0°-90°	2529.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2529.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	8132	8132	8132	8132	8132	
5°	7868	7861	7859	7876	7869	716
15°	4312	4260	4288	4274	4267	1154
25°	1013	1052	1143	1025	992	485
35°	170	174	163	162	136	115
45°	45	56	56	56	45	32
55°	7	8	14	8	8	7
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P763121

CATALOG NUMBER: LD6D25D010-EU6DR3020359030-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	8131.9	8131.9	8131.9	8131.9	8131.9
2.5°	8078.0	8072.5	8075.7	8079.6	8081.2
5°	7868.4	7860.9	7859.3	7875.7	7868.8
7.5°	7445.7	7434.8	7418.5	7455.6	7490.4
10°	6737.4	6725.4	6689.9	6707.4	6735.8
12.5°	5691.8	5653.0	5652.2	5708.1	5700.5
15°	4311.5	4259.6	4288.4	4274.4	4266.8
17.5°	2899.4	2879.4	2917.8	2906.2	2856.3
20°	2085.7	2090.9	2163.9	2127.2	2082.9
22.5°	1521.9	1540.7	1627.4	1532.7	1498.0
25°	1013.3	1051.7	1142.6	1024.9	992.5
27.5°	623.3	640.8	733.0	615.2	597.7
30°	387.7	378.9	422.4	362.5	337.8
32.5°	254.3	243.2	257.1	230.8	210.8
35°	170.1	173.7	162.9	161.7	136.5
37.5°	106.2	122.2	107.8	115.0	87.8
40°	68.7	88.6	76.3	84.2	64.7
42.5°	56.3	68.3	62.7	66.7	57.5
45°	44.7	55.5	55.5	55.5	45.1
47.5°	24.8	37.1	47.5	37.9	26.4
50°	14.0	18.8	36.7	19.5	14.8
52.5°	9.6	10.8	25.2	11.2	10.0
55°	7.2	7.6	13.6	8.0	7.6
57.5°	5.6	6.0	7.2	6.0	5.6
60°	4.4	4.4	5.2	4.8	4.4
62.5°	3.2	3.2	3.6	3.2	3.2
65°	2.4	2.4	2.4	2.4	2.4
67.5°	1.2	1.6	1.6	1.6	1.6
70°	1.2	0.8	0.8	0.8	1.2
72.5°	0.8	0.4	0.4	0.4	0.4
75°	0.0	0.0	0.4	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)