

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763624

Luminaire Tested: LD6D25D010-EU6DR6020359040-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P763624
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D25D010-EU6DR6020359040-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2461.6 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763624

CATALOG NUMBER: LD6D25D010-EU6DR6020359040-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P763624

CATALOG NUMBER: LD6D25D010-EU6DR6020359040-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	319424
5°	327279
10°	331230
15°	315546
20°	278218
25°	225030
30°	152216
35°	76282
40°	12366
45°	12114
50°	12358
55°	12534
60°	12893
65°	13185
70°	13481
75°	13635
80°	13150
85°	11032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 13635 cd/sqm



TEST NUMBER: P763624

CATALOG NUMBER: LD6D25D010-EU6DR6020359040-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	285.2	11.6
10°-20°	771.6	31.3
20°-30°	830.2	33.7
30°-40°	360.9	14.7
40°-50°	60.6	2.5
50°-60°	58.9	2.4
60°-70°	50.4	2.0
70°-80°	33.7	1.4
80°-90°	10.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1887.0	76.7
0°-40°	2247.9	91.3
0°-60°	2367.4	96.2
0°-90°	2461.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2461.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2924	
5°	2984	285
15°	2790	772
25°	1867	830
35°	572	361
45°	78	61
55°	66	59
65°	51	50
75°	32	34
85°	9	10
90°	0	



TEST NUMBER: P763624

CATALOG NUMBER: LD6D25D010-EU6DR6020359040-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2923.5
2.5°	3005.7
5°	2984.0
7.5°	2990.9
10°	2985.5
12.5°	2923.9
15°	2789.6
17.5°	2609.3
20°	2392.8
22.5°	2161.1
25°	1866.6
27.5°	1492.9
30°	1206.5
32.5°	929.8
35°	571.9
37.5°	244.6
40°	86.7
42.5°	79.9
45°	78.4
47.5°	75.7
50°	72.7
52.5°	69.3
55°	65.8
57.5°	62.4
60°	59.0
62.5°	55.2
65°	51.0
67.5°	46.8
70°	42.2
72.5°	37.3
75°	32.3
77.5°	26.6
80°	20.9
82.5°	14.8
85°	8.8
87.5°	3.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)