

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763170

Luminaire Tested: LD6D25D010-EU6DR3020359050-6LBSQW1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P763170
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D25D010-EU6DR3020359050-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2495.8 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763170

CATALOG NUMBER: LD6D25D010-EU6DR3020359050-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P763170

CATALOG NUMBER: LD6D25D010-EU6DR3020359050-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	614276	614276	614276
5°	596638	595938	596668
10°	516780	513135	516656
15°	337173	335359	333679
20°	167660	173949	167432
25°	84456	95233	82725
30°	33816	36848	29459
35°	15689	15026	12596
40°	6775	7514	6375
45°	4774	5932	4817
50°	1643	4323	1739
55°	947	1788	1001
60°	674	781	674
65°	417	417	417
70°	269	179	269
75°	0	118	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 5932 cd/sqm



TEST NUMBER: P763170

CATALOG NUMBER: LD6D25D010-EU6DR3020359050-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	705.7	28.3
10°-20°	1136.5	45.5
20°-30°	491.1	19.7
30°-40°	111.9	4.5
40°-50°	38.4	1.5
50°-60°	9.4	0.4
60°-70°	2.4	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2333.3	93.5
0°-40°	2445.3	98.0
0°-60°	2493.1	99.9
0°-90°	2495.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2495.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	8025	8025	8025	8025	8025	
5°	7765	7758	7756	7772	7766	706
15°	4255	4204	4232	4218	4211	1139
25°	1000	1038	1128	1011	980	479
35°	168	171	161	160	135	114
45°	44	55	55	55	44	31
55°	7	8	13	8	8	7
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P763170

CATALOG NUMBER: LD6D25D010-EU6DR3020359050-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	8025.2	8025.2	8025.2	8025.2	8025.2
2.5°	7972.0	7966.5	7969.6	7973.5	7975.1
5°	7765.1	7757.6	7756.0	7772.2	7765.5
7.5°	7347.9	7337.2	7321.1	7357.7	7392.0
10°	6648.9	6637.1	6602.0	6619.4	6647.3
12.5°	5617.0	5578.8	5578.0	5633.1	5625.6
15°	4254.9	4203.7	4232.0	4218.2	4210.8
17.5°	2861.3	2841.6	2879.4	2868.0	2818.7
20°	2058.3	2063.4	2135.5	2099.3	2055.5
22.5°	1501.9	1520.5	1606.0	1512.6	1478.3
25°	1000.0	1037.8	1127.6	1011.4	979.5
27.5°	615.1	632.4	723.4	607.2	589.9
30°	382.6	373.9	416.9	357.8	333.3
32.5°	251.0	240.0	253.8	227.7	208.0
35°	167.9	171.4	160.8	159.6	134.8
37.5°	104.8	120.5	106.4	113.5	86.7
40°	67.8	87.5	75.2	83.1	63.8
42.5°	55.6	67.4	61.9	65.8	56.7
45°	44.1	54.8	54.8	54.8	44.5
47.5°	24.4	36.7	46.9	37.4	26.0
50°	13.8	18.5	36.3	19.3	14.6
52.5°	9.5	10.7	24.8	11.1	9.9
55°	7.1	7.5	13.4	7.9	7.5
57.5°	5.5	5.9	7.1	5.9	5.5
60°	4.4	4.4	5.1	4.8	4.4
62.5°	3.2	3.2	3.6	3.2	3.2
65°	2.3	2.3	2.3	2.3	2.3
67.5°	1.2	1.6	1.6	1.6	1.6
70°	1.2	0.8	0.8	0.8	1.2
72.5°	0.8	0.4	0.4	0.4	0.4
75°	0.0	0.0	0.4	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)